


TFA32 Series

Automotive Grade Tuning Fork Crystal

Features

- AEC-Q200 Compliant
- Hermetic Ceramic Surface Mount Package
- Tuning Fork Crystal Design
- 32.7680kHz Frequency Reference
- Frequency Tolerance, $\pm 20\text{ppm}$ Standard
- Parabolic Temperature Coefficient
- Tape and Reel Packaging, EIA-481



Part Dimensions:
3.2 x 1.5 x 0.9mm • 12.1467mg

Applications

- Automotive Electronics
- Car Navigation Systems
- Car Infotainment Systems
- Industrial Control Equipment
- M2M Communications
- FPGAs & Microcontrollers

Description

CTS TFA32 Series is ideal for supporting wide range of electronic designs requiring a Real Time Clock reference. This series will support general automotive and industrial applications.

Ordering Information

Model		Frequency Tolerance	Load Capacitance	Temperature Range	Frequency Code [kHz]	Packaging
TF	A32	2	P	I	327K	R
Code	Package		Code Capacitance		Code Frequency	
A	Automotive		P 12.5pF			
32	3.2x1.5mm		J 9pF			
			V 7pF			
			T 6pF			
					Frequency = 32.7680kHz	
Code	@ +25°C		Code Temp. Range		Code Packing	
2	$\pm 20\text{ppm}$		I -40°C to +85°C		R 3k pcs./reel	
1	$\pm 10\text{ppm}$		G -40°C to +105°C			
			H -40°C to +125°C ¹			

Notes:

1] Check with factory for availability.

**Not all performance combinations and frequencies may be available.
Contact your local CTS Representative or CTS Customer Service for availability.**

This product is specified for use only in standard commercial applications. Supplier disclaims all express and implied warranties and liability in connection with any use of this product in any non-commercial applications or in any application that may expose the product to conditions that are outside of the tolerances provided in its specification.

Electrical Specifications

Operating Conditions

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Operating Temperature	T_A	-	-40		+85	
			-40	+25	+105	°C
Turnover Temperature	T_M	-	+20	+25	+30	°C
Storage Temperature	T_{STG}	-	-55	-	+125	°C

Frequency Stability


PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Frequency	f_0	-	32.7680			kHz
Frequency Tolerance [Note 1]	$\Delta f/f_0$	Standard @ +25°C	-20	-	20	ppm
Parabolic Coefficient	β	See Figure 1		-0.034 ±0.010		ppm/°C ²
Aging	$\Delta f/f_0$	First Year @ +25°C	-3	-	3	ppm

Crystal Parameters

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Operating Mode	-	-		Flexural Mode [Tuning Fork]		-
Load Capacitance [Note 1]	C_L	Standard	-	12.5	-	pF
Shunt Capacitance	C_0	-	-	1.2	-	pF
Motional Capacitance	C_1	-	-	3.4	-	fF
Series Resistance	R_1	-	-	-	70	kΩ
Drive Level	DL	-	-	0.5	1.0	μW
Insulation Resistance	R_i	+100Vdc ±15Vdc	500	-	-	MΩ

1.] See Ordering Information for available options.

Figure 1



Frequency Stability [Δf] at a given temperature,

$$\Delta f = \beta [T_A - T_M]^2$$

β = Parabolic Coefficient

T_A = Ambient Temperature

T_M = Turnover Temperature

Ex. Find frequency stability at $T_A = +60^\circ\text{C}$



$$\Delta f = -0.034[60-25]^2$$

$$\Delta f = -0.034[35]^2$$


$$\Delta f = -41.65\text{ppm}$$

Mechanical Specifications

Package Drawing



Recommended Pad Layout



Marking Information


Contact factory for marking formats that apply to this model series.

Notes


1. JEDEC termination code (e4). Barrier-plating is nickel [Ni] with gold [Au] flash plate.
2. Reflow conditions per JEDEC J-STD-020; +260°C maximum, 20 seconds.
3. MSL = 1.
4. Due to the large world-wide production volumes for this model series, product variability may exist between production date codes, such as package coloring and product marking format. CTS guarantees form-fit-function performance to published data sheet parameters. Contact your local CTS Representative or CTS Customer Service with specific questions.

Packaging - Tape and Reel

Tape Drawing



Reel Drawing



Notes

1. Device quantity is 3k pieces maximum per 180mm reel.
2. Complete CTS part number, frequency value, date code and manufacturing site code information must appear on reel and carton labels.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

[TFA322PH327KR](#) [TFA322PG327KR](#) [TFA321JG327KR](#) [TFA321JH327KR](#) [TFA321JI327KR](#) [TFA321PG327KR](#)
[TFA321PH327KR](#) [TFA321PI327KR](#) [TFA321TG327KR](#) [TFA321TI327KR](#) [TFA321VG327KR](#) [TFA321VH327KR](#)
[TFA321VI327KR](#) [TFA322JG327KR](#) [TFA322PI327KR](#) [TFA322VG327KR](#) [TFA322JH327KR](#) [TFA322JI327KR](#)
[TFA322VH327KR](#) [TFA322TG327KR](#) [TFA322VI327KR](#) [TFA322TI327KR](#)