


TUNS50F

TUN S 50 F 05 -□

① ② ③ ④ ⑤ ⑥



*Providing heat sink
as option



- ① Series name
② Single output
③ Output wattage
④ Universal Input
⑤ Output voltage
⑥ Optional
T : with Mounting hole
(ϕ 3.4 thru)

*Avoid short circuit between +BC and -BC. It may cause the failure of inside components.

*Keep TRM open, if output voltage adjustment is not necessary.

MODEL	TUNS50F05	TUNS50F12	TUNS50F24
MAX OUTPUT WATTAGE[W]	50.0	50.4	50.4
DC OUTPUT	5V 10A	12V 4.2A	24V 2.1A

SPECIFICATIONS



	MODEL		TUNS50F05	TUNS50F12	TUNS50F24
INPUT	VOLTAGE[V]		AC85 - 264 1 φ (Please refer to the instruction manual, 6.5 Derating)		
	CURRENT[A]	ACIN 100V	0.67typ (Io=100%)		
		ACIN 200V	0.35typ (Io=100%)		
	FREQUENCY[Hz]		50/60 (47 - 63)		
	EFFICIENCY[%]	ACIN 100V	79typ	83typ	84typ
		ACIN 200V	81typ	84typ	86typ
	POWER FACTOR (Io=100%)	ACIN 100V	0.95typ		
		ACIN 200V	0.90typ		
INRUSH CURRENT		Limited by external components (Thermistor)			
LEAKAGE CURRENT[ma]		0.75max (ACIN 240V 60Hz, Io=100%, According to IEC60950-1)			
OUTPUT	VOLTAGE[V]		5	12	24
	CURRENT[A]		10	4.2	2.1
	LINE REGULATION[mV]		10max	24max	48max
	LOAD REGULATION[mV]		10max	24max	48max
	RIPPLE[mVp-p]	0 to +100℃ *1	80max	120max	120max
		-40 to 0℃ *1	120max	150max	150max
		0 to 15% Load *1	200max	280max	380max
	RIPPLE NOISE[mVp-p]	0 to +100℃ *1	120max	150max	150max
		-40 to 0℃ *1	200max	200max	250max
		0 to 15% Load *1	280max	360max	460max
	TEMPERATURE REGULATION[mV]	0 to +65℃	50max	120max	240max
		-40 to +100℃	100max	240max	480max
	DRIFT[mV]		*2	20max	40max
	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]		Fixed (TRM pin open), adjustable by external resistor or external signal		
OUTPUT VOLTAGE SETTING[V]		4.50 - 6.00	10.80 - 13.20	21.60 - 26.40	
OUTPUT VOLTAGE SETTING[V]		4.97 - 5.13	11.91 - 12.29	23.62 - 24.38	
PROTECTION CIRCUIT AND OTHERS	OVERCURRENT PROTECTION		Works over 105% of rating and recovers automatically		
	OVERVOLTAGE PROTECTION[V]		6.30 - 7.00	13.90 - 16.35	27.60 - 32.40
	REMOTE SENSING		Not provided		
	REMOTE ON/OFF		Not provided		
ISOLATION	INPUT-OUTPUT		AC3,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (20±15℃)		
	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (20±15℃)		
	OUTPUT-FG		AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (20±15℃)		
ENVIRONMENT	OPERATING TEMP., HUMID. AND ALTITUDE		-40 to +100℃ (On aluminum base plate), 20 - 95%RH (Non condensing) (Refer to DERATING CURVE), 3,000m (10,000 feet) max		
	STORAGE TEMP., HUMID. AND ALTITUDE		-40 to +100℃, 20 - 95%RH (Non condensing), 9,000m (30,000 feet) max		
	VIBRATION		10 - 55Hz, 49.0m/s² (5G), 3minutes period, 60minutes each along X, Y and Z axis		
	IMPACT		196.1m/s² (20G), 11ms, once each along X, Y and Z axis		
SAFETY AND NOISE REGULATIONS	AGENCY APPROVALS		UL60950-1, C-UL (CSA60950-1), EN60950-1, EN50178		
	HARMONIC ATTENUATOR		Complies with IEC61000-3-2 (Class A) *3		
OTHERS	CASE SIZE/WEIGHT		58.4×12.7×37.3mm [2.3×0.5×1.47 inches] (W×H×D) / 80g max		
	COOLING METHOD		Conduction cooling (e.g. heat radiation from the aluminum base plate to the attached heat sink)		

*1 Refer to instruction manual for measuring method of electric characteristics.

*2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.

*3 Please contact us about another class.

External view



※ Tolerance : ± 0.3 [± 0.012]

※ Weight : 80g max


※ Dimensions in mm, []=inches

※ Mounting hole screwing torque : 0.49N · m (5.0kgf · cm) max


TUNS100F

TUN S 100 F 05 -□

① ② ③ ④ ⑤ ⑥



*Providing heat sink
as option



- ① Series name
② Single output
③ Output wattage
④ Universal Input
⑤ Output voltage
⑥ Optional
T : with Mounting hole
(ϕ 3.4 thru)

*Avoid short circuit between +BC and -BC. It may cause the failure of inside components.

*Keep TRM open, if output voltage adjustment is not necessary.

*If remote sensing is not necessary, connect between +Vout & +S and between -Vout & -S.

MODEL	TUNS100F05	TUNS100F12	TUNS100F24
MAX OUTPUT WATTAGE[W]	100.0	100.8	100.8
DC OUTPUT	5V 20A	12V 8.4A	24V 4.2A

SPECIFICATIONS



	MODEL		TUNS100F05	TUNS100F12	TUNS100F24
INPUT	VOLTAGE[V]		AC85 - 264 1 ϕ (Please refer to the instruction manual, 6.5 Derating)		
	CURRENT[A]	ACIN 100V	1.3typ (Io=100%)		
		ACIN 200V	0.7typ (Io=100%)		
	FREQUENCY[Hz]		50/60 (47 - 63)		
	EFFICIENCY[%]	ACIN 100V	82typ	83typ	84typ
		ACIN 200V	85typ	85typ	86typ
	POWER FACTOR (Io=100%)	ACIN 100V	0.95typ		
		ACIN 200V	0.90typ		
INRUSH CURRENT			Limited by external components (Thermistor)		
LEAKAGE CURRENT[ma]			0.75max (ACIN 240V 60Hz, Io=100%, According to IEC60950-1)		
OUTPUT	VOLTAGE[V]		5	12	24
	CURRENT[A]		20	8.4	4.2
	LINE REGULATION[mV]		10max	24max	48max
	LOAD REGULATION[mV]		10max	24max	48max
	RIPPLE[mVp-p]	0 to +100°C *1	80max	120max	120max
		-40 to 0°C *1	120max	150max	150max
		0 to 15% Load *1	160max	240max	240max
	RIPPLE NOISE[mVp-p]	0 to +100°C *1	120max	150max	150max
		-40 to 0°C *1	200max	200max	250max
		0 to 15% Load *1	240max	300max	300max
	TEMPERATURE REGULATION[mV]	0 to +65°C	50max	120max	240max
		-40 to +100°C	100max	240max	480max
	DRIFT[mV]		*2	20max	40max
	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]		Fixed (TRM pin open), adjustable by external resistor or external signal		
		4.50 - 6.00	10.80 - 13.20	21.60 - 26.40	
OUTPUT VOLTAGE SETTING[V]		4.97 - 5.13	11.91 - 12.29	23.62 - 24.38	
PROTECTION CIRCUIT AND OTHERS	OVERCURRENT PROTECTION		Works over 105% of rating and recovers automatically		
	OVERVOLTAGE PROTECTION[V]		6.30 - 7.00	13.90 - 16.35	27.60 - 32.40
	REMOTE SENSING		Provided		
	REMOTE ON/OFF		Not provided		
ISOLATION	INPUT-OUTPUT		AC3,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (20 $\pm$ 15°C)		
	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (20 $\pm$ 15°C)		
	OUTPUT-FG		AC500V 1minute, Cutoff current = 100mA, DC500V 50M Ω min (20 $\pm$ 15°C)		
ENVIRONMENT	OPERATING TEMP., HUMID. AND ALTITUDE		-40 to +100°C (On aluminum base plate), 20 - 95%RH (Non condensing) (Refer to DERATING CURVE), 3,000m (10,000 feet) max		
	STORAGE TEMP., HUMID. AND ALTITUDE		-40 to +100°C, 20 - 95%RH (Non condensing), 9,000m (30,000 feet) max		
	VIBRATION		10 - 55Hz, 49.0m/s ² (5G), 3minutes period, 60minutes each along X, Y and Z axis		
	IMPACT		196.1m/s ² (20G), 11ms, once each along X, Y and Z axis		
SAFETY AND NOISE REGULATIONS	AGENCY APPROVALS		UL60950-1, C-UL (CSA60950-1), EN60950-1, EN50178		
	HARMONIC ATTENUATOR		Complies with IEC61000-3-2 (Class A) *3		
OTHERS	CASE SIZE/WEIGHT		58.4 X 12.7 X 61.0mm [2.3 X 0.5 X 2.4 inches] (W X H X D) / 120g max		
	COOLING METHOD		Conduction cooling (e.g. heat radiation from the aluminum base plate to the attached heat sink)		

*1 Refer to instruction manual for measuring method of electric characteristics.

*2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.

*3 Please contact us about another class.

External view




- ※ Tolerance : ± 0.3 [± 0.012]
- ※ Weight : 120g max
- ※ Dimensions in mm, []=inches
- ※ Mounting hole screwing torque : 0.49N · m (5.0kgf · cm) max

TUNS300F

TUN S 300 F 48 -□

① ② ③ ④ ⑤ ⑥



- ① Series name
 ② Single output
 ③ Output wattage
 ④ Universal Input
 ⑤ Output voltage
 ⑥ Optional
 T : with Mounting hole
 (φ 3.4 thru)
 Y1: Output voltage adjustment
 range ±20% (Only 48V)
 R1: with Remote ON/OFF
 R2: with Remote ON/OFF
 (Low standby power)

* Avoid short circuit between +BC/R and -BC. It may cause the failure of inside components.

* Keep TRM open, if output voltage adjustment is not necessary.

* If remote sensing is not necessary, connect between +Vout & +S and between -Vout & -S.

MODEL	TUNS300F12	TUNS300F28	TUNS300F48
MAX OUTPUT WATTAGE[W]	300	308	312
DC OUTPUT	12V 25A	28V 11A	48V 6.5A

SPECIFICATIONS

	MODEL		TUNS300F12	TUNS300F28	TUNS300F48
INPUT	VOLTAGE[V]		AC85 - 264 1 φ		
	CURRENT[A]	ACIN 100V	3.6typ (Io=100%)		
		ACIN 200V	1.8typ (Io=100%)		
	FREQUENCY[Hz]		50/60 (47 - 63)		
	EFFICIENCY[%]	ACIN 100V	84typ	87typ	
		ACIN 200V	86typ	89typ	
	POWER FACTOR (Io=100%)	ACIN 100V	0.96typ		
		ACIN 200V	0.93typ		
INRUSH CURRENT		Limited by external resistance			
LEAKAGE CURRENT[ma]		0.75max (ACIN 240V 60Hz, Io=100%, According to IEC60950-1)			
OUTPUT	VOLTAGE[V]		12	28	48
	CURRENT[A]		25	11	6.5
	LINE REGULATION[mV]		24max	56max	96max
	LOAD REGULATION[mV]		24max	56max	96max
	RIPPLE[mVp-p]	0 to +100℃ *1	120max	180max	250max
		-40 to 0℃ *1	150max	200max	300max
	RIPPLE NOISE[mVp-p]	0 to +100℃ *1	150max	200max	300max
		-40 to 0℃ *1	200max	300max	450max
	TEMPERATURE REGULATION[mV]	0 to +65℃	120max	280max	480max
		-40 to +100℃	240max	560max	960max
	DRIFT[mV] *2		40max	90max	180max
	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]		Fixed (TRM pin open), adjustable by external resistor or external signal		
PROTECTION CIRCUIT AND OTHERS	OUTPUT VOLTAGE SETTING[V]		11.91 - 12.29	27.56 - 28.44	47.24 - 48.76
	OVERCURRENT PROTECTION		Works over 105% of rating and recovers automatically		
	OVERVOLTAGE PROTECTION[V]		15.00 - 16.80	35.00 - 39.20	55.20 - 64.80 (-Y1 Option : 60.0 - 67.2)
	REMOTE SENSING		Provided		
	REMOTE ON/OFF		Optional (External power supply is required)		
ISOLATION	INPUT-OUTPUT · RC *4		AC3,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (20±15℃)		
	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (20±15℃)		
	OUTPUT · RC-FG *4		AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (20±15℃)		
	OUTPUT-RC *4		AC100V 1minute, Cutoff current = 100mA, DC100V 10MΩ min (20±15℃)		
ENVIRONMENT	OPERATING TEMP.,HUMID.AND ALTITUDE		-40 to +100℃ (On aluminum base plate), 20 - 95%RH (Non condensing) (Refer to DERATING CURVE), 3,000m (10,000 feet) max		
	STORAGE TEMP.,HUMID.AND ALTITUDE		-40 to +100℃ , 20 - 95%RH (Non condensing), 9,000m (30,000 feet) max		
	VIBRATION		10 - 55Hz, 49.0m/s² (5G), 3minutes period, 60minutes each along X, Y and Z axis		
SAFETY AND NOISE REGULATIONS	IMPACT		196.1m/s² (20G), 11ms, once each along X, Y and Z axis		
	AGENCY APPROVALS		UL60950-1, C-UL (CSA60950-1), EN60950-1		
OTHERS	HARMONIC ATTENUATOR		Complies with IEC61000-3-2 (Class A) *3		
	CASE SIZE/WEIGHT		117.3×12.7×61.5mm [4.62×0.5×2.42 inches] (W×H×D) / 190g max		
	COOLING METHOD		Conduction cooling (e.g. heat radiation from the aluminum base plate to the attached heat sink)		



*1 Refer to instruction manual for measuring method of electric characteristics.

*2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.

*3 Please contact us about another class.

*4 "RC" is applicable when remote control (optional) is added.

External view




- ※ Tolerance : ±0.3 [±0.012]
- ※ Weight : 190g max
- ※ Dimensions in mm, []=inches
- ※ Mounting hole screwing torque : 0.49N · m (5.0kgf · cm) max

TUNS500F

TUN S 500 F 48 -□

① ② ③ ④ ⑤ ⑥



- ① Series name
 ② Single output
 ③ Output wattage
 ④ Universal Input
 ⑤ Output voltage
 ⑥ Optional
 T : with Mounting hole
 (ϕ 3.4 thru)
 Y1: Output voltage adjustment
 range $\pm 20\%$ (Only 48V)
 R1: with Remote ON/OFF
 R2: with Remote ON/OFF
 (Low standby power)

* Avoid short circuit between +BC/R and -BC. It may cause the failure of inside components.

* Keep TRM open, if output voltage adjustment is not necessary.

* If remote sensing is not necessary, connect between +Vout & +S and between -Vout & -S.

MODEL	TUNS500F12	TUNS500F28	TUNS500F48
MAX OUTPUT WATTAGE[W]	504	504	504
DC OUTPUT	12V 42A (Peak 55A)	28V 18A (Peak 24A)	48V 10.5A (Peak 14A)

SPECIFICATIONS

	MODEL	TUNS500F12	TUNS500F28	TUNS500F48
INPUT	VOLTAGE[V]	AC85 - 264 1 ϕ		
	CURRENT[A]	ACIN 100V 6.0typ (Io=100%)		
		ACIN 200V 3.0typ (Io=100%)		
	FREQUENCY[Hz]	50/60 (47 - 63)		
	EFFICIENCY[%]	ACIN 100V 84typ	87typ	88typ
		ACIN 200V 86typ	90typ	90.5typ
	POWER FACTOR (Io=100%)	ACIN 100V 0.96typ		
		ACIN 200V 0.93typ		
OUTPUT	INRUSH CURRENT	Limited by external resistance		
	LEAKAGE CURRENT[ma]	0.75max (ACIN 240V 60Hz, Io=100%, According to IEC60950-1)		
	VOLTAGE[V]	12	28	48
	CURRENT[A]	*3 42 (Peak 55)	18 (Peak 24)	10.5 (Peak 14)
	LINE REGULATION[mV]	24max	56max	96max
	LOAD REGULATION[mV]	24max	56max	96max
	RIPPLE[mVp-p]	0 to +100°C *1 120max	180max	250max
		-40 to 0°C *1 150max	200max	300max
	RIPPLE NOISE[mVp-p]	0 to +100°C *1 150max	200max	300max
		-40 to 0°C *1 200max	300max	450max
PROTECTION CIRCUIT AND OTHERS	TEMPERATURE REGULATION[mV]	0 to +65°C 120max	280max	480max
		-40 to +100°C 240max	560max	960max
		-40 to +100°C 40max	90max	180max
	DRIFT[mV]	*2		
	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]	Fixed (TRM pin open), adjustable by external resistor or external signal		
		9.60 - 14.40	22.40 - 33.60	38.40 - 52.80 (-Y1 Option : 38.4 - 57.6)
	OUTPUT VOLTAGE SETTING[V]	11.91 - 12.29	27.56 - 28.44	47.24 - 48.76
	OVERCURRENT PROTECTION	Works over 101% of peak current and recovers automatically		
	OVERVOLTAGE PROTECTION[V]	15.00 - 16.80	35.00 - 39.20	55.20 - 64.80 (-Y1 Option : 60.0 - 67.2)
	REMOTE SENSING	Provided		
ISOLATION	REMOTE ON/OFF	Optional (External power supply is required)		
	INPUT-OUTPUT · RC	*5 AC3,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (20 $\pm$ 15°C)		
	INPUT-FG	AC2,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (20 $\pm$ 15°C)		
	OUTPUT · RC-FG	*5 AC500V 1minute, Cutoff current = 100mA, DC500V 50M Ω min (20 $\pm$ 15°C)		
	OUTPUT-RC	*5 AC100V 1minute, Cutoff current = 100mA, DC100V 10M Ω min (20 $\pm$ 15°C)		
ENVIRONMENT	OPERATING TEMP., HUMID. AND ALTITUDE	-40 to +100°C (On aluminum base plate), 20 - 95%RH (Non condensing) (Refer to DERATING CURVE), 3,000m (10,000 feet) max		
	STORAGE TEMP., HUMID. AND ALTITUDE	-40 to +100°C, 20 - 95%RH (Non condensing), 9,000m (30,000 feet) max		
	VIBRATION	10 - 55Hz, 49.0m/s ² (5G), 3minutes period, 60minutes each along X, Y and Z axis		
	IMPACT	196.1m/s ² (20G), 11ms, once each along X, Y and Z axis		
SAFETY AND NOISE REGULATIONS	AGENCY APPROVALS	UL60950-1, C-UL (CSA60950-1), EN60950-1		
	HARMONIC ATTENUATOR	Complies with IEC61000-3-2 (Class A) *4		
OTHERS	CASE SIZE/WEIGHT	117.3×12.7×61.5mm [4.62×0.5×2.42 inches] (W×H×D) / 190g max		
	COOLING METHOD	Conduction cooling (e.g. heat radiation from the aluminum base plate to the attached heat sink)		

*1 Refer to instruction manual for measuring method of electric characteristics.



*2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.

*3 () means peak current. Avoid operating with peak current continuously. It may cause failure of the components inside the product. There are limitation of available condition of the peak current, such as peak time, duty etc. (Refer to the instruction manual in detail.)

*4 Please contact us about another class.

*5 "RC" is applicable when remote control (optional) is added.

External view




- ※ Tolerance : ± 0.3 [± 0.012]
- ※ Weight : 190g max
- ※ Dimensions in mm, []=inches
- ※ Mounting hole screwing torque : $0.49\text{N} \cdot \text{m}$ (5.0kgf · cm) max

TUNS700F

TUN S 700 F 48 -□

① ② ③ ④ ⑤ ⑥



- ① Series name
② Single output
③ Output wattage
④ Universal Input
⑤ Output voltage
⑥ Optional
T : with Mounting hole
(ϕ 3.4 thru)
Y1: Output voltage adjustment
range $\pm 20\%$ (Only 48V)
R1: with Remote ON/OFF
R2: with Remote ON/OFF
(Low standby power)
P : Parallel operation

* Avoid short circuit between +BC/R and -BC. It may cause the failure of inside components.

* Keep TRM open, if output voltage adjustment is not necessary.

* If remote sensing is not necessary, connect between +Vout & +S and between -Vout & -S.

MODEL	TUNS700F12	TUNS700F28	TUNS700F48
MAX OUTPUT WATTAGE[W]	700.8	700.0	700.8
DC OUTPUT	12V 58.4A	28V 25A	48V 14.6A

SPECIFICATIONS

	MODEL		TUNS700F12	TUNS700F28	TUNS700F48
INPUT	VOLTAGE[V]		AC85 - 264 1ϕ		
	CURRENT[A]	ACIN 100V	8.6typ (Io=100%)		
		ACIN 200V	4.1typ (Io=100%)		
	FREQUENCY[Hz]		50/60 (47 - 63)		
	EFFICIENCY[%]	ACIN 100V	83typ	86typ	87typ
		ACIN 200V	86typ	89typ	90typ
	POWER FACTOR (Io=100%)	ACIN 100V	0.96typ		
		ACIN 200V	0.93typ		
INRUSH CURRENT		Limited by external resistance			
LEAKAGE CURRENT[ma]		0.75max (ACIN 240V 60Hz, Io=100%, According to IEC60950-1)			
OUTPUT	VOLTAGE[V]		12	28	48
	CURRENT[A]		58.4	25	14.6
	LINE REGULATION[mV]		24max	56max	96max
	LOAD REGULATION[mV]		24max	56max	96max
	RIPPLE[mVp-p]	0 to +100℃ *1	120max	180max	250max
		-40 to 0℃ *1	150max	200max	300max
	RIPPLE NOISE[mVp-p]	0 to +100℃ *1	150max	200max	300max
		-40 to 0℃ *1	200max	300max	450max
	TEMPERATURE REGULATION[mV]	0 to +65℃	120max	280max	480max
		-40 to +100℃	240max	560max	960max
	DRIFT[mV]	*2	40max	90max	180max
	OUTPUT VOLTAGE ADJUSTMENT		Fixed (TRM pin open), adjustable by external resistor or external signal		
RANGE[V]		9.60 - 14.40	22.40 - 33.60	38.40 - 52.80 (-Y1 Option : 38.4 - 57.6)	
OUTPUT VOLTAGE SETTING[V]		11.91 - 12.29	27.56 - 28.44	47.24 - 48.76	
PROTECTION CIRCUIT AND OTHERS	OVERCURRENT PROTECTION		Works over 105% of rating and recovers automatically		
	OVERVOLTAGE PROTECTION[V]		15.00 - 16.80	35.00 - 39.20	55.20 - 64.80 (-Y1 Option : 60.0 - 67.2)
	REMOTE SENSING		Provided		
	REMOTE ON/OFF		Optional (External power supply is required)		

MODEL	TUNS700F12-P	TUNS700F28-P	TUNS700F48-P
MAX OUTPUT WATTAGE[W]	700.8	700.0	700.8
DC OUTPUT	12V 58.4A	28V 25A	48V 14.6A

SPECIFICATIONS

	MODEL		TUNS700F12-P	TUNS700F28-P	TUNS700F48-P
INPUT	VOLTAGE[V]		AC85 - 264 1ϕ		
	CURRENT[A]	ACIN 100V	8.6typ (Io=100%)		
		ACIN 200V	4.1typ (Io=100%)		
	FREQUENCY[Hz]		50/60 (47 - 63)		
	EFFICIENCY[%]	ACIN 100V	83typ	86typ	87typ
		ACIN 200V	86typ	89typ	90typ
	POWER FACTOR (Io=100%)	ACIN 100V	0.96typ		
		ACIN 200V	0.93typ		
INRUSH CURRENT		Limited by external resistance			
LEAKAGE CURRENT[ma]		0.75max (ACIN 240V 60Hz, Io=100%, According to IEC60950-1)			
OUTPUT	VOLTAGE[V]		12	28	48
	CURRENT[A]		58.4	25	14.6
	VOLTAGE ACCURACY[%]		+5, -3	+5, -3	+5, -3
	RIPPLE[mVp-p]	0 to +100℃ *1	240max	360max	600max
		-40 to 0℃ *1	300max	400max	700max
		0 to +30% Load *1	360max	540max	900max
	RIPPLE NOISE[mVp-p]	0 to +100℃ *1	300max	400max	700max
		-40 to 0℃ *1	400max	600max	1000max
		0 to +30% Load *1	450max	600max	1000max
	PROTECTION CIRCUIT AND OTHERS	OVERCURRENT PROTECTION		Works over 105% of rating and recovers automatically	
OVERVOLTAGE PROTECTION[V]		15.00 - 16.80	35.00 - 39.20	55.20 - 64.80	
REMOTE ON/OFF		Optional (External power supply is required)			

GENERAL SPECIFICATIONS

ISOLATION	INPUT-OUTPUT · RC	*4 AC3,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (20 $\pm$ 15 $^{\circ}$ C)
	INPUT-FG	AC2,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (20 $\pm$ 15 $^{\circ}$ C)
	OUTPUT · RC-FG	*4 AC500V 1minute, Cutoff current = 100mA, DC500V 50M Ω min (20 $\pm$ 15 $^{\circ}$ C)
	OUTPUT-RC	*4 AC100V 1minute, Cutoff current = 100mA, DC100V 10M Ω min (20 $\pm$ 15 $^{\circ}$ C)
ENVIRONMENT	OPERATING TEMP., HUMID. AND ALTITUDE	-40 to +100 $^{\circ}$ C (On aluminum base plate), 20 - 95%RH (Non condensing) (Refer to DERATING CURVE), 3,000m (10,000 feet) max
	STORAGE TEMP., HUMID. AND ALTITUDE	-40 to +100 $^{\circ}$ C, 20 - 95%RH (Non condensing), 9,000m (30,000 feet) max
	VIBRATION	10 - 55Hz, 49.0m/s 2 (5G), 3minutes period, 60minutes each along X, Y and Z axis
	IMPACT	196.1m/s 2 (20G), 11ms, once each along X, Y and Z axis
SAFETY AND NOISE REGULATIONS	AGENCY APPROVALS	UL60950-1, C-UL (CSA60950-1), EN60950-1
	HARMONIC ATTENUATOR	Complies with IEC61000-3-2 (Class A) *3
OTHERS	CASE SIZE/WEIGHT	117.3 $\times$ 12.7 $\times$ 61.5mm [4.62 $\times$ 0.5 $\times$ 2.42 inches] (W $\times$ H $\times$ D) / 190g max
	COOLING METHOD	Conduction cooling (e.g. heat radiation from the aluminum base plate to the attached heat sink)



*1 Refer to instruction manual for measuring method of electric characteristics.

*2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25 $^{\circ}$ C, with the input voltage held constant at the rated input/output.

*3 Please contact us about another class.

*4 "RC" is applicable when remote control (optional) is added.

External view



※ Tolerance : $\pm$ 0.3 [$\pm$ 0.012]

※ Weight : 190g max

※ Dimensions in mm, []=inches

※ Mounting hole screwing torque : 0.49N $\cdot$ m (5.0kgf $\cdot$ cm) max

