

## Specification Sheet

Part Number: 156-00406

Tie/mount combination eliminates the need to carry multiple sizes of fixed bundle diameter clamps.

Can be assembled directly on harnesses or on production line for installation versatility.

Available in PA66 heat-stabilized or PA46, they are suitable for various temperature grades.

Designed to meet strict automotive standards, they are well adapted to vibration and lateral forces.

Metal inserts withstand high-torque tightening.



H-design allows full contact with harnesses or other tubes and hoses.

Mainly adapted to T120R and T120S cable ties but can also be assembled with smallest sizes.

Article Number 156-00406

Type T120RHD6

Color Black (BK)

Quantity Per bag

**Product Description**

These cable tie mounts attach with a screw or bolt to an existing hole, or secure to a stud with a nut. They provide an attachment point for securing and routing a single bundle and deliver the highest level of fastening strength for critical cable security.

**Short Description**

2-Piece Cable Tie/Screw Mount, 15" Long, M6 Hole, 120lb, PA66HIRHS, Black, 100/bag

**Global Part Name**

T120RHD6-PA66HIRHS-BK

Minimum Tensile Strength (Imperial) 120

Minimum Tensile Strength (Metric) 535

Length L (Imperial) 15.0

Length L (Metric) 390.0

Fixation Method Screw Mount

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.30

Width W (Metric) 7.6

Bundle Diameter Min (Imperial)	0.59
Bundle Diameter Min (Metric)	15.0
Bundle Diameter Max (Imperial)	3.937
Bundle Diameter Max (Metric)	105.0
Thickness T (Imperial)	0.07
Thickness T (Metric)	1.8
Height H (Imperial)	0.61
Height H (Metric)	16.0
Mounting Hole Diameter D (Imperial)	0.24
Mounting Hole Diameter D (Metric)	6.2 mm
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Material Cable Tie	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No

Operating Temperature -40°F to +230°F (-40°C to +110°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 100

Package Quantity (Metric) 100

Customs Number 3926909988

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)