



HIGH SPEED LTE
NETWORKING
PLATFORM



DIGI TRANSPORT® LR54

High speed LTE Advanced and Wi-Fi router in a durable hardware package for demanding M2M applications

Digi TransPort LR54 is a high speed LTE Advanced networking platform designed for self-service, retail and managed networking applications across distributed enterprises. Each device features an LTE Advanced CAT6 modem with speeds up to 300 Mbps and support for global deployments with a single hardware version, as well as a 4-port Gigabit Ethernet switch and serial port for console access. The routers include license-free enterprise software features like VPN, firewall and SNMP.

The Wi-Fi variant features dual-band, dual-concurrent 5 GHz and 2.4 GHz radios, personal/enterprise security, and multiple SSIDs for maximum range and throughput performance in M2M applications.

Digi TransPort LR54 is ideal for connecting:

- Retail branch sites
- Digital media installations
- Temporary “pop-up” stores
- Security monitoring equipment
- Self-service kiosks
- Guest and employee Wi-Fi users

FEATURES AND BENEFITS

- High speed LTE Advanced for digital content and business networking applications
- Powerful dual Wi-Fi radios provide 802.11 b/g/n/ac connection to local users and end devices
- Automated fail-over/fail-back between Ethernet, Cellular (dual SIMs), and IPsec tunnels
- Extended operating temp (-20° C to +70° C) ensures the Digi TransPort LR54 works reliably in cabinets and kiosks
- Digi Remote Manager® provides mass configuration, device management and troubleshooting tools
- 3-year warranty included

RELATED PRODUCTS



Digi TransPort®
WR11



Digi TransPort®
WR21



Digi TransPort®
WR44 R




Accessories



Digi Remote
Manager®

APPLICATION EXAMPLE



SPECIFICATIONS		Digi TransPort® LR54	
WIRELESS INTERFACES			
WWAN*			
LTE/HSPA+		LTE Bands: 1, 2, 3, 4, 5, 7, 8, 12, 13, 20, 25, 26, 29, 30, 41 HSPA+ Bands: 1, 2, 3, 4, 5, 8	
CONNECTOR		2 x 50 Ω SMA (Center pin: female)	
SIM SLOTS		2, Mini-SIM (2FF)	
SIM SECURITY		SIM slot cover plate included	
WI-FI			
802.11		Wi-Fi maximum data rates: 54 Mbps (802.11a); 11 Mbps (802.11b); 54 Mbps (802.11g); 300 Mbps (802.11n); 866 Mbps (802.11ac)	
TX POWER		2.4 GHz 19 dBm (802.11g/n), 19 dBm (802.11b) 5 GHz 22.9 dBm for all modes	
RX SENSITIVITY		-87 dBm / 11 Mbps (802.11b) -71 dBm / 54 Mbps and -90 dBm / 6 Mbps (802.11a) -74 dBm / 54 Mbps and -92 dBm / 6 Mbps (802.11g) -66 dBm / 300 Mbps and -92 dBm / 6 Mbps (802.11n 2.4 GHz) -67 dBm / 300 Mbps and -89 dBm / 6 Mbps (802.11n 5 GHz) -57 dBm / 866 Mbps and -83 dBm / 29 Mbps (802.11ac)	
MODES		Access point, support for multiple SSID	
SECURITY		Mixed WPA/WPA2 Personal; WPA2 Personal; Mixed WPA/WPA2 Enterprise; WPA2 Enterprise	
CONNECTORS		2 x 50 Ω RP-SMA (Center pin: male)	
WIRED INTERFACES			
SERIAL			
PORTS		(1) RS232 console port with TxD, RTS, and CTS. DB-9 female.	
ASYNC/SYNC		Async	
DTE/DCE		DCE	
FLOW CONTROL		Software (XON/XOFF), Hardware supported	
ETHERNET			
PORTS		4	
STANDARD/PHYSICAL LAYER		IEEE 802.3; 10/100/1000 Base-T	
DATA RATE/MODE/INTERFACE		10/100/1000 Mbit/s; Full or Half duplex; Auto MDI/MDIX	
CONNECTOR		RJ-45	
MANAGEMENT			
REMOTE MANAGEMENT		Digi Remote Manager SM (cloud based); SNMP v1/v2c/v3 (user installed/managed)	
LOCAL MANAGEMENT		Web Interface (HTTPS); CLI (SSH, Serial port)	
MEMORY		256 MB of Flash; 100 MB user available memory	
POWER			
INPUT		12 VDC	
CONNECTOR		4-pin terminal block	
CONSUMPTION		13.68W max, 11.4W average	
DC POWER SUPPLY		100-240 VAC 50/60 Hz	
PHYSICAL			
DIMENSIONS (L X W X H)		8.15 in x 4.5 in x 1.5 in (207 mm x 138.5 mm x 38 mm)	
WEIGHT		2.90 lb (1.32 kg)	
STATUS LEDs		Power, WWAN Signal, WWAN Service, SIM 1, SIM2, 2.4 GHz and 5 GHz LEDs on Wi-Fi version	
MATERIAL/RATING**		Industrial (Metal) / IP30	
MOUNTING		Wall mount bracket sold separately	

* Transfer rates are network operator dependent


**The enclosure rating is self-declared and has not been formally verified by an independent lab.

SPECIFICATIONS		Digi TransPort® LR54	
ENVIRONMENTAL			
OPERATING TEMPERATURE **		-20° C to +70° C	
STORAGE TEMPERATURE		-40° C to +85° C	
RELATIVE HUMIDITY		0% to 95% (non-condensing) @ 25° C	
APPROVALS			
GSM/UMTS		PTCRB	
WI-FI		Wi-Fi Alliance Wi-Fi CERTIFIED™	
MATERIALS		RoHS	
CELLULAR CARRIERS		Verizon, AT&T; Compatible with most major carriers	
SAFETY		CB Scheme, IEC 60950-1	
EMISSIONS/IMMUNITY		CE, FCC Part 15 Class B	
WARRANTY			
PRODUCT WARRANTY		3 years	

ENTERPRISE SOFTWARE	DESCRIPTION
MANAGEMENT PROTOCOLS	HTTPS, TLS1.0/1.1/1.2, SFTP, SCP,SNMP (v1/v2c/v3), SSHv2,CLI for web management; remote management via Digi Remote Manager; protocol analyzer, ability to capture PCAP for use with Wireshark
SECURITY/VPN	Stateful inspection firewall with scripting; VPN: IPsec with IKEv1; VPN Tunnels included: 32; Cryptology: SHA-1/SHA256, RSA, DH Groups 5,14,15,16,17,18 ; Encryption: AES up to 256-bit; Ethernet Port Isolation
ROUTING/FAILOVER	NAT, NAPT with IP Port Forwarding; IP Failover: Automatic failover/failback to second GSM network/Standby APN, IP Port forwarding
OTHER PROTOCOLS	DHCP

PRODUCT IMAGES

DIGI TRANSPORT LR54




DIGI TRANSPORT LR54 W



**The enclosure rating is self-declared and has not been formally verified by an independent lab.



DIGI REMOTE MANAGER®



CAPABILITIES

- Centralized management of remote devices over 3G/4G LTE
- Define standard configurations and automatically monitor individual devices for PCI security compliance
- Report and alert on performance statistics, including connection history, signal quality, latency, data usage and packet loss
- No servers or applications to operate and maintain
- Complete tasks for your entire device network in minutes
- Edit configurations and update firmware for your individual devices or groups
- Monitor the status and location of your remote device via a web browser
- Active or deactivate cellular lines and monitor data to ensure you never incur overage charges

INFRASTRUCTURE

- Hosted in multiple commercial-grade SAS 70 certified facilities in North America
- Superior availability, operating to 99.9% or greater
- Open APIs available to support application development

SECURITY

- Certified SSAE-16 and ISO27001 facilities
- Member of the Cloud Security Alliance
- Over 175 Security Controls in place to protect your data
- Enables compliance with security frameworks like PCI, HIPAA, NIST and more
- Earned SkyHigh's Cloud Trust Program highest ranking of Enterprise-Ready

PART NUMBERS	DESCRIPTION
LR54-AA401	Digi TransPort LR54, LTE, Power Supply, Ethernet Cable, and Antenna Included
LR54-AW401	Digi TransPort LR54, LTE, Wi-Fi, Power Supply, Ethernet Cable, and Antenna Included

FOR MORE INFORMATION
PLEASE VISIT WWW.DIGI.COM

DIGI SERVICE AND SUPPORT / You can purchase with confidence knowing that Digi is always available to serve you with expert technical support and our industry leading warranty. For detailed information visit www.digi.com/support.

© 1996-2016 Digi International Inc. All rights reserved.
All trademarks are the property of their respective owners.

95003316
A5/1016

DIGI INTERNATIONAL WORLDWIDE HQ
877-912-3444 / 952-912-3444 / www.digi.com

DIGI INTERNATIONAL FRANCE
+33-1-55-61-98-98 / www.digi.fr

DIGI INTERNATIONAL JAPAN
+81-3-5428-0261 / www.digi-intl.co.jp

DIGI INTERNATIONAL SINGAPORE
+65-6213-5380

DIGI INTERNATIONAL CHINA
+86-21-50492199 / www.digi.com.cn

