



KILOVAC EV202 High-Voltage Contactors

High Performance in a Compact, Lightweight Contactor
Designed for Harsh Environments

EV202 High-Voltage Contactors


Hermetically Sealed Double Pole 350 Amp DC Contactors

Hermetically sealed and designed for harsh environments and loads, KILOVAC EV202 high-voltage contactors from TE Connectivity (TE) offers exceptional performance in an extremely small and lightweight device.

Available with 12 or 24-V coils, the contactors are suited to 270 and 400-VDC power systems. They are available with two optional auxiliary contacts.

High break levels—2000 A at 270 VDC and 700 A at 400 VDC—help increase system flexibility and reliability.

EV202 contactors provide reliable and long-lasting performance in military and commercial electric ground vehicles, energy storage systems, and power distribution and motion control applications.



TE Components . . . TE Technology . . . TE Know-how . . .

AMP | AGASTAT | CII | HARTMAN | KILOVAC | MICRODOT | NANONICS | POLAMCO | Raychem | Rochester | DEUTSCH
SEACON Phoenix | LL Rowe | Phoenix Optix | AFP | SEACON

Get your product to market faster with a smarter, better solution.



HERMETICALLY SEALED

- Suitable for application in harsh, explosive, and corrosive environments
- EMC compliant: no radiated coil emissions

SPACE AND WEIGHT SAVINGS

- Extremely small size
- Lightweight contactor: 0.77 kg

VERSATILE

- Bidirectional switching
- Main contacts not polarity sensitive
- Not position sensitive: mounts in any orientation




EFFICIENT

- Integrated dual-coil electronic economizer with coil suppression

APPLICATIONS


- Energy Storage/Battery Storage
- Power Distribution
- Power Motion Control
- High-Voltage DC Converter Systems
- Alternative Energy
- Military and Commercial Electric Vehicles
- Test Equipment

Product Dimensions (Inches)



Typical Schematic

(Shown with Auxiliary Contacts)





Specifications

ELECTRICAL DATA

- **Configuration:** Double pole, single throw, normally open
- **Voltage Rating, Main Contacts:** 600 VDC, max.
- **Make Current:** 700 A, max.
- **DWV and Insulation Resistance over Life, Terminal to Terminal/Terminals to Coil**
Dielectric Withstand Voltage: 1 mA max @ 2200 V_{rms}
Insulation Resistance: 50 mΩ min. @ 500 VDC
- **Hot Switch Life:**

Make/Break Current	@ Voltage	Hot Switch Life
100 A	270 VDC	40,000
	400 VDC	10,000
250 A	270 VDC	7500
	400 VDC	2500
700 A Break Only	400 VDC	10
2000 A Break Only	270 VDC	2

COIL DATA (over -40°C to +85°C unless noted)

Coil Voltage, nom./max.	12/16 VDC	24/32 VDC
Pick up voltage, max. (applied as step voltage only)	8 VDC	16 VDC
Dropout Voltage	2.5-4 VDC	3-8 VDC
Coil Inrush Current @ V-nom., max.	5 A	4.5 A
Coil Inrush Time, nom./max.	75/150 ms	75/150 ms
Hold Current @ V-nom., max.	0.6 A	0.2 A
Coil Suppression, max.	40 VDC	60 VDC
Operate Times		
Operate Time, nom./max.	13/20 ms	13/20 ms
Operate Bounce, nom./max.	3/10 ms	3/10 ms
Release Time, nom./max.	5 ms	5 ms
Release Time, max. (including max. arc time)	25 ms	25 ms

OPTIONAL AUXILIARY CONTACTS

- **Configuration:** Two SPDT switch outputs
- **Ratings:** 30 VDC/2A switching or 5 V/5 mA signal

ENVIRONMENTAL

- **Operating Temperature Range:** -55°C to + 85°C
- **Hermetically Sealed:** Safe for harsh/corrosive environments
- **Nonoxidizing:** No contact oxidation over periods of nonuse
- **RoHS Compliant**
- **Economizer:** Integrated electronically switched coil economizer with coil suppression
- **EMC Compliant:** No radiated coil emissions

MECHANICAL

- **Shock:** 11 ms 1/2 sine (operating): 20 g peak
- **Sine Vibration:** 10 g peak: 10 to 2000 Hz
- **Random Vibration:** 14 g_{rms}:

Hz	15	100	300	900	2000
g ² /Hz	0.01	0.01	0.2	0.2	0.01

- **Bidirectional Switching:** Main contacts not polarity sensitive
- **Mounting:** Mounts in any orientation; not position sensitive
- **Mechanical Life:** 100,000 cycles
- **Weight:** 0.77 kg

Part Numbers

Coil Voltage	Aux Contacts	Lead Length	Connector	Description	Part No.
24 VDC	2	6"	Yes	EV202MSBFD	5-1618407-2
24 VDC	2	15.3	No	EV202MSAND	5-1618407-3
24 VDC	0	15.3	No	EV202ASAND	8-1618406-3
12 VDC	0	15.3	No	EV202AVAND	9-1618406-9



TE PART NUMBERING SYSTEM

SERIES

EV202 = Two Form X, DPST-NO-DM Contactor

AUXILIARY CONTACT OUTPUTS (SPDT form C)

A None

M Two

COIL VOLTAGE

S 24 V

V 12 V (With Built-In Dual Coil Economizer)

COIL AND AUX WIRE LENGTH (inches)

A 15.3

B 6

X Customer-Specified Configuration

COIL AND AUX CONNECTOR

N None

F D-Subminiature Plug on Flying Leads (May Affect Wire Length)

MOUNTING AND POWER TERMINALS

D Two M5 Bottom Mount with Four M6 X 1 Female thread terminals

EV202 M S B F D



LET'S CONNECT

We make it easy to connect with our experts and are ready to provide all the support you need. Just call your local support number or visit www.te.com/industrial to chat with a Product Information Specialist.

Technical Support

te.com/support-center

North America	+1 800 522 6752	Asia Pacific	+86 400 820 6015
North America (Toll)	+1 717 986 7777	Japan	+81 044 844 8180
EMEA/South Africa	+800 0440 5100	Australia	+61 2 9554 2695
EMEA (Toll)	+31 73 624 6999	New Zealand	+64 (0) 9 634 4580
India (Toll-Free)	+800 440 5100		

te.com/ev202

AMP, AGASTAT, CII, DEUTSCH, HARTMAN, KILOVAC, LL Rowe, MICRODOT, NANONICS, POLAMCO, Raychem, SEACON, TE, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

Consult TE for the latest dimensions and design specifications.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.

1-1773900-8 11/16 Original