


# Minitek® Pwr 3.0 High Current Connector System

## Dual Row

### ROBUST, VERSATILE AND HIGH CURRENT PERFORMANCE

Minitek® Pwr 3.0 High Current Connector (HCC) is designed for power applications with current rating up to 12A per contact and wire gauge range from 20 to 16AWG for Wire-to-Wire and Wire-to-Board applications. It is available in 2 to 24 circuits for dual row.

- Rated current up to 12A per contact
- Fully isolated terminals
- High retention force in housing
- Fully polarized housing



#### TARGET MARKETS



#### FEATURES

- High current alloy material used for contacts
- Fully isolated terminals
- Positive locking on housing with low thumb latch operation
- Fully polarized housings
- High retention force in housing
- Interchangeable hand crimping and terminal extraction tools
- Glow wire compliant option
- UL94V-0 flammability rated nylon material
- RoHS compliant and lead-free

#### BENEFITS

- Rated up to 12A per contact
- Prevents terminals from potential damage during operation
- Ensures secured mating retention
- Prevents accidental mismating
- Well secured terminals in housing
- New crimping tools are not required
- Complies with International Standard IEC 60335-1 for household appliances
- High flammability rating
- Meets environmental, health and safety requirements

## TECHNICAL INFORMATION

### MATERIAL

- Board Connector: High Current Alloy with optional Tin and Gold Flash plating
- Housing: High Temperature Thermoplastic, Black, UL94V-0
- Crimping Terminal: High Current Alloy with optional Tin and Gold Flash plating

### MECHANICAL PERFORMANCE

- Terminal Insertion Force: 5N max.
- Terminal Withdrawal Force: 2N min.
- Durability: 100 mating cycles
- Wire Pullout Force: Refer to product specifications

### ELECTRICAL PERFORMANCE

- Low Level Contact Resistance: 20mΩ max.
- Insulation Resistance: 1000MΩ min.
- Voltage Rating: 250Vrms
- Current Rating: Up to 12A/contact
- Dielectric Withstand Voltage: 1500VAC
- Temperature Rise: 30°C max

### PACKAGING

- PCB Header: Tray
- Crimping Housing: Bag
- Terminal: Reel

### APPROVALS & CERTIFICATION

- Glow Wire Ignition Temperature (GWIT) per IEC 60695-2-13
- Glow Wire Flammability Index (GWFI) per IEC 60695-2-12

### SPECIFICATION

- Amphenol Product Specification: GS-12-1291 and GS-12-1374
- Amphenol Application Specification: GS-20-0399
- Amphenol Packaging Specification: GS-14-2419

### ENVIRONMENTAL

- Operating Temperature: -40°C to +105°C  
\*Includes 30°C terminal temperature rise at rated current

### TOOLING INFORMATION

- Ratchet Hand Crimping Tool: 10129483-001LF
- Terminal Extraction Tool: 10129274-030LF

### TARGET MARKETS/APPLICATIONS



1U Rack Box  
Customer Premises Equipment  
Generic Telecom Box  
Interface Converter  
WiMax Box



Air Conditioner  
Microwave Oven  
Refrigerator  
Set Top Box



Blade Server  
Desktop PC and Motherboard  
HDD Application  
Rack-Mount Server  
Server-Orthogonal Configuration



Defibrillator  
Hospital Bed  
Patient Monitor  
Ultrasound Equipment



Chemical Detection System  
Radar Equipment

## PART NUMBERS

| Type                      | Description                                | Part Numbers      |
|---------------------------|--------------------------------------------|-------------------|
| Dual Row                  | Right angle PCB header                     | 10132449          |
|                           | Vertical PCB header                        | 10132450          |
|                           | Receptacle housing                         | 10132445          |
|                           | Header housing                             | 10132446          |
| Single Row                | Right angle PCB header                     | 10142730          |
|                           | Receptacle housing                         | 10142744          |
| Applicable for both types | Receptacle terminal (post-plated solution) | 10132447/10134160 |
|                           | Header terminal                            | 10132448          |