

MIL-DTL-83526 CERTIFIED

Cinch Connectivity Solutions – Mil-Junior

The Cinch Advantage

Our military certified expanded beam connectors have been designed for use in the most demanding harsh environment applications including military tactical communications, outside broadcast, petrochemical plant, mining, and offshore systems. The connectors are terminated using an epoxy-polish ferrule termination process with standard fiber optic termination tools and equipment. The terminated ferrules are simply inserted into the expanded beam housing and fixed in place via a spring and cover-plate. Ferrule alignment to the lenses is achieved automatically by the unique optical arrangement developed and patented by Cinch-Fibreco.

In the event of the connector suffering severe damage in use, the connector design enables replacement of the expanded beam insert, connector front body and grip ring without the need to re-terminate the fibers. Typically, an expanded beam insert can be replaced within 30 minutes in field conditions.

The MIL-DTL-83526 Certified expanded beam connectors offer high performance, flexibility and cost effectiveness, combined with a simple termination process allowing rapid in-field termination and repair.

Features

- MIL-DTL-83526/20 /21 QPL
- German Defence Standard VG 95319-100 & 102
- Singlemode, multimode and mixed-mode insert options
- Field terminable using standard termination tools & equipment
- Field repairable: EB insert & shell parts replaceable / re-useable
- 1, 2 & 4 channel plugs and bulkhead receptacles
- Low insertion loss / high return loss
- Cage Code - 71785



cinch
CONNECTIVITY SOLUTIONS

a bel group

US +1 507.833.8822
ccsorders@us.cinch.com

EMEA +44 (0) 1245 342060
CinchConnectivity@eu.cinch.com
cinch.com

299 Johnson Drive SW
Suite 100
Waseca, MN 56093 USA

© 2015 Cinch Connectors, Inc.

m8352606.15


Outline Specification

MIL-DTL-83526 Certified Expanded Beam Connector - Outline Specification


Insertion Loss	Singlemode	-2.5dB (typical -1.5dB)*
	Multimode	-2.0dB (typical -1.0dB)*
Return Loss		≥35dB (typical 40dB) singlemode
Durability		3000 Matings minimum
Operating Temperature		-46°C to +71°C
Storage Temperature		-57°C to +85°C
Water Immersion		15m for 24 hours (Plug & Bulkhead; mated & open-face)
Free Fall Resistance		500 Falls from 1.2m height
Vibration/Shock		As per MIL-DTL-83526/20 /21
Crush Resistance		6.7kN
Corrosion Resistance		500 Hours Salt Spray
Cable Retention		1800N (Cable Dependant)
Weight (approx)		Plug: 120g Bulkhead: 110g
Connector Shell Material / Color		Aluminium, Plug: black anodised Bulkhead: zinc cobalt Grip & boot: black, fluorosilicone

*performance is dependent on assembly & termination; figures relate to CCS terminated harnesses.


Insert Arrangements




3153 - 1CH OPTICAL




2410 - 2CH OPTICAL




2411 - 4CH OPTICAL



Plug Connector



Bulkhead Connector



US +1 507.833.8822

ccsorders@us.cinch.com

EMEA +44 (0) 1245 342060

CinchConnectivity@eu.cinch.com

cinch.com