



Product Brief

The new TRENCHSTOP™ 5 S5 IGBT

High speed, soft switching IGBT with full rated current diode


Developed with the customer in mind

TRENCHSTOP™ 5 S5 is the new IGBT family addressing applications switching between 10 kHz and 40 kHz to deliver high efficiency, faster time to market cycles, circuit design complexity reduction and PCB bill of material cost optimization.

Packed with features to help the designers achieve their goals without the need to increase circuit complexity

- › Static behavior - mild positive temperature coefficient $V_{CE(sat)}$, meaning paralleling is no problem and efficiency isn't compromised during high temperature operation. At 175°C, typical $V_{CE(sat)}$ is a low 1.6 V.
- › Dynamic behavior – single gate resistance selection for turn-on / turn-off due to the soft switching behavior. Clean gate signals, low dV/dt , low and very symmetrical voltage overshoot.

To highlight the dynamic behavior, TRENCHSTOP™ 5 S5 switching turn-off waveforms are added*



1. Soft current fall characteristic with no tail current
2. Symmetrical, low voltage overshoot
3. Gate voltage under control (no oscillation). No risk of unwanted turn-on of device and no need for gate clamping

Main features

- › Very low $V_{CE(sat)}$ of 1.35 V at 25°C, 20% lower than TRENCHSTOP™ 5 H5
- › $I_{C(n)} =$ four times nominal current (100°C T_c)
- › Soft current fall characteristic with no tail current
- › Symmetrical, low voltage overshoot
- › Gate voltage under control (no oscillation). No risk of unwanted turn-on of device and no need for gate clamping
- › Maximum junction temperature $T_{vj}=175^\circ\text{C}$
- › Qualified according to JEDEC standards

Main benefits

- › $V_{CE(peak)}$ clamping circuits not required
- › Suitable for use with single turn-on / turn-off gate resistor
- › No need for gate clamping components
- › Gate drivers with Miller clamping not required
- › Reduction in the EMI filtering needed
- › Excellent for paralleling

*IKW40N65ES5 measured on in-house welding test bench with $R_g=33\ \Omega$, total loop parasitic inductance $L_o=90\ \text{nH}$, $I_c=33\ \text{A}$.

I_c at 10 A/div, V_{CE} at 100 V/div, V_{GE} at 5 V/div, P_D (E_{off})=2 kW/div, $t=20\ \text{ns/div}$




The new TRENCHSTOP™ 5 S5 IGBT

High speed, soft switching IGBT with full rated current diode

Single turn-on / turn-off gate resistor. Seriously? You bet!

The figures below show the advantage of taking a single gate resistor with the TRENCHSTOP™ 5 S5, when compared to the TRENCHSTOP™ 5 H5.



Portfolio

Product part number	I _C @ 100°C [A]	V _{CE(sat)} [V]	E _{on} [mJ]	E _{off} [mJ]	Q _G [nC]	I _F @ 100°C [A]	Q _{rr} [μC]
IKW30N65ES5	39.5	1.35	0.56	0.32	70	39.5	0.83
IKW40N65ES5	50	1.35	0.86	0.4	95	50	1.1
JKW50N65ES5	60.5	1.35	1.23	0.55	120	60.5	1.25
IKW75N65ES5	80	1.42	1.92	0.95	164	80	1.86

Specification details

Testing conditions:

V_{CE(sat)}: typ. values, 25°C, V_{GE}=15 V, I_C=I_{C(nom)}

E_{on} and E_{off}: typ. values, 25°C, V_{CC} = 400 V, I_C = I_{C(nom)}, V_{GE} = 0/15 V, R_G = R_{G(nom)}, L_σ = 30 nH, C_σ = 30 pF

Q_G: typ. values, 25°C, V_{CC} = 520 V, V_{GE} = 15 V, I_C = I_{C(nom)}

Q_{rr}: typ. values, 25°C, V_{CC} = 400 V, I_F = I_{F(nom)}, di_F/dt = -1.2 kA/μs for the 30 A and 50 A, = -0.8 kA/μs for the 40 A, = -1.5 A/ns for the 75 A

Published by
Infineon Technologies Austria AG
9500 Villach, Austria

© 2015 Infineon Technologies AG.
All Rights Reserved.

Please note!

THIS DOCUMENT IS FOR INFORMATION PURPOSES ONLY AND ANY INFORMATION GIVEN HEREIN SHALL IN NO EVENT BE REGARDED AS A WARRANTY, GUARANTEE OR DESCRIPTION OF ANY FUNCTIONALITY, CONDITIONS AND/OR QUALITY OF OUR PRODUCTS OR ANY SUITABILITY FOR A PARTICULAR PURPOSE. WITH REGARD TO THE TECHNICAL SPECIFICATIONS OF OUR PRODUCTS, WE KINDLY ASK YOU TO REFER TO THE RELEVANT PRODUCT DATASHEETS PROVIDED BY US. OUR CUSTOMERS AND THEIR TECHNICAL DEPARTMENTS ARE REQUIRED TO EVALUATE THE SUITABILITY OF OUR PRODUCTS FOR THE INTENDED APPLICATION.

WE RESERVE THE RIGHT TO CHANGE THIS DOCUMENT AND/OR THE INFORMATION GIVEN HEREIN AT ANY TIME.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life endangering applications, including but not limited to medical, nuclear, military, life critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.