

Flush-type connector - SACC-DSI-M8FS-8CON-M10-L180 SH - 1424235

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator flush-type plug-in connector, socket, 8-pos. M8, rear/screw mounting with M10 fastening thread, with straight solder connection



Key commercial data

Packing unit	0
Minimum order quantity	1
GTIN	 4 046356 712477
Custom tariff number	85366990
Country of origin	GERMANY

Technical data

General data

Rated current at 40°C	1.5 A
Rated voltage	30 V
Number of positions	8
Volume resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Ambient temperature (operation)	-25 °C ... 85 °C

General characteristics

Standards/regulations	M8 plug-in connector IEC 61076-2-104
Surge voltage category	II
Pollution degree	3
Degree of protection	IP67
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PA 66
Material, knurls	Zinc die-cast, nickel-plated
Mounting type	Rear mounting M8 x 1 With flat nut

Flush-type connector - SACC-DSI-M8FS-8CON-M10-L180 SH - 1424235

Technical data

General characteristics

Connection method	Solder pins
Status display	No

Classifications

ETIM


ETIM 4.0	EC002635
ETIM 5.0	EC002635

eCl@ss

eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001

Drawings


Schematic diagram



Connector pin assignment of M8 socket, 8-pos., view of socket side

Flush-type connector - SACC-DSI-M8FS-8CON-M10-L180
SH - 1424235

Drilling diagram



Socket drilling diagram

Flush-type connector - SACC-DSI-M8FS-8CON-M10-L180 SH - 1424235

Dimensioned drawing

