

Quick Reference Guide

0.6mm CL High Speed CHAMP Docking Connector

The docking connector series is designed for high density, low profile (3.8mm) shield applications featuring two rows of contacts on 0.6mm pitch centerlines. Contacts on a 0.6mm centerline can save 30% of linear board space, while the 3.8mm low profile housing reduces connector height by approximately 25% when compared with 0.8mm CL laptop PC docking series connector. Multiple options are available including right angle receptacles, right angle offset receptacles, and a vertical plug for dock and cable.

When compared with 0.5mm pitch docking connector, TE Connectivity's (TE's) 0.6mm pitch product is more reliable and performs better in high frequency signals.

TE's 0.6mm CL high speed CHAMP docking connector is designed to meet various industry transmission standards including USB 3.0, HDMI (high definition multimedia interface) and DisplayPort.

FEATURES

- Strong sense of contacting from the side latches when pushing/pulling
- Signal/ground to conform EMI prevention
- Mis-insertion prevented and guide rail equipped for mating


BENEFITS

- USB 3.0 transmission compliance
- High definition differential signal of HDMI, DisplayPort transmission compliance
- Guaranteed 10,000 plug-ins

APPLICATIONS

- Tablet PC
- Laptop PC
- MID (Mobile Internet Devices)
- Converged mobile phone

Application



0.6mm CL High Speed CHAMP Docking Connector


	Part Number	Type	Mount Style	Direction	Description	Finish	Package	Mating Parts
	2129260-1	Receptacle	2-Row T/H, 1-Row SMT	Right-angle	With screwlock	15µ Au & Sn	T&R	2129261-1, 2129276-1
	2129260-2	Receptacle	2-Row T/H, 1-Row SMT	Right-angle	Without screwlock	15µ Au & Sn	T&R	2129261-1, 2129276-1
	2129273-1	Receptacle	2-Row T/H, 1-Row SMT	Right-angle mid-mount	Without screwlock	15µ Au & Sn	T&R	2129261-1, 2129276-1
	2129261-1	Plug	2-Row T/H, 1-Row SMT	Vertical	Cradle	15µ Au & Sn	T&R	2129260-1/-2, 2129273-1
	2129276-1	Plug	Soldering	N/A	Cable plug	15µ Au & Sn	Tray	2129260-1/-2, 2129273-1

* Note: Each of these are 40 pos, other positions can be added later as they are tooled.

Product Sizes



P/N: **2129260-1**

Receptacle with screwlock





P/N: **2129273-1**

Receptacle without screwlock



P/N: **2129261-1**

Cradle plug



P/N: **2129260-2**

Receptacle without screwlock

Dimensions: mm

Frequently asked questions

Question 1

Why did TE develop 0.6 mm CL (centerline) high speed CHAMP docking connector? Is it more compatible with tablets in the market?

Answer 1

0.6 mm CL high speed CHAMP docking connectors perform better in signal transmission than similar connectors of 0.5mm pitch, which ensures the differential signaling of USB3.0, DisplayPort and HDMI standards. We also expect that more tablet PCs will be equipped with the advanced industry-standard I/Os in the near future.

Question 2

Why does the PCB layout feature one row of SMT (surface mount technology), and two rows of through-hole?

Answer 2

Dual rows of SMT soldering may make it difficult to control coplanarity. So we suggest customers use one row of SMT contact for differential signaling and two rows of through-hole for other pin assignments.

Question 3

How does TE arrange production to meet increasing market demand? Does the product reserve any IP (intellectual property) rights?

Answer 3

TE has strong production capability to serve the market. As the owner of IP rights for the product design, TE can grant licenses to qualified, reliable suppliers to increase production if necessary.

Question 4

Can TE support a customer's specific pin assignment requirements?

Answer 4

TE is renowned for its strong signal evaluation capability. We can provide engineering resources to address specific customer pin assignment requirements to satisfy a customer's needs.

Question 5

Will TE offer any other options of contact positions besides the current 40-position?

Answer 5

TE currently offers only 0.6 mm CL high speed CHAMP docking connectors in a 40-position configuration. But we will certainly develop 20-, 30- and 50-position connectors.

FOR MORE INFORMATION

TE Connectivity Technical Support Center

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/South America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

For other country number go to te.com/supportcenter

Part numbers in this brochure are RoHS Compliant*, unless marked otherwise.

*as defined www.te.com/leadfree

te.com

© 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved.

6-1773457-9 CIS PDF 04/2011

DisplayPort is a trademark of the Video Electronics Standards Association.

HDMI is a trademark of HDMI Licensing, LLC.

CHAMP, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks. Other logos, product and/or Company names might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

