



Application Note

AS5x47y DAEC

Dynamic Angle Error Compensation Details

Content Guide

1	General Description	3
2	What is the dynamic angle error (DAE)?	3
3	Why integrated compensation is better.....	3
4	DAEC error budget.....	4
5	DAEC for different outputs	4
6	Summary.....	5
7	Contact Information.....	6
8	Copyrights & Disclaimer.....	7
9	Revision Information	8

1 General Description

One of the main features of the AS5x47y magnetic position sensors is the dynamic angle error compensation (DAEC). It allows the AS5x47y to output the angular position nearly latency-free with respect to a defined maximum acceleration.

A big advantage is, that compared with other solutions, the AS5x47p position sensors don't need a special synchronization between controller and position sensor. It is used with the encoder output to replace an existing optical encoder or can be read over the digital interface.

The total position error results from static (eg. output noise and non-linearity) and dynamic components (eg. dynamic angle error).

The dynamic angle error comes from the propagation delay and is zero for standstill and increases with the angular speed up to maximum speed of the application (eg. 14,5 krpm). The DAE is calculated for a typical propagation delay. (eg. 200 μ s). Using the automatic compensation feature DAEC, this error is dramatically reduced to a negligible component. (Please note that values are exemplary – for product details refer to the product datasheet)

2 What is the dynamic angle error (DAE)?

Digital sensor outputs have a propagation delay resulting from the signal processing. When measuring the angle of a sensor magnet in static condition, the propagation delay will not cause additional angle error.

As soon as the magnet is rotating, the propagation delay of the output signal will cause an angle error at the sensor output. The error is as big as the angle of rotation during the propagation delay and for constant angular speed it can be calculated as:

Equation 1: Dynamic Angle Error

$$DAE = Propagation\ delay \times \frac{Speed(rpm) \times 360\ deg}{60\ s} = 0,0002s \times \frac{3000 \times 360\ deg}{60\ s} = 3.6\ deg$$

For the maximum possible rotation speed of 14,5 krpm (AS5147) the DAE grows up to 17.4 degree (For the AS5147P the max. rotating speed is 28 krpm and would therefore result in a maximum DAE of 33.6 degree). As the DAE depends on the angular velocity, it could be compensated in the application by calculating the DAE and adding it to the measured angle. The propagation delay has a tolerance of $\pm 10\%$ and therefore the compensation cannot be better than $\pm 10\%$ of the DAE. (eg. ± 0.36 deg @ 3krpm) (Please note that values are exemplary – for product details refer to the product datasheet)

In addition, a compensation algorithm will load the MCU and it takes time to implement the software and qualified software has to be changed in case of replacing a existing system.

3 Why integrated compensation is better...


Basically the internal compensation follows the compensation principle introduced above but performing the compensation internally offers following advantages:

- **Independent from oscillator** variation because angle conversion and DAEC use same timebase

- Almost **NO DAE** at the **encoder output** because close implementation with integrated interpolator
- **Latency-free angle** information in the **DAECANG** register resulting from very high update rate of the compensation value of the internal interpolator

The block diagram of the DEAC is shown below in Figure 1.

Figure 1: DAEC block diagram



4 DAEC error budget

With activated DAEC(default), the dynamic angle error depends on the acceleration of the angle signal. For constant speed, the dynamic angle error is compensated and the latency is reduced to $\pm 1.9\mu\text{s}$. For constant speed at 14.5krpm the DAE is reduced to $\pm 0.165\text{deg}$ as shown in Equation 2. (Please note that values are exemplary – for product details refer to the product datasheet.)

Equation 2: DAE after compensation at constant speed

$$DAE = \text{Propagation delay} \times \frac{\text{Speed(rpm)} \times 360 \text{ deg}}{60 \text{ s}} = 0,0000019\text{s} \times \frac{14500 \times 360 \text{ deg}}{60 \text{ s}} \\ = 0.165 \text{ deg}$$

During an acceleration the dynamic angle error will increase according to Equation 3 because of the deviation of the estimated position and the real position. It consists of the error during acceleration caused by the propagation delay and the speed measurement delay.

Equation 3: DAE during acceleration

$$DAE_{ACC} = \frac{\text{acceleration}(\text{rad/s}^2)}{2} \times (PD^2 + PD * \Delta t_{speed}) \\ = ((0,0002\text{s})^2 + 0,0008 \times 0,0002) \times \frac{100000 \text{ rad/s}^2}{2} \times \frac{180}{\pi} = 0.6 \text{ deg}$$

5 DAEC for different outputs


The latency-free encoder output is based on the DAEC and allows to use the magnetic position sensors in high-speed encoder applications where high robustness is required. The digital readout benefits a lot from this feature as shown in Table 1.

Table 1: Output interface performance

Output Type	Resolution	Refresh Rate	Latency
DAECANG (SPI)	14 bit	222ns	1.9µs
Encoder (ABI)	12 bit	222ns	1.9µs

While with other digital sensors require synchronization with the controller at high rotation speeds, the AS5x47y position sensor always outputs the latest compensated angle data over SPI which can directly be used in the controller without synchronization. An illustration for the benefits for the Encoder Output and SPI output are shown in Figure 2.

Figure 2: Encoder output and SPI output profit from DAEC



6 Summary

The dynamic angle error compensation is an essential feature for position sensors which are used in applications that require high resolution angle feedback with low latency output. With the DEAC feature activated, the advantages of magnetic position sensors are as well applicable in high speed motor applications.

The dynamic angle error is reduced to a negligible value and can be calculated as explained in Equation 2. For high dynamic drives, the DAE present during an acceleration is calculated as shown in Equation 3.

The different interfaces available on the AS5x47y series position sensors make the device flexible to be used in different motor control applications in the automotive market and for industrial or consumer robotics.

7 Contact Information

Buy our products or get free samples online at:

www.ams.com/ICdirect

Technical Support is available at:

www.ams.com/Technical-Support

Provide feedback about this document at:

www.ams.com/Document-Feedback

For further information and requests, e-mail us at:

ams_sales@ams.com

For sales offices, distributors and representatives, please visit:

www.ams.com/contact

Headquarters

ams AG

Tobelbaderstrasse 30

8141 Unterpremstaetten

Austria, Europe

Tel: +43 (0) 3136 500 0

Website: www.ams.com

8 Copyrights & Disclaimer

Copyright ams AG, Tobelbader Strasse 30, 8141 Unterpremstaetten, Austria-Europe. Trademarks Registered. All rights reserved. The material herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner.

Information in this document is believed to be accurate and reliable. However, ams AG does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Applications that are described herein are for illustrative purposes only. ams AG makes no representation or warranty that such applications will be appropriate for the specified use without further testing or modification. ams AG takes no responsibility for the design, operation and testing of the applications and end-products as well as assistance with the applications or end-product designs when using ams AG products. ams AG is not liable for the suitability and fit of ams AG products in applications and end-products planned.

ams AG shall not be liable to recipient or any third party for any damages, including but not limited to personal injury, property damage, loss of profits, loss of use, interruption of business or indirect, special, incidental or consequential damages, of any kind, in connection with or arising out of the furnishing, performance or use of the technical data or applications described herein. No obligation or liability to recipient or any third party shall arise or flow out of ams AG rendering of technical or other services.

ams AG reserves the right to change information in this document at any time and without notice.

9 Revision Information

Changes from previous version to current revision 1-02 (2015-Aug-27)	Page
Applied minor changes and corrected typos	
Updated section 1	

Note: Page numbers for the previous version may differ from page numbers in the current revision.

Correction of typographical errors is not explicitly mentioned.