


# ASMB-589

**LGA 1851 Intel® Core™ Ultra 9/7/5  
MicroATX Server Board with 4 x DDR5,  
4 x PCIe (2 x Gen 5, 2 x Gen 4),  
8 x USB 3.2, 5 x SATA3, Quad/Dual LANs**

**NEW**



CE FCC

## Features

- LGA 1851 Intel® Core™ Ultra 9/7/5 processors with W880 chipset
- DDR5 ECC/Non-ECC 5600\*/4800/4400/ MT/s UDIMM up to 192 GB
- One PCIe x16 (Gen 5), one PCIe x4 (Gen 5) and two PCIe x4 (Gen 4) slots
- Triple displays - DP, VGA, and HDMI 2.0 ports
- Five SATA 3 ports and eight USB 3.2 ports
- One M.2 2280 (PCIe x4)
- Rackmount optimized placement with positive air flow design
- 0 ~ 60 °C (32 ~ 140 °F) ambient operating temperature range

Note: Supported OS including Windows 10/ 11 (64-bit) and Server 2022 (64-bit) have been validated.

## Specifications

Form Factor	Micro ATX form factor					
Processor System	Socket	Intel® LGA 1851				
	CPU type	Intel® Core™ Ultra 9/7/5 processors (TDP up to 125W)				
Core Logic	Chipset	Intel® W880 chipset				
	Total slots	4 (Dual Channel)				
Memory	Capacity	Maximum 192 GB				
	Memory type	DDR5 ECC/Non-ECC 5600*/4800/4400 MT/s UDIMM (288-pin)				
	Memory size	8 GB, 16 GB, 32 GB, 48 GB				
Expansion Slots	Total PCIe slots	4				
	Slot location 1	-				
	Slot location 2	-				
	Slot location 3	-				
	Slot location 4	PCIe x4 slot (Gen 4 x4 link)				
	Slot location 5	PCIe x4 slot (Gen 4 x4 link)				
	Slot location 6	PCIe x16 slot (Gen 5 x16 link)				
Graphics	Slot location 7	PCIe x4 slot (Gen 5 x4 link)				
	Controller	Intel® HD Graphics				
Storage	VRAM	1 GB maximum shared memory with 2 GB and above system memory installed				
	SATA controller	Intel® W880: 5 SATA3 6Gb/s ports with Rapid Storage Technology support (for Windows only) (Supports software RAID 0, 1, 10 & 5)				
Networking	SAS controller	-				
	GbE LAN	1 x Intel® I219LM + 2 x Intel® I226 + 1 x Intel® I210AT				
Onboard I/O Connector	LPT connector	-				
	PSU connector	24-pin SSI power connector + 8-pin SSI 12 V power connector				
	USB connector	9 (2 x USB 3.2 Gen1, 4 x USB 2.0, 1 x USB 2.0 Type-A, 1 x USB3.2 Type-A, 1 x USB 3.2 Gen2 Type-C)				
	M.2 connector	1 x M.2 2280 (PCIe G4 x4 link)				
	Fan header	5 x (4-pin)				
	SMBus	1				
	Chassis intrusion	1				
	Front LAN LED	2				
	Serial port header	4 (2 x RS-232 dual-port (2 ports))				
	Audio Header	1 x (ALC 888S)				
	PS/2 KB/Mouse	1 x (Optional PS/2 KB/Mouse cable and bracket required)				
	Rear I/O Connector	External serial port	1 (via COM cable in the package)			
External USB port		4 x (USB 3.2 Gen 2)				
VGA port		1 x (Resolution up to 1920 x 1200 @ 60 Hz)				
HDMI		1 x (Resolution up to 4096 x 2160 @ 60 Hz)				
Display Port		2 x (Resolution up DP* with DSC to 8K60 Hz 30bpp)				
RJ-45		4				
Power Requirement	PS/2 KB/mouse	-				
	Audio	2 x (Mic-in, Line-out)				
	Power On	3.3 V	5 V	12 V	12V_8P	5 V <sub>SS</sub>
	(Ultra5 245K 4.2GHz DDR5 5600 16 GB x 4)	1.56 A	1.91 A	0.36 A	0.33 A	0.63 A
	Environment	Temperature	Operating		Non-operating	
	Humidity	0 ~ 60 °C, depends on CPU speed and cooler solution		-40 ~ 85 °C		
Watchdog Timer	Output	System reset				
	Interval	Programmable 1 ~ 255 sec/min				
Physical Characteristics	Dimensions	244 x 244 mm (9.6 x 9.6 in)				

\* 5600MT/s can only be supported with 1 DIMM per channel configuration (2 DIMMs in total).

