




Industry Applications.



Bulgin is widely recognised as a leading manufacturer of environmentally sealed connectors & components.

With over 95 years of experience in the industry, Bulgin continues to innovate & develop products and services to cater for its global customer base across a variety of markets.

Industrial.



Industrial environments are often exposed to many harsh elements such as water, vibration, chemicals and extreme temperatures, but with demand growing for automated processes, there is more pressure than ever before on production and motion control systems. To overcome these challenging conditions, our connectivity solutions with metal or plastic housings are used around the world to facilitate secure power, signal and data connections in the harshest of environments.

Our robust range of vandal proof push button switches are also a perfect solution for operating heavy duty tools, metal and wood processing equipment, food and beverage processing systems and packaging machinery.



Automation.

With an increasing demand for automated machines and systems, secure and reliable connections are vital for industrial automation applications where efficiency and uptime is of the utmost importance. Our waterproof circular connectors are the perfect solution for automation systems such as factory automation, industrial networks and robotics.

From movement signals to manufacturing and material handling processes, our robust sealed connector range for power, signal and data perform excellently in harsh environments where moisture, extreme temperatures and vibration are present. With IP66, IP67, IP68 & IP69K ratings, they are particularly ideal for production lines that are prone to dust & liquid build up.

With IP66, IP67, IP68 & IP69K ratings, they are particularly ideal for production lines that are prone to dust & liquid build up.

- **Industrial Robotics**
- **Pharmaceutical Manufacturing**
- **Automotive Manufacturing**
- **Food & Beverage Processing**
- **Material Handling Equipment**
- **Packaging Equipment**
- **Process Control Systems**
- **Machining & Metal Processing**
- **Semiconductor Manufacturing**
- **Factory Automation Machines**



Products Related To This Industry:

M5 Series

Circular Automation Connectors



- A-Coding
- Ratings up to 1A, 60V ac/dc
- IP67 protection
- 3 & 4 contacts
- PUR & PVC cable options

M8 Series

Circular Automation Connectors



- A & B Coding
- Ratings up to 3A, 60V ac/dc
- IP67 protection
- 3, 4 & 5 contacts
- PUR & PVC cable options

M12 Series

Circular Automation Connectors



- A, B & D Coding
- Max rating 4A, 250V ac/dc
- IP67 protection
- 3, 4, 5, 8 & 12 contacts
- PUR & PVC cable options

Photoelectric Sensor

Sensors



- Sealed to IP67
- Stainless Steel 316 shell
- Detection distance 1 - 40mm
- Light point diameter 5.0mm at 30mm
- Ambient humidity 35 - 85%

M23 Series

Circular Automation Connectors



- A-Coding
- Max Rating 8A, 200V ac/dc
- IP67 protection
- 12 & 19 contacts
- Straight & angled options

Distribution Units

Circular Automation Connectors



- Anodised aluminium housing
- M12 inputs M8 outputs
- Operating Temp Range -25°C / 80°C
- IP67 rated
- 5, 8 & 9 port configurations

Standard Ethernet

Circular Data Connectors



- Cat5e RJ45 Ethernet Connectors
- Data rates up to 100MHz
- IP66, IP67, IP68 & IP69K protection
- Shielded system
- Noise immunity & EMI protection

6000 Series

Circular Power Connectors



- 2 - 22 Contacts
- Plastic or Metal Housing
- IP66, IP67, IP68 & IP69K protection
- Secure, quick mating / release
- cULus, UL, VDE Approvals

Tools & Machinery.

Industrial environments are exposed to many impeding elements such as water, vibration, chemicals and extreme temperatures. With demand growing for automated processes, there is more pressure than ever before on production and motion control systems.

To overcome these potentially detrimental conditions, our connectivity solutions with metal or plastic housings are used around the world to facilitate secure power, signal and data connections in the harshest of environments. Our robust range of vandal proof push button switches are also a perfect solution for operating heavy duty tools, metal and wood processing equipment, food and beverage processing systems and packaging machinery.

- Industrial Food Slicer
- Vacuum Packaging Machine
- Printed Electronics Machinery
- Heavy Industrial Food Processor
- Industrial Grade Printer
- Industrial Automated Saws
- Industrial Coating Machinery
- Industrial Sand Blaster



Products Related To This Industry:

Standard Series

Circular Power Connectors



- Rating up to 12A, 277V ac/dc
- 2, 3, 4, 6, 7, 9, 12 & 25 contacts
- IP66, IP67, IP68 & IP69K protection
- Plug & receptacle connectors
- CCC, UL, CSA & VDE approvals

900 Series

Circular Power Connectors



- 32A, 600V ac/dc max rating
- 2, 3, 4, 5, 7 & 10 contacts
- IP66, IP67, IP68 & IP69K protection
- Single or 3 phase applications
- CCC, UL, CSA & VDE approvals

Standard Ethernet

Circular Data Connectors



- Cat5e RJ45 Ethernet Connectors
- Data rates up to 100MHz
- IP66, IP67, IP68 & IP69K protection
- Shielded system
- Noise immunity & EMI protection

6000 Series

Circular Power Connectors



- 2 - 22 Contacts
- Plastic or Metal Housing
- IP66, IP67, IP68 & IP69K protection
- Secure, quick mating / release
- cULus, UL, VDE Approvals

Photoelectric Sensor

Sensors



- Sealed to IP67
- Stainless Steel 316 shell
- Detection distance 1 - 40mm
- Light point diameter 5.0mm at 30mm
- Ambient humidity 35 - 85%

M16 Series

Circular Automation Connectors



- A-Coding
- Max Rating 7A, 250V ac/dc
- IP67 protection
- 3, 4, 5, 6, 8 & 12 contacts
- Metal shells with good shielding

M23 Series

Circular Automation Connectors



- A-Coding
- Max Rating 8A, 200V ac/dc
- IP67 protection
- 12 & 19 contacts
- Straight & angled options

Vandal Resistant

Switches



- High corrosion resistance
- Domed, low & prominent profiles
- IP66 & IP68 sealing versions
- Illuminated & non-illuminated
- Front & rear panel mount versions

Instrumentation & Measurement.

Instrumentation and measurement systems are vital for ensuring productivity, reliability, safety and continuity in the industrial sector. Accurate and consistent measurements allow for process control and automated manufacturing systems to be optimised for maximum efficiency. Reliable electronic components are essential for achieving this.

That's where we come in. From control interfaces to power and data connections, Bulgin has a diverse choice of electronic solutions ideal for systems that measure a variety of parameters including pressure, moisture, flow, temperature and vibration.

- Handheld Moisture Detectors
- Wireless Data Logger
- Flow Meters & Industrial Scales
- Solar Water Pump Controller
- Terrain Monitoring
- Handheld Radiation Detection
- Pipe Inspection System
- Pressure Transmitter
- Wireless Load Sensors
- Moisture Meters



Products Related To This Industry:

Standard Series

Circular Power Connectors



- Rating up to 12A, 277V ac/dc
- 2, 3, 4, 6, 7, 9, 12 & 25 contacts
- IP66, IP67, IP68 & IP69K protection
- Plug & receptacle connectors
- CCC, UL, CSA & VDE approvals

Photoelectric Sensor

Sensors



- Sealed to IP67
- Stainless Steel 316 shell
- Detection distance 1 - 40mm
- Light point diameter 5.0mm at 30mm
- Ambient humidity 35 - 85%

Standard Ethernet

Circular Data Connectors



- Cat5e RJ45 Ethernet Connectors
- Data rates up to 100MHz
- IP66, IP67, IP68 & IP69K protection
- Shielded system
- Noise immunity & EMI protection

6000 Series

Circular Power Connectors



- 2 - 22 Contacts
- Plastic or Metal Housing
- IP66, IP67, IP68 & IP69K protection
- Secure, quick mating / release
- cULus, UL, VDE Approvals

Vandal Resistant

Switches



- High corrosion resistance
- Domed, low & prominent profiles
- IP66 & IP68 sealing versions
- Illuminated & non-illuminated
- Front & rear panel mount versions

Battery Holders

Battery Holders



- AAA, AA, C, D & PP3 battery sizes
- Accommodating 1, 2, 3 or 4 cells
- IP67 sealed versions
- Suitable for PCB mounting
- Panel mounting versions

M16 Series

Circular Automation Connectors



- A-Coding
- Max Rating 7A, 250V ac/dc
- IP67 protection
- 3, 4, 5, 6, 8 & 12 contacts
- Metal shells with good shielding

400 Series SMB

Circular Data Connectors



- 50Ω impedance SMB antenna
- Frequency range 0 - 4GHz
- IP66, IP67, IP68 & IP69K protection
- Rewireable & pre-wired options
- RG-174 cables

Bulgin has you covered.

**Our components are available through a
large network of National and International
Distributors Worldwide.**

Search for stock at:

www.bulgin.com/products/stock



www.bulgin.com

Europe

Bulgin
200 Cambridge Science Park
Milton Road
Cambridge, CB4 0GZ, UK
tel: +44 (0) 1803 407757
e: info@bulgin.com

Americas

Bulgin
11849 Telegraph Road
Santa Fe Springs
CA 90670, USA
tel: +1 760-343-3650
e: info@bulgin.com

Asia Pacific

Bulgin
11849 Telegraph Road
Santa Fe Springs
CA 90670, USA
tel: +1 760-343-3650
e: info@bulgin.com