


Sherex Fastening Solutions, LLC.

400 Riverwalk Pkwy, Suite 600

Tonawanda, NY 14150

Toll Free: 866.474.3739

Tel: 716.875.0315

Fax: 716.875.0358

Email: info@sherex.com

CAK Series – Steel (Inches) | Small Flange Knurled Body Thin Wall Rivet Nut

Small Flange Knurled Body Thin Wall Rivet Nut Series

Small flange knurled rivet nut grip range can be affected by parent material and hole size. Sherex recommends trial installations to determine the proper grip range for the application. [Contact Sherex](#) for details.

CAK, small flange knurled style rivet nuts are available closed end designs. Other specials available upon request.

Finish: Zinc Plated–Yellow Trivalent Chromate SFS-01-001, SC2 ***Special finish or material available upon request!***

[+ more](#)


Item #	Thread Size	Grip Range (Min.-Max.)	L $\pm .015$ (inch)	D (Max.) (inches)	LB $\pm .015$ (inch)	Hole Size $+.006/- .000$ (inches)	3D CAD
<u>CAK2-0632-080</u>	#6-32 UNC	.020-.080	.420	.265	.740	.266	
<u>CAK2-0832-080</u>	#8-32 UNC	.020-.080	.420	.265	.740	.266	
<u>CAK2-1024-130</u>	#10-24 UNC	.020-.130	.475	.296	.990	.297	
<u>CAK2-1032-130</u>	#10-32 UNF	.020-.130	.475	.296	.990	.297	
<u>CAK2-0632-080(mt.021)</u>	#6-32 UNC	.020-.080	.420	.265	.740	.266	
<u>CAK2-0832-080(mt.021)</u>	#8-32 UNC	.020-.080	.420	.265	.740	.266	
<u>CAK2-1024-130(mt.021)</u>	#10-24 UNC	.020-.130	.475	.296	.990	.297	
<u>CAK2-1032-130(mt.021)</u>	#10-32 UNF	.020-.130	.475	.296	.990	.297	
<u>CAK2-0632-080(mt.022)</u>	#6-32 UNC	.020-.080	.420	.265	.740	.266	
<u>CAK2-0832-080(mt.022)</u>	#8-32 UNC	.020-.080	.420	.265	.740	.266	
<u>CAK2-1024-130(mt.022)</u>	#10-24 UNC	.020-.130	.475	.296	.990	.297	

Item #	Thread Size	Grip Range (Min.-Max.)	L $\pm .015$ (inch)	D (Max.) (inches)	LB $\pm .015$ (inch)	Hole Size $+.006/- .000$ (inches)	3D CAD
<u>CAK2-1032-130(mt.022).</u>	#10-32 UNF	.020-.130	.475	.296	.990	.297	
<u>CAK2-0632-080(mt.023).</u>	#6-32 UNC	.020-.080	.420	.265	.740	.266	
<u>CAK2-0832-080(mt.023).</u>	#8-32 UNC	.020-.080	.420	.265	.740	.266	
<u>CAK2-1024-130(mt.023).</u>	#10-24 UNC	.020-.130	.475	.296	.990	.297	
<u>CAK2-1032-130(mt.023).</u>	#10-32 UNF	.020-.130	.475	.296	.990	.297	
<u>CAK2-0632-080(mt.024).</u>	#6-32 UNC	.020-.080	.420	.265	.740	.266	
<u>CAK2-0832-080(mt.024).</u>	#8-32 UNC	.020-.080	.420	.265	.740	.266	
<u>CAK2-1024-130(mt.024).</u>	#10-24 UNC	.020-.130	.475	.296	.990	.297	
<u>CAK2-1032-130(mt.024).</u>	#10-32 UNF	.020-.130	.475	.296	.990	.297	
<u>CAK2-0632-080(mt.025).</u>	#6-32 UNC	.020-.080	.420	.265	.740	.266	
<u>CAK2-0832-080(mt.025).</u>	#8-32 UNC	.020-.080	.420	.265	.740	.266	

Item #	Thread Size	Grip Range (Min.-Max.)	L $\pm .015$ (inch)	D (Max.) (inches)	LB $\pm .015$ (inch)	Hole Size $+.006/- .000$ (inches)	3D CAD
<u>CAK2-1024-130(m.t.025).</u>	#10-24 UNC	.020-.130	.475	.296	.990	.297	
<u>CAK2-1032-130(m.t.025).</u>	#10-32 UNF	.020-.130	.475	.296	.990	.297	
<u>CAK2-0632-080(m.t.026).</u>	#6-32 UNC	.020-.080	.420	.265	.740	.266	