

ISSUE 6; November 2024

Description

- Standard 2.5 x 2mm SMD crystal in a hermetically sealed ceramic package with a seam sealed metal lid. Please see our CFPX-181 for a low ageing version.

Frequency Parameters

- Frequency: 12.0MHz to 60.0MHz
- Frequency Tolerance: $\pm 10.00\text{ppm}$ to $\pm 50.00\text{ppm}$
- Tolerance Condition: @ 25°C
- Frequency Stability: $\pm 15.00\text{ppm}$ to $\pm 100.00\text{ppm}$
- Ageing: $\pm 3\text{ppm}$ max per year @ 25°C

Electrical Parameters

- Load Capacitance (CL): 8.0pF to 47.0pF
- Shunt Capacitance (C0): 3pF max
- Drive Level: 100µW max

Operating Temperature Ranges

- 20 to 70°C
- 40 to 85°C
- 40 to 125°C

Environmental Parameters

- Storage Temperature Range: -55 to 125°C
- Drop: 100cm drop (3 times) onto hard wooden board.
- Vibration: MIL-STD-883F, Method 2007.3: 20G (20Hz-2000Hz), 1.52mm amplitude, 20mins in 3 mutually perpendicular planes (total 4hrs).

Manufacturing Details

- RoHS Terminations: NiAu
- RoHS Reflow: 260°C max for 10secs max

Ordering Information


- Frequency*
- Model*
- Frequency Tolerance (@ 25°C)*
- Frequency Stability (over operating temperature range)*
- Operating Temperature Range*
- Load Capacitance*
- Overtone
- (*minimum required)
- Example
- 20.0MHz CFPX-218
- 20/20/-40 to 85C/16 FUND

Compliance


- RoHS Status (2015/863/EU): Compliant
- REACH Status: Compliant
- MSL Rating (JDEC-STD-033): Not Applicable



Outline (mm)



Recommended Solder Pad Layout



Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com

Packaging Details

- Tape & reel in accordance with EIA-481
Quantities below the standard reel size to be supplied on cut tape.
Standard Pack Quantity: 3,000

Electrical Specification - maximum limiting values

Frequency Min	Frequency Max	Temperature Range	Stability (Min)	Over Tone Order	ESR
		°C	ppm		Ω
12.0MHz	15.999999MHz	-20 to 70	±15	Fundamental	180
		-40 to 85	±20		180
		-40 to 125	±50		180
16.0MHz	19.999999MHz	-20 to 70	±15	Fundamental	150
		-40 to 85	±20		150
		-40 to 125	±50		150
20.0MHz	29.999999MHz	-20 to 70	±15	Fundamental	100
		-40 to 85	±20		100
		-40 to 125	±50		100
30.0MHz	60.0MHz	-20 to 70	±15	Fundamental	60
		-40 to 85	±20		60
		-40 to 125	±50		60

*Stability Maximum values ±100ppm

This document was correct at the time of printing; please contact your local sales office for the latest version.

[Click to view latest version on our website.](#)

Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com