

Using Direct Test Mode

BL653 μ Series

Application Note

v1.0

1 INTRODUCTION

The BL653 μ firmware natively supports Direct Test Mode (DTM) commands as specified in the Bluetooth SIG's *Bluetooth Core Specifications v 5.0 vol. 6 part F - Direct Test Mode*, accessible from the following link:
www.bluetooth.com/specifications/bluetooth-core-specification

The purpose of DTM is to test the radio operation at the physical layers such as for transmit power and receiver sensitivity. This is useful for regulatory EMC testing or for co-located radio testing with another radio system.

This radio test can be carried out by dedicated test equipment (such as RFCreations Moreph30, Anritsu MT8852, or similar) with the BL653 μ in DTM mode as the device under test. Alternatively, you can send DTM commands from a PC using a terminal program such as UwTerminalX. In both cases, the DTM commands remain the same.

This document describes BL653 μ radio testing using the in-built Direct Test Mode (DTM) firmware and Nordic nRF Connect for Desktop Direct Test Mode tool.

- Entering DTM mode for the BL653 μ
- Using Nordic nRF Connect for Desktop Direct Test Mode tool to BLE radio test the BL653 μ in either BLE transmit or BLE receive mode
- How to manually send DTM command (via UwTerminalX) to produce continuous wave [CW] RF TX signal
- Exiting DTM mode for the BL653 μ

2 REQUIREMENTS

To use DTM, you need the following:

- Customer's host board with BL653 μ module fitted (and access to BL653 μ UART)
- Windows PC
- UwTerminalX by Laird (available at <https://github.com/LairdCP/UwTerminalX/releases>)

Nordic nRF Connect for Desktop Direct Test Mode tool – This Nordic Direct Test Mode tool is installed when the **Nordic nRF Connect** is installed.

Nordic nRF Connect for Desktop application software (the complete install) found at the following link:

<https://www.nordicsemi.com/Software-and-Tools/Development-Tools/nRF-Connect-for-desktop>
<https://www.nordicsemi.com/Software-and-tools/Development-Tools/nRF-Connect-for-desktop/Download#infotabs>

Note: Please install the correct version for your operating system.

3 SETUP

We assume the customer has BL653 μ module on a customer's own host board (or end product design). BL653 μ module should set to be in AT or interactive mode (no smartBASIC application loaded or running) on power up. **Below example is BL653 μ on Laird internal host devboard (not commercially available).**




Figure 1: Laird internal devboard BL653 μ switch and jumper positions

4 ENTERING DIRECT TEST MODE

To enter DTM, follow these steps:

1. Open UwTerminalX.
2. Ensure you're using the latest version of UwTerminalX by clicking the Update tab and then, in the UwTerminalX panel, click Check for Updates.
3. When you're running the newest version of UwTerminalX, open the Config tab.
4. In the device drop down, select BL653 μ to populate the default communications settings.
5. Select the correct COM port.

If you cannot select BL653 μ , manually select the following UART settings (shown in Figure 2):

COM Port	Port corresponding to your development kit
Baud Rate	115200
Parity	None
Stop Bits	1
Data Bits	8
Handshaking	CTS/RTS




Figure 2: UwTerminalX settings

6. Click **OK** to connect.
7. Set up the module into Direct Test Mode. You must retrieve two sets of four characters each which function as a unique passcode to enter direct test mode. To retrieve the characters, issue the following command:

```
AT I 14
```

You should receive a response such as:

```
10 14 01 123456789ABC
```

Note the characters in the highlighted positions above. In our example in Figure 3, they are **EF35** and **4A0D**.



Figure 3: Return from at i 14

8. To enter Direct Test Mode, using the characters you found in the previous steps, issue the AT+DTM command as follows:

AT+DTM 0x EF354A0D

The module is now in Direct Test mode.

9. Click **Close Port** to disconnect the development board from UwTerminalX.

5 USING DIRECT TEST MODE

Now that the module is in Direct Test Mode, it accepts DTM commands as specified in the *BT SIG Bluetooth Core Specifications*. See *Bluetooth Core Specifications v 5.0 vol. 6 part F - Direct Test Mode*, at <https://www.bluetooth.com/specifications/bluetooth-core-specification>.

To use Direct Test Mode, you need Nordic's **nRF Connect Direct Test Mode** tool, found at:

<https://www.nordicsemi.com/Software-and-Tools/Development-Tools/nRF-Connect-for-desktop> then Download tab.

Once the BL653 μ is in DTM mode, you can communicate with the BL653 μ over the UART with UwTerminalX using the following communications settings:

COM Port	Same as before
Baud Rate	19200
Parity	None
Stop Bits	1
Data Bits	8
Handshaking	None

5.1 Configuration of Module Settings (Optional)

Before entering DTM Mode, you may configure TX power, baud rate, and DCDC (REG1). Changing these values is optional. However, if you choose, you may set these values as follows:

TX RF Power (dBm)

Command	AT+DTMCFG 1 n
Values for n	8, 7, 6, 5, 4, 3, 2, 0, -4, -8, -12, -16, -20, -40
Default	4

Baud Rate (bps)

Command	AT+DTMCFG 2 n
Values for n	9600, 14400, 19200, 38400, 57600, 115200
Default	19200

DCDC (REG1) (for Normal Voltage Mode operation)

Command	AT+DTMCFG 3 n
Values for n	0 (Disabled), 1 (enabled)
Default	1

Enable 32KHz Crystal based LF Clock

Command	AT+DTMCFG 4 n
Values for n	0 (Disabled), 1 (enabled)
Default	1

Refer to the Appendix, for setting a GPIO if it needs to be set for some particular purpose whilst in DTM mode.

5.2 Start Direct Test Mode Tool Within nRF Connect

Nordic's **nRF Connect Direct Test Mode** tool allows all BLE PHY data rates to be tested, 1 Mbps, 2 Mbps, and coded PHY 500 kbps (s=2) and 125 kbps (s=8).

To begin using Nordic **nRF Connect Direct Test Mode** tool, follow these steps:

1. Open nRF Connect.

Note: If a new version of the app becomes available, an **Update** button displays next to the **Open** button. Click this button to install the latest version.

2. Then click **Open** in **Direct Test Mode** tool, as shown in [Figure 4](#).




Figure 4: Click **Open** in **Direct Test Mode**

Note: Press the drop-down arrow to view release notes or more information (which we recommend) () .




Figure 5: Access release notes and more information




Figure 6: Opening the Nordic nRF Connect Direct Test Mode tool

3. Select device for the COM port of the connected Device Under test (from the drop-down menu).




Figure 7: Device selection

4. From here, you can place the module in BLE (duty cycled) TX or CW (sine wave) TX or BLE RX mode.

Note: If at any time, the Nordic nRF Connect for Desktop Direct Test Mode tool is not responding or there is unexpected behavior (see example in Figure 8), press **CTRL+R** to refresh the **nRF Connect for Desktop Direct Test Mode** tool.




Figure 8: Unexpected behavior when opening or running the Nordic nRF Connect for Desktop Direct Test Mode tool

5.3 Nordic nRF Connect Direct Test Mode tool TX and RX Tests

nRF Connect for Desktop Direct Test Mode tool allows all BLE PHY data rates to be tested, 1 Mbps, 2 Mbps, and coded PHY 500 kbps (s=2) and 125 kbps (s=8).

5.3.1 Transmit Test

To perform a transmit test, follow these steps:

1. Configure the applicable BLE transmitter options in the **nRF Connect for Desktop Direct Test Mode** tool.

Table 1: Transmitter test Direct Test Mode options

COM Port	D.U.T COM port																
Test Type	Select Transmitter, Single																
Channel	17 (2440 MHz, for example)																
Update period (ms)	30 (default)																
Physical layer	Select <i>LE 1 Mbps</i> (as an example). Other options are LE 2 Mbps, LE Coded S8 (500 kbps), LE Coded S2 (125 kbps).																
Timeout (ms)	Not enabled. This is a timeout for the specific command. Setting timeout to 1000 ms stops the current operation when the timer expires.																
Packets Type	<table border="1"> <thead> <tr> <th>Packet Type</th> <th>Value</th> <th>Description</th> </tr> </thead> <tbody> <tr> <td>PRBS9</td> <td></td> <td>PRBS9 Packet Payload (Pkt Type 00)</td> </tr> <tr> <td>11110000</td> <td></td> <td>11110000 Packet Payload (Pkt Type 01)</td> </tr> <tr> <td>10101010</td> <td></td> <td>10101010 Packet Payload (Pkt Type 10)</td> </tr> <tr> <td>TBD</td> <td></td> <td>Vendor-specific (Pkt Type 11)</td> </tr> </tbody> </table> <p>Currently Nordic nRF Connect for Desktop Direct Test Mode tool does not have vendor-specific type that produces a 100% ON continuous wave (CW) RF TX signal. Refer to the <i>DTM Command to Produce CW RF Tx Signal</i> for additional information on how to do this.</p>		Packet Type	Value	Description	PRBS9		PRBS9 Packet Payload (Pkt Type 00)	11110000		11110000 Packet Payload (Pkt Type 01)	10101010		10101010 Packet Payload (Pkt Type 10)	TBD		Vendor-specific (Pkt Type 11)
Packet Type	Value	Description															
PRBS9		PRBS9 Packet Payload (Pkt Type 00)															
11110000		11110000 Packet Payload (Pkt Type 01)															
10101010		10101010 Packet Payload (Pkt Type 10)															
TBD		Vendor-specific (Pkt Type 11)															
Payload Length (bytes)	Options range from 1 byte to 255 bytes.																
TX Power [dBm]	Options include: 7 dBm, 6 dBm, 5 dBm, 4 dBm, 3 dBm, 2 dBm, 0 dBm, -4 dBm, -8 dBm, 12 dBm, -16 dBm, -20 dBm, -40 dBm.																
TRANSMIT	To start TX test, press Start test .																

2. Once configured, click **Start test**. Figure 9 shows an active BLE transmitter test.




Figure 9: Successful initiation of BLE transmitter test

With the module is in a transmit test, you can measure the RF Tx signal on a spectrum analyzer. Check the RF Tx packet duration of your RF transmission (using zero span mode on the spectrum analyzer). The RF Tx signal is NOT 100% on and has a Tx duty cycle as per *BT SIG Bluetooth Core Specifications*. See *Bluetooth Core Specifications v 5.0 vol. 6 Part F - Direct Test Mode*.

5.3.2 Receive Test

To conduct the BLE receive test, do the following:

1. Configure the applicable BLE receiver options in the nRF Connect for Desktop Direct Test Mode tool.

Table 2: Receive test Direct Test Mode options

COM Port	DUT COM port
Test Type	Select Receiver, Single
Channel	17 (2440 MHz, for example)
Update period (ms)	30 (default)
Physical layer	Options include: LE 2 Mbps, LE Coded S8 (500 kbps), LE Coded S2 (125 kbps)
Timeout (ms)	Not enabled. This is a timeout for the specific command. Setting timeout to 1000 ms will stop the current operation when the timer expires.
RECEIVER	To start RX test, press Start test .

Note: DUT RX mode produces an RX LO leakage at the following frequency: $(2*f_{Rx})-1\text{MHz}$.

2. Once configured, to start Receiver test, click **Start test**. Figure 10 shows a BLE receiver test running.

The **Received packets** shows how many packets are received. Since the number of packets sent per second by transmitter is known (as per Bluetooth SIG's *Bluetooth Core Specifications v 5.0 vol. 6 part F - Direct Test Mode*), the DUT received packets Rx Packet Error Rate can be calculated.




Figure 10: Successful initiation of BLE receiver rest (received packets)

Note: nRF Connect v3.3.3 Direct Test Mode 1.1.2 has a known issue with counting **Received packets** inaccurately. Please look out for a fix from Nordic in future version of nRF Connect Direct Test Mode tool.

6 DTM COMMAND TO PRODUCE CW RF TX SIGNAL

nRF Connect for Desktop Direct Test Mode tool currently (20 May 2020) does not have a way to produce continuous wave (CW) RF Transmit signal. You can send a DTM command manually using UwTerminalX to produce continuous wave (CW) RF Transmit signal.

To do this, follow these steps:

1. Open UwTerminalX with the following settings:

COM Port	Same as previous
Baud Rate	19200
Parity	None
Stop Bits	1
Data Bits	8
Handshaking	None

2. Click **OK** to connect.




Figure 11: Opened UwTerminalX

3. Right-click the terminal screen and in the context menu, click **Automation**.
4. In the following screen, modify the fields as shown in [Figure 12](#).
 - In the first field, enter **\00\00** (the DTM command for reset)
 - In the second field, enter **\93\00** (the DTM command to produce a CW RF transmit signal)
For example, at frequency **2440 MHz**.
 - Tick the box for De-Escape Strings.




Figure 12: Automation dialogue for entering DTM commands

5. Click **Send** to send DTM command **\00\00** for reset (always do this first).

If successful you should get a response back **\00\00**.




Figure 13: Automation dialogue DTM command **\00\00** for reset and response.

6. Click **Send** to send DTM command **\93\00** to produce a CW RF transmit signal at frequency 2440 MHz. If successful, you should get a response back **\00\00**.




Figure 14: Automation dialogue DTM command \93\00 to produce continuous wave (CW) RF Transmit signal at frequency 2440 MHz and response.

The following table (Table 3) shows the DTM command to produce continuous wave (CW) RF TX signal frequency.

Table 3: DTM command to send for each RF TX frequency to produce a CW RF transmit signal

Continuous Wave RF Transmit Signal Frequency	DTM Command	Continuous Wave RF Transmit Signal Frequency	DTM Command	Continuous Wave RF Transmit Signal Frequency	DTM Command
2402 MHz	\80\03	2430 MHz	\8E\03	2458 MHz	\9C\03
2404 MHz	\81\03	2432 MHz	\8F\03	2460 MHz	\9D\03
2406 MHz	\82\03	2434 MHz	\90\03	2462 MHz	\9E\03
2408 MHz	\83\03	2436 MHz	\91\03	2464 MHz	\9F\03
2410 MHz	\84\03	2438 MHz	\92\03	2466 MHz	\A0\03
2412 MHz	\85\03	2440 MHz	\93\03	2468 MHz	\A1\03
2414 MHz	\86\03	2442 MHz	\94\03	2470 MHz	\A2\03
2416 MHz	\87\03	2444 MHz	\95\03	2472 MHz	\A3\03
2418 MHz	\88\03	2446 MHz	\96\03	2474 MHz	\A4\03
2420 MHz	\89\03	2448 MHz	\97\03	2476 MHz	\A5\03
2422 MHz	\8A\03	2450 MHz	\98\03	2478 MHz	\A6\03
2424 MHz	\8B\03	2452 MHz	\99\03	2480 MHz	\A7\03
2426 MHz	\8C\03	2454 MHz	\9A\03		
2428 MHz	\8D\03	2456 MHz	\9B\03		

7 EXITING DTM MODE

To exit DTM, follow these steps:

1. Open UwTerminalX with the following settings:

COM Port	Same as previous
Baud Rate	19200
Parity	None
Stop Bits	1
Data Bits	8
Handshaking	None

2. Click **OK** to connect.
3. Right-click the terminal screen and in the context menu, click **Automation**.
4. In the following screen, modify the fields as shown in [Figure 15](#).
5. In the first field, enter **\3F\FF**.
6. Tick the box for **De-Escape Strings**.
7. Click **Send**.




Figure 15: Automation dialogue

8. After this command is complete, close UwTerminalX. Then re-open it and connect to the BL653μ with the following default parameters:

COM Port	Same as previous
Baud Rate	115200
Parity	None
Stop Bits	1
Data Bits	8
Handshaking	CTS/RTS


9. Click **OK** to connect.
10. Check that you get a response by pressing **Enter** in the terminal window. You should see the following response:

00

11. Issue the following command to erase non-volatile data and the module's file system:

at&f*

The module erases its file system and reboots, as shown in [Figure 16](#).



```
00
at&f*
FFS Erased, Rebooting...
00
```

Figure 16: at&f to erase and reboot module*

8 APPENDIX

This section describes how to set a GPIO if necessary whilst in DTM mode.

8.1 Configuration of Module GPIO Settings (Optional)

GPIO control enable

Command	AT+DTMCFG 5 <i>n</i>
Values for n	0 (Disabled), 1 (enabled)
Default	0

GPIO (0..31) Enable Bitmask

This will be ignored if AT+DTMCFG 5 is set to 0 (which is the default). If a bit is set then the bit number corresponds to the GPIO number which is enabled.

Command	AT+DTMCFG 6 bitmask
Values for n	0x00000000 to 0xFFFFFFFF (bit 0 is the lowest significant bit)
Default	0

GPIO (0..31) Direction Bitmask

This will be ignored if AT+DTMCFG 5 is set to 0 (which is the default). If a bit is set then the bit number corresponds to the GPIO number will have the direction input when the bit is 0 and an output when the bit is 1.

Command	AT+DTMCFG 7 bitmask
Values for n	0x00000000 to 0xFFFFFFFF (bit 0 is the lowest significant bit)
Default	0

GPIO (0..31) State Bitmask

This will be ignored if AT+DTMCFG 5 is set to 0 (which is the default). If a bit is set then the bit number corresponds to the GPIO number will have the output set to this value if DTMCFG 7 was used to set the direction as output; or enables a pull-up resistor if the bit is set and DTMCFG 7 is used to set the direction as input.

Command	AT+DTMCFG 8 bitmask
Values for n	0x00000000 to 0xFFFFFFFF (bit 0 is the lowest significant bit)
Default	0xFFFFFFFF

GPIO (32..47) Enable Bitmask

This will be ignored if AT+DTMCFG 5 is set to 0 (which is the default). If a bit is set then the bit number corresponds to the GPIO number which is enabled.

Command	AT+DTMCFG 16 bitmask
Values for n	0x0000 to 0xFFFF (bit 0 is the lowest significant bit)
Default	0

GPIO (32..47) Direction Bitmask

This will be ignored if AT+DTMCFG 5 is set to 0 (which is the default). If a bit is set then the bit number corresponds to the GPIO number will have the direction input when the bit is 0 and an output when the bit is 1.

Command	AT+DTMCFG 17 bitmask
Values for n	0x0000 to 0xFFFF (bit 0 is the lowest significant bit)
Default	0

GPIO (32..47) State Bitmask

This will be ignored if AT+DTMCFG 5 is set to 0 (which is the default). If a bit is set then the bit number corresponds to the GPIO number will have the output set to this value if DTMCFG 7 was used to set the direction as output; or enables a pull-up resistor if the bit is set and DTMCFG 7 is used to set the direction as input.

Command	AT+DTMCFG 18 bitmask
Values for n	0x0000 to 0xFFFF (bit 0 is the lowest significant bit)
Default	0xFFFFFFFF

9 REVISION HISTORY

Version	Date	Notes	Contributor(s)	Approver
1.0	13 August 2020	Initial Release	Raj Khatri	Jonathan Kaye