



Declaration of Conformity

Manufacturer:

CUI Inc.

**15575 SW Sequoia Parkway, Suite 100
Portland, Oregon 97224**

For the following equipment:

DC-DC Converter

CUI Series: PRA100

Models: 24V, 48V nominal input, see next page

This declaration of conformity is issued under the sole responsibility of the manufacturer. The object of the declaration described above is in conformity with the relevant UK designated legislations (and their amendments) and relevant designated standards or other technical specifications.

UK SI 2016 no. 1101: The Electrical Equipment (Safety) Regulations 2016 for Electrical Equipment Used within Certain Voltage Limits - as amended in 2019, 2020

UK SI 2016 no. 1091: The Electromagnetic Compatibility Regulations 2016 - as amended in 2019, 2020

UK SI 2012 no. 3032: The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 - as amended in 2019, 2020

References to the used, including the date of the standard, or references to the other technical specifications, including the date of the specification, in relation to which conformity is declared:

Health & Safety BS EN IEC 62368-1:2020+A11:2020
IEC 62368-1:2018

EMC BS EN 55032:2015+A11:2020; BS EN 55035:2017+A11:2020

RoHS BS EN IEC 63000:2018

Note: These component level power supplies are intended exclusively for inclusion within other equipment. Protection against electric shock and Electromagnetic Compatibility (EMC) must be checked when the equipment is built-in a completed product or forms a part of a complete system.

Approved by:



(manufacturer)

Editha Vergara
Global Director, Safety, Environmental

Portland, Oregon, USA

(place)

05/31/2025

(date)

UK Representative:



(manufacturer)

Cliff Gore
European Sales Director
Bel Power Solutions

Maidstone, UK

(place)

05/31/2025

(date)

MODEL LIST

PRA100-24-SXX, PRA100-48-SXX (where XX = 5, 12, 24, 48, 54 denote output voltage)

Model	Input voltage (typ.)	Input voltage (range)	Output voltage (Vdc)
PRA100-24-S5	24	9-40	5
PRA100-24-S12	24	9-40	12
PRA100-24-S24	24	9-40	24
PRA100-24-S48	24	9-40	48
PRA100-24-S54	24	9-40	54
PRA100-48-S5	48	16.5-74	5
PRA100-48-S12	48	16.5-74	12
PRA100-48-S24	48	16.5-74	24
PRA100-48-S48	48	16.5-74	48
PRA100-48-S54	48	16.5-74	54

Note: Model name maybe followed by additional characters as described on below model naming configuration.

Model Naming Configuration

PRA100	-	XX	-	S	XX	X	X
I	-	II	-	III	IV	V	VI

I - Base Number: PRA100
II - Nom. Input Voltage: 24 = 24 V; 48 = 48 V
III - Output: S = single
IV - Output Voltage: 5 = 5 V; 12 = 12 V; 24 = 24 V; 48 = 48 V; 54 = 54 V
V - Mounting Style: blank = without baseplate
 B = baseplate with M2.5 mounting insert
 blank = Positive logic
VI - Remote ON/OFF Ctl: N = Negative logic

REVISION HISTORY

rev.	description	date
1.0	initial release	05/31/25

The revision history provided is for informational purposes only and is believed to be accurate.