



Declaration of Conformity

Manufacturer:

CUI Inc.

**15575 SW Sequoia Parkway, Suite 100
Portland, Oregon 97224**

For the following equipment:

DC-DC Converter

CUI Series: PTM2-S

Models: See next page

This declaration of conformity is issued under the sole responsibility of the manufacturer. The object of the declaration described above is in conformity with the relevant UK designated legislations (and their amendments) and relevant designated standards or other technical specifications.

UK SI 2002 no. 618: General Medical Devices Regulations 2002 - as amended in 2002

UK SI 2016 no. 1091: The Electromagnetic Compatibility Regulations 2016 - as amended in 2019, 2020

UK SI 2012 no. 3032: The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 - as amended in 2019, 2020

References to the used, including the date of the standard, or references to the other technical specifications, including the date of the specification, in relation to which conformity is declared:

Health & Safety BS EN 60601-1:2006+A1:2013+A12:2014+A2:2021,
IEC 60601-1:2005+A1:2012+A2:2020 (equivalent)

EMC BS EN 55011:2016+A11:2020

RoHS BS EN IEC 63000:2018

Note: These component level power supplies are intended exclusively for inclusion within other equipment. Protection against electric shock and Electromagnetic Compatibility (EMC) must be checked when the equipment is built-in a completed product or forms a part of a complete system.

Approved by:



(manufacturer)

Editha Vergara
Global Director, Safety, Environmental

Portland, Oregon, USA

(place)

07/11/2024

(date)

UK Representative:



(manufacturer)

Cliff Gore
European Sales Director
Bel Power Solutions

Maidstone, UK

(place)

07/11/2024

(date)

MODEL LIST

PTM2-3-SXX-S, PTM2-5-SXX-S, PTM2-12-SXX-S, PTM2-24-SXX-S (where XX = 3, 5, 9, 12, 15 denote output voltage)
PTM2-3-DXX-S, PTM2-5-DXX-S, PTM2-12-DXX-S, PTM2-24-DXX-S (where XX = 5, 12, 15 denote output voltage)

Model	Input voltage (Vdc) typ.	Input voltage tolerance	Output voltage (Vdc)
PTM2-3-S3-S	3.3	±10%	3.3
PTM2-3-S5-S	3.3	±10%	5
PTM2-3-S12-S	3.3	±10%	12
PTM2-3-S15-S	3.3	±10%	15
PTM2-5-S3-S	5	±10%	3.3
PTM2-5-S5-S	5	±10%	5
PTM2-5-S12-S	5	±10%	12
PTM2-5-S15-S	5	±10%	15
PTM2-12-S3-S	12	±10%	3.3
PTM2-12-S5-S	12	±10%	5
PTM2-12-S12-S	12	±10%	12
PTM2-12-S15-S	12	±10%	15
PTM2-24-S3-S	24	±10%	3.3
PTM2-24-S5-S	24	±10%	5
PTM2-24-S9-S	24	±10%	9
PTM2-24-S12-S	24	±10%	12
PTM2-24-S15-S	24	±10%	15
PTM2-3-D5-S	3.3	±10%	±5
PTM2-3-D12-S	3.3	±10%	±12
PTM2-3-D15-S	3.3	±10%	±15
PTM2-5-D5-S	5	±10%	±5
PTM2-5-D12-S	5	±10%	±12
PTM2-5-D15-S	5	±10%	±15
PTM2-12-D5-S	12	±10%	±5
PTM2-12-D12-S	12	±10%	±12
PTM2-12-D15-S	12	±10%	±15
PTM2-24-D5-S	24	±10%	±5
PTM2-24-D12-S	24	±10%	±12
PTM2-24-D15-S	24	±10%	±15

Model Naming Configuration

PTM2	-	S	-	XX	-	S	XX
I	-		-	II	-	III	IV

I	-	Base Number:	PTM2-S
II	-	Input voltage:	3 = 3.3 V; 5 = 5 V; 12 = 12 V; 24 = 24 V
III	-	Output:	S = single, D = dual
IV	-	Output Voltage:	3 = 3.3 V; 5 = 5 V; 9 = 9 V; 12 = 12 V; 15 = 15 V; 24 = 24 V (prefix with ± when dual outputs)

REVISION HISTORY

rev.	description	date
1.0	initial release	07/11/24

The revision history provided is for informational purposes only and is believed to be accurate.