

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME
CB TEST CERTIFICATE

Product

Switch Mode Power Supply

Name and address of the applicant

VOX POWER LTD
Unit 2
Redcow Interchange Estate Dublin 22
Ireland

Name and address of the manufacturer

VOX POWER LTD
Unit 2
Redcow Interchange Estate Dublin 22
Ireland

Name and address of the factory

Panyu Trio Microtronics Co Ltd
SHIJI INDUSTRIAL ESTATE
DONGYONG
NANSHA GUANGZHOU, GUANGDONG, 511453
China

Note: When more than one factory, please report on page 2

[Additional Information on page 2](#)

Ratings and principal characteristics

Input rating: 100-240 V ac, 7 A, 50-60 Hz

[Additional Information on page 2](#)

Trademark / Brand (if any)



VOX POWER

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

VCCM600S-abcd-zzzz

[Additional Information on page 2](#)

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to: EN 62368-1:2014, EN 62368-1:2014/A11:2017
The report was revised to include technical modifications.

[Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E316486-A6003-CB-2 issued on 2022-08-23

This CB Test Certificate is issued by the National Certification Body



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Denmark), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2022-08-23

Original Issue Date: 2021-04-28

Signature:

Jan-Erik Storgaard

Factory(ies):

Trio-Tronics (Thailand) Ltd
7/295 Mu. 6
Map Yang Phon Sub-District Pluak Daeng District, Rayong Province,
Thailand

Additional Model Detail(s):

VCCM600S-abcd-zzzz, where abcd is optional and denotes respectively slot 1, slot 2, slot 3, slot 4 and each may be as follows:
0, A, B, C, or D. zzzz may be blank or alphanumeric characters.

Output modules:

OPA, OPB, OPC, OPD

Additional Ratings:

Maximum output power is 600 W.
Individual outputs rated according to modules fitted.
Output modules output ratings (optional):
OPA = 1.5 - 7.5 V dc, 25 A, 125 W
OPB = 4.5 - 15 V dc, 15 A, 150 W
OPC = 9 - 30 V dc, 7.5 A, 150 W
OPD = 18 - 58 V dc, 3.75 A, 150 W
All output modules current and power ratings are the maximum allowable.

Summary of Modifications:

Components revised, manual updated. See test report for details.

Additional information (if necessary)

☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2022-08-23
Original Issue Date: 2021-04-28

Signature:


Jan-Erik Storgaard