

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME
CB TEST CERTIFICATE

Product	AC-DC Power Supply
Name and address of the applicant	VOX POWER LTD Unit 2 Redcow Interchange Estate Dublin 22 Ireland
Name and address of the manufacturer	VOX POWER LTD Unit 2 Redcow Interchange Estate Dublin 22 Ireland
Name and address of the factory	Panyu Trio Microtronics Co Ltd SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU, GUANGDONG, 511453 China Additional Information on page 2
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	VCCM600S input rating: 100-240 V ac (or 120-370 V dc) 7 A, 50-60 Hz Additional Information on page 2
Trademark / Brand (if any)	 VOX POWER
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	VCCM600S Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to: EN 60950-1:2006, EN 60950-1:2006/A1:2010, EN 60950-1:2006/A2:2013, EN 60950-1:2006/A11:2009 The report was revised to include technical modifications. Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60950-1:2005, IEC 60950-1:2005/AMD1:2009, IEC 60950-1:2005/AMD2:2013
As shown in the Test Report Ref. No. which forms part of this Certificate	E316486-A9-CB-2 issued on 2021-04-28

This CB Test Certificate is issued by the National Certification Body



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

 For full legal entity names see www.ul.com/ncbnames

 Date: 2022-08-23
 Original Issue Date: 2021-04-28

 Signature:
 Jan-Erik Storgaard

Factory(ies):

Trio-Tronics (Thailand) Ltd
7/295 Mu. 6
Map Yang Phon Sub-District Pluak Daeng District, Rayong Province,
Thailand

Additional Model Detail(s):

VCCM600S, The VOX POWER PART NUMBER is optional and may be blank, or comprised of VCCM600S and may also be followed by: -1234

where:

1 (Slot 1) = 0, A, B, C, or D.
2 (Slot 2) = 0, A, B, C, or D.
3 (Slot 3) = 0, A, B, C, or D.
4 (Slot 4) = 0, A, B, C, or D. and

where 0 = No Module Fitted, and where A = OPA, B = OPB, C = OPC and D = OPD

May also be followed by alphanumeric characters to indicate non-safety related information.

Output Modules:

OPA, OPB, OPC, OPD

Additional Ratings:

Maximum output power is 600 W.

Individual outputs rated according to modules fitted.

Output modules output ratings (optional):

OPA = 1.5 - 7.5 V dc, 25 A, 125 W

OPB = 4.5 - 15 V dc, 15 A, 150 W

OPC = 9 - 30 V dc, 7.5 A, 150 W

OPD = 18 - 58 V dc, 3.75 A, 150 W

All output modules current and power ratings are the maximum allowable.

Additionally evaluated to:

EN 60950-1:2006/A12:2011

Summary of Modifications:

Components revised. Manual updated. See test report for details.

Additional information (if necessary)

- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Signature: 
Jan-Erik Storgaard

Date: 2022-08-23
Original Issue Date: 2021-04-28