

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switch mode modular power supplies for installation into medical equipment.

Name and address of the applicant

 VOX POWER LTD
 Unit 2, Redcow Interchange Estate
 Ballymount, Dublin 22, D22 Y8H2
 IRELAND

Name and address of the manufacturer

 VOX POWER LTD
 Unit 2, Redcow Interchange Estate
 Ballymount, Dublin 22, D22 Y8H2
 IRELAND

Name and address of the factory

 Panyu Trio Microtronics Co. Ltd.
 SHIJI INDUSTRIAL ESTATE, DONGYONG, NANSHA, GUANGZHOU
 GUANGDONG 511453
 CHINA

 Additional Information on page 2

Input rating: 100-240 V ac (or 120-370 V dc) 7 A, 50-60 Hz

 Additional Information on page 2


Trademark / Brand (if any)

Customer's Testing Facility (CTF) Stage used

VCCM600M(i)

 Additional Information on page 2

Model / Type Ref.

The risk management requirements of the standard were not addressed.

National Differences: CA, US

 Additional Information on page 2

Additional information (if necessary may also be reported on page 2)

 IEC 60601-1:2005, IEC 60601-1:2005/AMD1:2012,
 IEC 60601-1:2005/AMD2:2020

A sample of the product was tested and found to be in conformity with

E316486-D1000-3/A0/C0-CB issued on 2024-01-22

As shown in the Test Report Ref. No. which forms part of this Certificate


 Solutions

- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
 UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
 UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
 UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

 For full legal entity names see www.ul.com/ncbnames

Date: 2024-02-01

Signature:

Thomas Wilson



Ref. Certif. No.

DK-148726-UL

Factory(ies):

Trio-Tronics (Thailand) Ltd.
7/295 Mu. 6, Map Yang Phon Sub-District Pluak Daeng District, Rayong Province
Thailand

Additional Model Detail(s):

Switch Mode Power Supplies: VCCM600M(i), (i) may be blank, or comprised of VCCM600M which may be followed by: 1, 2, 3 or 4, and maybe followed by alphanumeric characters to indicate non-safety related information.

Where:

1 (Slot 1) = 0, A, B, C or D

2 (Slot 2) = 0, A, B, C or D

3 (Slot 3) = 0, A, B, C or D

4 (Slot 4) = 0, A, B, C or D

Where 0 = No output module fitted, A = Module OPA, B = Module OPB, C = Module OPC, D = Module OPD

Additional Ratings:

Maximum output power is 600 W.

Individual outputs rated according to modules fitted.

Output modules output ratings (optional):

OPA = 1.5 - 7.5 V dc, 25 A, 125 W

OPB = 4.5 - 15 V dc, 15 A, 150 W

OPC = 9 - 30 V dc, 7.5 A, 150 W

OPD = 18 - 58 V dc, 3.75 A, 150 W

All output modules current and power ratings are the maximum allowable.

Additional information (if necessary)



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2024-02-01

Signature:

Thomas Wilson