

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

AC/DC switch mode power supply

Name and address of the applicant

 VOX POWER LTD
 Unit 2
 Redcow Interchange Estate Dublin 22
 Ireland

Name and address of the manufacturer

 VOX POWER LTD
 Unit 2
 Redcow Interchange Estate Dublin 22
 Ireland

Name and address of the factory

 Trio-Tronics (Thailand) Ltd
 7/295 Mu. 6
 Map Yang Phon Sub-District
 Pluak Daeng District Rayong Province
 Thailand

 Additional Information on page 2

Ratings and principal characteristics

 Input: 100 - 240 Vac, 50-60 Hz, 3A
 Output: 12Vdc to 58Vdc (depends on model), max. 300 W

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

VCCS300S-aaaa-bbb

- aaaa denotes the output voltage and may be blank or any value from 12 to 58 (including decimals to one significant digit);
- bbb may be blank or alphanumeric characters;

Additionally evaluated to:

 EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020
 National Differences specified in the CB Test Report.

IEC 62368-1:2018

E316486-A6008-CB-1 issued on 2023-01-16

This CB Test Certificate is issued by the National Certification Body



Ref. Certif. No.

DK-135965-UL

Factory(ies):

Panyu Trio Microtronics Co Ltd
SHIJI INDUSTRIAL ESTATE
DONGYONG
NANSHA GUANGZHOU
GUANGDONG 511453
China

Additional information (if necessary)



Date: 2023-01-16

- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Signature:

Jan-Erik Storgaard