

Data Surge Protector SPD DPR Indoor Gigabit Ethernet PoE++ Shielded RJ45 SASD, GDT CE Compliant, EN/IEC 60950-1, UL 497B



DPR-F140

Features

- FDOT APL 620-004-012
- NEMA TS2 Tested and Compliant
- UL 497B, EN/IEC 60950-1, CE, RoHS
- Purpose Designed Modules for all Common Data Protocols
- Configurable Mixed Signal Protection
- RJ-45 Connectivity
- Mount into DPR Chassis, DIN-Rail Mount or Wall Mount

Applications

- Traffic Control Systems
- Gigabit Ethernet/PoE++ Networks
- Telecommunications Base Stations
- WISP/ISP
- IT & Data Centers
- Point-to-Point Links
- Control Lines and Sense Loops
- Oil & Gas

Description

Data surge protector (also known as SPD or lightning protector) DPR-F140 from Transtector is an indoor style SPD that utilizes state of the art SASD/GDT technology to protect critical equipment in Gigabit Ethernet PoE++ protocol data networks while remaining transparent to data throughput. This surge protector provides effective protection against electrical transient surges that are generated both by external lightning events and by internal switching events and supports long-term system reliability by absorbing high amounts of transient energy while maintaining a very low clamping voltage. Transtector Data Signal surge protectors are available in stock with same day shipping.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Connectors		Shielded RJ45		
Compatible Cables		Cat5/5e UTP/STP, Cat6/6A STP		
Data Protocols		Gigabit Ethernet PoE++		
Data Rate			1,000	Mb/s
Characteristic Impedance		100		Ohms
Capacitance (Differential)			30	pF
Capacitance (Common)			5	pF
Power over Ethernet Protocols			PoE++	
Vdc Rating (Data)	48		60	Vdc
PoE Power			100	W
PoE Current Per Pin			1.5	A

Surge Protection Specification

Description	Minimum	Typical	Maximum	Units
Surge Protection Technology		SASD, GDT		
Protected Pins	[1,2], [3,6], [4,5], [7,8]			
Protection Modes	L-G, L-L, S-G			

Data Surge Protector SPD DPR Indoor Gigabit
 Ethernet PoE++ Shielded RJ45 SASD, GDT
 CE Compliant, EN/IEC 60950-1, UL 497B



DPR-F140

Surge Protection Specification

Description	Minimum	Typical	Maximum	Units
10/000 μ s Surge Current				
L-G			100	A
8/20 μ s Surge Current				
L-G			2	kA
L-L			0.1	kA
S-G			20	kA
Response Time			5	ns

Mechanical Specifications

Size

Length	0.94 in	[23.88 mm]
Width/Diameter	0.97 in	[24.64 mm]
Height	3.67 in	[93.22 mm]
Weight	0.2 lbs	[90.72 g]

Mechanical Specification Notes:

Environmental Specifications

Temperature

Operating Temperature	-40 to +75 deg C
Storage Temperature	-40 to +75 deg C

Environmental Specification Notes:

Installation

Mount Type	Wall, DIN, Rack
Installation Hardware	Ground Clip, 4-40 PH Phillips Screw, #4 Split Lock Washer
Grounding	DIN Clip

Compliance Certifications

CE Compliant	Yes
UL Compliant	Yes
Certifications	UL 497B EN/IEC 60950-1 NOM NEMA TS2

Data Surge Protector SPD DPR Indoor Gigabit Ethernet PoE++ Shielded RJ45 SASD, GDT
CE Compliant, EN/IEC 60950-1, UL 497B



DPR-F140

Transtector Systems specializes in protection of highly sensitive, low voltage equipment through its patented, non-degrading silicon diode technology and custom filters. Our power quality expertise translates into a diverse product offering including AC, DC, and signal applications as well as integrated cabinets, power distribution panels and EMP hardened devices.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Data Surge Protector SPD DPR Indoor Gigabit Ethernet PoE++ Shielded RJ45 SASD, GDT CE Compliant, EN/IEC 60950-1, UL 497B DPR-F140](https://www.transtector.com/data-surge-protector-spd-dpr-indoor-gigabit-dpr-f140-p.aspx)

URL: <https://www.transtector.com/data-surge-protector-spd-dpr-indoor-gigabit-dpr-f140-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Transtector reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Transtector does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Transtector does not assume liability arising out of the use of any part or document.

DPR-F140 CAD Drawing

Data Surge Protector SPD DPR Indoor Gigabit Ethernet PoE++ Shielded
RJ45 SASD, GDT CE Compliant, EN/IEC 60950-1, UL 497B

