

USB 3.2 Type C

USB 3.2 Gen 1 (5Gb/s), USB 3.2 Gen 2 (10Gb/s), USB 3.2 Gen 2x2 (20Gb/s), USB Type C compliant, high-speed solution

USB 3.2 high-speed Type C is a standard interface that is expected to spread to a wide variety of devices in the consumer, industrial, and automotive markets.

- Compliant with USB Type C specification
- High-speed transmission up to 20Gb/s super speed
- Power rating up to 240W
- Optimized contact design for superior signal integrity performance
- Reversible plug and cable orientation



TARGET MARKETS



FEATURES

- High-speed transmission up to 20Gb/s
- High power and fast charging
- Various mounting types (Top, Middle, Vertical)
- Reversible plug orientation ensures easy insertion
- Mid-plate tongue design
- All-in-one simplicity

BENEFITS

- High-speed data communication
- Extended 5A current rating for USB Power delivery and up to 240W
- Offer design flexibility
- Connect cable without worrying about the plug's orientation or the cable's direction
- Ensure high reliability while preventing damage from connector mishandling
- Support power delivery, data transfer, video output in one connector

TECHNICAL INFORMATION

MATERIAL

- Housing: PA46 or LCP, Receptacle: PA46 or LCP
- Molding Housing: Black, High temperature plastic
- Top Terminal: Copper Alloy
- Bottom Terminal: Copper Alloy
- Mid Plate: Stainless steel, Nickel 30 μ min.
- Outer Shell: Stainless steel, Solder Nickel 30 μ min.
- Main Shell: Stainless steel, NI plated or Cleaning
- Small Shell: Stainless steel, NI plated or Cleaning
- LIM: Silica Gel, Black

MECHANICAL PERFORMANCE

- Durability: 10000 cycles
- After Durability Extraction Force: 6~20N
- Insertion Force: 5~20 N
- Extraction Force: 8~20 N

ELECTRICAL PERFORMANCE

- Low-level Contact Resistance: 40m Ω max.
- Insulation Resistance: 100m Ω min.
- Contact Current Rating: 5A max.
- Dielectric Withstanding Voltage: 100VAC

PART NUMBERS

Description	Part Numbers
USB3.2 Gen 2, Type C, Receptacle, R/A, Top mount, Center Height 1.58mm, Dual Row SMT	12401598E4#2A
USB3.2 Gen 2, Type C, Receptacle, R/A, Top mount, Center Height 1.58mm, Dual Row SMT	12401610E4#2A
USB3.2 Gen 2, Type C, Receptacle, R/A, Top mount, Center Height 1.58mm, Dual Row SMT	12401832E402A
USB3.2 Gen 2, Type C, Receptacle, R/A, Top mount, Center Height 1.58mm, Dual Row SMT	12401824E412A
USB3.2 Gen 2, Type C, Receptacle, R/A, Top mount, Center Height 1.58mm, Dual Row SMT	12401808E412A
USB3.2 Gen 2, Type C, Receptacle, R/A, Top mount, Center Height 1.75mm, Dual Row SMT	12401899E412A
USB3.2 Gen 2, Type C, Receptacle, R/A, Mid mount, Center Height 1.10mm, Dual Row SMT	124018402112A
USB3.2 Gen 2, Type C, Receptacle, R/A, Top mount, Center Height 1.57mm, Dual Row SMT	12402143E512A
USB3.2 Gen 2, Type C, Receptacle, R/A, Mid mount, Center Height 0.47mm, Dual Row SMT	12402144E512A
USB3.2 Gen 2, Type C, Vertical, Length 12mm, Dual Row SMT	12401951E412A
USB3.2 Gen 1, Type C, Vertical, Length 6.5mm, Dual Row SMT	12402032E202A
USB3.2 Gen 1, Type C, Vertical, Length 6.5mm, Dual Row SMT	12402069E202A
USB3.2 Gen 1, Type C, Receptacle, R/A, Top mount, Center Height 1.68mm, Dual Row SMT	GSB3C3133DSYHR
USB3.2 Gen 1, Type C, Receptacle, R/A, Top mount, Center Height 1.93mm, Dual Row SMT	GSB3C31331DYHR

CMI01USBTYPEC1023EA4

PACKAGING

- Tape & Reel

SPECIFICATION

- Amphenol Product Specification: SSN002

APPROVALS AND CERTIFICATIONS

- RoHS
- Halogen-free

ENVIRONMENTAL

- Operating Temperature Range: -40°C to +85°C

TARGET MARKETS/APPLICATIONS



Wearable Devices
Power Banks
Smart Home Devices
E-Cigarettes
TWS (True Wireless Stereo) Headphone Markets