







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-





CODE A (2385514-1 & 1-2385514-1)



CODE B (2385514-2 & 1-2385514-2)



CODE C (2385514-3 & 1-2385514-3)



CODE D (2385514-4 & 1-2385514-4)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRAVEEN HM	11FEB2021	 TE Connectivity	
		CHK Z. KRNETIC	11FEB2021		
DIMENSIONS:		APVD D. RHEIN	15FEB2021	NAME 2POS,HC-STAK 35, HDR OUTER HSG ASSY	
mm		PRODUCT SPEC			

11. UNLESS OTHERWISE SPECIFIED:
ALL DIMENSIONS FOR THE HEADER TAB INTERFACE ARE ± 0.10
ALL DIMENSIONS ARE AFTER PLATING




2. PLATING 0.0030-0.0060 Ag PER ASTM B 700, TYPE 3,
16 Ra MINIMUM FINISH OVER 0.0010-0.0040 NICKEL

3. DIMENSION TO THEORETICAL SHARP CORNER


14. BREAK EDGE IN THIS REGION BOTH SIDES OF MATERIAL

15. PART MUST BE FREE OF EXCESSIVE BURRS, CRACKS OR OTHER
VISUAL IMPERFECTIONS THAT MAY AFFECT FIT OR FUNCTION




16. 0.1 MAX BROKEN EDGE





HEADER TAB INTERFACE
SCALE 2:1



HEADER TAB INSTALLATION AND TPA FUNCTION





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: PRAVEEN HM 11FEB2021	TE Connectivity	
		CHK: Z. KRNETIC 11FEB2021		
DIMENSIONS:		APVD: D. RHEIN 15FEB2021	NAME: 2POS, HC-STAK 35, HDR OUTER HSG ASSY	
mm		PRODUCT SPEC		
		108-160704	SIZE: CAGE CODE: DRAWING NO: 00779 C=2385514	
		APPLICATION SPEC		
		114-160508	RESTRICTED TO: -	
MATERIAL: -		WEIGHT: SEE TABLE A		
		CUSTOMER DRAWING	SCALE: 1:1 SHEET 3 OF 4 REV A2	




HEADER MOUNTING INTERFACE, TYPE-1 (CODE-A SHOWN)

CODE D	19.25	6.25	INTERFACE-4_TYPE-1
CODE C	6.25	6.25	INTERFACE-3_TYPE-1
CODE B	6.25	19.25	INTERFACE-2_TYPE-1
CODE A	19.25	19.25	INTERFACE-1_TYPE-1
CODE	DIM Y	DIM X	PART NUMBER



HEADER MOUNTING INTERFACE, TYPE-2 (CODE-A SHOWN)



CODE D	19.25	6.25	INTERFACE-4_TYPE-2
CODE C	6.25	6.25	INTERFACE-3_TYPE-2
CODE B	6.25	19.25	INTERFACE-2_TYPE-2
CODE A	19.25	19.25	INTERFACE-1_TYPE-2
CODE	DIM Y	DIM X	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: PRAVEEN HM 11FEB2021	TE Connectivity	
DIMENSIONS: mm		CHK: Z. KRNETIC 11FEB2021	NAME: 2POS, HC-STAK 35, HDR OUTER HSG ASSY	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: D. RHEIN 15FEB2021	SIZE: CAGE CODE: DRAWING NO: RESTRICTED TO	
0 PLC ±°		PRODUCT SPEC: 108-160704	A 00779 ©=2385514	
1 PLC ±°		APPLICATION SPEC: 114-160508	SCALE: 1:1 SHEET 4 OF 4 REV A2	
2 PLC ±°		WEIGHT: SEE TABLE A		
3 PLC ±°		CUSTOMER DRAWING		
4 PLC ±°				
ANGLES FINISH				