





- 1

SUPPLY CONDITION: LEVER (ITEM 10) IN CLOSED POSITION
- 2

SUPPLY CONDITION: CPA (ITEM 11) IN CLOSED POSITION
- 3


LASER MARK DATE CODE YYDD HH:MM FORMAT
- 4

LASER MARK TE PART NUMBER
- 5

LASER MARK WORK CENTER
- 6

DISCOLORATION ON THESE SURFACES DUE TO TRAPPED GAS IS PERMITTED
7.

NONMETALLIC INCLUSIONS/SPECKS ARE PERMISSIBLE UP TO Ø1 IN MOLDED COMPONENTS



1	1	1	1	RED	PA66-GF35	CPA, WITH PUSH PAD	11
1	1	1	1	BLACK	PA66-GF35	LEVER	10
2	2	2	2	—	SEE DRAWING C-929454	MOS SOCKET CONTACT(X-928999-6)	9
1	1	1	1	BLACK	PA66-GF35	FRONT SEAL RETAINER	8
1	1	1	1	YELLOW	40 DUROMETER SILICONE, LUBRICATED	FRONT SEAL	7
1	1	1	1	BLACK	PA66-GF35	REAR SEAL HOUSING	6
1	1	1	1	BLUE	40 DUROMETER SILICONE, LUBRICATED	REAR SEAL	5
1	1	1	1	—	CuNiSi PLATING: Ag OVER Ni	PLUG SHIELD	4
2	2	2	2	—	SS	TAB RETAINER	3
1	1	1	1	—	—	INNER HOUSING ASSEMBLY	2
1	-	-	-	ORANGE	PA66-GF33	OUTER HOUSING, CODE D	1
-	1	-	-	ORANGE	PA66-GF33	OUTER HOUSING, CODE C	
-	-	1	-	ORANGE	PA66-GF33	OUTER HOUSING, CODE B	
-	-	-	1	ORANGE	PA66-GF33	OUTER HOUSING, CODE A	
2385722-4	2385722-3	2385722-2	2385722-1	COLOR	MATERIAL	DESCRIPTION	ITEM NO.
261	261	261	261	WEIGHT (g)			
CODE D	CODE C	CODE B	CODE A	CODINGS			
QTY REQ PER ASSY				REVISION OF EACH ASSY NO (WHEN BLANK, USE DRAWING REVISION)			
				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±.0
1 PLC	±.0
2 PLC	±0.50
3 PLC	±
4 PLC	±
ANGLES	±5°

MATERIAL

FINISH

OWN: PRAVEEN HM 10FEB2021

CHK: Z. KRNETIC 11FEB2021

APVD: D. RHEIN 15FEB2021

PRODUCT SPEC

108-160704

APPLICATION SPEC

114-160380

WEIGHT: SEE TABLE A

CUSTOMER DRAWING

NAME: 2POS,HC-STAK35 TAB OUTER HSG ASSY

SIZE: 00779

CAGE CODE: 00779

DRAWING NO: 2385722

RESTRICTED TO: -

SCALE: 1:1

SHEET: 1 OF 1

REV: A1

TE Connectivity