


Next Generation Low Power, Sized Optimized, and Smart IoT: Power Efficient NXP Edge Processing

Our customers asked for a low power, compact, peripheral rich, and robust SoM that simplifies their BOM. One with multiple software options, a proven security architecture, long term software support, and security fixes.

Our new Nitrogen8ULP SOM is powered by the next generation low power **NXP i.MX 8ULP** processor and it's specifically designed **NXP PMIC PCA9460A**. It features power efficient LPDDR4 RAM and eMMC storage. We combine this with a specifically designed carrier board; together they serve as a single board computer (SBC) that can speed your product to market. Alternately, work with us to create a custom carrier that fits your mechanical, environmental, temperature, and interface requirements.

- **Low Power Heterogenous Multiprocessing:** Up to 800 MHz dual-core Cortex-A35, ARM's lowest power 64-bit MPU architecture, and 216 MHz Cortex-M33 MCU to run Linux and an RTOS on dedicated, hardware-firewalled subsystems.
- **Power Efficient:** µPower management subsystem in the i.MX 8ULP, delivering 20 different power modes, combined with an NXP PMIC, power optimized LPDDR4 and eMMC memory to optimize core shut off, clock/voltage scaling, low power interfaces, all to enable highly optimized power consumption.
- **Tensilica® HiFi 4 DSP:** High-performance audio DSP for advanced audio/voice processing while using minimal power consumption.
- **Tensilica® Fusion F1 DSP:** Low power DSP for keyword detection and sensors.
- **Graphics and Display:** 4-lane MIPI-DSI with GPU supporting 3D accelerated OpenGL ES 3.1, Vulkan, OpenVG 1.1, OpenCL 2.x, OpenVG 1.1 and 2D graphics.
- **Diversity of Interfaces:** Display, network, data, audio, camera.
- **Compact and Rugged Form Factor:** Size optimized 51mm x 32mm form factor with board-to-board connectors



- **Advanced carrier/Development Board:** Display, camera, audio, Ethernet, USB, CAN, I2C, SPI, UART, and more. Use in development, as an SBC equivalent in a product, or as reference designs for your carrier board.
- **Easy Integration** with Ezurio's portfolio of compact and low power Wi-Fi and Bluetooth modules
- **Operating Temp:** Commercial (0° to +70 °C) / Industrial (-40° to +85 °C) (For I-Temp options, contact Sales)
- **High performance memory:** 2GB LPDDR4 / 16GB eMMC
- **US based manufacturing with Global Options:** Assembled in USA for local customer base and US market needs. Global manufacturing capability as part of Ezurio footprint, growing reach to EMEA & APAC regions
- **Diverse Software and Board Support Options:** including Yocto Linux, Buildroot Linux, Ubuntu Linux, and Android for the Cortex-A35 and FreeRTOS for the Cortex-M33. **Long-term software support** options include LTS Yocto Linux with vulnerability remediation.
- **Secure and Encrypted Boot, Secure Enclave, and Secure File Storage:** Robust, secure, and optionally encrypted boot mechanism to ensure only trusted software boots on your device. Optionally store and use secure keys, certificates, and credentials in run-time isolated trusted environment.
- **Long term hardware availability:** Ezurio's products are specifically designed to meet the needs of the industrial and medical markets, which typically require 10 year or more product lifecycles.

Key Features



Low Power Multiprocessing w/ Dedicated Power Management

ARM's lowest power 64-bit microprocessor architecture, Cortex-A35, plus NXP's dedicated µPower management subsystem which delivers 20 different power modes.



Graphics, Vision, Audio, DSPs, and Industrial Peripherals

3D GPU, 2D Engine, MIPI-DSI display interface, MIPI-CSI camera interface, HiFi 4 DSP, Fusion F1 DSP, I2S audio interfaces, CAN/CAN-FD, USB, Ethernet, and more



Secure Enclave and Secure Boot Powered by i.MX 8ULP

Dedicated on-board security hardware, secure boot Linux, and high-performance and flexible secure storage system for passwords, certificates, and data storage.



Robust Software and Speed to Market

Choose from Yocto Linux, Buildroot Linux, Ubuntu, and Android for the Cortex-A35s, FreeRTOS for the Cortex-M33.



Long Term Hardware Availability

Specifically designed to meet the needs of the industrial and medical markets, which typically require 10 year or more product lifecycles.



Personal Support from Design to Manufacture

Our industry-renowned support and field application engineering team is passionate about helping you speed your design to market.

Application Areas



Energy Meters, Energy Storage
Smart Electrical Panels



Smart City, Smart Camera



Smart Building Control, HVAC



Portable Patient Monitors,
Medical Devices



Handheld Printers and Scanners



Commercial Food and Beverage
Equipment

Specifications

Category	Feature	Specification
Processors	Microprocessor	2x Cortex®-A35 cores @ up to 800 MHz
	Microcontroller	1x Cortex®-M33F core @ 216 MHz
	Graphics	GC7000 nanoULTRA31 3D GPU and CC328 2D Engine
	Audio	Tensilica® HiFi 4 DSP
	Low Power DSP	Tensilica® Fusion F1 DSP
Memory	RAM	2GB (For custom sizes, please contact Sales)
	Storage	16GB (For custom sizes, please contact Sales)
Graphics and Video	Graphics Engine	<ul style="list-style-type: none"> 3D GPU OpenGL ES 3.1, Vulkan, OpenVG 1.1, OpenCL 2.x, OpenVG 1.1 2D Engine
	Display Interfaces	1x 4-lane MIPI DSI, up to 1920x1200p60
Vision	Camera	1x 2-lane MIPI CSI
Audio	Audio Interfaces	<ul style="list-style-type: none"> 7x I2S 7x DigMIC 5x SPDIF 1x MQS
Peripherals	Input/Output	<ul style="list-style-type: none"> 2x USB 2.0 with PHY 1x 10/100 Mbit/s Ethernet with support for IEEE® 1588 1x CAN/CAN-FD 8x UART 7x I2C 6x SPI 3x I3C <ul style="list-style-type: none"> 2x SDIO 3.0/eMMC 5.1 14x GPIO 2x 12-bit ADC 2x 12-bit DAC 2x Analog Comparator 8x 32-bit Timers 4x Watchdog Timers
Supply Voltage		5 V
Physical	Dimensions	Board to Board Connectors - 51mm x 32mm
Environmental	Temp Range	0°C to +70°C (Commercial) and -40° to +85 °C (Industrial) (For industrial temperature options, please contact Sales)
Miscellaneous	Lead Free	Lead-free and RoHS-compliant
	Carrier Board	Carrier board, accessories, and evaluation software

For full specifications on the Nitrogen8ULP, please see the appropriate datasheet.

Ordering Information

Part	Description
N8ULP_SOM_2r16e	Nitrogen8ULP SOM: i.MX 8ULP Dual / 2GB / 16GB eMMC / 0 to +70°C / Without Wireless
N8ULP_SOM_2r16e_i	Nitrogen8ULP SOM: i.MX 8ULP Dual / 2GB / 16GB eMMC / -40 to +85°C / Without Wireless
N8ULP_CAR_BRD	Nitrogen8ULP Carrier Board (Note - SOM sold separately)

Ezurio's products are subject to standard Terms & Conditions.