

# PowerFilm<sup>®</sup>

MADE IN THE USA

## SOLAR

## Electronic Component Solar Panels

### Classic Application Series


The Classic Application Series offer a new opportunity to solve the old problem of limited power for wireless electronics designed for portable and remote applications. Classic Application panels are lightweight, paper thin, and durable.

Their ultra-thin profile enables them to be easily integrated into devices for solar recharging or for direct power. Panels have been specifically developed to recharge a variety of common battery sizes. These panels do not have a UV-stabilized surface, but are suitable for intermittent outdoor use.

Looking for a custom Electronic Component Solar Panel? We offer custom sizes, voltages, encapsulations and substrates. Contact us at [www.powerfilmsolar.com](http://www.powerfilmsolar.com) to learn more.


#### SP3-37

Power: 0.07W  
Operating Voltage: 3.0V  
Operating Current: 22mA  
Max Voc: 4.6V  
Size: 2.52 in x 1.45 in /  
64 mm x 36.9 mm  
Weight 0.03 oz




#### MPT3.6-75

Power: 0.18W  
Operating Voltage: 3.6V  
Operating Current: 50mA  
Max Voc: 5.5V  
Size: 2.91 in x 2.87 in /  
73.9 mm x 72.9 mm  
Weight: 0.06 oz



#### MP3-25

Power: 0.09W  
Operating Voltage: 3.0V  
Operating Current: 31mA  
Max Voc: 4.6V  
Size: 4.49 in x 0.94 in /  
114 mm x 24 mm  
Weight: 0.03 oz




#### MPT3.6-150

Power: 0.36W  
Operating Voltage: 3.6V  
Operating Current: 100mA  
Max Voc: 5.5V  
Size: 2.91 in x 5.75 in /  
73.9 mm x 146 mm  
Weight: 0.10 oz




#### MP3-37

Power: 0.15W  
Operating Voltage: 3.0V  
Operating Current: 50mA  
Max Voc: 4.6V  
Size: 4.49 in x 1.45 in /  
114 mm x 36.8 mm  
Weight: 0.04 oz



#### SP4.2-37

Power: 0.09W  
Operating Voltage: 4.2V  
Operating Current: 22mA  
Max Voc: 6.5V  
Size: 3.31 in x 1.45 in /  
84.1 mm x 36.8 mm  
Weight: 0.03 oz




# PowerFilm<sup>®</sup>

MADE IN THE USA

## SOLAR


### MPT4.8-75

Power: 0.24W  
Operating Voltage: 4.8V  
Operating Current: 50mA  
Max Voc: 7.4V  
Size: 3.7 in x 2.87 in /  
94 mm x 72.9 mm  
Weight: 0.07 oz



### MP7.2-75F

Power: 0.86W  
Operating Voltage: 7.2V  
Operating Current: 120mA  
Max Voc: 11.1V  
Size: 9.96 in x 2.87 in /  
253 mm x 72.9 mm  
Weight: 0.50 oz




### MP4.8-150

Power: 0.48W  
Operating Voltage: 4.8V  
Operating Current: 100mA  
Max Voc: 7.4V  
Size: 3.7 in x 5.75 in /  
94 mm x 146 mm  
Weight: 0.10 oz




### MP7.2-150F

Power: 1.73W  
Operating Voltage: 7.2V  
Operating Current: 240mA  
Max Voc: 11.1V  
Size: 9.96 in x 5.75 in /  
253 mm x 146 mm  
Weight: 0.90 oz




### MPT6-75

Power: 0.30W  
Operating Voltage: 6.0V  
Operating Current: 50mA  
Max Voc: 9.3V  
Size: 4.49 x 2.87 in /  
114 mm x 72.9 mm  
Weight: 0.08 oz



### MPT15-75

Power: 0.77W  
Operating Voltage: 15.4V  
Operating Current: 50mA  
Max Voc: 22.2V  
Size: 9.96 in x 2.87 in /  
253 mm x 72.9 mm  
Weight: 0.50 oz



### MPT6-150

Power: 0.60W  
Operating Voltage: 6.0V  
Operating Current: 100mA  
Max Voc: 9.3V  
Size: 4.49 in x 5.75 in /  
114 mm x 146 mm  
Weight: 0.10 oz



### MPT15-150

Power: 1.54W  
Operating Voltage: 15.4V  
Operating Current: 100mA  
Max Voc: 22.2V  
Size: 9.96 in x 5.75 in /  
253 mm x 146 mm  
Weight: 0.50 oz

