




GRF2051 (1200 – 1400 MHz)

Discussion:


GRF2051 evaluated as per shown bias condition:

Bias Point	Vdd V	Iddq mA	Ven V	Ien mA
5.0V/70mA	5	70	2.5	4.1


GRF2051 Schematic:




GRF2051 Response:




GRF2051 Stability Mu Factor:




GRF2051 Noise Figure:




GRF2051 Gain:




GRF2051 IIP3:




GRF2051 OIP3:



GRF2051 IP1dB:



GRF2051 OP1dB:





Jeff Broxson

Vice President - Sales

Phone (336) 339-9314

jbroxson@guerrilla-rf.com

Alan Ake

Vice President - Applications/Technical Marketing

Phone (336) 708-4581

aake@guerrilla-rf.com

Guerrilla RF

1196 Pleasant Ridge Road, Suite 5
Greensboro, NC 27409

Phone: (336) 510-7840

www.guerrilla-rf.com

