





GRF5020 (1300 – 2700 MHz) ACLR
WCDMA TM1 64 DPCH, PAR = 10.2 dB


GRF5020 Schematic:



GRF5020 Response:




GRF5020 Stability Mu Factor:




GRF5020 5.0V ACLR:

GRF5020, Vdd/Iddq = 5.0V/90mA: WCDMA TM1, PAR = 10.2 dB



GRF5020 8.0V ACLR:

GRF5020, Vdd/Iddq = 8.0V/120mA: WCDMA TM1, PAR = 10.2 dB





Jeff Broxson

Vice President - Sales

Phone (336) 339-9314

jbroxson@guerrilla-rf.com

Alan Ake

Vice President - Applications/Technical Marketing

Phone (336) 708-4581

aake@guerrilla-rf.com

Guerrilla RF

1196 Pleasant Ridge Road, Suite 5
Greensboro, NC 27409

Phone: (336) 510-7840

www.guerrilla-rf.com

