

RIVET NUT PNEUMATIC SPIN - SPIN TOOLS

Designed for installing steel or aluminum CAL, CAK, CAH, CAO, CFT/CAT*, CFW/CAW* and CPB rivet nut inserts. Features quick change nose piece for head set replacement without tools.

*Can install stainless steel.

**RIVET NUT
PNEUMATIC
SPIN-SPIN
TOOLS**

**SSG-800
PISTOL GRIP STYLE**



**SSG-910
RIGHT ANGLE STYLE**



**SSG-900
INLINE STYLE**



Part Number	Thread Size	Tool RPM		Air Pressure (Dynamic) PSI	Weight LBS	Air Inlet NPT	Air Use CFM	Minimum Hose Size IN	Complete Head Assembly	Hex Driver	Mandrel	Bearing Set	Complete Head Assembly Rivet Nut Stud
		801&901	911										
SSG - 801, 901 & 911	4-40	3000	2200	35-45	3.0	1/4"	5	3/8	HS-0440	HD-4	M-0440-150	BS-4	
	6-32	3000	2200	70-80	3.0	1/4"	5	3/8	HS-0632	HD-6	M-0632-150	BS-6	HSS-0632
	8-32	3000	2200	70-90	3.0	1/4"	5	3/8	HS-0832	HD-8	M-0832-150	BS-8	
	M3	3000	2200	35-45	3.0	1/4"	5	3/8	HS-M3	HD-M3	M-M3-30	BS-M3	
	M4	3000	2200	35-45	3.0	1/4"	5	3/8	HS-M4	HD-M4	M-M4-35	BS-M4	
		802&902	912										
SSG - 802, 902 & 912	10-24	1500	1100	60-80	3.0	1/4"	5	3/8	HS-1024	HD-10	M-1024-175	BS-10	
	10-32	1500	1100	60-80	3.0	1/4"	5	3/8	HS-1032	HD-10	M-1032-175	BS-10	HSS-1032
	1/4-20	1500	1100	70-90	3.0	1/4"	5	3/8	HS-2520	HD-25	M-2520-175	BS-25	HSS-2520
	1/4-28	1500	1100	70-90	3.0	1/4"	5	3/8	HS-2528	HD-25	M-2528-200	BS-25	
	M5	1500	1100	60-80	3.0	1/4"	5	3/8	HS-M5	HD-M5	M-M5-40	BS-M5	HSS-M5
	M6	1500	1100	70-90	3.0	1/4"	5	3/8	HS-M6	HD-M6	M-M6-40	BS-M6	HSS-M6
		803&903	913										
SSG - 803, 903 & 913	5/16-18	600	400	90-110	3.0	1/4"	5	3/8	HS-3118	HD-31	M-3118-175	BS-31	
	5/16-24	600	400	90-110	3.0	1/4"	5	3/8	HS-3124	HD-31	M-3124-175	BS-31	
	3/8-16	600	400	90-110	3.0	1/4"	5	3/8	HS-3716	HD-37	M-3716-200	BS-37	HSS-3716
	3/8-24	600	400	90-110	3.0	1/4"	5	3/8	HS-3724	HD-37	M-3724-200	BS-37	
	M8	600	400	90-110	3.0	1/4"	5	3/8	HS-M8	HD-M8	M-M8-40	BS-M8	HSS-M8
M10	600	400	90-110	3.0	1/4"	5	3/8	HS-M10	HD-M10	M-M10-45	BS-M10		
SSG - 804	5/16-18	400		90-110	3.0	1/4"	5	3/8	HS-3118	HD-31	M-3118-175	BS-31	
	5/16-24	400		90-110	3.0	1/4"	5	3/8	HS-3124	HD-31	M-3124-175	BS-31	
	3/8-16	400		90-110	3.0	1/4"	5	3/8	HS-3716	HD-37	M-3716-200	BS-37	
	3/8-24	400		90-110	3.0	1/4"	5	3/8	HS-3724	HD-37	M-3724-200	BS-37	
	M8	400		90-110	3.0	1/4"	5	3/8	HS-M8	HD-M8	M-M8-40	BS-M8	HSS-M8
M10	400		90-110	3.0	1/4"	5	3/8	HS-M10	HD-M10	M-M10-45	BS-M10		
SSG-808	1/2-13	275		75-120	4.0	1/4"	5	3/8	HS-5013	HD-50	M-5013-250	BS-50	
	1/2-20	275		75-120	4.0	1/4"	5	3/8	HS-5020	HD-50	M-5020-225	BS-50	
	M12	275		75-120	4.0	1/4"	5	3/8	HS-M12	HD-M12	M-M12-60	BS-M12	

*Contact Sherex for Prebulbed (CPB) Mandrel part numbers and for SSG replacement part numbers.