

cannon veam

Heavy and Off Road Vehicle Product Selection Guide



ITT

cannon veam

We Connect When it matters most

1

CABIN TO CHASSIS INTERFACE

PRODUCT SOLUTIONS:

CA COM, Trident, APD,
APD Interface, APD
Modular Interface, IT

2

ENGINES

PRODUCT SOLUTIONS:

CA Bayonet, CA COM,
APD 7 Way, IT, VPT

3

LIGHTING SYSTEMS

PRODUCT SOLUTIONS:

Sure Seal, CTC, SLC,
APM, IT, VRPC



Resistant to shock, vibration, water and other fluids, humidity, mud, dust, heat, cold and virtually anything else you can throw at them. Built for the toughest, dirtiest jobs that make our modern way of life possible. ITT Cannon and Veam connectors withstand the most demanding environments. A vast range of applications means solutions must be versatile - but never at the expense of reliability. Our family of connectors is designed to deliver the ultimate in flexibility, durability and performance.

4

JUNCTION BOXES

PRODUCT SOLUTIONS:

Trident, CA Bayonet, CA COM, IT

5

CONTROL BOXES

PRODUCT SOLUTIONS:

Trident, APD, CA Bayonet, CA COM, IT, KPTC

6

SELECTIVE CATALYTIC REDUCTION

PRODUCT SOLUTIONS:

APD

7

BATTERIES

PRODUCT SOLUTIONS:

APD, CA Bayonet



		SURE SEAL	TRIDENT	APD	CTC	Cannon IT Series	SLC
							
APPLICATIONS		• Meterological Station • Signal Lighting	• Engines • Controllers/ Signal Connecting • Harnessing for Dashboard of Crane • Relais • Cabin Chassis Interface • Harnessing for Steering Column Module • Cabin Accessories / In-line Interconnects • Control Panel • Control Box • Junction Box	• Battery Connection • Controllers / Signal Connecting • Selective Catalytic Reduction • Power Transmission • Control Box • Engines	• Chassis Cable Harness • Controllers / Signal Connecting • Lighting Systems • Cabin Accessories / In-line Interconnects • Sensors • Seat and Window Control • Wipers / Under Hood Electronics	• Engine & transmission harnessing • Lighting systems • Controllers • Signal interface • Cabin harnessing/accessories • Seat & window controls • Wipers/under hood electronics • LCD displays & accessories • Sensors (electrical, pressure, temperature)	• Jake brake • Lighting Systems • Cabin accessories / In-line Interconnects
GENERAL	Standards / Connector Specifications	-	EN61984 / UL 1977	ISO 15170	Consult Factory	SAE J2030	SAE J2030 USCar
	Fire & Smoke standards	-	UL 94 V-0 and I2/F2 according to NFF 16-101 (snap-together series)	-	-	UL94 V-0	-
ELECTRICAL	Number of Circuits	2 to 10	4 to 48	1 to 51	2, 4, 8, 16, 24	2, 3, 4, 6, 8, 12	5, 8, 10, 15
	Max. Operating Voltage	48 V DC	250 V AC - 500 V DC/AC	48 V DC High Voltage: 500 V DC/AC	250 V AC	250 V AC	300 V AC
	Max. Dielectric Withstanding Voltage	1200 V AC	2000 V AC - 3500 V AC	1000 V AC High Voltage: 3500 V AC	1550 V AC	1550 V AC	1000 V AC
	Max. Current Rating	17 A	30 A	245 A	16 A	13A	13 A
CONTACTS	EMI/RFI shielding	No	Yes	No	No	No	No
	Wire range AWG	20 to 14	26 to 12	22 to 0	24 to 16	24 to 12	20 to 16
	Wire Range mm²	0,4 - 1,5	0,14 - 4,0	0,35 - 50	0,25 - 1,5	0,25 - 2,50	0,50 - 1,5
	Contact plating	Tin / Silver	Tin / Silver / Gold	Tin / Silver / Gold	Tin / Gold	Nickel / Silver / Gold flash	Tin / Gold
	Crimp, machined	Yes	Yes	Yes	Yes	24-14 AWG	Yes
	Crimp, stamped	Yes	Yes	Yes	Yes	20-12 AWG	Yes
	Solder	No	Yes	Yes	No	NA	No
	PCB	No	Consult factory	Yes	Consult Factory	NA	Yes
	Coax	No	Yes	No	No	NA	No
	Ethernet Interface	No	No	No	No	NA	No
	Fiber Optic Interface	No	No	No	No	NA	No
	Power and Signal Layouts	No	Yes	No	No	No	No
MECHANICAL	Mating cycles (max.)	100	500	50	200	200 (stamped contacts) 500 (machined contacts)	25
	Max. shock resistance (g's)	50	50	50	50	50	100
	Max. vibration resistance	500 m/s² at 10-55 Hz	100 m/s² at 10-500 Hz	100 m/s² at 10-500 Hz	100 m/s² at 10-500 Hz	20 G's at 10 to 2000 Hz	100 m/s² at 10-2000 Hz
	Mechanical coding	No	Yes	Yes	Yes	Up to 5 coding	Yes
	Type of coupling	Ring-Snap	Bayonet	Bayonet	Snap-Lock	Wire to wire	Snap-Lock
ENVIRONMENTAL	Configurations / Mounting options	Flange, Inline	Jamnut, Flange	Flange/ Jamnut/ Inline	Inline, Mounting Bracket	-	Inline, Panel Mount
	Temperature range	-40°C to 105°C (-40°F to 221°F)	-55°C to 105°C (-67°F to 221°F)	-40°C to 125°C (-40°F to 257°F)	-55°C to 105°C (-67°F to 221°F)	-55°C to +125 °C C31 (-67°F to +257°F)	-40°C to 150°C (-40°F to 302°F)
	IP rating mated	IP 68 (1 bar/ 12h)	Up to IP67	IP67 / IP69K	Up to IP 69K	IP67, IP68 (1m water with 24H), and IP6K9K	IP68 (0,03 bar / 24h)
	Individual wire sealing	Yes	Grommet	Yes	Grommet	Silicone rubber	Grommet
	Cable jacket sealing	Yes	Yes	Yes	Yes	NA	Yes
	Shell material	NBR	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
	Insert material	NBR	Thermoplastic	Thermoplastic	No	Silicone Rubber, PBT	No
	Other platings: Consult factory	No	No	No	No	-	No
SHELL PLATINGS	RoHS Electroless Nickel - Conductive (<48h)	No	Yes	No	No	-	No
	RoHS Zinc Cobalt black - Conductive - (200h)	No	No	No	No	NA	No
	RoHS Zinc Cobalt black, VG approved, Conductive (48h)	No	No	No	No	NA	No
	Cadmium Olive drab - Conductive (500h)	No	No	No	No	NA	No
	RoHS Zinc Cobalt green - Conductive (200h)	No	No	No	No	NA	No
	RoHS Zinc Nickel blue - Conductive (500h)	No	No	No	No	NA	No
	RoHS Black Epoxyurethanic varnish - Not conductive (500h)	No	No	No	No	NA	No

STANDARD PRODUCTS

CA Bayonet	CA-COM	KPTC	APE	APM	CLC	CIR-FRCIR
						
• Junction Box • Sensors • Control Box • Cabin Chassis Interface • Engines	• Junction Box • Sensors • Control Box • Cabin Chassis Interface • Engines	• Control Box • Control Panel	• ABS Braking Systems	• Switches • Relais • Actuators • Wipers • Engines • Lighting Systems	• GPS systems • Fuel injectors • Cabin accessories / in-line interconnects	• Hybrid Transmission • Control • Control Systems / Units • Power Transmission • Gear Box • Sensors
VG95234 (Where applicable)	Derived from VG95234 / SAE-AS50151 (formerly MIL- DTL-5015)	MIL-DTL 26482 Series 1, VG 95328	-	-	SAE J2030 USCar	VG95234 / MIL-DTL-5015 (where applicable)
acc. VG95234	acc. VG95234	acc. VG95328	-	-	-	EN 45545-2 NFPA 130
1 to 65	1 to 48	2 to 61	2, 3	4	2, 4	1 to 159
50 V AC - 75 V DC (acc. Low Voltage Directive)	50 V AC - 75 V DC (acc. Low Voltage Directive)	50 V DC	48 V DC	16 V DC	300 V AC	4200 V DC - 3000 V AC
4500 V AC	4500 V AC	2300 V AC	1000 V DC	1000 V AC	1000 V AC	7000 V AC
245 A	245 A	22 A	13 A	5 A (at 70°C)	5 A	350 A
Yes	Yes	Yes	No	No	No	Yes
26 to 0	26 to 0	24 to 16	18 to 16	20 to 18	20 to 16	26 to 4/0
0,14 - 50	0,14 - 50	0,2 - 2,0	0,75 - 1,5	0,4 - 0,75	0,50 - 1,5	0,15 - 120
Gold / Silver	Silver	Gold	Silver	Tin	Tin / Gold	Gold / Silver
Yes	Yes	Yes	Yes	No	Yes	Yes
No	No	No	No	Yes	Yes	No
Yes	Yes	Yes	No	No	No	Yes
Yes	Yes	Yes	No	No	Yes	Yes
No	No	No	No	No	No	Yes
No	No	No	No	No	No	See CIR M12 family
No	No	No	No	No	No	See Fiber Optic family
Yes	Yes	No	No	No	No	Yes
500	500	500	25	25	25	2000
50	50	50	-	-	100	50
200 m/s ² at 10-2000 Hz	200 m/s ² at 10-2000 Hz	200 m/s ² at 10-2000 Hz	100 m/s ² at 10-500 Hz	-	100 m/s ² at 10-2000 Hz	200 m/s ² at 10-2000 Hz
Yes	Yes	Yes	Yes	No	Yes	Yes
Bayonet	Bayonet	Bayonet	Push-On	Snap-in	Clip-Lock	Bayonet
Flange, Jamnut, others	Flange, Jamnut, others	Flange, Jamnut, others	Inline	Inline	Inline, Panel Mount	Flange, Jamnut, others
-55°C to 125°C (-67°F to 257°F) optional 200°C (392°F)	-55°C to 125°C (-67°F to 257°F)	-55°C to 125°C (-67°F to 257°F)	-40°C to 125°C (-40°F to 257°F)	-40°C to 105°C (-40°F to 221°F)	-40°C to 150°C (-40°F to 302°F)	-40°C to 125°C (-40°F to 257°F)
IP67 / IP68 (1 bar/16h) / IP69k	CA-COM Bayonet IP67 / IP68 (1 bar / 16h) CA-COM Threaded IP65	IP68 (0,2 bar / 48h)	IP69K	IP50	IP68 (0,1bar / 4h)	IP67
Yes	Yes	Yes	Yes	No	Yes	Yes
Yes	Yes	Yes	Yes	No	Yes	Yes
Aluminium	Aluminium, Zinc, Nickel Plated	Aluminium	Thermoplastic	Thermoplastic	Thermoplastic	Aluminium, Stainless Steel, Marine Bronze
CR, FKM	CR	CR	No	PBT	No	Flame Retardant Rubber, Viton, Silicone Rubber
Yes	Yes	Yes	No	No	No	Yes
Yes	No	Yes	No	No	No	Yes
Yes	No	No	No	No	No	No
Yes	No	Yes	No	No	No	Yes
Yes	No	Yes	No	No	No	Yes
No	No	No	No	No	No	Yes
No	No	No	No	No	No	Yes

cannon veam		CUSTOM PRODUCTS									
		MODULAR APD INTERFACE	APD INTERFACE	GEAR BOX CONNECTOR	APD 7-WAY WITH GROMMET	VPT	SENSOR CONNECTOR	VA900			
											
APPLICATIONS		• Cabin Chassis Interface • Control Systems / Units	• Cabin Chassis Interface • Control Systems / Units	• Power Transmission • Gear box	• Engine	• Engine	• Sensors	• Hybrid Traction Systems			
GENERAL	Standards / Connector Specifications			Similar to ISO 15170	ISO15170	MIL-DTL 26482 Series 1, VG 95328 (where applicable)	Similar to ISO 15170	VG95234 (where applicable)			
	Fire & Smoke standards			Material UL-listed	-	-	-	EN 45545-2 NF F 16-101/102			
	Number of Circuits			2, 4, 6	7	10 to 12	4	1			
ELECTRICAL	Max. Operating Voltage			48 V DC	48 V DC	50 V DC	48 V DC	1800 V DC			
	Max. Dielectric Withstanding Voltage			1000 V AC	1000 V AC	2300 V AC	1000 V AC	5000 V AC			
	Max. Current Rating			30 A	13 A	22 A	Consult factory	750 A			
CONTACTS	EMI/RFI shielding	Used with APD Connector Series Snap-in version. Customized solutions on request. For further information please consult factory.	Used with APD Connector Series Snap-in version.	No	No	Consult factory	No	Yes			
	Wire range AWG			12	26 to 12	24 to 16	12	4/0			
	Wire Range mm²			0,35 - 4,0	0,14 - 2,5	0,2 - 2,0	0,35 - 4,0	95 - 240			
	Contact plating			Tin / Silver / Gold	Tin / Gold	Gold	Tin / Silver / Gold	Silver			
	Crimp, machined			Yes	Yes	Yes	Yes	Yes			
	Crimp, stamped			Yes	Yes	No	Yes	No			
	Solder			Consult factory	No	No	Consult factory	No			
	PCB			Consult factory	No	No	Consult factory	No			
	Coax			No	No	No	No	No			
	Ethernet Interface			No	No	No	No	No			
	Fiber Optic Interface			No	No	No	No	No			
	Power and Signal Layouts			Consult factory	No	Yes	No	No			
	MECHANICAL			Mating cycles (max.)			30	200	500	30	500
				Max. shock resistance (g's)			50	50	50	50	50
				Max. vibration resistance			-	100 m/s² at 10-500 Hz	200 m/s² at 10-2000 Hz	-	200 m/s² at 10-2000 Hz
Mechanical coding		Yes	Yes	Yes			Yes	Yes			
Type of coupling		Bayonet	Bayonet	Bayonet			Bayonet	Bayonet			
Configurations / Mounting options		Jamnut	Jamnut	Flange, others			Jamnut	Flange			
ENVIRONMENTAL	Temperature range			-40°C to 105°C (-40°F to 221°F)	-40°C to 125°C (-40°F to 257°F)	-55°C to 125°C (-67°F to 257°F)	-40°C to 125°C (-40°F to 257°F)	-40°C to 100°C (-40°F to 212°F)			
	IP rating mated			IP69K	up to IP67	IP67	IP69K	IP67			
	Individual wire sealing			Yes	No	No	Yes	No			
	Cable jacket sealing			Yes	Yes	Yes	Yes	Yes			
	Shell material			Thermoplastic	Thermoplastic	Aluminium	Thermoplastic	Aluminium, Stainless Steel, Marine Bronze			
	Insert material			Thermoplastic	Thermoplastic	FPM	Thermoplastic	Thermoplastic			
SHELL PLATINGS	RoHS Electroless Nickel - Conductive (<48h)			No	No	No	No	No			
	RoHS Zinc Cobalt black - Conductive - (200h)			No	No	Yes	No	Yes			
	RoHS Zinc Cobalt black, VG approved, Conductive (48h)			No	No	No	No	No			
	Cadmium Olive drab - Conductive (500h)			No	No	No	No	No			
	RoHS Zinc Cobalt green - Conductive (200h)			No	No	No	No	No			
	RoHS Zinc Nickel blue - Conductive (500h)			No	No	Yes	No	Yes			
	Black Epoxyurethane varnish - Not conductive (500h)			No	No	Yes	No	Yes			
	Other platings: Consult factory			No	No	Yes	No	Yes			

We Connect

When it matters most

For more than a century, ITT has developed innovative connector solutions for the world's harshest environments. With facilities in the United States, Germany, Italy, Mexico, China and Japan, each with its unique strengths, we offer our customers interconnect solutions that are truly Engineered for Life.

In addition to this truly global footprint, we offer highly specialized segmented industry expertise. We have a proven track record as an industry leader in harsh-environment vehicle applications. This has equipped us with the knowledge needed to continue to produce extremely advanced, resilient and reliable connectors for our customers' most challenging applications.

Global Interconnect Solutions for the Heavy and Off-Road Vehicle Industry.

The ITT Cannon and Veam difference

- Global capabilities & local support
- Proven application expertise
- A century of interconnect leadership
- A committed innovator & business partner

cannon
veam

About ITT

ITT is a diversified leading manufacturer of highly engineered critical components and customized technology solutions for the transportation, industrial, and energy markets. Building on its heritage of innovation, ITT partners with its customers to deliver enduring solutions to the key industries that underpin our modern way of life. ITT is headquartered in Stamford, Connecticut, with employees in more than 35 countries and sales in approx. 125 countries. For more information visit itt.com.



Connect with your ITT Cannon and Veam representative today or visit us at ittcannon.com

Connect with the experts

ITT Cannon and Veam brands are world leaders in the design and manufacture of highly engineered interconnect solutions for the harshest of environments.



Why ITT

ITT is a focused multi-industrial company that designs and manufactures highly engineered critical components and customized technology solutions. ITT's Cannon brand is a leading global manufacturer of connector products serving international customers in aerospace, defense, medical, industrial and transportation end markets. ITT's Connector business, which also includes the Veam and BIW Connector Systems brand, manufactures and supplies a variety of connectors and interconnects that make it possible to transfer data, signal and power in an increasingly connected world.

Connect with your ITT Cannon representative today or visit us at ittcannon.com

Follow us 

CHINA - Shenzhen City +86.755.2726.7888	GERMANY - Weinstadt +49.7151.699.0	ITALY - Lainate +39.02938721	KOREA +82.2.702.7111	SHANGHAI + 86.21.2231.2222	UK - Basingstoke +44.1256.347400
FRANCE +33.1.60.04.93.93	HONG KONG +852.2732.2720	JAPAN - Kanagawa +81.462.57.2010	MEXICO - Nogales +52.631.3110050	SINGAPORE +65 66974205	USA - Irvine, CA +1.800.854.3028