



We make green mobility smarter

Infineon automotive PSoC overview


Q2 2024

ATV MC SBS



Infineon Microcontroller – most scalable portfolio

Successfully covering the entire range of automotive applications



PSoC™: One-stop-shop for a range of automotive HMI & smart sensor applications



Door handle and foot-kick detection



**Buttons/sliders
Force detection/haptics**



Interior Lighting



Touchpads



Touchscreens



Segment LCD cluster



Capacitive navigation



Occupant detection



Hands-on detection



Biometrics & Navigation



PTC Heater



Level Sensing



Intelligent Battery Sensors



Li Ion Battery Management Systems



Legend

HMI

Beyond HMI

HMI = Human Machine Interface

Automotive PSoC microcontroller roadmap

Precision Analog	High Voltage	BMS + 			PSoC next gen BMS family ASIL D
		BMS 	PSoC 4 HVPA-144k 12V supply (42V max), 24-48 MHz Cortex M0+, ASIL C 144kB Flash, embedded LIN-SBC (12V-LDO & PHY) 16/20-bit ΔΣ ADC (Lead acid focus)		PSoC 4 HVPA-SPM Smart Battery Pack & Shunt Monitor (Li ion battery focus)
HMI & Smart Sensing	3-5V supply	Capsense 	PSoC 4 HVMS family 12V supply (42V max), 24-48 MHz Cortex M0+, 32-128kB Flash, embedded LIN-SBC (12V-LDO & PHY)		
			PSoC 4xxx family 3-5V supply, 24-48 MHz Cortex M0 / M0+, 16-384kB Flash, Optional Op-Amps, comparators, CAN/CAN-FD, USB, Crypto		
HMI	3-5V supply	Multitouch 	PSoC Multitouch TSG6, 6L, 6XL 8.5" – 15" touchscreens	PSoC Multitouch TSG7, 7L, 7XL 12" – 15" touchscreens Multichip-support for >15"	PSoC Multitouch TSG8 OLED, Up to 24" touchscreens (55" with multichip-support)
		Fingerprint 	PSoC Fingerprint FGP 1		
			Sampling or available today		In development

PSoC™ - One stop shop for Automotive HMI & Smart Sensors

PSoC™ Key Features

- › **Low Power** ARM® Cortex® Based
- › Robust & Reliable CAPSENSE™, Inductive Sense & Multi-Sense Converter
- › “Edge-Connectivity” through **LIN, CXPI, CAN FD, iso-UART**, options with integrated **LIN-SBC-functionality**
- › Safety: ISO 26262 up to **ASIL B (SEooC) / ASIL C (App-specific)**
- › Security: **ISO 21434-ready** - process compliance and partial (“off the shelf”) product support
- › **Upcoming:**
 - › Extension of the BMS portfolio to higher voltages & with increased safety
 - › Support for Ultra-Large touchscreens and **OLED**
 - › Full **ISO21434** security support (“out off context”, for devices starting development after ISO-release date)

Smart Sensing


HMI

PSoC™ next gen	<ul style="list-style-type: none"> – Next gen (ASIL D) 	<ul style="list-style-type: none"> • Please contact Infineon representative
PSoC™ 4 HVPA	<ul style="list-style-type: none"> – High Voltage Precision Analog MCUs, ARM® M0+, 64KB – 144KB Flash – 16/20-bit ΔΣ ADC for precise Current and Voltage measurement, 12V LDO, LIN PHY, ASIL-C compliant 	<ul style="list-style-type: none"> • LV Battery management (12V Lead acid, ASIL C) • HV Battery and Pack & Shunt Monitoring (Li-ion batteries)
PSoC™ 4 HVMS	<ul style="list-style-type: none"> – High Voltage Mixed Signal MCUs, ARM® M0+, 32KB – 128KB Flash – Programmable Analog, Robust HMI, 12V LDO, LIN PHY, ASIL-B compliant 	<ul style="list-style-type: none"> • Smart Sensing Applications such as Steering Wheel (HOD, buttons) or Liquid Level Sensing actuators (eg. PTC Heater, int/ext. lighting)
PSoC™ 4 S	<ul style="list-style-type: none"> – Scalable General Purpose MCU platform, ARM M0+ – 16KB – 384KB Flash – Programmable Analog & Robust HMI – CAPSENSE™, MSC, OpAmps (PGA, TIA), Comparators 	<ul style="list-style-type: none"> • HMI applications such as Capacitive/Inductive buttons, sliders, touchpads • Smart sensor applications such as hands off-, or passenger occupancy detection (HOD/POD)
PSoC™ Multitouch	<ul style="list-style-type: none"> – Scalable MCU-based Touch sensing platform – Supporting display-sizes up to 15” (24”) – Preprogrammed by Infineon-firmware – Detecting up to 3 fingers simultaneously 	<ul style="list-style-type: none"> • Multitouch - touchpads, touchscreens (LCD/OLED) • touch integrated cockpit • touch-enabled rear view mirror etc.
PSoC™ Fingerprint	<ul style="list-style-type: none"> – Cost optimized substrate based architecture – MCU-based, preprogrammed & factory tuned firmware – Partnering with Precise™ Biometrics for embedded matching algorithm support 	<ul style="list-style-type: none"> • Fingerprint sensors used for authentication e.g. for in-car payments, biometric indicators, unlocking glove-box, etc.

Scalable Human Machine Interface Roadmap

Configurable Sense

Programmable Sense & MCU



PSoC 4 scalable family

One stop shop for Driver Information, POS systems and HMI




Driver Information / HMI requirements

HMI (Capacitive/Inductive buttons, sliders & touchpads)

- High accuracy CapSense or Multi Sense converter IPs enable high performance capacitive and inductive sensing on Human-Machine interfaces such as buttons, sliders, touchpads.
- Targeted for HVAC controls, infotainment buttons, sliders and touchpads, door handles, POD, HOD, steering wheel buttons, sunroof control, foot kick/trunk opener
- ASIL-B ready, integrated CRYPTO hardware accelerator

Multitouch-Touch & Fingerprint Controllers

- Wide portfolio to support touch screens from 8" to 35", trackpads, slider and buttons
- Gen7XL controller supports advanced features: Hover, Force Sensing, Haptic, Acoustic, and wet-finger tracking
- Gen8 device to support OLED display



...and our Automotive microcontroller offering

PSoC 4100S Max 48MHz, 384KB/32KB, MSC,CRYPTO, CAN-FD
PSoC 4100L/4200L 48MHz, 256KB/32KB, 2x CAN,UDB,2xCSD,USB2.0
PSoC 4700S Plus 48MHz, 128KB/16KB, Inductive Sense
PSoC 4xxxS Plus 48MHz, 128KB/16KB, CAN, CapSense (CSDv2)
PSoC 4xxxM/ 48MHz, 128KB/16KB, UDB, 2xCAN, 2xCSD
CYAT8168X 61-88 I/O, 120-Hz RR
CYAT817 61-103 I/O, 120-Hz RR
CYAT817LS 72 I/O, 100-Hz RR, MCU
CYAT818xx OLED
CYFP1002xxxx Fingerprint Sensor

Automotive Interior HMI

- ✓ Touch-sensing buttons/sliders/touchpads with very thick overlays (>5mm) can be supported by CAPSENSE
- ✓ High refresh rates to provide intuitive / responsive HMI
- ✓ Support force-sensing with CAPSENSE (capacitive) or Inductive Sensing
- ✓ Metal touch surfaces can be enabled by Inductive Sense
- ✓ Drive LEDs brightness / effects with PWMs
- ✓ Scalable solution from 16KB/2KB (Flash/SRAM) up to 384KB/32KB

Multitouch Touch Controllers & Fingerprint

- ✓ High performance Multitouch technology supporting self and mutual capacitance sensing with high refresh rate (RR)
- ✓ Small footprint packages in TQFP / QFN
- ✓ Thick glove (5mm) and water rejection support
- ✓ Extensive EMI/EMC testing completed to CISPR-25 standard
- ✓ Automotive quality software with Auto SPICE level-2 and safety features to enable configuration and tuning
- ✓ Fingerprint: Excellent biometric performance: < 1% FRR at FAR 1:50K,360° finger placement,8.0x 8.0 mm sensing area,340 DPI

Scalable PSoC™ 4 Product lineup for General Purpose & BMS Sensing

	Smart Sensors, HMI and general-purpose application focus	BMS application focus																		
ASIL D compliant SEOC	<p>PSOC™ Safe Next gen*</p>	<p>PSOC™ Safe BMS Next gen*</p>																		
ISO 26262 compliant ASIL-C	<table border="1"> <tr> <td>HVAC</td> <td>Footkick</td> </tr> <tr> <td>HMI/Infotainment Buttons & Slider</td> <td>Hands-on-Detection (HOD)</td> </tr> <tr> <td>Interior Lighting</td> <td>Passenger Occupant Detection (POD)</td> </tr> <tr> <td>Door Handle</td> <td>Liquid Level & Quality Sensing</td> </tr> <tr> <td>Sunroof Control</td> <td>Wireless Charging</td> </tr> <tr> <td>Steering Wheel Buttons</td> <td>PTC Heater</td> </tr> <tr> <td>Touchpads</td> <td></td> </tr> </table>	HVAC	Footkick	HMI/Infotainment Buttons & Slider	Hands-on-Detection (HOD)	Interior Lighting	Passenger Occupant Detection (POD)	Door Handle	Liquid Level & Quality Sensing	Sunroof Control	Wireless Charging	Steering Wheel Buttons	PTC Heater	Touchpads		<table border="1"> <tr> <td> PSoC™ 4 HVPA-SPM Smart Pack Monitor, 16/20-bit ΔΣ VIO, CRYPTO, CAN FD, iso UART, ASIL C </td> <td>HV Li ion Battery Pack & Shunt Monitors</td> </tr> <tr> <td> PSoC™ 4 HVPA-144K 128KB/8KB, 16/20-bit ΔΣ, LIN/CXPI, ASIL C </td> <td>12V lead-acid Battery Pack & Shunt monitor</td> </tr> </table>	PSoC™ 4 HVPA-SPM Smart Pack Monitor, 16/20-bit ΔΣ VIO, CRYPTO, CAN FD, iso UART, ASIL C	HV Li ion Battery Pack & Shunt Monitors	PSoC™ 4 HVPA-144K 128KB/8KB, 16/20-bit ΔΣ, LIN/CXPI, ASIL C	12V lead-acid Battery Pack & Shunt monitor
HVAC	Footkick																			
HMI/Infotainment Buttons & Slider	Hands-on-Detection (HOD)																			
Interior Lighting	Passenger Occupant Detection (POD)																			
Door Handle	Liquid Level & Quality Sensing																			
Sunroof Control	Wireless Charging																			
Steering Wheel Buttons	PTC Heater																			
Touchpads																				
PSoC™ 4 HVPA-SPM Smart Pack Monitor, 16/20-bit ΔΣ VIO, CRYPTO, CAN FD, iso UART, ASIL C	HV Li ion Battery Pack & Shunt Monitors																			
PSoC™ 4 HVPA-144K 128KB/8KB, 16/20-bit ΔΣ, LIN/CXPI, ASIL C	12V lead-acid Battery Pack & Shunt monitor																			
ISO 26262 compliant ASIL-B	<table border="1"> <tr> <td> PSoC™ 4 HVMS-128K 128KB/16KB, Multi-sense/CAPSENSE, LIN-SBC, CXPI </td> </tr> <tr> <td> PSoC™ 4 HVMS-64K 64KB/8KB, Multi-Sense/CAPSENSE, LIN-SBC, CXPI </td> </tr> </table>	PSoC™ 4 HVMS-128K 128KB/16KB, Multi-sense/CAPSENSE, LIN-SBC, CXPI	PSoC™ 4 HVMS-64K 64KB/8KB, Multi-Sense/CAPSENSE, LIN-SBC, CXPI																	
PSoC™ 4 HVMS-128K 128KB/16KB, Multi-sense/CAPSENSE, LIN-SBC, CXPI																				
PSoC™ 4 HVMS-64K 64KB/8KB, Multi-Sense/CAPSENSE, LIN-SBC, CXPI																				
ISO 26262 Ready Entry level MCU with CAPSENSE™	<table border="1"> <tr> <td> PSoC™ 4100L/4200L 48 MHz, 256KB/32KB UDB, 2x CAN, USB 2.0 </td> <td> PSoC™ 4100S Max 48 MHz, 384KB/32KB Multi-Sense, CRYPTO LCD, CAN FD </td> <td></td> </tr> <tr> <td> PSoC™ 4100M/4200M 48 MHz, 256KB/32KB UDB, 2x CAN, USB 2.0 </td> <td> PSoC™ 4100S Plus 48 MHz, 128KB/16KB CAN </td> <td> PSoC™ 4700S Plus 48 MHz, 128KB/16KB Inductive Sense </td> </tr> <tr> <td></td> <td> PSoC™ 4100S 48 MHz, 64KB/8KB </td> <td></td> </tr> <tr> <td> PSoC™ 4100/4200 48 MHz, 32KB/4KB, UDB </td> <td> PSoC™ 4000S 48 MHz, 32KB/4KB </td> <td></td> </tr> <tr> <td> PSoC™ 4000 16 MHz, 16KB/2KB </td> <td></td> <td></td> </tr> </table>	PSoC™ 4100L/4200L 48 MHz, 256KB/32KB UDB, 2x CAN, USB 2.0	PSoC™ 4100S Max 48 MHz, 384KB/32KB Multi-Sense, CRYPTO LCD, CAN FD		PSoC™ 4100M/4200M 48 MHz, 256KB/32KB UDB, 2x CAN, USB 2.0	PSoC™ 4100S Plus 48 MHz, 128KB/16KB CAN	PSoC™ 4700S Plus 48 MHz, 128KB/16KB Inductive Sense		PSoC™ 4100S 48 MHz, 64KB/8KB		PSoC™ 4100/4200 48 MHz, 32KB/4KB, UDB	PSoC™ 4000S 48 MHz, 32KB/4KB		PSoC™ 4000 16 MHz, 16KB/2KB			<div style="border: 1px dashed orange; padding: 5px;"> <p>Legend</p> <p>* Subject to feasibility & market study</p> <p>Arm Cortex M0/M0+ Frequency, Flash/SRAM</p> <p>BLE = Bluetooth Low Energy</p> <p>BMS = Battery Management Systems</p> <p>HMI = Human Machine Interface</p> <p>OCD = Overcurrent Detection</p> <p>SBC = System Basis Chip</p> <p>UDB = Universal Digital Block</p> <p>CMC = Cell Monitor Controller (inc. balancer)</p> <p>VIO = Voltage / Current / Over-Current</p> </div>			
PSoC™ 4100L/4200L 48 MHz, 256KB/32KB UDB, 2x CAN, USB 2.0	PSoC™ 4100S Max 48 MHz, 384KB/32KB Multi-Sense, CRYPTO LCD, CAN FD																			
PSoC™ 4100M/4200M 48 MHz, 256KB/32KB UDB, 2x CAN, USB 2.0	PSoC™ 4100S Plus 48 MHz, 128KB/16KB CAN	PSoC™ 4700S Plus 48 MHz, 128KB/16KB Inductive Sense																		
	PSoC™ 4100S 48 MHz, 64KB/8KB																			
PSoC™ 4100/4200 48 MHz, 32KB/4KB, UDB	PSoC™ 4000S 48 MHz, 32KB/4KB																			
PSoC™ 4000 16 MHz, 16KB/2KB																				
	<p>PSoC™ 4 (5.5V, Cortex M0/M0+, 24/48 MHz)</p>	<p>PSoC™ 4 HV (42V, Cortex M0+, 24/48MHz) Mixed signal MCUs with 12V LDO and transceiver (LIN, CXPI or iso-UART)</p>																		
		<p>PSOC™ Safe (100V, dual core lockstep)</p>																		

PSoC™ 4 High Voltage - enabling Smart Sensing for future mobility

Enabling safe smart sensing systems




Battery management & Smart sensing requirements

Battery management system (Cell-balancing, Current-Sensing)

- High precision analog performance for longer range driving and better battery life
- Functional safety support up to ASIL-D ISO 26262
- Scalable and comprehensive solution supporting the latest xEV trend

Smart sensing (POD, HOD, Liquid level sensing, PTC heater ctrl)

- Multiple sensing interface support with robust operation
- Small footprint and cost-effective integrated solution with newest communication stacks
- Software solution for easy to design and quick market launch



...and our Automotive microcontroller offering

PSoC 4 HVPA-SPM
48MHz 128kB

PSoC 4 HVPA-144k
48MHz 128kB

PSoC 4 HVMS-64K
48MHz 64kB

PSoC 4 HVMS-128K
48MHz 128kB

Battery management system


- ✓ Integrated PSoC-solution with programmable MCU & high precision analog for current and voltage monitoring
- ✓ Scalable high voltage technology from 12V battery to HV battery
- ✓ NVM for increased flexibility, data-preconditioning, compression and storage (eg. for calibration, SOH for 2nd life)
- ✓ Synchronous cell voltage and current measurement with integrated transceivers (isoUART, BLE)
- ✓ Integrated overcurrent detection and drivers/triggers for battery disconnect switch
- ✓ Safety components supporting up to ISO 26262 ASIL-D
- ✓ Automotive quality and safety supported software

Smart sensing

- ✓ High performance analog (12b SAR ADC @1Msps), integrated OpAmps, comparators, CAPSENSE, Multi-Sense Converter
- ✓ Serial communication block supporting I2C, SPI, UART, LIN, CAN, CXPI
- ✓ Small footprint packages in wetttable flank QFN
- ✓ 12V battery directly operation with integrated high voltage subsystem (LDO, LIN PHY)
- ✓ Automotive quality and safety supported software

PSoC 4 HV: Functional Safety: A holistic system-level approach

- ISO 26262 Safety-Element-Out-of-Context product
- Supports safety critical applications:
 - HVMS & HVPA up to ASIL-B (SEOOc)
 - HVPA up to ASIL C for some BMS-specific functions
- Software is developed according to ISO 26262
- Supplemented by safety documents



PSoC 4 HV is ISO26262 compliant (supported by safety hardware, software, and collaterals)

PSoC 4xxx is ISO26262 ready (supported by safety-collateral like HW-safety manual, FMEDA allowing customers safety-assessment)

ISO 21434 Security Approach for automotive PSoC

Process Compliance:

- ISO/SAE 21434 was published end 2021
- Infineon received certificate for **Process Compliance** for Cyber Security Management System (CSMS) in 2022



Hiermit wird bescheinigt, dass die Firma / This certifies that the company

Infineon Technologies AG
 Am Campeon 1-15
 85579 Neubiberg
 Deutschland

ein Managementsystem konform zu den Anforderungen der ISO/SAE 21434 betreibt und innerhalb der Laufzeit des Zertifikats von 3 Jahren auf Konformität überwacht wird.
 operates a management system conforming to the requirements of ISO / SAE 21434 and within the the duration of the certificate of 3 years is monitored for conformity.

Road vehicles – Cybersecurity engineering
 gemäß/ according to ISO/SAE 21434:2021-08

Geltungsbereich:
 Scope of application: **CSMS related to CS Policy (Z8F80326733) and cybersecurity aspects of System Development Handbook (SDHB Rev. 6.16.00)**

Geprüft nach:
 Compliant in accordance with: **ISO/SAE 21434:2021-08**

Registrier-Nr. / Registration No. 44 135 222295001
 Prüferbericht Nr. / Test Report No. TNM_8120136144-D07-R_V1.0
 Aktenzeichen / File reference 8003046865_8003051377

Gültigkeit / Validity
 von / from 2022-10-25
 bis / until 2025-10-24


 Zertifizierungsstelle
 der TÜV NORD CERT GmbH

Essen, 2022-10-25

Product Compliance:

- Most automotive PSoC devices were starting their development before ISO/SAE 21434 was published:
 - Impossible to claim full ISO21434 (“out of context”) compliance
 - But Infineon will support partial (“off-the-shelf”) compliance for automotive PSoC – called “ISO21434 ready”
- New PSoC devices that started development after ISO/SAE 21434 was published:
 - Infineon targeting full ISO21434 (“Out-of-context”) compliance

Cyber Security Management System (CSMS)

ISO 21434 based Work Packages for CSMS	TC3x, T2G PSoC 4xxx, PSoC 4 HV	TC4x PSoC BMS next Gen
ISO 21434 Security claim	ISO21434 ready	SO21434 compliant
Cybersecurity Management 5. Organizational Cybersecurity Management 6. Project Dependent Cybersecurity Management		
Continuous Cybersecurity Activities 8.3. Cybersecurity Monitoring 8.4. Cybersecurity Event Evaluation 8.5. Vulnerability Analysis		
Risk Assessment Methods 15.3 - 15.9 Asset, Threat Scenario identification, impact rating, attack path analysis, attack feasibility rating, risk determination, and risk treatment decision	N/A	
Concept phase 9.4. Cybersecurity Goals 9.5. Cybersecurity Concept	N/A	
Product development Phase 10.4.1. Design 10.4.2. Integration and Verification	N/A	
Post-development Phase 12. Production 13.3. Cybersecurity Incident Response 13.4. Updates	Cyber incident response only 	

This is due to the fact that ISO21434 was not yet standardized during product development cycle

Automotive PSoC microcontroller roadmap

				Professional / payed	Demo / free
Precision Analog	High Voltage	BMS + 	PSoC next Gen BMS family	<ul style="list-style-type: none"> AutoPDL & SafeTlib 2.0 (ASIL D) 	<ul style="list-style-type: none"> tbd
		BMS 	PSoC 4 HVPA	<ul style="list-style-type: none"> AutoPDL & SafeTlib 1.0 (ASIL B) 	<ul style="list-style-type: none"> Q3'25: MTB-PDL (ModusToolbox)
HMI & Smart Sensing	3-5V supply	Capsense 	PSoC 4 HVMS family	<ul style="list-style-type: none"> AutoPDL & SafeTlib 1.0 (ASIL B) CapSense Middleware for AutoPDL 	<ul style="list-style-type: none"> Jan'25: MTB-PDL (ModusToolbox) Q4'24: CapSense Middleware for MTB-PDL
			PSoC 4xxx family	<ul style="list-style-type: none"> N/A 	<ul style="list-style-type: none"> MTB-PDL (ModusToolbox) CapSense Middleware for MTB-PDL
HMI	3-5V supply	Multitouch 	PSoC Multitouch TSG 6, 7, 8	<ul style="list-style-type: none"> PSoC Multitouch products come preprogrammed with Infineon Application Firmware On host side they are supported by TTDA driver (Linux & Android environment, Free) TSG7L as well comes preprogrammed, also supported in uVision Keil IDE (need IDE license) 	
		Fingerprint 	PSoC Fingerprint FPG1	<ul style="list-style-type: none"> PSoC Fingerprint products come preprogrammed with Infineon Application Firmware Host side software supported by Infineon Preferred Partner Precise Biometrics(need License) 	

Automotive quality software support for PSoC HV

- Software packages offered by Infineon for PSoC 4 HV devices are developed as per standard Automotive software development process
- The software is ASPICE qualified (MISRA 2012 AMD1, CERT C) and ISO 26262 compliant.

Peripheral driver library (PDL)

- › **Complete package of low-level drivers** comprising of analog, digital and communication components
- › **Enables shorter time to market** by reducing the customer development time
- › **Functional Safety (ASIL-B) compliant software** built as per ASPICE standards, using FuSa compliant IAR compiler with safety features based on SEooC

CAPSENSE middleware library

- › **Middleware to implement CAPSENSE functionality** such as basic control, filter, data processing and sensing for interface widgets etc...
- › **Configurable** various parameters such as number of widgets, capacitance settings, noise threshold settings etc. using a simple GUI based CAPSENSE configuration tool
- › **Enables shorter time to market** by reducing the customer development time

SafeTlib

- › **Integrates critical safety tests** which are mandatory as per the hardware safety manual to achieve ASIL-B compliance
- › **Enables shorter time to market** by reducing the customer development time
- › **Enables safe operation of the chip** during start-up and runtime

