

M1227HCT-SMA-GN

L1/L2 GPS GLONASS ACTIVE ANTENNA
Part #: 100-00105-01

Description

The M1227HCT-SMA-GN is a high performance antenna designed for the L1/L2 GPS and GLONASS bands for GNSS satellite applications. The antenna is built on proprietary Maxtena Helicore® technology. This technology provides exceptional pattern control, polarization purity and high efficiency in a very compact form factor. The M1227HCT-SMA-GN is rated IP-67 when mounted for added protection. The antenna is designed for applications requiring greater accuracy than what L1 only antennas can provide.

Electrical Specification

Parameter	Specification	
Frequency Range	1217-1250 MHz (L2)	1565-1610 MHz (L1)
Total peak gain	30 dBic	28 dBic
Axial Ratio	≤ 1 dB (0.5 dB typical)	≤ 1 dB (0.5 dB typical)
VSWR	<1.5	<1.5
Passive peak gain	2 dBic @ 1227 MHz	2 dBic @ 1575 MHz
Total gain	30 dBic @ 1227 MHz	28 dBic @ 1575 MHz 28 dBic @ 1602 MHz
Out-of-band rejection	>50 dB	
Current drain	25 mA (typ)	
Voltage	3-12 V	
Noise figure	1.5 dB (typical)	
RF interference rating	50 V/m out of band	

Mechanical Specification

Parameter	Specification
Antenna Dimensions	Ø 18.5 × 135 mm
Operating Temperature	-30°C to + 85°C
Storage Temperature	-40°C to + 85°C
RF Connector	SMA male
Antenna Housing	PC/ABS
Cable	Stainless Steel With Black Coathing
Indicator O-Ring	Red Silicone
Weight	45 g
Environmental	IP67







Features

- Very low axial ratio
- IP-67 mounted
- Ultra lightweight - 45 grams
- Ground plane independent

Applications

- Precision navigation
- Precision timing
- Military & security
- Asset tracking
- Oil & gas industries
- Navigation devices
- Mining equipment
- LBS & M2M applications
- Handheld devices
- Law enforcement




Maxtena Inc.
 7361 Calhoun Place, Suite 102
 Rockville, MD 20855
 1-877-629-8362
 info@maxtena.com
 www.maxtena.com

NOTES:

- CONNECTOR: SMA MALE.
- MATERIAL:
 - ANTENNA HOUSING: PC/ABS BLACK PLASTIC;
 - CABLE: STAINLESS STEEL WITH BLACK COATING;
 - INDICATOR O-RING: RED SILICONE.
- OPERATIONAL TEMPERATURE: -30°C~+85°C.
- STORAGE TEMPERATURE: -40°C~+85°C.
- WATERPROOF GRADE: IP67.

DRAWING REVISION HISTORY			
REV	DESCRIPTION	DATE	BY
1	INITIAL RELEASE	2019-06-05	ZX
2	UPDATE TO THREADED VERSION	2021-10-11	ZX



UNLESS OTHERWISE SPECIFIED:		NAME	DATE	MAXTENA, INC	
DIMENSIONS ARE IN MM		DRAWN	ZX		
TOLERANCES:		CHECKED		TITLE:	
FRACTIONAL $\pm$		ENG APPR.	NPC		
ANGULAR: MACH $\pm .5^\circ$ BEND $\pm$		MFG APPR.		100-00105-01 ASSEMBLY, TOP, M1227HCT-SMA-GN	
ONE PLACE DECIMAL $\pm .5$		Q.A.			
TWO PLACE DECIMAL $\pm .20$		CAD MAINTAINED. CHANGES SHALL BE INCORPORATED BY THE DESIGN ACTIVITY.		SIZE	DWG. NO.
INTERPRET GEOMETRIC TOLERANCING PER:				B	117-00285-01
THIRD ANGLE PROJECTION				REV	
DO NOT SCALE DRAWING				2	
				CAGE CODE: 5KQH7	SCALE: NONE
				SHEET 1 OF 1	

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF MAXTENA, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF MAXTENA, INC IS PROHIBITED.