

Open Frame Fan Motors

Orion Fans' AC fan motors offer reliability and ease of use for compact designs

Orion Fans' line of Open Frame Motors includes AC fan motors ranging in size from 85mm-125mm, are available in either 115V or 230V, and range from 33W to 120W. They can be mated with impeller sizes from 154mm to 300mm as well as additional mounting brackets and grilles for added support and safety. The impellers options offer varying pitch angles and offer the ability to reverse the airflow to either intake or exhaust. The motors and impellers are protected from the elements via a die cast aluminum frame and carry an IP42 rating. They feature ball bearings for added flexibility when mounting. Standards compliance including UL, VDE, CE, REACH, and RoHS, makes these fans a safe and highly reliable solution for applications such as commercial refrigeration, ventilation, transportation, or in an industrial setting.

- Ball Bearings
- 115V or 230V
- AC Motors (Available in EC)
- Impeller Options for Intake or Exhaust Airflow Direction
- Brackets and Grilles Available