

*“Stay Connected” with*



HEYware Products


a PennEngineering® Company



## Heyco®-Tite Quick Nut

- Quick nut offers a fast installation.
- Simply push the quick nut onto the threaded stud and tighten half a turn with a wrench. To remove, unscrew with a wrench.
- Insertion force onto the stud is low, while extraction force is high.

THREAD SIZE A		PART NO.		DESCRIPTION	PART DIMENSIONS			
METRIC	IMPERIAL	BLACK	NATURAL		B Thickness in. mm	C Wrenching Flats in. mm		
M3	#4	11560B	11560	HQN M3	.17	4,2	.27	6,9
M4	#8	11561B	11561	HQN M4	.19	4,8	.31	7,9
M5	#10	11562B	11562	HQN M5	.23	5,8	.39	9,9
M6	1/4-20	11563B	11563	HQN M6	.27	6,9	.50	12,7



*Quick  
Specs*

Material

PA66 UL94 V-2

Temperature range

-40°F (-40°C) to 185°F (85°C)