






REVISIONS				
PART REV.	DWG. ISSUE	DATE	ECN NO.	ENGINEER
-	-	8/7/2025	UMI8907	P. ASHOK
SEE TABLE	A	12/04/2025	UMI9011	P. ASHOK
SEE TABLE	B	12/18/2025	UMI9024	P. ASHOK



PART NO.	ENG. PART NO. CLIPSLOT	REV.
234200041	CQMR2S01-M1M1-A2A3-Z	UNRELEASED
234200042	CQMR2S01-M1M1-A2A3-A	UNRELEASED
234200043	CQMR2S01-M1M1-A2A3-B	UNRELEASED
234200044	CQMR2S01-M1M1-A2A3-C	UNRELEASED
234200045	CQMR2S01-M1M1-A2A3-D	UNRELEASED
234200046	CQMR2S01-M1M3-A2A3-Z	A
234200047	CQMR2S01-M1M3-A2A3-A	UNRELEASED
234200048	CQMR2S01-M1M3-A2A3-B	UNRELEASED
234200049	CQMR2S01-M1M3-A2A3-C	UNRELEASED
234200050	CQMR2S01-M1M3-A2A3-D	UNRELEASED
234200051	CQMR2S01-M3M3-A2A3-Z	UNRELEASED
234200052	CQMR2S01-M3M3-A2A3-A	UNRELEASED
234200053	CQMR2S01-M3M3-A2A3-B	UNRELEASED
234200054	CQMR2S01-M3M3-A2A3-C	UNRELEASED
234200055	CQMR2S01-M3M3-A2A3-D	UNRELEASED

PART NO.	ENG. PART NO.	REV.
234200001	CQMR2S01-M1M1-A2-Z	UNRELEASED
234200002	CQMR2S01-M1M1-A2-A	UNRELEASED
234200003	CQMR2S01-M1M1-A2-B	UNRELEASED
234200004	CQMR2S01-M1M1-A2-C	UNRELEASED
234200005	CQMR2S01-M1M1-A2-D	UNRELEASED
234200006	CQMR2S01-M1M3-A2-Z	A
234200007	CQMR2S01-M1M3-A2-A	UNRELEASED
234200008	CQMR2S01-M1M3-A2-B	UNRELEASED
234200009	CQMR2S01-M1M3-A2-C	UNRELEASED
234200010	CQMR2S01-M1M3-A2-D	UNRELEASED
234200011	CQMR2S01-M3M3-A2-Z	UNRELEASED
234200012	CQMR2S01-M3M3-A2-A	UNRELEASED
234200013	CQMR2S01-M3M3-A2-B	UNRELEASED
234200014	CQMR2S01-M3M3-A2-C	UNRELEASED
234200015	CQMR2S01-M3M3-A2-D	UNRELEASED

5 RECEPTACLE LATCH-COLOR CODE	
Z-KEY	NATURAL
A-KEY	GRAY
B-KEY	BLUE
C-KEY	YELLOW
D-KEY	GREEN



5 RECEPTACLE AND PLUG-LATCH KEYING ARE DISCRETE. MATE ONLY WITH MATCHING KEY TYPE.

4 SEE SHEET 2 FOR EXPLODED VIEW AND KITTING INFORMATION

3. PERFORMANCE: TBD

2 MARKING: MARK MODULE POS "#1", WIM WO NO., DATE CODE IN THE LOCATION SHOWN

1 MATERIALS:

SHELL: 6061-T6 ALUMINUM PER AMS-QQ-A200/8, NICKEL PLATED PER AMS 2404

INSULATOR AND LATCH: LCP/PBT/PPA


HARDWARE: PASSIVATED STAINLESS STEEL

RING TERMINAL: COPPER ALLOY, FINISH: TIN PLATED


NOTES: UNLESS OTHERWISE SPECIFIED

QUALITY SYMBOLS CRITICAL  MAJOR  NO SYMBOL = MINOR DIMENSION	UNLESS SPECIFIED: ALL DIMENSIONS IN INCHES/[MM] GENERAL TOLERANCES: 3 PLACE ±.005 2 PLACE ±.01 ANGULAR ±2° ALL EXTERNAL SPECIFICATIONS REFERENCED ON THIS DRAWING SHALL BE THE LATEST REVISION IN EFFECT WINCHESTER INTERCONNECT MICRO LLC CAGE CODE 58967	SCALE 2:1	DWG SIZE B	 THIRD ANGLE PROJECTION	REVISE ON CAD ONLY	
		DRAWN BY AA	TITLE MODULUS (CliqMate) KIT CQMR2S01-MXXM-A2XX-X			
		DATE DRAWN 8/7/2025				
		MATERIAL 	ENG PROJECT # TR6404	 MICRO ORANGE, CA		
		CAD FILENAME SD-234200001.sldrw	PART NO. SEE TABLE	DRAWING NO. SD-234200001	SHEET NO. 1 of 2	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO WINCHESTER INTERCONNECT MICRO LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.						
						PART REV. SEE TABLE

CONFIGURATION SHOWN.
CQMR2S01-M1M3-A2A3-A
USCAR 7mm CLIPSLOT OPTION




EXPLODED VIEW
SCALE: N/A



KITTING INFORMATION	
ITEM #	PACKAGING INSTRUCTION
①, ②	ITEMS TO BE PRE-ASSEMBLED
③, ④, ⑤	ITEMS TO BE GROUPED PER BOM QTY, BAGGED & SHIPPED LOOSE
⑥, ⑦, ⑧, ⑨	ITEMS TO BE GROUPED PER BOM QTY, BAGGED & SHIPPED LOOSE

NOTES: SEE SHEET 1

QUALITY SYMBOLS CRITICAL MAJOR NO SYMBOL = MINOR DIMENSION	UNLESS SPECIFIED: ALL DIMENSIONS IN INCHES/[MM] GENERAL TOLERANCES: 3 PLACE ±.005 2 PLACE ±.01 ANGULAR ±2° WINCHESTER INTERCONNECT MICRO LLC CAGE CODE 58967	 THIRD ANGLE PROJECTION	REVISE ON CAD ONLY		
		ALL EXTERNAL SPECIFICATIONS REFERENCED ON THIS DRAWING SHALL BE THE LATEST REVISION IN EFFECT		SCALE 2:1	DWG SIZE B
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO WINCHESTER INTERCONNECT MICRO LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	ENG PROJECT # TR6404	 Winchester Interconnect MICRO ORANGE, CA	
			PART NO. SEE TABLE		
			CAD FILENAME SD-234200001.slddrw		SHEET NO. 2 OF 2
			DRAWING NO. SD-234200001		PART REV. SEE TABLE