

Product data sheet

Specifications



Remote Display, Modicon M171/ M172/M173, flush mounted optimized display

TM173DLED

Main

Range of product	Modicon M171/M172/M173
Product or component type	Display module
Display colour	Monochrome
Supply	External source

Complementary

Display type	2 x 7-segment LED
Number of key	4
Colour	White
[Us] rated supply voltage	24 V AC/DC
Marking	CE UL
Overvoltage category	II
Height	3.2 in (80.5 mm)
Width	1.4 in (34.5 mm)
Depth	1.4 in (34.6 mm)
Product weight	0.090 lb(US) (0.041 kg)

Environment

Standards	UL 94 EN 60730-1 EN 60730-2-9
Product certifications	UKCA UL CSA
Ambient air temperature for operation	-4...149 °F (-20...65 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
IP degree of protection	IP65
Pollution degree	2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 in (7.000 cm)

Package 1 Width	3.66 in (9.300 cm)
Package 1 Length	5.20 in (13.200 cm)
Package 1 Weight	3.986 oz (113.000 g)
Unit Type of Package 2	S01
Number of Units in Package 2	5
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	26.596 oz (754.000 g)



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	49
--	----

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
--	-----

Packaging without single use plastic	Yes
--------------------------------------	-----

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-----------------------------------	--

SCIP Number	Ae86ba94-4547-4a45-9448-245a31615fc7
-------------	--------------------------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

Use Again





Repack and remanufacture

Circularity Profile	End of Life Information
---------------------	---

Take-back	No
-----------	----

Dimensions Drawings


Dimensions



Mounting and Clearance

Mounting

mm
in



(1) Insert the device

(2) Secure it with the special brackets provided

(3) Front panel only (tested in accordance with EN 60529 with a steel sheet 2 mm (0.08 in.) thick $\pm 10\%$)

Image of product / Alternate images

Alternative



