

Bundling and Securing

Cable Ties


Standard Cable Ties

T50R and T50L Series in Colors

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Features and Benefits

- Engineered and manufactured for maximum performance and quality.
- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serration for a strong grip onto bundles.
- Easy application either manually or with a tensioning tool.
- Bent tail allows for simpler insertion.



PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width (W) in. (mm)	Material	Color	Pkg. Qty.
T50R6C2*	T50R	50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Blue	100
T50R6M4*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Blue	1000
T50R1C2*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Brown	100
T50R1M4*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Brown	1000
T50R8C2*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Gray	100
T50R8M4*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Gray	1000
T50R5C2*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Green	100
T50R5M4*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Green	1000
T50R3C2*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Orange	100
T50R3M4*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Orange	1000
T50R7C2*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Purple	100
T50R7M4*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Purple	1000
T50R2C2*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Red	100
T50R2M4*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Red	1000
T50R10C2*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	White	100
T50R10M4*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	White	1000
T50R4C2*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Yellow	100
T50R4M4*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66	Yellow	1000

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P. *This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.

Standard Cable Ties

T50L and T50R Series in Colors

PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width (W) in. (mm)	Material	Color	Pkg. Qty.
T50L6C2*	T50L	50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Blue	100
T50L6M4*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Blue	1000
T50L1C2*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Brown	100
T50L8C2*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Gray	100
T50L8M4*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Gray	1000
T50L5C2*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Green	100
T50L5M4*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Green	1000
T50L3C2*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Orange	100
T50L3M4*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Orange	1000
T50L2C2*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Red	100
T50L2M4*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Red	1000
T50L10C2*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	White	100
T50L10M4*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	White	1000
T50L4C2*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Yellow	100
T50L4M4*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66	Yellow	1000

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P. *This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.