



Twistable and flexible rectangular waveguide R84, with PDR/PDR 84 flanges. Length = 0.9m, core with environmental impact resistant molded rubber jacket. Hardware and gasket (for PDR/PBR flanges) included.

FEATURES / BENEFITS

Waveguide installation

- The flexible and twistable rectangular waveguide component eliminates installation difficulties
- It isolates vibration
- It provides simple aid to positioning of antennas



Technical features

STRUCTURE

Type of Rectangular Waveguide Component		TwistFlex
Waveguide Size IEC (EIA)		R84 (WR112)
Flange A		PDR84
Flange B		PDR84
Flange Finish		Brass un-plated
Package Quantity		1

ELECTRICAL SPECIFICATIONS

Frequency Range	GHz	7.05 - 10
Minimum Return Loss (max. VSWR)	dB (VSWR)	26.4 (1.10)
Attenuation	dB	0.27
Power rating	W	1500

MECHANICAL SPECIFICATIONS

Maximum Twist	degree/m (degree/ft)	140 (42.7)
Minimum Bending Radius E-Plane	mm (in)	75 (3)
Minimum Bending Radius H-Plane	mm (in)	150 (5.9)
Length	mm (in)	900 (35.4)

MATERIAL

Material		Core: Brass silver plated Jacket: Vulcanised Neoprene Rubber Flange: Brass
Color		Black

External Document Links

[AN 030707-8 Application note for RFS Technologies Twistflex](#)

Notes