



SELV (Except for M&L Type)



Note 13



Note 9



Type HL



Note 9



(except for 48V/blank type)



CB



EAC



CE



UKCA

■ Features

- Wide input range 100~305VAC(class I)
- Full power output at 75~100% constant power mode operation
- Metal case with IP67,suitable for outdoor application
- Surge protection with 6KV/4KV
- 3 in 1 dimming (Dim-to-off and Isolation design)
- Protection Functions: OLP/SCP/OVP/OTP
- Lifetime>50,000 hours and 5 years warranty

■ Applications

- Bay lighting
- Stage lighting
- Floodlight lighting
- Fishing lighting
- Horticulture lighting
- Stadium lighting
- LED strip lighting (ABV type)
- Agricultural lighting (ABV type)
- DMX power supply
- Type "HL" for use in class I , Division 2


■ GTIN CODE

 MW Search: <https://www.meanwell.com/serviceGTIN.aspx>

■ Description

XLG-320 series is a 315W LED AC/DC driver featuring with constant power mode. XLG-320 operates from 120~305VAC and offers models with different rated current ranging between 1050mA and 7420mA. Thanks to the high efficiency up to 94.5% with the fanless design, the entire series is able to operate for -40°C ~+85°C case temperature under free air convection. The design of metal housing and IP67 ingress protection level allows this series to fit both indoor and outdoor applications. Moreover the innovative environment-adaptive capability allows this series to reliably light on the LEDs for all kinds of application environments in almost any spots that may install LED luminaires in the world. XLG-320 series comply with the latest version of IEC61347/GB7000.1-2015 and UL8750 international safety regulations. The output and dimming circuit are also completely in accordance with the new regulations and isolation to ensure the safety of both user and luminaire system during installation.

■ Model Encoding



Type	IP Level	Function	Note
Blank	IP67	Io and Vo fixed.(For harsh environment)	By request
A	IP67	Output constant power adjustable via built-in Io potentiometer	In Stock
AB	IP67	Output constant power adjustable via built-in Io potentiometer + 3 in 1 dimming function (0~10Vdc, 10V PWM signal and resistance)	In Stock
ABV (48V only)	IP67	Vo adjustable via built-in potentiometer + 3 in 1 dimming function (Flicker free C.V. Dimming)	In Stock

Note: 1.V model is constant voltage operation without the AB type

2.48-V/48-BV types are available by modification version, please consult MEANWELL for detail.

File Name:XLG-320-SPEC 2023-04-28


SPECIFICATION

MODEL	XLG-320-L-□	XLG-320-M-□	XLG-320-H-□	XLG-320-V-□
OUTPUT	RATED CURRENT (Default)	1400mA	2800mA	5600mA
	RATED POWER Note.10	315W	310.8W	312W
	CONSTANT CURRENT REGION	150~300V	74 ~ 148V	30 ~ 56V
	OUTPUT VOLTAGE ADJ. RANGE	NC	NC	24V or 12V
	FULL POWER CURRENT RANGE	1050~1400mA	2100~2800mA	5570~7420mA
	OPEN CIRCUIT VOLTAGE (max.)	340V	180V	60V
	CURRENT ADJ. RANGE	500~1400mA	1050~2800mA	2800~7420mA
	CURRENT RIPPLE	5.0% max. @rated current	5.0 max. @rated current	5.0% max. @rated current
	CURRENT TOLERANCE	±5%	±5%	±5%
	RISSLE & NOISE(max.)	NC	NC	240mV p-p
	VOLTAGE TOLERANCE	NC	NC	±3%
	LINE REGULATION	NC	NC	±0.5%
	LOAD REGULATION	NC	NC	±2%
	SET UP TIME Note.9	500ms/230VAC, 1200ms/115VAC		
	RISE TIME, HOLD UP TIME (Typ.)	160ms,10ms/230VAC/115VAC(only for V-type)		
INPUT	VOLTAGE RANGE Note.2	100 ~ 305VAC 142VDC ~ 431VDC (Please refer to "STATIC CHARACTERISTIC" and "DRIVING METHODS OF LED MODULE" section)		
	FREQUENCY RANGE	47 ~ 63Hz		
	POWER FACTOR (Typ.)	PF ≥ 0.98 / 115VAC, PF ≥ 0.95 / 230VAC, PF ≥ 0.92 / 277VAC at full load (Please refer to "Power Factor Characteristic" section)		
	TOTAL HARMONIC DISTORTION	THD < 10% @ load ≥ 50% at 115VAC/230VAC, THD < 15% @ Load > 75% at 277VAC; Please refer to "TOTAL HARMONIC DISTORTION (THD)" section		
	EFFICIENCY (Typ.)	94.5%	93.5%	92.5%
	AC CURRENT (Typ.)	3A / 120VAC 1.6A / 230VAC 1.3A / 277VAC		
	INRUSH CURRENT(Typ.)	COLD START 45A(twidth=1200μs measured at 50% Ipeak) at 230VAC; Per NEMA 410		
	MAX. NO. of PSUs on 16A CIRCUIT BREAKER	2 unit(circuit breaker of type B) / 4 units(circuit breaker of type C) at 230VAC		
	LEAKAGE CURRENT	<0.75mA / 277VAC		
	STANDBY POWER CONSUMPTION Note.5	Standby power consumption <0.5W for AB-Type(Dimming OFF)		
PROTECTION	SHORT CIRCUIT	Hiccup mode or Constant current limiting, recovers automatically after fault condition is removed		
	OVER VOLTAGE	350 ~ 380V 190 ~ 220V 63 ~ 78V 27 ~ 34V		
	OVER TEMPERATURE Note.11	L/M/H-Type: Tcase > 85°C ± 5°C, derate power automatically V-Type: Shut down output voltage, re-power on to recover		
	OVER LOAD Note.10	108~135%(only for V-type) Hiccup mode or Constant current limiting, recovers automatically after fault condition is removed		
ENVIRONMENT	WORKING TEMP.	Tcase = -40 ~ +85°C (Please refer to "OUTPUT LOAD vs TEMPERATURE" section)		
	MAX. CASE TEMP.	Tcase = +85°C		
	WORKING HUMIDITY	20 ~ 95% RH non-condensing		
	STORAGE TEMP., HUMIDITY	-40 ~ +80°C, 10 ~ 95% RH non-condensing		
	TEMP. COEFFICIENT	± 0.03%/°C (0 ~ 60°C)		
	VIBRATION	10 ~ 500Hz, 5G 12min./1cycle, period for 72min. each along X, Y, Z axes		
SAFETY & EMC	SAFETY STANDARDS	UL8750(type "HL"), CSA C22.2 No. 250.13-12; ENEC BS EN/EN61347-1, BS EN/EN61347-2-13 independent, BS EN/EN62384; GB19510.1, GB19510.14; EAC TP TC 004; IP67; IS15885(Part2/Sec13)(except for blank type), KC61347-1, KC61347-2-13 approved		
	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC I/P-FG:2KVAC O/P-FG:1.5KVAC		
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH		
	EMC EMISSION	Parameter	Standard	Test Level / Note
		Conducted	BS EN/EN55015(CISPR15), GB/T17743	----
		Radiated	BS EN/EN55015(CISPR15), GB/T17743	----
		Harmonic Current	BS EN/EN61000-3-2, GB/T17625.1	Class C @load ≥ 50%
	EMC IMMUNITY	Voltage Flicker	BS EN/EN61000-3-3	----
		BS EN/EN61547		
		Parameter	Standard	Test Level / Note
		ESD	BS EN/EN61000-4-2	Level 3, 8KV air ; Level 2, 4KV contact
		Radiated	BS EN/EN61000-4-3	Level 2
		EFT / Burst	BS EN/EN61000-4-4	Level 3
OTHERS	MTBF	1476.4K hrs min. Telcordia SR-332(Bellcore) ; 168.1K hrs min. MIL-HDBK-217F (25°C)		
	DIMENSION	246*77*39.5mm (L*W*H)		
	PACKING	1.45Kg;9pcs/14Kg/0.76CUFT		
NOTE	1. All parameters NOT specially mentioned are measured at 230VAC input, rated current and 25°C of ambient temperature. 2. De-rating may be needed under low input voltages. Please refer to "STATIC CHARACTERISTIC" sections for details. 3. The driver is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again. 4. This series meets the typical life expectancy >50,000 hours of operation when Tcase, particularly (C) point (or TMP, per DLC), is 75°C or less. 5. To fulfill requirements of the latest ErP regulation for lighting fixture, this LED driver can only be used behind a switch without permanently connected to the mains. 6. Please refer to the warranty statement on MEAN WELL's website at http://www.meanwell.com 7. The ambient temperature derating of 3.5°C/100m with fanless models and of 5°C/100m with fan models for operating altitude higher than 2000m(6500ft). 8. For any application note and IP water proof function installation caution, please refer our user manual before using. https://www.meanwell.com/Upload/PDF/LED_EN.pdf 9. Products sourced from the Americas regions may not have the ENEC/CCC/KC logo. Please contact your MEAN WELL sales for more information. 10. The output voltage of the V Type default is 24V, for 12V output, please adjust SVR by clockwise direction to the end, otherwise the OLP point is not within the specification range. 11. When the secondary OLP fails, there is also a primary OLP, which is protected by Shut down output voltage, re-power on to recovery for the H/M/L-type. 12. When the current adjustment is more than 110% of the rated current, it will be enter the Protection state. 13. V, H type : RCM is on a voluntary basis. Non IC classification Independent LED control gear is not suitable for residential installations. M, L type : RCM is on a voluntary basis and meets relevant IEC or AS/NZS standards complying with AS/NZS 4417.1. 14. It may has an over-shoot status at output current when AC On/Off operate with lower Vf and lower loading conditions. 15. If you need the NOM (Mexico) certificate, Please contact MEAN WELL sales representative for details. 16. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. 17. Please refer to "DRIVING METHODS OF LED MODULE". ※ Product Liability Disclaimer : For detailed information, please refer to https://www.meanwell.com/serviceDisclaimer.aspx			

SPECIFICATION


MODEL		XLG-320-48-ABV	
OUTPUT	RATED CURRENT	6.5A	
	RATED POWER (Max.)	312W	
	DC VOLTAGE	48V(Adjustable 43.2~52.8V)	
	RIPLE & NOISE(max.)	250mVp-p	
	VOLTAGE TOLERANCE	± 2.0%	
	LINE REGULATION	± 0.5%	
	LOAD REGULATION	± 0.5%	
	SET UP TIME Note.9	500ms/230VAC, 1200ms/115VAC	
INPUT	RISE TIME,HOLD UP TIME (Typ.)	160ms,10ms/230VAC/115VAC	
	VOLTAGE RANGE Note.2	100 ~ 305VAC 142VDC ~ 431VDC (Please refer to "STATIC CHARACTERISTIC")	
	FREQUENCY RANGE	47 ~ 63Hz	
	POWER FACTOR (Typ.)	PF ≥ 0.98 / 115VAC, PF ≥ 0.95 / 230VAC, PF ≥ 0.92 / 277VAC at full load	
	TOTAL HARMONIC DISTORTION	THD < 10% @ load ≥ 50% at 115VAC/230VAC, THD < 15% @ Load > 75% at 277VAC;	
	EFFICIENCY (Typ.)	93.5%	
	AC CURRENT (Typ.)	3A / 120VAC 1.6A / 230VAC 1.3A / 277VAC	
	INRUSH CURRENT(Typ.)	COLD START 45A(twidth=1200μs measured at 50% Ipeak) at 230VAC; Per NEMA 410	
	MAX. NO. of PSUs on 16A CIRCUIT BREAKER	2 unit(circuit breaker of type B) / 4 units(circuit breaker of type C) at 230VAC	
	LEAKAGE CURRENT	<0.75mA / 277VAC	
PROTECTION	STANDBY POWER CONSUMPTION	Standby power consumption <0.5W for ABV/BV-Type(Dimming OFF)	
	SHORT CIRCUIT	Hiccup mode or Constant current limiting, recovers automatically after fault condition is removed	
	OVER VOLTAGE	54 ~ 60V Shut down output voltage, re-power on to recovery	
	OVER TEMPERATURE Note.10	Shut down output voltage, re-power on to recovery	
	OVER LOAD	105~135% Hiccup mode or Constant current limiting, recovers automatically after fault condition is removed	
ENVIRONMENT	WORKING TEMP.	Tcase=-20 ~ +85°C (Please refer to "OUTPUT LOAD vs TEMPERATURE" section)	
	MAX. CASE TEMP.	Tcase=+85°C	
	WORKING HUMIDITY	20 ~ 95% RH non-condensing	
	STORAGE TEMP., HUMIDITY	-20 ~ +80°C, 10 ~ 95% RH non-condensing	
	TEMP. COEFFICIENT	± 0.03%/°C (0 ~ 60°C)	
	VIBRATION	10 ~ 500Hz, 5G 12min./cycle, period for 72min. each along X, Y, Z axes	
SAFETY & EMC	SAFETY STANDARDS	UL8750(type "HL"), CSA C22.2 No. 250.13-12; ENEC BS EN/EN61347-1, BS EN/EN61347-2-13 independent, BS EN/EN62384; GB19510.1, GB19510.14;EAC TP TC 004; IP67 approved	
	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC I/P-FG:2KVAC O/P-FG:1.5KVAC	
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH	
	EMC EMISSION	Parameter	Standard
		Conducted	BS EN/EN55015(CISPR15),GB/T17743
		Radiated	BS EN/EN55015(CISPR15),GB/T17743
		Harmonic Current	BS EN/EN16100-3-2, GB/T17625.1
	EMC IMMUNITY	Voltage Flicker	BS EN/EN16100-3-3
		BS EN/EN1547	
		Parameter	Standard
		ESD	BS EN/EN16100-4-2
		Radiated	BS EN/EN16100-4-3
		EFT / Burst	BS EN/EN16100-4-4
		Surge	BS EN/EN16100-4-5
		Conducted	4KV/Line-Line 6KV/Line-Earth
OTHERS	Magnetic Field	BS EN/EN16100-4-6	Level 2
	Voltage Dips and Interruptions	BS EN/EN16100-4-8	Level 4
			>95% dip 0.5 periods, 30% dip 25 periods, >95% interruptions 250 periods
NOTE	MTBF	1476.4K hrs min. Telcordia SR-332(Bellcore) ; 168.1 K hrs min. MIL-HDBK-217F (25°C)	
	DIMENSION	246*77*39.5mm (L*W*H)	
	PACKING	1.45Kg;9pcs/14Kg/0.76CUFT	
1. All parameters NOT specially mentioned are measured at 230VAC input, rated current and 25°C of ambient temperature. 2. De-rating may be needed under low input voltages. Please refer to "STATIC CHARACTERISTIC" sections for details. 3. The driver is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again. 4. This series meets the typical life expectancy >50,000 hours of operation when Tcase, particularly (② point (or TMP, per DLC), is 75°C or less. 5. To fulfill requirements of the latest ErP regulation for lighting fixture, this LED driver can only be used behind a switch without permanently connected to the mains. 6. Please refer to the warranty statement on MEAN WELL's website at http://www.meanwell.com 7. The ambient temperature derating of 3.5°C/1000m with fanless models and of 5°C/1000m with fan models for operating altitude higher than 2000m(6500ft). 8. For any application note and IP water proof function installation caution, please refer our user manual before using. https://www.meanwell.com/Upload/PDF/LED_EN.pdf 9. Products sourced from the Americas regions may not have the ENEC/CCC/KC logo. Please contact your MEAN WELL sales for more information. 10. When the secondary OTP fails, there is also a primary OTP, which is protected by Shut down output voltage, re-power on to recovery. 11. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. 12. Please refer to "DRIVING METHODS OF LED MODULE". 13. 48 type : RCM is on a voluntary basis. Non IC classification Independent LED control gear is not suitable for residential installations. 14. Product Liability Disclaimer : For detailed information, please refer to https://www.meanwell.com/serviceDisclaimer.aspx			

■ BLOCK DIAGRAM




■ DRIVING METHODS OF LED MODULE


◎ XLG-320-L




◎ XLG-320-M



◎ XLG-320-H




◎ XLG-320-V



※ V type output voltage adjustable via built-in potentiometer



■ DIMMING OPERATION





※ 3 in 1 dimming function (for AB-Type)

- Output constant current level can be adjusted by applying one of the three methodologies between DIM+ and DIM-:
0 ~ 10VDC, or 10V PWM signal or resistance.
- Direct connecting to LEDs is suggested. It is not suitable to be used with additional drivers.
- Dimming source current from power supply: 100 μ A (typ.)



◎ Applying additive 0 ~ 10VDC



◎ Applying additive 10V PWM signal (frequency range 100Hz ~ 3KHz):



◎ Applying additive resistance:




Note : 1. Min. dimming level is about 8% and the output current is not defined when 0% < lout < 8%.

2. The output current could drop down to 0% when dimming input is about 0V or 0Vdc, or 10V PWM signal with 0% duty cycle.

3. When PWM frequency >2K HZ, the lighting will be triggered at 10~15% PWM duty .



■ DIMMING OPERATION





※ 3 in 1 dimming function (for ABV-Type)

- Output constant voltage can be adjusted by applying one of the three methodologies between DIM+ and DIM-:
0 ~ 10VDC, or 10V PWM signal or resistance.
- Direct connecting to LEDs is suggested. It is not suitable to be used with additional drivers.
- Dimming source current from power supply: 100µA (typ.)



◎ Applying additive 0 ~ 10VDC



◎ Applying additive 10V PWM signal (frequency range 200Hz ~ 3KHz):





◎ Applying additive resistance:




Note : 1. Min. dimming level is about 50% of output voltage and the output voltage is not defined when Vout<50%

2. The output voltage could drop down to 0V when dimming input is about 0k or 0Vdc, or 10V PWM signal with 0% duty cycle.

■ OUTPUT LOAD vs TEMPERATURE




■ STATIC CHARACTERISTIC




INPUT VOLTAGE (V) 60Hz

■ POWER FACTOR (PF) CHARACTERISTIC




LOAD

■ TOTAL HARMONIC DISTORTION (THD)

 ※ XLG-320-L Model, T_{case} at 85°C


■ EFFICIENCY vs LOAD

XLG-320 series possess superior working efficiency that up to 94.5% can be reached in field applications.

 ※ XLG-320-L Model, T_{case} at 85°C





LOAD

■ CONSTANT VOLTAGE DIMMING OPERATION:

48-ABV type

Note: flicker free design for agricultural lighting


flicker free design for Indoor LED strip lighting


■ LIFE TIME




■ MECHANICAL SPECIFICATION

Case No.:266A Unit:mm

※ V-A-Type





※ H/L/M-A-Type



■ MECHANICAL SPECIFICATION

Case No.:266A Unit:mm

※ AB/ABV-Type



■ INSTALLATION MANUAL

 Please refer to : <http://www.meanwell.com/manual.html>