



Test Report

Report No. A2260024018101001

Page 1 of 4

Company Name GLOBAL CONNECTOR TECHNOLOGY LTD
shown on Report
Address UNIT B, 8/F, HANG CHEONG FACTORY BUILDING, 1 WING MING STREET,
CHEUNG SHA WAN, KOWLOON, HK

The following sample(s) and sample information was/were submitted and identified by/on the behalf of the applicant

Sample Name FFC jumper insulator UL logo
Sample Received Date Jan. 9, 2026
Testing Period Jan. 9, 2026 to Jan. 14, 2026

Test Requested As specified by client, to screen the 1 substance of very high concern (SVHC) under Regulation(EC) No 1907/2006 of REACH in the submitted sample(s).

Test Method Please refer to the following page(s).

Test Result(s) Please refer to the following page(s).

Summary	According to the analytical results, concentration of 1 SVHC is $\leq$ 0.1% (w/w) in the submitted sample(s).	PASS
----------------	---	-------------



Approved by

Anso Fang

Date

Jan. 14, 2026

Anso Fang

Lab Authorized Signatory

No. R735791116

Centre Testing International Group Co., Ltd.

CTI Building, Xing Dong Community, Xin'an Sub-district, Bao'an District, Shenzhen City, Guangdong Province, P.R. China

Test Report

Report No. A2260024018101001

Page 2 of 4

Test Result(s)

Substance Name(s)	CAS No.	Concentration (%)	RL (%)
		001	
1,1'-(ethane-1,2-diyl)bis[pentabromobenzene]	84852-53-9	N.D.	0.05

Test Method:

Refer to US EPA 3550C:2007 for sample pretreatment.

Analyzed by GC-MS.

Sample/Part Description

No.	CTI Sample ID	Description
1	001	White film with green printing

Remark:

1. w/w = weight by weight; 0.1% = 1000 mg/kg = 1000 ppm
2. N.D. = Not Detected (< RL)
3. RL = Report Limit (Concentration value will be shown if it $\geq$ RL. RL is not regulatory limit.)


Test Report

Report No. A2260024018101001

Page 3 of 4

REACH Regulation obligation:

1. In accordance with Article 7(2) of the EU REACH Regulation (No. 1907/2006), any producer or importer of articles shall notify the European Chemicals Agency as stipulated in Article 7(4), if an article contains a substance from the Candidate List of Substances of Very High Concern (SVHCs) and both the following conditions are met:
 - (a) the substance is present in those articles in quantities totalling over one tonne per producer or importer per year;
 - (b) the substance is present in those articles above a concentration of 0.1 % weight by weight (w/w).
2. Any supplier of an article containing a substance that is included in the Candidate List in a concentration above 0.1 % weight by weight (w/w) has the duty to communicate information in accordance with Article 33 of EU REACH Regulation (No. 1907/2006).
 - 1) Any supplier shall provide the recipient of the article with sufficient information to allow safe use of the article including, as a minimum, the name of that substance.
 - 2) On request by a consumer any supplier shall provide the consumer with sufficient information to allow safe use of the article including, as a minimum, the name of that substance within 45 days of receipt of the request, free of charge.
3. In accordance with Article 31 of the EU REACH Regulation (No. 1907/2006), the supplier of a substance or a mixture shall provide the recipient of the substance or mixture with a safety data sheet (SDS) for free compiled in accordance with Annex II of REACH.
 - 1) where a substance or mixture meets the criteria for classification as hazardous in accordance with Regulation (EC) No 1272/2008; or
 - 2) where a substance is persistent, bioaccumulative and toxic or very persistent and very bioaccumulative in accordance with the criteria set out in Annex XIII; or
 - 3) where a substance is included in the list established in accordance with Article 59(1) for reasons other than those referred to in points (a) and (b);
 - 4) the supplier shall provide the recipient at his request with a safety data sheet (SDS) compiled in accordance with Annex II, where a mixture does not meet the criteria for classification as hazardous in accordance with Titles I and II of Regulation (EC) No 1272/2008, but contains:
 - (a) in an individual concentration of ≥ 1 % by weight for non-gaseous mixtures and ≥ 0.2 % by volume for gaseous mixtures at least one substance posing human health or environmental hazards; or
 - (b) in an individual concentration of ≥ 0.1 % by weight for non-gaseous mixtures at least one substance that has been included in the Candidate List of Substances of Very High Concern (SVHCs); or
 - (c) a substance for which there are Community workplace exposure limits.
4. Companies supplying articles containing Substances of Very High Concern (SVHCs) on the Candidate List in a concentration above 0.1% weight by weight (w/w) on the EU market have to submit information on these articles to ECHA in accordance with Waste Framework Directive (WFD) (No 2008/98, as from 5 January 2021).


Test Process

Test Report

Report No. A2260024018101001

Page 4 of 4

Photo(s) of the sample(s)



Statement:

1. This report is considered invalid without approved signature, special seal and the seal on the perforation;
2. The Company Name shown on Report and Address, the sample(s) and sample information was/were provided by the applicant who should be responsible for the authenticity which CTI hasn't verified;
3. The result(s) shown in this report refer(s) only to the sample(s) tested;
4. Unless otherwise stated, the decision rule for conformity reporting is based on Binary Statement for Simple Acceptance Rule ($w=0$) stated in ILAC-G8:09/2019 / CNAS-GL015:2022;
5. Without written approval of CTI, this report can't be reproduced except in full;
6. In case of any discrepancy between the English version and Chinese version of the reports (if generated), the Chinese version shall prevail.

*** End of Report ***