



“QUICK TURN” PROGRAM


CNC Precision Components

RAF ELECTRONIC
HARDWARE

MW Industries, Inc.

- BeCu contacts (heat treated and gold plated).
 - Other products may be considered within size range.
- Parts must be under 0.390" (10mm) diameter.
- Maximum quantity of 1,000 pieces.
- RFQs will be answered within 24 hours of receipt by RAF.
- Purchase orders must be received by RAF within 24 hours of initial quotation.
- Parts ship within 3 weeks from receipt of purchase order.
 - Additional lead time will be required for: outside services requiring a Nadcap approved source and for right angle contacts.

For more information, contact: (203) 888-2133



CNC PRECISION MACHINED PARTS

- Precision contacts and bodies to Military specs
- Tolerance on diameters to +/- .0002"
- Short run and prototype
- Right angle and 45° bent contacts
- Turned diameters from .010" to .750"
- Turn key product, heat treated and plated

CNC precision machining made to your blueprint, featuring primary, secondary, and complete engineering support. Capabilities include: crimping, plating, slotting, knurling, assembling, threading, heat treating, and zone annealing. Short to medium runs with quick turnaround are our specialty.



Contacts and Sub-Assemblies



Right Angle Contacts



Contacts and Bodies