








Notes:

1. Material: See chart
2. Material color: See chart
3. Maximum percent regrind permissible: 25%
4. Maximum allowable flash to be: 0.25 mm
5. Maximum allowable mismatch to be: 0.10 mm
6. A dimension without an inspection report symbol  does not require inspection. It may be controlled on the individual component drawing.
 - a. Total number of inspections required: 11
 - b. Last number used: 11
 - c. Missing symbols: -
7. Mounting screw size:
 - M4
 - #8 [0.164 in]
8. Accommodates cable tie series: T18 - T120
9. Accommodates 3/8in grip tie: GT.375
10. Tape may be flush or inside the mount edge
11. Tape may be flush or extend beyond the edge of the mount
12. Store product in its original packaging between 4°C to 38°C (40°F to 100°F) and 0-95% relative humidity, the optimum storage conditions are 22°C (72°F) and 50% relative humidity out of direct sunlight

01.3	Part Description		Mount		Adhesive Tape		
			Material	Color	Storage Conditions	Adhesive Material	Color
	AMB6AHB-PA66HS-BK		PA66HS	Black (BK)	See note 12	241-002-05 acrylic foam tape	Black (BK)
	AMB6AHB-PA66HS-WH		PA66HS	White (WH)			

Revision level			Revision Record				All drawing revision are stored in CAD PDM database	The copyright of this drawing is reserved by HellermannTyton.	Drawn	Date (YYYY/MM/DD)	Title Anchor mounting base with high bond adhesive, 62 x 62mm		Scale 1:1 Global Project Number 25-0174	
Drawing	State	Part	ECN 312321	Spangler	2025/03/12									
01.3	Design Release	-		Approved	Date (YYYY/MM/DD)									
Changed		Date (YYYY/MM/DD)			Toll	2025/03/12		Drawing-No		Format A3				
Spangler		2025/07/08						25-0174-101-CSU		Sheet 1/1				
Approved		Date (YYYY/MM/DD)												
Mann		2025/08/19												

Units
mm

HellermannTyton

www.HellermannTyton.com