


Qualified to AS85049, D38999 and Mil-Spec
Sunbank backshells and accessories



Powering Business Worldwide



Backshells and accessories

Typical applications



Versatile, ruggedized solutions for your applications

Sunbank backshells are qualified to various military specifications and come in a variety of materials and plating options to meet the most stringent requirements: aluminum, composite, stainless steel, nickel, cadmium, black anodized and passivated.

Lightweight, durable and efficient

Composite backshells meet all of the requirements of AS85049, offering the lightest weight for fuel savings in aircraft. In addition, composite backshells offer up to 2,000 hours salt spray protection with various composite plating options.

Built to the highest standards

Sunbank backshells are built to withstand temperatures from -65°C to 200°C , shell-to-shell conductivity, shielding and various configurations such as straight, 45° and 90° options. In addition, we offer all other accessories such as dust caps, shield-supporting split rings, clamping bands and bushing strips.



Sunbank backshells and accessories



1 Overview	
Range overview	5
Technical features	7
2 Backshells	
AS85049 series	8
3 Protective covers	
AS25 series	86
D38999 series	87
MS275 series	89
MS31 series	93
4 Accessories for AS85049 series	
Shield support ring	95
Bushing strip	96
Clamping bands	97
5 Appendix	
Part number index	98

Backshells



Cable clamp strain relief

Connector type	AS85049 series
AS50151 solder	AS85049/42 - page 57 ■
MIL-DTL-26482 series 2	AS85049/43 - page 58 ■
MIL-DTL-83723 series 3	AS85049/51 - page 63 ■
EN2997 & EN3646	AS85049/52 - page 65 ■
MIL-DTL-27599	AS85049/47 - page 61 ■
MIL-DTL-38999 series I & II	AS85049/49-2 - page 62 ■ ●
MIL-DTL-38999 series III & IV	AS85049/21 - page 34 ■
EN3645	AS85049/38 - page 55 ■ ●
	AS85049/39 - page 56 ■ ●
	AS85049/91, 92 - page 83 ▲
	AS85049/103 - page 84 ▲
	AS85049/104 - page 84 ▲
	AS85049/105 - page 84 ■ ●



Cable tie strain relief

Connector type	AS85049 series
AS50151 crimp	AS85049/53 - page 67 ■
MIL-DTL-26482 series 2	AS85049/54 - page 67 ■
MIL-DTL-83723 series 3	AS85049/55 - page 67 ■
EN2997 & EN3646	
MIL-DTL-38999 series I & II	AS85049/57 - page 68 ■
	AS85049/63 - page 74 ■
MIL-DTL-38999 series III & IV	AS85049/15 - page 29 ■
EN3645	AS85049/16 - page 29 ■



EMI & environmental backshell

Connector type	AS85049 series
AS50151 crimp	AS85049/6 - page 8 ■ ●
	AS85049/8 - page 14 ■ ●
	AS85049/10 - page 20 ■ ●
MIL-DTL-38999 series I & II	AS85049/17 - page 30 ■
	AS85049/76 - page 76 ■
	AS85049/77 - page 77 ■
MIL-DTL-38999 series III & IV	AS85049/18 - page 31 ■
	AS85049/78 - page 78 ■
	AS85049/79 - page 79 ■



Banding backshell

Connector type	AS85049 series
AS50151 crimp	AS85049/82 - page 80 ■
MIL-DTL-26482 series 2	AS85049/83 - page 80 ■
MIL-DTL-83723 series 3	AS85049/84 - page 80 ■
EN2997 & EN3646	
MIL-DTL-27599	AS85049/85 - page 81 ■
MIL-DTL-38999 series I & II	AS85049/86 - page 81 ■
	AS85049/87 - page 81 ■
MIL-DTL-38999 series III & IV	AS85049/88 - page 82 ■ ▲
EN3645	AS85049/89 - page 82 ■ ▲
	AS85049/90 - page 82 ■ ▲



EMI/RFI backshell

Connector type	AS85049 series
AS50151 crimp	AS85049/23 - page 35 ■ ●
MIL-DTL-26482 series 2	AS85049/24 - page 38 ■
MIL-DTL-83723 series 3	AS85049/25 - page 41 ■
EN2997 & EN3646	AS85049/26-1 - page 46 ■
	AS85049/26-2 - page 47 ■
	AS85049/26-3 - page 46 ■
MIL-DTL-27599	AS85049/29 - page 49 ■
MIL-DTL-38999 series I & II	AS85049/33-2 - page 52 ■
	AS85049/36 - page 53 ■
	AS85049/37 - page 54 ■
MIL-DTL-38999 series III & IV	AS85049/19 - page 32 ■
EN3645	AS85049/20 - page 33 ■



Environmental backshell

Connector type	AS85049 series
AS50151 crimp	AS85049/7 - page 11 ■ ●
MIL-DTL-26482 series 2	AS85049/9 - page 17 ■ ●
MIL-DTL-83723 series 3	AS85049/11 - page 24 ■ ●
EN2997 & EN3646	

Materials: ■ Aluminum ● Stainless steel ▲ Composite

Backshells



Grommet nut

Connector type	AS85049 series
MIL-DTL-38999 series I & II	AS85049/27 - page 48 ■
AS50151 crimp	AS85049/14 - page 28 ■
MIL-DTL-26482 series 2	AS85049/31 - page 50 ■
MIL-DTL-83723 series 3	
EN2997 & EN3646	



Strain relief flexible plastic body

Connector type	AS85049 series
MIL-DTL-38999 series I & II	AS85049/45 - page 59 ■
	AS85049/46 - page 60 ■



Potting & shrink boot adapter

Connector type	AS85049 series
AS50151 crimp	AS85049/60-1 - page 70 ■
MIL-DTL-26482 series 2	AS85049/60-2G - page 71 ■
MIL-DTL-83723 series 3	
EN2997 & EN3646	
MIL-DTL-27599	AS85049/61 - page 72 ■
MIL-DTL-27599	AS85049/62 - page 73 ■
MIL-DTL-38999 series I & II	
MIL-DTL-38999 series I & II	AS85049/58 - page 69 ■
MIL-DTL-38999 series III & IV	AS85049/69 - page 75 ■
EN3645	

Protective covers



Threaded mating

Connector type	Dust cover series
AS50151	AS25042 - page 85 ■
	AS25043 - page 86 ■
MIL-DTL-38999 series III	D38999/32 - page 87 ■
	D38999/33 - page 88 ■



Bayonet mating

Connector type	Dust cover series
MIL-DTL-38999 series I	MS27501 - page 89 ■
	MS27502 - page 90 ■
MIL-DTL-38999 series I & II	MS27510 - page 91 ■
	MS27511 - page 92 ■
MIL-DTL-38999 series III & IV	MS3180 - page 93 ■
	MS3181 - page 94 ■

Accessories



Shield support ring

Connector type	AS85049 series
All	AS85049/93 - page 95 ▲



Bushing strip

Connector type	AS85049 series
All	AS85049/127 - page 96



Clamping band

Connector type	AS85049 series
All	AS85049/128 - page 97 ●



Technical features

Materials

- Aluminum, Stainless steel, composite.

Electrical

- Shell conductivity:
 - Aluminum: $R < 2.5\text{m}\Omega$
 - Stainless steel: $R < 2.5\text{m}\Omega$
 - Composite: $R < 5\text{m}\Omega$


Environmental

- Plating:
 - Nickel, Cadmium, Black anodized,
 - Passivate (for stainless steel only)
- Temperature range:
 - Electroless Nickel: -65°C to $+200^{\circ}\text{C}$
 - Passivate: -65°C to $+200^{\circ}\text{C}$
 - Other plating: -65°C to $+175^{\circ}\text{C}$
- Salt spray resistance:
 - Aluminum shell:
 - Electroless Nickel: 96 hours
 - Black anodized: 500 hours
 - Cadmium: 1.000 hours
 - Stainless steel shell:
 - Passivate: 1.000 hours
- Composite shell:
 - Electroless Nickel: 2.000 hours
 - Cadmium: 2.000 hours


For connectors:

- AS50151 crimp
- EN2997 & EN3646
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection



Dimensions



Dash number	Shell size	Style	B $\pm 0.062"/1.57$ inches mm	C reference inches mm	$\varnothing$ D max inches mm	E $\pm 0.125"/3.17$ inches mm	F max inches mm	Cable entry min inches mm	Cable entry max inches mm
3	8	1	1.182 30.02	1.544 39.21	0.617 15.67	0.500 12.70	2.88 73.15	0.125 3.2	0.250 6.4
4	10	1	1.850 46.99	1.544 39.21	0.734 18.64	0.561 14.24	3.41 86.61	0.125 3.2	0.312 7.9
5	10	1	1.245 31.62	1.544 39.21	0.734 18.64	0.561 14.24	3.05 77.46	0.250 6.4	0.375 9.5
6	12	1	1.910 48.51	1.544 39.21	0.858 21.79	0.625 15.87	3.52 89.40	0.125 3.2	0.312 7.9
7	12	1	1.910 48.51	1.544 39.21	0.858 21.79	0.625 15.87	3.58 90.93	0.250 6.4	0.437 11.1
8	12	1	1.910 48.51	1.844 46.83	0.858 21.79	0.625 15.87	3.86 98.04	0.350 8.9	0.500 12.7
9	14	1	2.000 50.80	1.544 39.21	0.984 24.99	0.688 17.47	3.71 94.23	0.250 6.4	0.437 11.1
10	14	1	1.655 42.03	1.844 46.83	0.984 24.99	0.688 17.47	3.74 94.99	0.350 8.9	0.575 14.6
11	16	1	2.110 53.59	1.544 39.21	1.112 28.24	0.781 19.83	3.88 98.55	0.250 6.4	0.437 11.1
12	16	1	1.750 44.44	1.916 48.66	1.112 28.24	0.781 19.83	4.03 102.36	0.500 12.7	0.700 17.8
13	18	1	2.300 58.41	1.844 46.83	1.218 30.93	0.968 24.58	4.48 113.79	0.350 8.9	0.625 15.9
14	18	1	1.938 49.22	2.000 50.80	1.218 30.93	0.968 24.58	4.49 114.04	0.625 15.9	0.779 19.8
15	20	1	2.300 58.41	1.844 46.83	1.345 34.16	0.968 24.58	4.48 113.79	0.350 8.9	0.625 15.9
16	20	1	1.938 49.22	2.000 50.80	1.345 34.16	0.968 24.58	4.49 114.04	0.625 15.9	0.904 23.0
17	22	1	2.450 62.23	1.916 48.66	1.468 37.28	1.063 27.00	4.81 122.17	0.500 12.7	0.750 19.1

Continued on pages 9 and 10

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
 Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/6 series - EMI/RFI environmental backshell - Aluminum 45° (continued)

Dash number	Shell size	Style	B $\pm 0.062"/1.57$ inches mm	C reference inches mm	Ø D max inches mm	E $\pm 0.125"/3.17$ inches mm	F max inches mm	Cable entry min inches mm	Cable entry max inches mm
18	22	1	2.093 53.16	2.230 56.64	1.468 37.28	1.063 27.00	4.98 126.49	0.875 22.2	1.029 26.1
19	24	1	2.450 62.23	1.916 48.66	1.593 40.46	1.063 27.00	4.81 122.17	0.500 12.7	0.750 19.1
20	24	1	2.093 53.16	2.230 56.64	1.593 40.46	1.063 27.00	4.98 126.49	0.875 22.2	1.144 29.1
21	28	1	2.500 63.50	2.000 50.80	1.969 50.01	1.188 30.17	5.11 129.79	0.625 15.9	0.937 23.8
22	28	1	2.156 54.76	2.024 51.40	1.969 50.01	1.188 30.17	5.09 129.28	1.000 25.4	1.375 34.9
23	32	1	2.600 66.03	2.000 50.80	2.219 56.36	1.250 31.75	5.24 133.85	0.625 15.9	0.937 23.8
24	32	1	2.600 66.03	2.230 56.64	2.219 56.36	1.250 31.75	5.52 140.20	0.875 22.2	1.250 31.8
25	32	1	2.250 57.15	2.550 64.77	2.219 56.36	1.250 31.75	5.73 145.54	1.250 31.8	1.625 41.3
26	36	1	2.690 68.32	2.000 50.80	2.469 62.71	1.281 32.53	5.33 135.38	0.625 15.9	0.937 23.8
27	36	1	2.690 68.32	2.024 51.40	2.469 62.71	1.281 32.53	5.56 141.22	1.000 25.4	1.375 34.9
28	36	1	2.344 59.53	2.600 66.03	2.489 63.22	1.281 32.53	5.95 151.13	1.437 36.5	1.840 46.7
29	40	1	2.690 68.32	2.000 50.80	2.719 69.06	2.031 51.58	6.08 154.43	0.625 15.9	0.937 23.8
30	40	1	2.690 68.32	2.024 51.40	2.719 69.06	2.031 51.58	6.31 160.27	1.000 25.4	1.375 34.9
31	40	1	2.344 59.53	2.600 66.03	2.719 69.06	2.031 51.58	6.70 170.18	1.437 36.5	1.875 47.6
32	44	1	2.690 68.32	2.000 50.80	2.969 75.41	2.031 51.58	6.08 154.43	0.625 15.9	0.937 23.8
33	44	1	2.690 68.32	2.024 51.40	2.969 75.41	2.031 51.58	6.31 160.27	1.000 25.4	1.375 34.9
34	44	1	2.344 59.53	2.600 66.03	2.969 75.41	2.031 51.58	6.70 170.18	1.437 36.5	1.875 47.6
35	48	1	2.690 68.32	2.000 50.80	3.219 81.76	2.031 51.58	6.08 154.43	0.625 15.9	0.937 23.8
36	48	1	2.690 68.32	2.024 51.40	3.219 81.76	2.031 51.58	6.31 160.27	1.000 25.4	1.375 34.9
37	48	1	2.344 59.53	2.600 66.03	3.219 81.76	2.031 51.58	6.70 170.18	1.437 36.5	1.875 47.6
40	16	1	2.110 53.59	1.844 46.83	1.112 28.24	0.781 19.83	4.16 105.66	0.350 8.9	0.625 15.9
41	18	1	2.300 58.41	1.544 39.21	1.218 30.93	0.968 24.58	4.13 104.90	0.125 3.2	0.312 7.9
42	18	1	2.300 58.41	1.544 39.21	1.218 30.93	0.968 24.58	4.20 106.67	0.250 6.4	0.437 11.1
43	20	1	2.300 58.41	1.544 39.21	1.345 34.16	0.968 24.58	4.20 106.67	0.250 6.4	0.437 11.1
44	22	1	2.450 62.23	1.544 39.21	1.488 37.79	1.063 27.00	4.34 110.23	0.125 3.2	0.312 7.9
45	22	1	2.450 62.23	1.544 39.21	1.468 37.28	1.063 27.00	4.40 111.76	0.250 6.4	0.437 11.1
46	24	1	2.450 62.23	1.844 46.83	1.593 40.46	1.063 27.00	4.68 118.87	0.350 8.9	0.625 15.9
47	36	1	2.690 68.32	1.916 48.66	2.469 62.71	1.281 32.53	5.20 132.07	0.500 12.7	0.750 19.1
48	40	1	2.690 68.32	1.916 48.66	2.719 69.06	2.031 51.58	5.95 151.13	0.500 12.7	0.750 19.1
49	10	2	1.910 48.51	1.544 39.21	0.734 18.64	1.375 34.92	4.33 109.98	0.250 6.4	0.437 11.1
50	14	2	2.300 58.41	1.916 48.66	0.984 24.99	1.717 43.61	5.36 136.17	0.500 12.7	0.750 19.1
51	16	2	2.450 62.23	2.000 50.80	1.112 28.24	1.812 46.02	5.70 144.78	0.625 15.9	0.937 23.8
52	18	1	2.300 58.41	1.916 48.66	1.218 30.93	0.968 24.58	4.61 117.09	0.500 12.7	0.750 19.1
54	20	1	2.300 58.41	1.916 48.66	1.345 34.16	0.968 24.58	4.61 117.09	0.500 12.7	0.750 19.1
55	20	2	2.500 63.50	2.230 56.64	1.345 34.16	1.936 49.17	6.14 155.95	0.875 22.2	1.250 31.8
56	22	1	2.450 62.23	1.844 46.83	1.468 37.28	1.063 27.00	4.68 118.87	0.350 8.9	0.625 15.9
57	22	1	2.450 62.23	2.000 50.80	1.468 37.28	1.063 27.00	4.95 125.73	0.625 15.9	0.937 23.8
58	22	2	2.500 63.50	2.230 56.64	1.468 37.28	1.936 49.17	6.14 155.95	0.875 22.2	1.250 31.8
59	24	1	2.450 62.23	2.000 50.80	1.593 40.46	1.063 27.00	4.95 125.73	0.625 15.9	0.937 23.8
60	28	1	2.500 63.50	1.916 48.66	1.969 50.01	1.188 30.17	4.97 126.23	0.500 12.7	0.750 19.1
61	28	1	2.500 63.50	2.230 56.64	1.969 50.01	1.188 30.17	5.39 136.90	0.875 22.2	1.250 31.8
62	32	1	2.600 66.03	2.024 51.40	2.219 56.36	1.250 31.75	5.47 138.93	1.000 25.4	1.375 34.9
63	36	1	2.690 68.32	2.230 56.64	2.469 62.71	1.281 32.53	5.62 142.74	0.875 22.2	1.250 31.8

Continued on page 10

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

Dash number	Shell size	Style	B $\pm 0.002"/1.57$		C reference		$\varnothing$ D max		E $\pm 0.125"/3.17$		F max		Cable entry min		Cable entry max	
			inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
64	36	1	2.690	68.32	2.550	64.77	2.469	62.71	1.281	32.53	6.08	154.43	1.250	31.8	1.625	41.3
65	40	1	2.690	68.32	2.230	56.64	2.719	69.06	2.031	51.58	6.37	161.79	0.875	22.2	1.250	31.8
66	40	1	2.690	68.32	2.550	64.77	2.719	69.06	2.031	51.58	6.83	173.48	1.250	31.8	1.625	41.3
67	44	1	2.690	68.32	2.230	56.64	2.969	75.41	2.031	51.58	6.37	161.79	0.875	22.2	1.250	31.8
68	44	1	2.690	68.32	2.550	64.77	2.969	75.41	2.031	51.58	6.83	173.48	1.250	31.8	1.625	41.3
69	48	1	2.690	68.32	2.230	56.64	3.219	81.76	2.031	51.58	6.37	161.79	0.875	22.2	1.250	31.8
70	48	1	2.690	68.32	2.550	64.77	3.219	81.76	2.031	51.58	6.83	173.48	1.250	31.8	1.625	41.3
71	12	2	2.110	53.59	1.844	46.83	0.858	21.79	1.529	38.83	4.90	124.46	0.350	8.9	0.625	15.9
72	18	2	2.450	62.23	2.000	50.80	1.218	30.93	1.812	46.02	5.69	144.52	0.625	15.9	0.937	23.8
73	24	2	2.500	63.50	2.230	56.64	1.593	40.46	1.936	49.17	6.13	155.70	0.875	22.2	1.250	31.8
74	14	1	2.000	50.80	1.544	39.21	0.984	24.99	0.688	17.47	3.64	92.45	0.125	3.2	0.312	7.9
75	16	1	2.110	53.59	1.544	39.21	1.112	28.24	0.781	19.83	3.81	96.77	0.125	3.2	0.312	7.9


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/7 Series - Environmental backshell - Aluminum 45°


For connectors:

- AS50151 crimp
- EN2997 & EN3646
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection



Dimensions



Dash number	Shell size	Style	B $\pm 0.062"/1.57$ inches mm	C reference inches mm	$\emptyset$ D max inches mm	E $\pm 0.125"/3.17$ inches mm	F max inches mm	Cable entry min inches mm	Cable entry max inches mm
3	8	1	1.182 30.02	1.544 39.21	0.617 15.67	0.500 12.70	2.88 73.15	0.125 3.2	0.250 6.4
4	10	1	1.850 46.99	1.544 39.21	0.734 18.64	0.561 14.24	3.41 86.61	0.125 3.2	0.312 7.9
5	10	1	1.245 31.62	1.544 39.21	0.734 18.64	0.561 14.24	3.05 77.46	0.250 6.4	0.375 9.5
6	12	1	1.910 48.51	1.544 39.21	0.858 21.79	0.625 15.87	3.52 89.40	0.125 3.2	0.312 7.9
7	12	1	1.910 48.51	1.544 39.21	0.858 21.79	0.625 15.87	3.58 90.93	0.250 6.4	0.437 11.1
8	12	1	1.910 48.51	1.844 46.83	0.858 21.79	0.625 15.87	3.86 98.04	0.350 8.9	0.500 12.7
9	14	1	2.000 50.80	1.544 39.21	0.984 24.99	0.688 17.47	3.71 94.23	0.250 6.4	0.437 11.1
10	14	1	1.655 42.03	1.844 46.83	0.984 24.99	0.688 17.47	3.74 94.99	0.350 8.9	0.575 14.6
11	16	1	2.110 53.59	1.544 39.21	1.112 28.24	0.781 19.83	3.88 98.55	0.250 6.4	0.437 11.1
12	16	1	1.750 44.44	1.916 48.66	1.112 28.24	0.781 19.83	4.03 102.36	0.500 12.7	0.700 17.8
13	18	1	2.300 58.41	1.844 46.83	1.218 30.93	0.968 24.58	4.48 113.79	0.350 8.9	0.625 15.9
14	18	1	1.938 49.22	2.000 50.80	1.218 30.93	0.968 24.58	4.49 114.04	0.625 15.9	0.779 19.8
15	20	1	2.300 58.41	1.844 46.83	1.345 34.16	0.968 24.58	4.48 113.79	0.350 8.9	0.625 15.9
16	20	1	1.938 49.22	2.000 50.80	1.345 34.16	0.968 24.58	4.49 114.04	0.625 15.9	0.904 23.0
17	22	1	2.450 62.23	1.916 48.66	1.468 37.28	1.063 27.00	4.81 122.17	0.500 12.7	0.750 19.1

Continued on pages 12 and 13

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/7 Series - Environmental backshell - Aluminum 45° (continued)

Dash number	Shell size	Style	B $\pm 0.002"/1.57$ inches mm	C reference inches mm	Ø D max inches mm	E $\pm 0.125"/3.17$ inches mm	F max inches mm	Cable entry min inches mm	Cable entry max inches mm
18	22	1	2.093 53.16	2.230 56.64	1.468 37.28	1.063 27.00	4.98 126.49	0.875 22.2	1.029 26.1
19	24	1	2.450 62.23	1.916 48.66	1.593 40.46	1.063 27.00	4.81 122.17	0.500 12.7	0.750 19.1
20	24	1	2.093 53.16	2.230 56.64	1.593 40.46	1.063 27.00	4.98 126.49	0.875 22.2	1.144 29.1
21	28	1	2.500 63.50	2.000 50.80	1.969 50.01	1.188 30.17	5.11 129.79	0.625 15.9	0.937 23.8
22	28	1	2.156 54.76	2.024 51.40	1.969 50.01	1.188 30.17	5.09 129.28	1.000 25.4	1.375 34.9
23	32	1	2.600 66.03	2.000 50.80	2.219 56.36	1.250 31.75	5.24 133.85	0.625 15.9	0.937 23.8
24	32	1	2.600 66.03	2.230 56.64	2.219 56.36	1.250 31.75	5.52 140.20	0.875 22.2	1.250 31.8
25	32	1	2.250 57.15	2.550 64.77	2.219 56.36	1.250 31.75	5.73 145.54	1.250 31.8	1.625 41.3
26	36	1	2.690 68.32	2.000 50.80	2.469 62.71	1.281 32.53	5.33 135.38	0.625 15.9	0.937 23.8
27	36	1	2.690 68.32	2.024 51.40	2.469 62.71	1.281 32.53	5.56 141.22	1.000 25.4	1.375 34.9
28	36	1	2.344 59.53	2.600 66.03	2.489 63.22	1.281 32.53	5.95 151.13	1.437 36.5	1.840 46.7
29	40	1	2.690 68.32	2.000 50.80	2.719 69.06	2.031 51.58	6.08 154.43	0.625 15.9	0.937 23.8
30	40	1	2.690 68.32	2.024 51.40	2.719 69.06	2.031 51.58	6.31 160.27	1.000 25.4	1.375 34.9
31	40	1	2.344 59.53	2.600 66.03	2.719 69.06	2.031 51.58	6.70 170.18	1.437 36.5	1.875 47.6
32	44	1	2.690 68.32	2.000 50.80	2.969 75.41	2.031 51.58	6.08 154.43	0.625 15.9	0.937 23.8
33	44	1	2.690 68.32	2.024 51.40	2.969 75.41	2.031 51.58	6.31 160.27	1.000 25.4	1.375 34.9
34	44	1	2.344 59.53	2.600 66.03	2.969 75.41	2.031 51.58	6.70 170.18	1.437 36.5	1.875 47.6
35	48	1	2.690 68.32	2.000 50.80	3.219 81.76	2.031 51.58	6.08 154.43	0.625 15.9	0.937 23.8
36	48	1	2.690 68.32	2.024 51.40	3.219 81.76	2.031 51.58	6.31 160.27	1.000 25.4	1.375 34.9
37	48	1	2.344 59.53	2.600 66.03	3.219 81.76	2.031 51.58	6.70 170.18	1.437 36.5	1.875 47.6
40	16	1	2.110 53.59	1.844 46.83	1.112 28.24	0.781 19.83	4.16 105.66	0.350 8.9	0.625 15.9
41	18	1	2.300 58.41	1.544 39.21	1.218 30.93	0.968 24.58	4.13 104.90	0.125 3.2	0.312 7.9
42	18	1	2.300 58.41	1.544 39.21	1.218 30.93	0.968 24.58	4.20 106.67	0.250 6.4	0.437 11.1
43	20	1	2.300 58.41	1.544 39.21	1.345 34.16	0.968 24.58	4.20 106.67	0.250 6.4	0.437 11.1
44	22	1	2.450 62.23	1.544 39.21	1.488 37.79	1.063 27.00	4.34 110.23	0.125 3.2	0.312 7.9
45	22	1	2.450 62.23	1.544 39.21	1.468 37.28	1.063 27.00	4.40 111.76	0.250 6.4	0.437 11.1
46	24	1	2.450 62.23	1.844 46.83	1.593 40.46	1.063 27.00	4.68 118.87	0.350 8.9	0.625 15.9
47	36	1	2.690 68.32	1.916 48.66	2.469 62.71	1.281 32.53	5.20 132.07	0.500 12.7	0.750 19.1
48	40	1	2.690 68.32	1.916 48.66	2.719 69.06	2.031 51.58	5.95 151.13	0.500 12.7	0.750 19.1
49	10	2	1.910 48.51	1.544 39.21	0.734 18.64	1.375 34.92	4.33 109.98	0.250 6.4	0.437 11.1
50	14	2	2.300 58.41	1.916 48.66	0.984 24.99	1.717 43.61	5.36 136.17	0.500 12.7	0.750 19.1
51	16	2	2.450 62.23	2.000 50.80	1.112 28.24	1.812 46.02	5.70 144.78	0.625 15.9	0.937 23.8
52	18	1	2.300 58.41	1.916 48.66	1.218 30.93	0.968 24.58	4.61 117.09	0.500 12.7	0.750 19.1
54	20	1	2.300 58.41	1.916 48.66	1.345 34.16	0.968 24.58	4.61 117.09	0.500 12.7	0.750 19.1
55	20	2	2.500 63.50	2.230 56.64	1.345 34.16	1.936 49.17	6.14 155.95	0.875 22.2	1.250 31.8
56	22	1	2.450 62.23	1.844 46.83	1.468 37.28	1.063 27.00	4.68 118.87	0.350 8.9	0.625 15.9
57	22	1	2.450 62.23	2.000 50.80	1.468 37.28	1.063 27.00	4.95 125.73	0.625 15.9	0.937 23.8
58	22	2	2.500 63.50	2.230 56.64	1.468 37.28	1.936 49.17	6.14 155.95	0.875 22.2	1.250 31.8
59	24	1	2.450 62.23	2.000 50.80	1.593 40.46	1.063 27.00	4.95 125.73	0.625 15.9	0.937 23.8
60	28	1	2.500 63.50	1.916 48.66	1.969 50.01	1.188 30.17	4.97 126.23	0.500 12.7	0.750 19.1
61	28	1	2.500 63.50	2.230 56.64	1.969 50.01	1.188 30.17	5.39 136.90	0.875 22.2	1.250 31.8
62	32	1	2.600 66.03	2.024 51.40	2.219 56.36	1.250 31.75	5.47 138.93	1.000 25.4	1.375 34.9
63	36	1	2.690 68.32	2.230 56.64	2.469 62.71	1.281 32.53	5.62 142.74	0.875 22.2	1.250 31.8

Continued on page 13

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/7 Series - Environmental backshell - Aluminum 45° (continued)


Dash number	Shell size	Style	B $\pm 0.002"/1.57$ inches mm	C reference inches mm	Ø D max inches mm	E $\pm 0.125"/3.17$ inches mm	F max inches mm	Cable entry min inches mm	Cable entry max inches mm
64	36	1	2.690 68.32	2.550 64.77	2.469 62.71	1.281 32.53	6.08 154.43	1.250 31.8	1.625 41.3
65	40	1	2.690 68.32	2.230 56.64	2.719 69.06	2.031 51.58	6.37 161.79	0.875 22.2	1.250 31.8
66	40	1	2.690 68.32	2.550 64.77	2.719 69.06	2.031 51.58	6.83 173.48	1.250 31.8	1.625 41.3
67	44	1	2.690 68.32	2.230 56.64	2.969 75.41	2.031 51.58	6.37 161.79	0.875 22.2	1.250 31.8
68	44	1	2.690 68.32	2.550 64.77	2.969 75.41	2.031 51.58	6.83 173.48	1.250 31.8	1.625 41.3
69	48	1	2.690 68.32	2.230 56.64	3.219 81.76	2.031 51.58	6.37 161.79	0.875 22.2	1.250 31.8
70	48	1	2.690 68.32	2.550 64.77	3.219 81.76	2.031 51.58	6.83 173.48	1.250 31.8	1.625 41.3
71	12	2	2.110 53.59	1.844 46.83	0.858 21.79	1.529 38.83	4.90 124.46	0.350 8.9	0.625 15.9
72	18	2	2.450 62.23	2.000 50.80	1.218 30.93	1.812 46.02	5.69 144.52	0.625 15.9	0.937 23.8
73	24	2	2.500 63.50	2.230 56.64	1.593 40.46	1.936 49.17	6.13 155.70	0.875 22.2	1.250 31.8
74	14	1	2.000 50.80	1.544 39.21	0.984 24.99	0.688 17.47	3.64 92.45	0.125 3.2	0.312 7.9
75	16	1	2.110 53.59	1.544 39.21	1.112 28.24	0.781 19.83	3.81 96.77	0.125 3.2	0.312 7.9

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- AS50151 crimp
- EN2997 & EN3646
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection



Dimensions



Dash number	Shell size	Style	B $\pm 0.062"/1.57$ inches mm	C reference inches mm	$\varnothing$ D max inches mm	E $\pm 0.125"/3.17$ inches mm	F max inches mm	Cable entry min inches mm	Cable entry max inches mm
3	8	1	1.182 30.02	1.544 39.21	0.617 15.67	0.500 12.70	2.88 73.15	0.125 3.2	0.250 6.4
4	10	1	1.850 46.99	1.544 39.21	0.734 18.64	0.561 14.24	3.41 86.61	0.125 3.2	0.312 7.9
5	10	1	1.245 31.62	1.544 39.21	0.734 18.64	0.561 14.24	3.05 77.46	0.250 6.4	0.375 9.5
6	12	1	1.910 48.51	1.544 39.21	0.858 21.79	0.625 15.87	3.52 89.40	0.125 3.2	0.312 7.9
7	12	1	1.910 48.51	1.544 39.21	0.858 21.79	0.625 15.87	3.58 90.93	0.250 6.4	0.437 11.1
8	12	1	1.910 48.51	1.844 46.83	0.858 21.79	0.625 15.87	3.86 98.04	0.350 8.9	0.500 12.7
9	14	1	2.000 50.80	1.544 39.21	0.984 24.99	0.688 17.47	3.71 94.23	0.250 6.4	0.437 11.1
10	14	1	1.655 42.03	1.844 46.83	0.984 24.99	0.688 17.47	3.74 94.99	0.350 8.9	0.575 14.6
11	16	1	2.110 53.59	1.544 39.21	1.112 28.24	0.781 19.83	3.88 98.55	0.250 6.4	0.437 11.1
12	16	1	1.750 44.44	1.916 48.66	1.112 28.24	0.781 19.83	4.03 102.36	0.500 12.7	0.700 17.8
13	18	1	2.300 58.41	1.844 46.83	1.218 30.93	0.968 24.58	4.48 113.79	0.350 8.9	0.625 15.9
14	18	1	1.920 48.76	2.000 50.80	1.218 30.93	1.016 25.80	1.97 50.03	0.625 15.9	0.779 19.8

Continued on pages 15 and 16

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/8 series - EMI/RFI environmental backshell - Aluminum 45° (continued)

Dash number	Shell size	Style	B $\pm 0.062"/1.57$ inches mm	C reference inches mm	Ø D max inches mm	E $\pm 0.125"/3.17$ inches mm	F max inches mm	Cable entry min inches mm	Cable entry max inches mm
15	20	1	2.270 57.65	1.844 46.83	1.345 34.16	1.016 25.80	1.80 45.72	0.350 8.9	0.625 15.9
16	20	1	1.920 48.76	2.000 50.80	1.345 34.16	1.016 25.80	1.97 50.03	0.625 15.9	0.904 23.0
17	22	1	2.380 60.45	1.916 48.66	1.468 37.28	1.166 29.61	2.11 53.59	0.500 12.7	0.750 19.1
18	22	1	2.025 51.43	2.230 56.64	1.468 37.28	1.166 29.61	2.29 58.16	0.875 22.2	1.029 26.1
19	24	1	2.380 60.45	1.916 48.66	1.593 40.46	1.166 29.61	2.11 53.59	0.500 12.7	0.750 19.1
20	24	1	2.025 51.43	2.230 56.64	1.593 40.46	1.166 29.61	2.29 58.16	0.875 22.2	1.144 29.1
21	28	1	2.550 64.77	2.000 50.80	1.969 50.01	1.266 32.15	2.33 59.18	0.625 15.9	0.937 23.8
22	28	1	2.195 55.75	2.024 51.40	1.969 50.01	1.266 32.15	2.51 63.75	1.000 25.4	1.375 34.9
23	32	1	2.800 71.11	2.000 50.80	2.219 56.36	1.616 41.04	2.81 71.37	0.625 15.9	0.937 23.8
24	32	1	2.800 71.11	2.230 56.64	2.219 56.36	1.616 41.04	2.81 71.37	0.875 22.2	1.250 31.8
25	32	1	2.445 62.10	2.550 64.77	2.219 56.36	1.616 41.04	3.07 77.97	1.250 31.8	1.625 41.3
26	36	1	2.770 70.35	2.000 50.80	2.469 62.71	1.816 46.12	3.13 79.50	0.625 15.9	0.937 23.8
27	36	1	2.770 70.35	2.024 51.40	2.469 62.71	1.816 46.12	3.13 79.50	1.000 25.4	1.375 34.9
28	36	1	2.415 61.34	2.600 66.03	2.489 63.22	1.816 46.12	3.39 86.10	1.437 36.5	1.840 46.7
29	40	1	2.770 70.35	2.000 50.80	2.719 69.06	2.566 65.17	3.88 98.55	0.625 15.9	0.937 23.8
30	40	1	2.770 70.35	2.024 51.40	2.719 69.06	2.566 65.17	3.88 98.55	1.000 25.4	1.375 34.9
31	40	1	2.415 61.34	2.600 66.03	2.719 69.06	2.566 65.17	4.14 105.15	1.437 36.5	1.875 47.6
32	44	1	2.770 70.35	2.000 50.80	2.969 75.41	2.566 65.17	3.88 98.55	0.625 15.9	0.937 23.8
33	44	1	2.770 70.35	2.024 51.40	2.969 75.41	2.566 65.17	3.88 98.55	1.000 25.4	1.375 34.9
34	44	1	2.415 61.34	2.600 66.03	2.969 75.41	2.566 65.17	4.14 105.15	1.437 36.5	1.875 47.6
35	48	1	2.770 70.35	2.000 50.80	3.219 81.76	2.566 65.17	3.88 98.55	0.625 15.9	0.937 23.8
36	48	1	2.770 70.35	2.024 51.40	3.219 81.76	2.566 65.17	3.88 98.55	1.000 25.4	1.375 34.9
37	48	1	2.415 61.34	2.600 66.03	3.219 81.76	2.566 65.17	4.14 105.15	1.437 36.5	1.875 47.6
40	16	1	2.100 53.33	1.844 46.83	1.112 28.24	0.926 23.52	1.66 42.16	0.350 8.9	0.625 15.9
41	18	1	2.270 57.65	1.544 39.21	1.218 30.93	1.016 25.80	1.80 45.72	0.125 3.2	0.312 7.9
42	18	1	2.270 57.65	1.544 39.21	1.218 30.93	1.016 25.80	1.80 45.72	0.250 6.4	0.437 11.1
43	20	1	2.270 57.65	1.544 39.21	1.345 34.16	1.016 25.80	1.80 45.72	0.250 6.4	0.437 11.1
44	22	1	2.380 60.45	1.544 39.21	1.488 37.79	1.166 29.61	2.11 53.59	0.125 3.2	0.312 7.9
45	22	1	2.380 60.45	1.544 39.21	1.468 37.28	1.166 29.61	2.11 53.59	0.250 6.4	0.437 11.1
46	24	1	2.380 60.45	1.844 46.83	1.593 40.46	1.166 29.61	2.11 53.59	0.350 8.9	0.625 15.9
47	36	1	2.770 57.65	1.916 48.66	2.469 62.71	1.816 46.12	3.13 79.50	0.500 12.7	0.750 19.1
48	40	1	2.770 70.35	1.916 48.66	2.719 69.06	1.816 46.12	3.88 98.55	0.500 12.7	0.750 19.1
49	10	2	1.940 49.27	1.544 39.21	0.734 18.64	1.391 35.33	2.03 51.56	0.250 6.4	0.437 11.1
50	14	2	2.270 57.65	1.916 48.66	0.984 24.99	1.766 44.85	2.61 66.29	0.500 12.7	0.750 19.1
51	16	2	2.380 60.45	2.000 50.80	1.112 28.24	1.916 48.66	2.87 72.89	0.625 15.9	0.937 23.8
52	18	1	2.270 57.65	1.916 48.66	1.218 30.93	1.016 25.80	1.86 47.24	0.500 12.7	0.750 19.1
54	20	1	2.270 57.65	1.916 48.66	1.345 34.16	1.016 25.80	1.86 47.24	0.500 12.7	0.750 19.1
55	20	2	2.550 64.77	2.230 56.64	1.345 34.16	2.016 51.20	3.14 79.75	0.875 22.2	1.250 31.8
56	22	1	2.380 60.45	1.844 46.83	1.468 37.28	1.166 29.61	2.11 53.59	0.350 8.9	0.625 15.9
57	22	1	2.380 60.45	2.000 50.80	1.468 37.28	1.166 29.61	2.12 53.84	0.625 15.9	0.937 23.8
58	22	2	2.550 64.77	2.230 56.64	1.468 37.28	2.016 51.20	3.14 79.75	0.875 22.2	1.250 31.8
59	24	1	2.380 60.45	2.000 50.80	1.593 40.46	1.166 29.61	2.14 54.35	0.625 15.9	0.937 23.8
60	28	1	2.550 64.77	1.916 48.66	1.969 50.01	1.266 30.88	2.33 59.18	0.500 12.7	0.750 19.1

Continued on page 16

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/8 Series - Environmental backshell - Aluminum 45° (continued)

Dash number	Shell size	Style	B $\pm 0.062"/1.57$		C reference		$\varnothing$ D max		E $\pm 0.125"/3.17$		F max		Cable entry min		Cable entry max	
			inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
61	28	1	2.550	64.77	2.230	56.64	1.969	50.01	1.266	30.88	2.39	60.70	0.875	22.2	1.250	31.8
62	32	1	2.800	71.11	2.024	51.40	2.219	56.36	1.616	41.04	2.86	72.64	1.000	25.4	1.375	34.9
63	36	1	2.770	70.35	2.230	56.64	2.469	62.71	1.816	46.12	3.13	79.50	0.875	22.2	1.250	31.8
64	36	1	2.770	70.35	2.550	64.77	2.469	62.71	1.816	46.12	3.27	83.05	1.250	31.8	1.625	41.3
65	40	1	2.770	70.35	2.230	56.64	2.719	69.06	2.566	65.17	3.88	98.55	0.875	22.2	1.250	31.8
66	40	1	2.770	70.35	2.550	64.77	2.719	69.06	2.566	65.17	4.02	102.10	1.250	31.8	1.625	41.3
67	44	1	2.770	70.35	2.230	56.64	2.969	75.41	2.566	65.17	3.88	98.55	0.875	22.2	1.250	31.8
68	44	1	2.770	70.35	2.550	64.77	2.969	75.41	2.566	65.17	4.02	102.10	1.250	31.8	1.625	41.3
69	48	1	2.770	70.35	2.230	56.64	3.219	81.76	2.566	65.17	3.88	98.55	0.875	22.2	1.250	31.8
70	48	1	2.770	70.35	2.550	64.77	3.219	81.76	2.566	65.17	4.02	102.10	1.250	31.8	1.625	41.3
71	12	2	2.100	53.33	1.844	46.83	0.858	21.79	1.686	42.82	2.42	61.46	0.350	8.9	0.625	15.9
72	18	2	2.380	60.45	2.000	50.80	1.218	30.93	1.926	48.92	2.88	73.015	0.625	15.9	0.937	23.8
73	24	2	2.550	64.77	2.230	56.64	1.593	40.46	2.026	51.46	3.15	80.00	0.875	22.2	1.250	31.8
74	14	1	2.010	51.05	1.544	39.21	0.984	24.99	0.741	18.82	1.31	33.27	0.125	3.2	0.312	7.9
75	16	1	2.100	53.33	1.544	39.21	1.112	28.24	0.926	23.52	1.59	40.38	0.125	3.2	0.312	7.9


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/9 Series - Environmental backshell - Aluminum 90°


For connectors:

- AS50151 crimp
- EN2997 & EN3646
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection



Dimensions



Dash number	Shell size	Style	B $\pm 0.062"/1.57$ inches mm	C reference inches mm	$\varnothing$ D max inches mm	E $\pm 0.125"/3.17$ inches mm	F max inches mm	Cable entry min inches mm	Cable entry max inches mm
3	8	1	1.200 30.47	1.027 26.1	0.617 15.67	0.541 13.74	1.48 37.59	0.125 3.2	0.250 6.4
4	10	1	1.920 48.76	1.027 26.1	0.734 18.64	0.636 16.15	1.57 39.87	0.125 3.2	0.312 7.9
5	10	1	1.320 33.52	1.027 26.1	0.734 18.64	0.636 16.15	1.66 42.16	0.250 6.4	0.375 9.5
6	12	1	1.940 49.27	1.027 26.1	0.858 21.79	0.641 16.28	1.57 39.87	0.125 3.2	0.312 7.9
7	12	1	1.940 49.27	1.027 26.1	0.858 21.79	0.641 16.28	1.67 42.41	0.250 6.4	0.437 11.1
8	12	1	1.335 33.90	1.027 26.1	0.858 21.79	0.641 16.28	1.76 44.70	0.350 8.9	0.500 12.7
9	14	1	2.012 51.10	1.027 26.1	0.984 24.99	0.741 18.82	1.77 44.95	0.250 6.4	0.437 11.1
10	14	1	1.655 42.03	1.027 26.1	0.984 24.99	0.741 18.82	1.86 47.24	0.350 8.9	0.575 14.6
11	16	1	2.100 53.33	1.027 26.1	1.112 28.24	0.926 23.52	1.98 50.29	0.250 6.4	0.437 11.1
12	16	1	1.745 44.32	1.059 26.9	1.112 28.24	0.926 23.52	2.16 54.86	0.500 12.7	0.700 17.8
13	18	1	2.270 57.65	1.027 26.1	1.218 30.93	1.016 25.80	2.19 55.62	0.350 8.9	0.625 15.9
14	18	1	1.920 48.76	1.156 29.4	1.218 30.93	1.016 25.80	2.36 59.94	0.625 15.9	0.779 19.8

Continued on pages 18 and 19

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/9 Series - Environmental backshell - Aluminum 90° (continued)

Dash number	Shell size	Style	B $\pm 0.062/1.57$ inches mm	C reference inches mm	Ø D max inches mm	E $\pm 0.125/3.17$ inches mm	H max inches mm	Cable entry min inches mm	Cable entry max inches mm
15	20	1	2.270 57.65	1.027 26.1	1.345 34.16	1.016 25.80	2.19 55.62	0.350 8.9	0.625 15.9
16	20	1	1.920 48.76	1.156 29.4	1.345 34.16	1.016 25.80	2.36 59.94	0.625 15.9	0.904 23.0
17	22	1	2.380 60.45	1.059 26.9	1.468 37.28	1.166 29.61	2.50 63.50	0.500 12.7	0.750 19.1
18	22	1	2.025 51.43	1.375 34.9	1.468 37.28	1.166 29.61	2.68 68.07	0.875 22.2	1.029 26.1
19	24	1	2.380 60.45	1.059 26.9	1.593 40.46	1.166 29.61	2.50 63.50	0.500 12.7	0.750 19.1
20	24	1	2.025 51.43	1.375 34.9	1.593 40.46	1.166 29.61	2.68 68.07	0.875 22.2	1.144 29.1
21	28	1	2.550 64.77	1.156 29.4	1.969 50.01	1.266 32.15	2.88 73.15	0.625 15.9	0.937 23.8
22	28	1	2.195 55.75	1.500 38.1	1.969 50.01	1.266 32.15	3.06 77.72	1.000 25.4	1.375 34.9
23	32	1	2.800 71.11	1.156 29.4	2.219 56.36	1.616 41.04	3.36 85.34	0.625 15.9	0.937 23.8
24	32	1	2.800 71.11	1.375 34.9	2.219 56.36	1.616 41.04	3.36 85.34	0.875 22.2	1.250 31.8
25	32	1	2.445 62.10	1.781 45.2	2.219 56.36	1.616 41.04	3.62 91.94	1.250 31.8	1.625 41.3
26	36	1	2.770 70.35	1.156 29.4	2.469 62.71	1.816 46.12	3.68 93.47	0.625 15.9	0.937 23.8
27	36	1	2.770 70.35	1.500 38.1	2.469 62.71	1.816 46.12	3.68 93.47	1.000 25.4	1.375 34.9
28	36	1	2.415 61.34	1.830 46.5	2.489 63.22	1.816 46.12	3.94 100.07	1.437 36.5	1.840 46.7
29	40	1	2.770 70.35	1.156 29.4	2.719 69.06	2.566 65.17	4.43 112.52	0.625 15.9	0.937 23.8
30	40	1	2.770 70.35	1.500 38.1	2.719 69.06	2.566 65.17	4.43 112.52	1.000 25.4	1.375 34.9
31	40	1	2.415 61.34	1.830 46.5	2.719 69.06	2.566 65.17	4.69 119.12	1.437 36.5	1.875 47.6
32	44	1	2.770 70.35	1.156 29.4	2.969 75.41	2.566 65.17	4.43 112.52	0.625 15.9	0.937 23.8
33	44	1	2.770 70.35	1.500 38.1	2.969 75.41	2.566 65.17	4.43 112.52	1.000 25.4	1.375 34.9
34	44	1	2.415 61.34	1.830 46.5	2.969 75.41	2.566 65.17	4.69 119.12	1.437 36.5	1.875 47.6
35	48	1	2.770 70.35	1.156 29.4	3.219 81.76	2.566 65.17	4.43 112.52	0.625 15.9	0.937 23.8
36	48	1	2.770 70.35	1.500 38.1	3.219 81.76	2.566 65.17	4.43 112.52	1.000 25.4	1.375 34.9
37	48	1	2.415 61.34	1.830 46.5	3.219 81.76	2.566 65.17	4.69 119.12	1.437 36.5	1.875 47.6
40	16	1	2.100 53.33	1.027 26.1	1.112 28.24	0.926 23.52	2.05 52.06	0.350 8.9	0.625 15.9
41	18	1	2.270 57.65	1.027 26.1	1.218 30.93	1.016 25.80	2.19 55.62	0.125 3.2	0.312 7.9
42	18	1	2.270 57.65	1.027 26.1	1.218 30.93	1.016 25.80	2.19 55.62	0.250 6.4	0.437 11.1
43	20	1	2.270 57.65	1.027 26.1	1.345 34.16	1.016 25.80	2.19 55.62	0.250 6.4	0.437 11.1
44	22	1	2.380 60.45	1.027 26.1	1.488 37.79	1.166 29.61	2.50 63.50	0.125 3.2	0.312 7.9
45	22	1	2.380 60.45	1.027 26.1	1.468 37.28	1.166 29.61	2.50 63.50	0.250 6.4	0.437 11.1
46	24	1	2.380 60.45	1.027 26.1	1.593 40.46	1.166 29.61	2.50 63.50	0.350 8.9	0.625 15.9
47	36	1	2.770 57.65	1.059 26.9	2.469 62.71	1.816 46.12	3.68 93.47	0.500 12.7	0.750 19.1
48	40	1	2.770 70.35	1.059 26.9	2.719 69.06	1.816 46.12	4.43 112.52	0.500 12.7	0.750 19.1
49	10	2	1.940 49.27	1.027 26.1	0.734 18.64	1.391 35.33	2.42 61.46	0.250 6.4	0.437 11.1
50	14	2	2.270 57.65	1.059 26.9	0.984 24.99	1.766 44.85	3.00 76.19	0.500 12.7	0.750 19.1
51	16	2	2.380 60.45	1.156 29.4	1.112 28.24	1.916 48.66	3.26 82.80	0.625 15.9	0.937 23.8
52	18	1	2.270 57.65	1.059 26.9	1.218 30.93	1.016 25.80	2.25 57.15	0.500 12.7	0.750 19.1
54	20	1	2.270 57.65	1.059 26.9	1.345 34.16	1.016 25.80	2.25 57.15	0.500 12.7	0.750 19.1
55	20	2	2.550 64.77	1.375 34.9	1.345 34.16	2.016 51.20	3.53 64.26	0.875 22.2	1.250 31.8
56	22	1	2.380 60.45	1.027 26.1	1.468 37.28	1.166 29.61	2.50 63.50	0.350 8.9	0.625 15.9
57	22	1	2.380 60.45	1.156 29.4	1.468 37.28	1.166 29.61	2.51 63.75	0.625 15.9	0.937 23.8
58	22	2	2.550 64.77	1.375 34.9	1.468 37.28	2.016 51.20	3.53 64.26	0.875 22.2	1.250 31.8
59	24	1	2.380 60.45	1.156 29.4	1.593 40.46	1.166 29.61	2.53 64.26	0.625 15.9	0.937 23.8
60	28	1	2.550 64.77	1.059 26.9	1.969 50.01	1.266 30.88	2.88 73.15	0.500 12.7	0.750 19.1

Continued on page 19

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/9 Series - Environmental backshell - Aluminum 90° (continued)


Dash number	Shell size	Style	B $\pm 0.062"/1.57$		C reference		$\varnothing$ D max		E $\pm 0.125"/3.17$		H max		Cable entry min		Cable entry max	
			inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
61	28	1	2.550	64.77	1.375	34.9	1.969	50.01	1.266	30.88	2.94	74.67	0.875	22.2	1.250	31.8
62	32	1	2.800	71.11	1.500	38.1	2.219	56.36	1.616	41.04	3.41	86.61	1.000	25.4	1.375	34.9
63	36	1	2.770	70.35	1.375	34.9	2.469	62.71	1.816	46.12	3.68	93.47	0.875	22.2	1.250	31.8
64	36	1	2.770	70.35	1.781	45.2	2.469	62.71	1.816	46.12	3.82	97.02	1.250	31.8	1.625	41.3
65	40	1	2.770	70.35	1.375	34.9	2.719	69.06	2.566	65.17	4.43	112.52	0.875	22.2	1.250	31.8
66	40	1	2.770	70.35	1.781	45.2	2.719	69.06	2.566	65.17	4.57	116.07	1.250	31.8	1.625	41.3
67	44	1	2.770	70.35	1.375	34.9	2.969	75.41	2.566	65.17	4.43	112.52	0.875	22.2	1.250	31.8
68	44	1	2.770	70.35	1.781	45.2	2.969	75.41	2.566	65.17	4.57	116.07	1.250	31.8	1.625	41.3
69	48	1	2.770	70.35	1.375	34.9	3.219	81.76	2.566	65.17	4.43	112.52	0.875	22.2	1.250	31.8
70	48	1	2.770	70.35	1.781	45.2	3.219	81.76	2.566	65.17	4.57	116.07	1.250	31.8	1.625	41.3
71	12	2	2.100	53.33	1.027	26.1	0.858	21.79	1.686	42.82	2.81	71.37	0.350	8.9	0.625	15.9
72	18	2	2.380	60.45	1.156	29.4	1.218	30.93	1.926	48.92	3.27	83.05	0.625	15.9	0.937	23.8
73	24	2	2.550	64.77	1.375	34.9	1.593	40.46	2.026	51.46	3.54	89.91	0.875	22.2	1.250	31.8
74	14	1	2.010	51.05	1.027	26.1	0.984	24.99	0.741	18.82	1.70	43.18	0.125	3.2	0.312	7.9
75	16	1	2.100	53.33	1.027	26.1	1.112	28.24	0.926	23.52	1.98	50.29	0.125	3.2	0.312	7.9

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- AS50151 crimp
- EN2997 & EN3646
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection



Dimensions



Dash number	Shell size	Style	B $\pm 0.125/3.17$ inches mm	C reference inches mm	$\varnothing$ D max inches mm	Cable entry min inches mm	Cable entry max inches mm
5	8	1	2.00 50.80	1.544 39.21	0.617 15.67	0.125 3.2	0.250 6.4
6	8	1	3.00 76.19	1.544 39.21	0.617 15.67	0.125 3.2	0.250 6.4
7	8	2	2.75 69.85	1.544 39.21	0.617 15.67	0.250 6.4	0.437 11.1
8	8	2	3.75 95.25	1.544 39.21	0.617 15.67	0.250 6.4	0.437 11.1
9	10	1	2.00 50.80	1.544 39.21	0.734 18.64	0.125 3.2	0.312 7.9
10	10	1	3.00 76.19	1.544 39.21	0.734 18.64	0.125 3.2	0.312 7.9
11	10	2	2.75 69.85	1.544 39.21	0.734 18.64	0.250 6.4	0.437 11.1
12	10	2	3.75 95.25	1.544 39.21	0.734 18.64	0.250 6.4	0.437 11.1
13	12	1	2.00 50.80	1.544 39.21	0.858 21.79	0.250 6.4	0.437 11.1
14	12	1	3.00 76.19	1.544 39.21	0.858 21.79	0.250 6.4	0.437 11.1
15	12	2	2.75 69.85	1.844 46.83	0.858 21.79	0.350 8.9	0.625 15.9
16	12	2	3.75 95.25	1.844 46.83	0.858 21.79	0.350 8.9	0.625 15.9
17	14	1	2.00 50.80	1.844 46.83	0.984 24.99	0.350 8.9	0.625 15.9
18	14	1	3.00 76.19	1.844 46.83	0.984 24.99	0.350 8.9	0.575 14.6
19	14	2	2.75 69.85	1.916 48.66	0.984 24.99	0.500 12.7	0.750 19.1
20	14	2	3.75 95.25	1.916 48.66	0.984 24.99	0.500 12.7	0.750 19.1

Continued on pages 21 to 23

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/10 Series - EMI/RFI environmental backshell - Aluminum straight (continued)

Dash number	Shell size	Style	B $\pm 0.125/3.17$ inches mm	C reference inches mm	Ø D max inches mm	Cable entry min inches mm	Cable entry max inches mm
21	16	1	2.00 50.80	1.916 48.66	1.112 28.24	0.500 12.7	0.700 17.8
22	16	1	3.00 76.19	1.916 48.66	1.112 28.24	0.500 12.7	0.700 17.8
23	16	2	2.75 69.85	2.000 50.80	1.112 28.24	0.625 15.9	0.937 23.8
24	16	2	3.75 95.25	2.000 50.80	1.112 28.24	0.625 15.9	0.937 23.8
25	18	1	2.00 50.80	1.844 46.83	1.218 30.93	0.350 8.9	0.625 15.9
26	18	1	3.00 76.19	1.844 46.83	1.218 30.93	0.350 8.9	0.625 15.9
27	18	1	2.00 50.80	1.916 48.66	1.218 30.93	0.500 12.7	0.750 19.1
28	18	1	3.00 76.19	1.916 48.66	1.218 30.93	0.500 12.7	0.750 19.1
29	18	1	2.75 69.85	2.000 50.80	1.218 30.93	0.625 15.9	0.937 23.8
30	18	1	3.75 95.25	2.000 50.80	1.218 30.93	0.625 15.9	0.937 23.8
31	20	1	3.00 76.19	1.844 46.83	1.345 34.16	0.350 8.9	0.625 15.9
32	20	1	4.00 101.6	1.844 46.83	1.345 34.16	0.350 8.9	0.625 15.9
33	20	1	3.00 76.19	1.916 48.66	1.345 34.16	0.500 12.7	0.750 19.1
34	20	1	4.00 101.6	1.916 48.66	1.345 34.16	0.500 12.7	0.750 19.1
35	20	2	3.75 95.25	2.000 50.80	1.345 34.16	0.625 15.9	0.937 23.8
36	20	2	4.75 120.65	2.000 50.80	1.345 34.16	0.625 15.9	0.937 23.8
37	20	2	3.75 95.25	2.230 56.64	1.345 34.16	0.875 22.2	1.250 31.7
38	20	2	4.75 120.65	2.230 56.64	1.345 34.16	0.875 22.2	1.250 31.7
39	22	1	3.00 76.19	1.844 46.83	1.468 37.28	0.350 8.9	0.625 15.9
40	22	1	4.00 101.6	1.844 46.83	1.468 37.28	0.350 8.9	0.625 15.9
41	22	1	3.00 76.19	1.916 48.66	1.468 37.28	0.500 12.7	0.750 19.1
42	22	1	4.00 101.6	1.916 48.66	1.468 37.28	0.500 12.7	0.750 19.1
43	22	1	3.00 76.19	2.000 50.80	1.468 37.28	0.625 15.9	0.937 23.8
44	22	1	4.00 101.6	2.000 50.80	1.468 37.28	0.625 15.9	0.937 23.8
45	22	2	3.75 95.25	2.230 56.64	1.468 37.28	0.875 22.2	1.250 31.7
46	22	2	4.75 120.65	2.230 56.64	1.468 37.28	0.875 22.2	1.250 31.7
47	24	1	3.00 76.19	1.916 48.66	1.593 40.46	0.500 12.7	0.750 19.1
48	24	1	4.00 101.6	1.916 48.66	1.593 40.46	0.500 12.7	0.750 19.1
49	24	1	3.00 76.19	2.000 50.80	1.593 40.46	0.625 15.9	0.812 20.6
50	24	1	4.00 101.6	2.000 50.80	1.593 40.46	0.625 15.9	0.812 20.6
51	24	1	4.00 101.6	2.000 50.80	1.593 40.46	0.625 15.9	0.937 23.8
52	24	1	4.00 101.6	2.000 50.80	1.593 40.46	0.625 15.9	0.937 23.8
53	24	2	3.75 95.25	2.230 56.64	1.593 40.46	0.875 22.2	1.250 31.8
54	24	2	4.75 120.65	2.230 56.64	1.593 40.46	0.875 22.2	1.250 31.8
55	28	1	3.00 76.19	1.916 48.66	1.969 50.01	0.500 12.7	0.750 19.1
56	28	1	4.00 101.6	1.916 48.66	1.969 50.01	0.500 12.7	0.750 19.1
57	28	1	3.00 76.19	2.000 50.80	1.969 50.01	0.625 15.9	0.937 23.8
58	28	1	4.00 101.6	2.000 50.80	1.969 50.01	0.625 15.9	0.937 23.8
59	28	1	3.00 76.19	2.230 56.64	1.969 50.01	0.875 22.2	1.250 31.8
60	28	1	4.00 101.6	2.230 56.64	1.969 50.01	0.875 22.2	1.250 31.8
61	28	1	3.00 76.19	2.024 51.40	1.969 50.01	1.000 25.4	1.375 34.9
62	28	1	4.00 101.6	2.024 51.40	1.969 50.01	1.000 25.4	1.375 34.9
63	32	1	3.00 76.19	2.000 50.80	2.219 56.36	0.625 15.9	0.937 23.8

Continued on pages 22 to 23

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/10 Series - EMI/RFI environmental backshell - Aluminum straight (continued)

Dash number	Shell size	Style	B $\pm 0.125/3.17$ inches mm	C reference inches mm	Ø D max inches mm	Cable entry min inches mm	Cable entry max inches mm
64	32	1	4.00 101.6	2.000 50.80	2.219 56.36	0.625 15.9	0.937 23.8
65	32	1	3.00 76.19	2.230 56.64	2.219 56.36	0.875 22.2	1.250 31.8
66	32	1	4.00 101.6	2.230 56.64	2.219 56.36	0.875 22.2	1.250 31.8
67	32	1	3.00 76.19	2.024 51.40	2.219 56.36	1.000 25.4	1.375 34.9
68	32	1	4.00 101.6	2.024 51.40	2.219 56.36	1.000 25.4	1.375 34.9
69	32	1	3.00 76.19	2.550 64.77	2.219 56.36	1.250 31.8	1.625 41.3
70	32	1	4.00 101.6	2.550 64.77	2.219 56.36	1.250 31.8	1.625 41.3
71	36	1	4.00 101.6	2.230 56.64	2.469 62.71	0.875 22.2	1.250 31.8
72	36	1	5.00 127.00	2.230 56.64	2.469 62.71	0.875 22.2	1.250 31.8
73	36	1	4.00 101.6	2.024 51.40	2.469 62.71	1.000 25.4	1.375 34.9
74	36	1	5.00 127.00	2.024 51.40	2.469 62.71	1.000 25.4	1.375 34.9
75	36	1	4.00 101.6	2.550 64.77	2.469 62.71	1.250 31.8	1.625 41.3
76	36	1	5.00 127.00	2.550 64.77	2.469 62.71	1.250 31.8	1.625 41.3
77	36	2	4.88 123.95	2.600 66.03	2.469 62.71	1.437 36.5	1.875 47.6
78	36	2	5.88 149.35	2.600 66.03	2.469 62.71	1.437 36.5	1.875 47.6
79	40	1	4.00 101.6	2.230 56.64	2.719 69.06	0.875 22.2	1.250 31.8
80	40	1	5.00 127.00	2.230 56.64	2.719 69.06	0.875 22.2	1.250 31.8
81	40	1	4.00 101.6	2.024 51.40	2.719 69.06	1.000 25.4	1.375 34.9
82	40	1	5.00 127.00	2.024 51.40	2.719 69.06	1.000 25.4	1.375 34.9
83	40	1	4.00 101.6	2.550 64.77	2.719 69.06	1.250 31.8	1.625 41.3
84	40	1	5.00 127.00	2.550 64.77	2.719 69.06	1.250 31.8	1.625 41.3
85	40	1	4.00 101.6	2.600 66.03	2.719 69.06	1.437 36.5	1.875 47.6
86	40	1	5.00 127.00	2.600 66.03	2.719 69.06	1.437 36.5	1.875 47.6
87	44	1	4.00 101.6	2.230 56.64	2.969 75.41	0.875 22.2	1.250 31.8
88	44	1	5.00 127.00	2.230 56.64	2.969 75.41	0.875 22.2	1.250 31.8
89	44	1	4.00 101.6	2.024 51.40	2.969 75.41	1.000 25.4	1.375 34.9
90	44	1	5.00 127.00	2.024 51.40	2.969 75.41	1.000 25.4	1.375 34.9
91	44	1	4.00 101.6	2.550 64.77	2.969 75.41	1.250 31.8	1.625 41.3
92	44	1	5.00 127.00	2.550 64.77	2.969 75.41	1.250 31.8	1.625 41.3
93	44	1	4.00 101.6	2.600 66.03	2.969 75.41	1.437 36.5	1.875 47.6
94	44	1	5.00 127.00	2.600 66.03	2.969 75.41	1.437 36.5	1.875 47.6
95	48	1	4.00 101.6	2.230 56.64	3.219 81.76	0.875 22.2	1.250 31.8
96	48	1	5.00 127.00	2.230 56.64	3.219 81.76	0.875 22.2	1.250 31.8
97	48	1	4.00 101.6	2.024 51.40	3.219 81.76	1.000 25.4	1.375 34.9
98	48	1	5.00 127.00	2.024 51.40	3.219 81.76	1.000 25.4	1.375 34.9
99	48	1	4.00 101.6	2.550 64.77	3.219 81.76	1.250 31.8	1.625 41.3
100	48	1	5.00 127.00	2.550 64.77	3.219 81.76	1.250 31.8	1.625 41.3
101	48	1	4.00 101.6	2.600 66.03	3.219 81.76	1.437 36.5	1.875 47.6
102	48	1	5.00 127.00	2.600 66.03	3.219 81.76	1.437 36.5	1.875 47.6
111	12	1	2.00 50.80	1.844 46.83	0.858 21.79	0.350 8.9	0.500 12.7
112	16	1	2.00 50.80	1.544 39.21	1.112 28.24	0.250 6.4	0.437 11.1
113	16	1	3.00 76.19	1.544 39.21	1.112 28.24	0.250 6.4	0.437 11.1
114	12	1	2.00 50.80	1.544 39.21	0.858 21.79	0.125 3.2	0.312 7.9

Continued on page 23

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/10 Series - EMI/RFI environmental backshell - Aluminum straight (continued)

Dash number	Shell size	Style	B $\pm 0.125/3.17$		C reference		$\varnothing$ D max		Cable entry min		Cable entry max	
			inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
115	12	1	3.00	76.19	1.544	39.21	0.858	21.79	0.125	3.2	0.312	7.9
116	14	1	2.00	50.80	1.544	39.21	0.984	24.99	0.250	6.4	0.437	11.1
117	14	1	3.00	76.19	1.544	39.21	0.984	24.99	0.250	6.4	0.437	11.1
118	16	1	2.00	50.80	1.844	46.83	1.112	28.24	0.350	8.9	0.625	15.9
119	16	1	3.00	76.19	1.844	46.83	1.112	28.24	0.350	8.9	0.625	15.9
120	18	1	2.00	50.80	1.544	39.21	1.218	30.93	0.125	3.2	0.312	7.9
121	18	1	3.00	76.19	1.544	39.21	1.218	30.93	0.125	2.3	0.312	7.9
122	18	1	2.00	50.80	1.544	39.21	1.218	30.93	0.250	6.4	0.437	11.1
123	18	1	3.00	76.19	1.544	39.21	1.218	30.93	0.250	6.4	0.437	11.1
124	20	1	3.00	76.19	1.544	39.21	1.345	34.16	0.250	6.4	0.437	11.1
125	20	1	4.00	101.6	1.544	39.21	1.345	34.16	0.250	6.4	0.437	11.1
126	22	1	3.00	76.19	1.544	39.21	1.468	37.28	0.125	3.2	0.312	7.9
127	22	1	4.00	101.6	1.544	39.21	1.468	37.28	0.125	3.2	0.312	7.9
128	22	1	3.00	76.19	1.544	39.21	1.468	37.28	0.250	6.4	0.437	11.1
129	22	1	4.00	101.6	1.544	39.21	1.468	37.28	0.250	6.4	0.437	11.1
130	24	1	3.00	76.19	1.844	46.83	1.593	40.46	0.350	8.9	0.625	15.9
131	24	1	4.00	101.6	1.844	46.83	1.593	40.46	0.350	8.9	0.625	15.9
132	36	1	4.00	101.6	1.916	48.66	2.469	62.71	0.500	12.7	0.750	19.1
133	36	1	5.00	127.00	1.916	48.66	2.469	62.71	0.500	12.7	0.750	19.1
134	40	1	4.00	101.6	1.916	48.66	2.719	69.06	0.500	12.7	0.750	19.1
135	40	1	5.00	127.00	1.916	48.66	2.719	69.06	0.500	12.7	0.750	19.1
136	10	1	2.00	50.80	1.544	39.21	0.734	18.64	0.250	6.4	0.375	9.5
137	10	1	3.00	76.19	1.544	39.21	0.734	18.64	0.250	6.4	0.375	9.5
138	12	1	2.00	50.80	1.844	46.83	0.858	21.79	0.350	8.9	0.500	12.7
139	12	1	3.00	76.19	1.844	46.83	0.858	21.79	0.350	8.9	0.500	12.7
140	20	1	3.00	76.19	2.000	50.80	1.345	34.16	0.625	15.9	0.904	23.0
141	20	1	4.00	101.6	2.000	50.80	1.345	34.16	0.625	15.9	0.904	23.0
142	22	1	3.00	76.19	2.230	56.64	1.468	37.28	0.875	22.2	1.029	26.1
143	22	1	4.00	101.6	2.230	56.64	1.468	37.28	0.875	22.2	1.029	26.1
144	24	1	3.00	76.19	2.230	56.64	1.593	40.46	0.875	22.2	1.144	29.1
145	24	1	4.00	101.6	2.230	56.64	1.593	40.46	0.875	22.2	1.144	29.1
146	36	1	4.00	101.6	2.600	66.03	2.469	62.71	1.437	36.5	1.840	46.7
147	36	1	5.00	127.00	2.600	66.03	2.469	62.71	1.437	36.5	1.840	46.7
148	36	1	4.00	101.6	2.000	50.80	2.469	62.71	0.625	15.9	0.937	23.8
149	36	1	5.00	127.00	2.000	50.80	2.469	62.71	0.625	15.9	0.937	23.8
150	14	1	2.00	50.80	1.544	39.21	0.984	24.99	0.125	3.2	0.312	7.9
151	14	1	3.00	76.19	1.544	39.21	0.984	24.99	0.125	3.2	0.312	7.9
152	16	1	2.00	50.80	1.544	39.21	1.112	28.24	0.125	3.2	0.312	7.9
153	16	1	3.00	76.19	1.544	39.21	1.112	28.24	0.125	3.2	0.312	7.9
154	44	1	4.00	101.6	2.000	50.80	2.969	75.41	0.625	15.9	0.937	23.8
155	44	1	5.00	127.00	2.000	50.80	2.969	75.41	0.625	15.9	0.937	23.8
156	40	1	4.00	101.6	2.000	50.80	2.719	69.06	0.625	15.9	0.937	23.8
157	40	1	5.00	127.00	2.000	50.80	2.719	69.06	0.625	15.9	0.937	23.8

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

For connectors:

- AS50151 crimp
- EN2997 & EN3646
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3
- AS81703 Series 3


Catalog number selection

M85049/11 24 W

Dash number
5 to 157

Material and plating
B = Stainless steel, black cadmium
N = Aluminum, electroless nickel
S = Stainless steel, passivated
W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray

Dimensions



Dash number	Shell size	Style	B $\pm 0.125/3.17$ inches mm	C reference inches mm	$\varnothing$ D max inches mm	Cable entry min inches mm	Cable entry max inches mm
5	8	1	2.00 50.80	1.027 26.08	0.617 15.67	0.125 3.2	0.250 6.4
6	8	1	3.00 76.19	1.027 26.08	0.617 15.67	0.125 3.2	0.312 7.9
7	8	2	2.75 69.85	1.027 26.08	0.617 15.67	0.250 6.4	0.437 11.1
8	8	2	3.75 95.25	1.027 26.08	0.617 15.67	0.250 6.4	0.437 11.1
9	10	1	2.00 50.80	1.027 26.08	0.734 18.64	0.125 3.2	0.312 7.9
10	10	1	3.00 76.19	1.027 26.08	0.734 18.64	0.125 3.2	0.312 7.9
11	10	2	2.75 69.85	1.027 26.08	0.734 18.64	0.250 6.4	0.437 11.1
12	10	2	3.75 95.25	1.027 26.08	0.734 18.64	0.250 6.4	0.437 11.1
13	12	1	2.00 50.80	1.027 26.08	0.858 21.79	0.250 6.4	0.437 11.1
14	12	1	3.00 76.19	1.027 26.08	0.858 21.79	0.250 6.4	0.437 11.1
15	12	2	2.75 69.85	1.027 26.08	0.858 21.79	0.350 8.9	0.625 15.9
16	12	2	3.75 95.25	1.027 26.08	0.858 21.79	0.350 8.9	0.625 15.9
17	14	1	2.00 50.80	1.027 26.08	0.984 24.99	0.350 8.9	0.575 14.6
18	14	1	3.00 76.19	1.027 26.08	0.984 24.99	0.350 8.9	0.575 14.6
19	14	2	2.75 69.85	1.059 26.89	0.984 24.99	0.500 12.7	0.750 19.1
20	14	2	3.75 95.25	1.059 26.89	0.984 24.99	0.500 12.7	0.750 19.1

Continued on pages 25 to 27

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/11 Series - Environmental backshell - Aluminum straight (continued)

Dash number	Shell size	Style	B $\pm 0.125/3.17$ inches mm	C reference inches mm	Ø D max inches mm	Cable entry min inches mm	Cable entry max inches mm
21	16	1	2.00 50.80	1.059 26.89	1.112 28.24	0.500 12.7	0.700 17.8
22	16	1	3.00 76.19	1.059 26.89	1.112 28.24	0.500 12.7	0.700 17.8
23	16	2	2.75 69.85	1.156 29.36	1.112 28.24	0.625 15.9	0.937 23.8
24	16	2	3.75 95.25	1.156 29.36	1.112 28.24	0.625 15.9	0.937 23.8
25	18	1	2.00 50.80	1.027 26.08	1.218 30.93	0.350 8.9	0.625 15.9
26	18	1	3.00 76.19	1.027 26.08	1.218 30.93	0.350 8.9	0.625 15.9
27	18	1	2.00 50.80	1.059 26.89	1.218 30.93	0.500 12.7	0.750 19.1
28	18	1	3.00 76.19	1.059 26.89	1.218 30.93	0.500 12.7	0.750 19.1
29	18	1	2.75 69.85	1.156 29.36	1.218 30.93	0.625 15.9	0.937 23.8
30	18	1	3.75 95.25	1.156 29.36	1.218 30.93	0.625 15.9	0.937 23.8
31	20	1	3.00 76.19	1.027 26.08	1.345 34.16	0.350 8.9	0.625 15.9
32	20	1	4.00 101.6	1.027 26.08	1.345 34.16	0.350 8.9	0.625 15.9
33	20	1	3.00 76.19	1.059 26.89	1.345 34.16	0.500 12.7	0.750 19.1
34	20	1	4.00 101.6	1.059 26.89	1.345 34.16	0.500 12.7	0.750 19.1
35	20	2	3.75 95.25	1.156 29.36	1.345 34.16	0.625 15.9	0.937 23.8
36	20	2	4.75 120.65	1.156 29.36	1.345 34.16	0.625 15.9	0.937 23.8
37	20	2	3.75 95.25	1.375 34.92	1.345 34.16	0.875 22.2	1.250 31.8
38	20	2	4.75 120.65	1.375 34.92	1.345 34.16	0.875 22.2	1.250 31.8
39	22	1	3.00 76.19	1.027 26.08	1.468 37.28	0.350 8.9	0.625 15.9
40	22	1	4.00 101.6	1.027 26.08	1.468 37.28	0.350 8.9	0.625 15.9
41	22	1	3.00 76.19	1.059 26.89	1.468 37.28	0.500 12.7	0.750 19.1
42	22	1	4.00 101.6	1.059 26.89	1.468 37.28	0.500 12.7	0.750 19.1
43	22	1	3.00 76.19	1.156 29.36	1.468 37.28	0.625 15.9	0.937 23.8
44	22	1	4.00 101.6	1.156 29.36	1.468 37.28	0.625 15.9	0.937 23.8
45	22	2	3.75 95.25	1.375 34.92	1.468 37.28	0.875 22.2	1.250 31.8
46	22	2	4.75 120.65	1.375 34.92	1.468 37.28	0.875 22.2	1.250 31.8
47	24	1	3.00 76.19	1.059 26.89	1.593 40.46	0.500 12.7	0.750 19.1
48	24	1	4.00 101.6	1.059 26.89	1.593 40.46	0.500 12.7	0.750 19.1
49	24	1	3.00 76.19	1.156 29.36	1.593 40.46	0.625 15.9	0.812 20.6
50	24	1	4.00 101.6	1.156 29.36	1.593 40.46	0.625 15.9	0.812 20.6
51	24	1	4.00 101.6	1.156 29.36	1.593 40.46	0.625 15.9	0.937 23.8
52	24	1	4.00 101.6	1.156 29.36	1.593 40.46	0.625 15.9	0.937 23.8
53	24	2	3.75 95.25	1.375 34.92	1.593 40.46	0.875 22.2	1.250 31.8
54	24	2	4.75 120.65	1.375 34.92	1.593 40.46	0.875 22.2	1.250 31.8
55	28	1	3.00 76.19	1.059 26.89	1.969 50.01	0.500 12.7	0.750 19.1
56	28	1	4.00 101.6	1.059 26.89	1.969 50.01	0.500 12.7	0.750 19.1
57	28	1	3.00 76.19	1.156 29.36	1.969 50.01	0.625 15.9	0.937 23.8
58	28	1	4.00 101.6	1.156 29.36	1.969 50.01	0.625 15.9	0.937 23.8
59	28	1	3.00 76.19	1.375 34.92	1.969 50.01	0.875 22.2	1.250 31.8
60	28	1	4.00 101.6	1.375 34.92	1.969 50.01	0.875 22.2	1.250 31.8
61	28	1	3.00 76.19	1.500 38.09	1.969 50.01	1.000 25.4	1.375 34.9
62	28	1	4.00 101.6	1.500 38.09	1.969 50.01	1.000 25.4	1.375 34.9
63	32	1	3.00 76.19	1.156 29.36	2.219 56.36	0.625 15.9	0.937 23.8

Continued on pages 26 to 27

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/11 Series - Environmental backshell - Aluminum straight (continued)

Dash number	Shell size	Style	B $\pm 0.125/3.17$		C reference		$\varnothing$ D max		Cable entry min		Cable entry max	
			inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
64	32	1	4.00	101.6	1.156	29.36	2.219	56.36	0.625	15.9	0.937	23.8
65	32	1	3.00	76.19	1.375	34.92	2.219	56.36	0.875	22.2	1.250	31.8
66	32	1	4.00	101.6	1.375	34.92	2.219	56.36	0.875	22.2	1.250	31.8
67	32	1	3.00	76.19	1.500	38.09	2.219	56.36	1.000	25.4	1.375	34.9
68	32	1	4.00	101.6	1.500	38.09	2.219	56.36	1.000	25.4	1.375	34.9
69	32	1	3.00	76.19	1.781	45.23	2.219	56.36	1.250	31.8	1.625	41.3
70	32	1	4.00	101.6	1.781	45.23	2.219	56.36	1.250	31.8	1.625	41.3
71	36	1	4.00	101.6	1.375	34.92	2.469	62.71	0.875	22.2	1.250	31.8
72	36	1	5.00	127.00	1.375	34.92	2.469	62.71	0.875	22.2	1.250	31.8
73	36	1	4.00	101.6	1.500	38.09	2.469	62.71	1.000	25.4	1.375	34.9
74	36	1	5.00	127.00	1.500	38.09	2.469	62.71	1.000	25.4	1.375	34.9
75	36	1	4.00	101.6	1.781	45.23	2.469	62.71	1.250	31.8	1.625	41.3
76	36	1	5.00	127.00	1.781	45.23	2.469	62.71	1.250	31.8	1.625	41.3
77	36	2	4.88	123.95	1.830	45.48	2.469	62.71	1.437	36.5	1.875	47.6
78	36	2	5.88	149.35	1.830	45.48	2.469	62.71	1.437	36.5	1.875	47.6
79	40	1	4.00	101.6	1.375	34.92	2.719	69.06	0.875	22.2	1.250	31.8
80	40	1	5.00	127.00	1.375	34.92	2.719	69.06	0.875	22.2	1.250	31.8
81	40	1	4.00	101.6	1.500	38.09	2.719	69.06	1.000	25.4	1.375	34.9
82	40	1	5.00	127.00	1.500	38.09	2.719	69.06	1.000	25.4	1.375	34.9
83	40	1	4.00	101.6	1.781	45.23	2.719	69.06	1.250	31.8	1.625	41.3
84	40	1	5.00	127.00	1.781	45.23	2.719	69.06	1.250	31.8	1.625	41.3
85	40	1	4.00	101.6	1.830	45.48	2.719	69.06	1.437	36.5	1.875	47.6
86	40	1	5.00	127.00	1.830	45.48	2.719	69.06	1.437	36.5	1.875	47.6
87	44	1	4.00	101.6	1.375	34.92	2.969	75.41	0.875	22.2	1.250	31.8
88	44	1	5.00	127.00	1.375	34.92	2.969	75.41	0.875	22.2	1.250	31.8
89	44	1	4.00	101.6	1.500	38.09	2.969	75.41	1.000	25.4	1.375	34.9
90	44	1	5.00	127.00	1.500	38.09	2.969	75.41	1.000	25.4	1.375	34.9
91	44	1	4.00	101.6	1.781	45.23	2.969	75.41	1.250	31.8	1.625	41.3
92	44	1	5.00	127.00	1.781	45.23	2.969	75.41	1.250	31.8	1.625	41.3
93	44	1	4.00	101.6	1.830	45.48	2.969	75.41	1.437	36.5	1.875	47.6
94	44	1	5.00	127.00	1.830	45.48	2.969	75.41	1.437	36.5	1.875	47.6
95	48	1	4.00	101.6	1.375	34.92	3.219	81.76	0.875	22.2	1.250	31.8
96	48	1	5.00	127.00	1.375	34.92	3.219	81.76	0.875	22.2	1.250	31.8
97	48	1	4.00	101.6	1.500	38.09	3.219	81.76	1.000	25.4	1.375	34.9
98	48	1	5.00	127.00	1.500	38.09	3.219	81.76	1.000	25.4	1.375	34.9
99	48	1	4.00	101.6	1.781	45.23	3.219	81.76	1.250	31.8	1.625	41.3
100	48	1	5.00	127.00	1.781	45.23	3.219	81.76	1.250	31.8	1.625	41.3
101	48	1	4.00	101.6	1.830	45.48	3.219	81.76	1.437	36.5	1.875	47.6
102	48	1	5.00	127.00	1.830	45.48	3.219	81.76	1.437	36.5	1.875	47.6
111	12	1	2.00	50.80	1.027	26.08	0.858	21.79	0.350	8.9	0.500	12.7
112	16	1	2.00	50.80	1.027	26.08	1.112	28.24	0.250	6.4	0.437	11.1
113	16	1	3.00	76.19	1.027	26.08	1.112	28.24	0.250	6.4	0.437	11.1
114	12	1	2.00	50.80	1.027	26.08	0.858	21.79	0.125	3.2	0.312	7.9

Continued on page 27

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.



AS85049/11 Series - Environmental backshell - Aluminum straight (continued)

Dash number	Shell size	Style	B $\pm 0.125/3.17$		C reference		$\varnothing$ D max		Cable entry min		Cable entry max	
			inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
115	12	1	3.00	76.19	1.027	26.08	0.858	21.79	0.125	3.2	0.312	7.9
116	14	1	2.00	50.80	1.027	26.08	0.984	24.99	0.250	6.4	0.437	11.1
117	14	1	3.00	76.19	1.027	26.08	0.984	24.99	0.250	6.4	0.437	11.1
118	16	1	2.00	50.80	1.027	26.08	1.112	28.24	0.350	8.9	0.625	15.9
119	16	1	3.00	76.19	1.027	26.08	1.112	28.24	0.350	8.9	0.625	15.9
120	18	1	2.00	50.80	1.027	26.08	1.218	30.93	0.125	3.2	0.312	7.9
121	18	1	3.00	76.19	1.027	26.08	1.218	30.93	0.125	2.3	0.312	7.9
122	18	1	2.00	50.80	1.027	26.08	1.218	30.93	0.250	6.4	0.437	11.1
123	18	1	3.00	76.19	1.027	26.08	1.218	30.93	0.250	6.4	0.437	11.1
124	20	1	3.00	76.19	1.027	26.08	1.345	34.16	0.250	6.4	0.437	11.1
125	20	1	4.00	101.6	1.027	26.08	1.345	34.16	0.250	6.4	0.437	11.1
126	22	1	3.00	76.19	1.027	26.08	1.468	37.28	0.125	3.2	0.312	7.9
127	22	1	4.00	101.6	1.027	26.08	1.468	37.28	0.125	3.2	0.312	7.9
128	22	1	3.00	76.19	1.027	26.08	1.468	37.28	0.250	6.4	0.437	11.1
129	22	1	4.00	101.6	1.027	26.08	1.468	37.28	0.250	6.4	0.437	11.1
130	24	1	3.00	76.19	1.027	26.08	1.593	40.46	0.350	8.9	0.625	15.9
131	24	1	4.00	101.6	1.027	26.08	1.593	40.46	0.350	8.9	0.625	15.9
132	36	1	4.00	101.6	1.059	26.89	2.469	62.71	0.500	12.7	0.750	19.1
133	36	1	5.00	127.00	1.059	26.89	2.469	62.71	0.500	12.7	0.750	19.1
134	40	1	4.00	101.6	1.059	26.89	2.719	69.06	0.500	12.7	0.750	19.1
135	40	1	5.00	127.00	1.059	26.89	2.719	69.06	0.500	12.7	0.750	19.1
136	10	1	2.00	50.80	1.027	26.08	0.734	18.64	0.250	6.4	0.375	9.5
137	10	1	3.00	76.19	1.027	26.08	0.734	18.64	0.250	6.4	0.375	9.5
138	12	1	2.00	50.80	1.027	26.08	0.858	21.79	0.350	8.9	0.500	12.7
139	12	1	3.00	76.19	1.027	26.08	0.858	21.79	0.350	8.9	0.500	12.7
140	20	1	3.00	76.19	1.156	29.36	1.345	34.16	0.625	15.9	0.904	23.0
141	20	1	4.00	101.6	1.156	29.36	1.345	34.16	0.625	15.9	0.904	23.0
142	22	1	3.00	76.19	1.375	34.92	1.468	37.28	0.875	22.2	1.029	26.1
143	22	1	4.00	101.6	1.375	34.92	1.468	37.28	0.875	22.2	1.029	26.1
144	24	1	3.00	76.19	1.375	34.92	1.593	40.46	0.875	22.2	1.144	29.1
145	24	1	4.00	101.6	1.375	34.92	1.593	40.46	0.875	22.2	1.144	29.1
146	36	1	4.00	101.6	1.830	45.48	2.469	62.71	1.437	36.5	1.840	46.7
147	36	1	5.00	127.00	1.830	45.48	2.469	62.71	1.437	36.5	1.840	46.7
148	36	1	4.00	101.6	1.156	29.36	2.469	62.71	0.625	15.9	0.937	23.8
149	36	1	5.00	127.00	1.156	29.36	2.469	62.71	0.625	15.9	0.937	23.8
150	14	1	2.00	50.80	1.027	26.08	0.984	24.99	0.125	3.2	0.312	7.9
151	14	1	3.00	76.19	1.027	26.08	0.984	24.99	0.125	3.2	0.312	7.9
152	16	1	2.00	50.80	1.027	26.08	1.112	28.24	0.125	3.2	0.312	7.9
153	16	1	3.00	76.19	1.027	26.08	1.112	28.24	0.125	3.2	0.312	7.9
154	44	1	4.00	101.6	1.156	29.36	2.969	75.41	0.625	15.9	0.937	23.8
155	44	1	5.00	127.00	1.156	29.36	2.969	75.41	0.625	15.9	0.937	23.8
156	40	1	4.00	101.6	1.156	29.36	2.719	69.06	0.625	15.9	0.937	23.8
157	40	1	5.00	127.00	1.156	29.36	2.719	69.06	0.625	15.9	0.937	23.8

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

For connectors:

- MIL-DTL-38999 Series III & IV

Catalog number selection**Dimensions**

Shell size	Ø A max inches	mm
9	0.858	21.8
11	0.984	25.0
13	1.157	29.29
15	1.279	32.49
17	1.406	35.71
19	1.516	38.50
21	1.642	41.71
23	1.768	44.91
25	1.889	47.98


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/15, 16 Series - Cable tie strain relief - Aluminum 45° and 90°


For connectors:

- EN3645
- MIL-DTL-38999 Series III & IV

Catalog number selection



Dimensions





Shell size	Ø C max inches	mm	D1 max inches	mm	D2 max inches	mm	Cable entry max inches	mm	E max inches	mm
9	0.858	21.8	0.88	22.4	1.220	31.0	0.264	6.7	1.030	26.2
11	0.984	25.0	0.88	22.4	1.290	32.8	0.392	10.0	1.030	26.2
13	1.160	29.5	0.94	23.9	1.620	41.1	0.506	12.9	1.030	26.2
15	1.280	32.5	1.25	31.8	1.660	42.2	0.631	16.0	1.090	27.7
17	1.410	35.8	1.31	33.3	1.720	43.7	0.756	19.2	1.110	28.2
19	1.520	38.6	1.38	35.1	1.720	43.7	0.845	21.5	1.210	30.7
21	1.640	41.7	1.50	38.1	1.790	45.5	0.970	24.6	1.260	32.0
23	1.770	45.0	1.69	42.9	1.850	47.0	1.095	27.5	1.300	33.0
25	1.890	48.0	1.75	44.5	1.910	48.5	1.220	31.0	1.340	34.0

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

For connectors:

- MIL-DTL-38999 Series I & II

Catalog number selection**Dimensions****Clamp size**

Dash number	Clamp size min	max
08	01	02
10	01	03
12	02	04
14	02	05
16	02	06
18	03	07
20	03	08
22	03	09
24	04	10

Length code

Code	Length inches	$\pm 0.32"/0.80$ mm
Standard	1.5	38.1
A	2.5	63.5
B	3.5	88.9
C	4.5	114.3

Clamp size	Y max in	mm	X max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
01	0.781	19.84	1.250	31.75	0.062	1.57	0.125	3.18
02	0.969	24.61			0.125	3.18	0.250	6.35
03	1.062	26.97			0.250	6.35	0.375	9.53
04	1.156	29.36			0.375	9.53	0.500	12.70
05	1.250	31.75	1.312	33.32	0.500	12.70	0.625	15.88
06	1.375	34.93	1.375	34.93	0.625	15.88	0.750	19.05
07	1.500	38.10	1.500	38.10	0.750	19.05	0.875	22.23
08	1.625	41.28			0.875	22.23	1.000	25.40
09	1.750	44.45	1.625	41.28	1.000	25.40	1.125	28.58
10	1.875	47.63			1.125	28.58	1.250	31.75


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/18 Series - EMI/RFI environmental backshell - Aluminum straight


For connectors:

- MIL-DTL-38999 Series III & IV

Catalog number selection



Dimensions



Clamp size

Clamp size	Clamp size min	Clamp size max	Ø A max inches	mm
9	01	02	0.75	19.1
11	01	03	0.85	21.6
13	02	04	1.00	25.4
15	02	05	1.15	29.2
17	02	06	1.25	31.8
19	03	07	1.40	35.6
21	03	08	1.55	39.4
23	03	09	1.65	41.9
25	04	10	1.85	47.0

Length code

Code	Length inches	mm $\pm 0.32/0.80$
Standard	1.5	38.1
A	2.5	63.5
B	3.5	88.9
C	4.5	114.3


Clamp size	Cable entry min inches	mm	max inches	mm	X max inches	mm	Y max inches	mm
01	0.062	1.6	0.125	3.2	1.250	31.75	0.800	20.3
02	0.125	3.2	0.250	6.4	1.250	31.75	1.000	25.4
03	0.250	6.4	0.375	9.5	1.250	31.75	1.100	27.9
04	0.375	9.5	0.500	12.7	1.250	31.75	1.200	30.5
05	0.500	12.7	0.625	15.9	1.350	34.29	1.250	31.8
06	0.625	15.9	0.750	19.1	1.375	34.93	1.400	35.6
07	0.750	19.0	0.875	22.2	1.500	38.10	1.500	38.1
08	0.875	22.2	1.000	25.4	1.625	41.28	1.650	41.98
09	1.000	25.4	1.125	28.6	1.625	41.28	1.750	44.5
10	1.125	28.6	1.250	31.8	1.625	41.28	1.900	48.3

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- EN3645
- MIL-DTL-38999 Series III & IV

Catalog number selection



Dimensions



Clamp size

Shell size	Clamp size min	Clamp size max	Ø A max inches	mm
9	01	02	0.75	19.1
11	01	03	0.85	21.6
13	02	04	1.00	25.4
15	02	05	1.10	27.9
17	02	06	1.25	31.8
19	03	07	1.40	35.6
21	03	08	1.50	38.1
23	03	09	1.65	41.9
25	04	10	1.75	44.5

Length code

Code	Length inches	mm $\pm 0.32"/0.80$
Standard	1.5	38.1
A	2.5	63.5
B	3.5	88.9
C	4.5	114.3

Clamp size	Cable entry min inches	mm	max inches	mm	Y max inches	mm
01	0.062	1.6	0.125	3.2	0.800	20.3
02	0.125	3.2	0.250	6.4	1.000	25.4
03	0.250	6.4	0.375	9.5	1.100	27.9
04	0.312	7.9	0.500	12.7	1.200	30.5
05	0.437	11.1	0.625	15.9	1.250	31.8
06	0.562	14.3	0.750	19.1	1.400	35.6
07	0.687	17.4	0.875	22.2	1.500	38.1
08	0.812	20.6	1.000	25.4	1.650	41.98
09	0.937	23.8	1.125	28.6	1.750	44.5
10	1.062	27.0	1.250	31.8	1.900	48.3


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/20 Series - EMI/RFI crimp ring backshell - Aluminum straight


For connectors:

- EN3645
- MIL-DTL-38999 Series III & IV

Catalog number selection



Dimensions




Shell size	Ø A max inches	mm	Ø B max inches	mm	Ø C $\pm .015"/.04$ inches	mm	Crimp ring reference
9	0.750	19.1	0.347	8.8	0.250	6.4	-8
11	0.850	21.6	0.498	12.6	0.325	8.3	-10
13	1.000	25.4	0.510	13.0	0.420	10.7	-12
15	1.100	27.9	0.630	16.0	0.540	13.7	-14
17	1.250	31.8	0.760	19.3	0.670	17.0	-16
19	1.400	35.6	0.890	22.6	0.789	20.0	-18
21	1.500	38.1	1.010	25.7	0.914	23.2	-20
23	1.650	41.9	1.130	28.7	1.039	26.4	-22
25	1.750	44.5	1.202	30.5	1.112	28.2	-24

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- EN3645
- MIL-DTL-38999 Series III & IV

Catalog number selection



Dimensions



Clamp size

Shell size	Clamp size min	Clamp size max	Ø A max inches	mm
9	01	02	0.75	19.1
11	01	03	0.85	21.6
13	02	04	1.00	25.4
15	02	05	1.10	27.9
17	02	06	1.25	31.8
19	03	07	1.40	35.6
21	03	08	1.50	38.1
23	03	09	1.65	41.9
25	04	10	1.75	44.5

Length code

Code	Length inches	mm $\pm 0.32"/0.80$
Standard	1.5	38.1
A	2.5	63.5
B	3.5	88.9
C	4.5	114.3

Clamp size	Cable entry min inches	mm	max inches	mm	Y max inches	mm
01	0.062	1.6	0.125	3.2	0.800	20.3
02	0.125	3.2	0.250	6.4	1.000	25.4
03	0.250	6.4	0.375	9.5	1.100	27.9
04	0.312	7.9	0.500	12.7	1.200	30.5
05	0.437	11.1	0.625	15.9	1.250	31.8
06	0.562	14.3	0.750	19.1	1.400	35.6
07	0.687	17.4	0.875	22.2	1.500	38.1
08	0.812	20.6	1.000	25.4	1.650	41.98
09	0.937	23.8	1.125	28.6	1.750	44.5
10	1.062	27.0	1.250	31.8	1.900	48.3

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/23 Series - EMI/RFI non-environmental backshell - Aluminum & stainless steel 45°

For connectors:

- AS50151 crimp
- EN2997 & EN3646
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3


Catalog number selection

M85049/23 11 W

Dash number
3 thru 75

Material and plating
B = Stainless steel, black cadmium
N = Aluminum, electroless nickel
S = Stainless steel, passivated
W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray

Dimensions



Dash number	Shell size	Style	B $\pm 0.125/3.17$		C reference		$\varnothing$ D max		E $\pm 0.125/3.17$		F max		Cable entry min		Cable entry max	
			inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
3	8	1	1.182	30.0	1.027	26.1	0.617	15.67	0.500	12.7	2.52	64.00	0.125	3.2	0.250	6.4
4	10	1	1.850	46.9	1.027	26.1	0.734	18.64	0.561	14.2	3.05	77.46	0.125	3.2	0.312	7.9
5	10	1	1.245	31.6	1.027	26.1	0.734	18.64	0.561	14.2	2.69	68.32	0.250	6.4	0.375	9.5
6	12	1	1.910	48.5	1.027	26.1	0.858	21.79	0.625	15.8	3.16	80.26	0.125	3.2	0.312	7.9
7	12	1	1.910	48.5	1.027	26.1	0.858	21.79	0.625	15.8	3.22	81.78	0.250	6.4	0.437	11.1
8	12	1	1.910	48.5	1.027	26.1	0.858	21.79	0.625	15.8	3.29	83.56	0.350	8.9	0.500	12.7
9	14	1	2.000	50.8	1.027	26.1	0.984	24.99	0.688	17.4	3.35	85.09	0.250	6.4	0.437	11.1
10	14	1	1.655	42.0	1.027	26.1	0.984	24.99	0.688	17.4	3.17	80.51	0.350	8.9	0.575	14.6
11	16	1	2.110	53.5	1.027	26.1	1.112	28.24	0.781	19.8	3.52	89.40	0.250	6.4	0.437	11.1
12	16	1	1.750	44.4	1.059	26.9	1.112	28.24	0.781	19.8	3.43	87.12	0.500	12.7	0.700	17.8
13	18	1	2.300	58.4	1.027	26.1	1.218	30.93	0.968	24.5	3.91	99.31	0.350	8.9	0.625	15.9

Continued on pages 36 and 37

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/23 Series - EMI/RFI non-environmental backshell - Aluminum & stainless steel 45°
(continued)

Dash number	Shell size	Style	B ±0.125"/3.17		C max		Ø D max		E ±0.125"/3.17		F max		Cable entry min		Cable entry max	
			inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
14	18	1	1.938	49.2	1.156	29.4	1.218	30.93	0.968	24.5	3.90	99.05	0.625	15.9	0.779	19.8
15	20	1	2.300	58.4	1.027	26.1	1.345	34.16	0.968	24.5	3.91	99.31	0.350	8.9	0.625	15.9
16	20	1	1.938	49.2	1.156	29.4	1.345	34.16	0.968	24.5	3.90	99.05	0.625	15.9	0.904	23.0
17	22	1	2.450	62.2	1.059	26.9	1.468	37.28	1.063	27.0	4.21	106.93	0.500	12.7	0.750	19.1
18	22	1	2.093	53.1	1.375	34.9	1.468	37.28	1.063	27.0	4.38	111.25	0.875	22.2	1.029	26.1
19	24	1	2.450	62.2	1.069	27.2	1.593	40.46	1.063	27.0	4.21	106.93	0.500	12.7	0.750	19.1
20	24	1	2.093	53.1	1.375	34.9	1.593	40.46	1.063	27.0	4.38	111.25	0.875	22.2	1.144	29.1
21	28	1	2.500	63.5	1.156	33.7	1.969	50.01	1.188	30.1	4.52	114.80	0.625	15.9	0.937	23.8
22	28	1	2.156	54.7	1.500	38.1	1.969	50.01	1.188	30.1	4.72	119.88	1.000	25.4	1.375	34.9
23	32	1	2.600	66.0	1.156	29.4	2.219	56.36	1.250	31.7	4.65	118.11	0.625	15.9	0.937	23.8
24	32	1	2.600	66.0	1.375	34.9	2.219	56.36	1.250	31.7	4.92	124.96	0.875	22.2	1.250	31.8
25	32	1	2.250	57.1	1.781	45.2	2.219	56.36	1.250	31.7	5.19	131.82	1.250	31.8	1.625	41.3
26	36	1	2.690	68.3	1.156	29.4	2.469	62.71	1.281	32.5	4.74	120.39	0.625	15.9	0.937	23.8
27	36	1	2.690	68.3	1.500	38.1	2.469	62.71	1.281	32.5	5.19	131.82	1.000	25.4	1.375	34.9
28	36	1	2.344	59.5	1.830	46.5	2.489	63.22	1.281	32.5	5.41	137.41	1.437	36.5	1.840	46.7
29	40	1	2.690	68.3	1.156	29.4	2.719	69.06	2.031	51.5	5.49	139.44	0.625	15.9	0.937	23.8
30	40	1	2.690	68.3	1.500	38.1	2.719	69.06	2.031	51.5	5.94	150.87	1.000	25.4	1.375	34.9
31	40	1	2.344	59.5	1.830	46.5	2.719	69.06	2.031	51.5	6.16	156.46	1.437	36.5	1.875	47.6
32	44	1	2.690	68.3	1.156	29.4	2.969	75.41	2.031	51.5	5.49	139.44	0.625	15.9	0.937	23.8
33	44	1	2.690	68.3	1.500	38.1	2.969	75.41	2.031	51.5	5.94	150.87	1.000	25.4	1.375	34.9
34	44	1	2.344	59.5	1.830	46.5	2.969	75.41	2.031	51.5	6.16	156.46	1.437	36.5	1.875	47.6
35	48	1	2.690	68.3	1.156	29.4	3.219	81.76	2.031	51.5	5.49	139.44	0.625	15.9	0.937	23.8
36	48	1	2.690	68.3	1.500	38.1	3.219	81.76	2.031	51.5	5.94	150.87	1.000	25.4	1.375	34.9
37	48	1	2.344	59.5	1.830	46.5	3.219	81.76	2.031	51.5	6.16	156.46	1.437	36.5	1.875	47.6
38	61	1	2.450	62.2	1.059	26.9	1.653	41.98	1.063	27.0	4.21	106.93	0.500	12.7	0.750	19.1
39	61	1	2.093	53.1	1.375	34.9	1.653	41.98	1.063	27.0	4.38	111.25	0.875	22.2	1.184	30.1
40	16	1	2.110	53.5	1.027	26.1	1.112	28.24	0.781	19.8	3.59	91.18	0.350	8.9	0.625	15.9
41	18	1	2.300	58.4	1.027	26.1	1.218	30.93	0.968	24.5	3.80	96.52	0.125	3.2	0.312	7.9
42	18	1	2.300	58.4	1.027	26.1	1.218	30.93	0.968	24.5	3.84	97.53	0.250	6.4	0.437	11.1
43	20	1	2.300	58.4	1.027	26.1	1.345	34.16	0.968	24.5	3.84	97.53	0.250	6.4	0.437	11.1
44	22	1	2.450	62.2	1.027	26.1	1.488	37.79	1.063	27.0	3.98	101.09	0.125	3.2	0.312	7.9
45	22	1	2.450	62.2	1.027	26.1	1.468	37.28	1.063	27.0	4.04	102.61	0.250	6.4	0.437	11.1
46	24	1	2.450	62.2	1.027	26.1	1.593	40.46	1.063	27.0	4.11	104.39	0.350	8.9	0.625	15.9
47	36	1	2.690	68.3	1.059	26.9	2.469	62.71	1.281	32.5	4.60	116.83	0.500	12.7	0.750	19.1
48	40	1	2.690	68.3	1.059	26.9	2.719	69.06	2.031	51.5	5.35	135.89	0.500	12.7	0.750	19.1
49	10	2	1.910	48.5	1.027	26.1	0.734	18.64	1.375	34.9	3.97	100.83	0.250	6.1	0.437	11.1
50	14	2	2.300	58.4	1.059	26.9	0.984	24.99	1.717	43.6	4.76	120.90	0.500	12.7	0.750	19.1
51	16	2	2.450	62.2	1.156	29.4	1.112	28.24	1.812	46.0	5.11	129.79	0.625	15.9	0.937	23.8
52	18	1	2.300	58.4	1.059	26.9	1.218	30.93	0.968	24.5	4.01	101.85	0.500	12.7	0.750	19.1
54	20	1	2.300	58.4	1.059	26.9	1.345	34.16	0.968	24.5	4.01	101.85	0.500	12.7	0.750	19.1
55	20	2	2.500	63.5	1.375	34.9	1.345	34.16	1.936	49.1	5.54	140.71	0.875	22.2	1.250	31.8
56	22	1	2.450	62.2	1.027	26.1	1.468	37.28	1.063	27.0	4.11	104.39	0.350	8.9	0.625	15.9
57	22	1	2.450	62.2	1.156	29.4	1.468	37.28	1.063	27.0	4.36	110.74	0.625	15.9	0.937	23.8

Continued on page 37

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/23 Series - EMI/RFI non-environmental backshell - Aluminum & stainless steel 45°
(continued)

Dash number	Shell size	Style	B $\pm 0.125"/3.17$		C max		$\varnothing$ D max		E $\pm 0.125"/3.17$		F max		Cable entry min		Cable entry max	
			inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
58	22	2	2.500	63.5	1.375	34.9	1.468	37.28	1.936	49.1	5.54	140.71	0.875	22.2	1.250	31.8
59	24	1	2.450	62.2	1.156	29.4	1.593	40.46	1.063	27.0	4.36	110.74	0.625	15.9	0.937	23.8
60	28	1	2.500	63.5	1.059	26.9	1.969	50.01	1.188	30.1	4.37	110.99	0.500	12.7	0.750	19.1
61	28	1	2.500	63.5	1.375	34.9	1.969	50.01	1.188	30.1	4.79	121.66	0.875	22.2	1.250	31.8
62	32	1	2.600	66.0	1.500	38.1	2.219	56.36	1.250	31.7	5.10	129.54	1.000	25.4	1.375	34.9
63	36	1	2.690	68.3	1.375	34.9	2.469	62.71	1.281	32.5	5.02	127.50	0.875	22.2	1.250	31.8
64	36	1	2.690	68.3	1.781	45.2	2.469	62.71	1.281	32.5	5.54	140.71	1.250	31.8	1.625	41.3
65	40	1	2.690	68.3	1.375	34.9	2.719	69.06	2.031	51.5	5.77	146.55	0.875	22.2	1.250	31.8
66	40	1	2.690	68.3	1.781	45.2	2.719	69.06	2.031	51.5	6.29	159.76	1.250	31.8	1.625	41.3
67	44	1	2.690	68.3	1.375	34.9	2.969	75.41	2.031	51.5	5.77	146.55	0.875	22.2	1.250	31.8
68	44	1	2.690	68.3	1.781	45.2	2.969	75.41	2.031	51.5	6.29	159.76	1.250	31.8	1.625	41.3
69	48	1	2.690	68.3	1.375	34.9	3.219	81.76	2.031	51.5	5.77	146.55	0.875	22.2	1.250	31.8
70	48	1	2.690	68.3	1.781	45.2	3.219	81.76	2.031	51.5	6.29	159.76	1.250	31.8	1.625	41.3
71	12	2	2.110	53.5	1.027	26.1	0.858	21.79	1.529	38.8	4.33	109.98	0.350	8.9	0.625	15.9
72	18	2	2.450	62.2	1.156	29.4	1.218	30.93	1.812	46.0	5.10	129.54	0.625	15.9	0.937	23.8
73	24	2	2.500	63.5	1.375	34.9	1.593	40.46	1.936	49.1	5.53	140.46	0.875	22.2	1.250	31.8
74	14	1	2.000	50.8	1.027	26.1	0.984	24.99	0.688	17.4	3.28	83.31	0.125	3.2	0.312	7.9
75	16	1	2.110	53.5	1.027	26.1	1.112	28.24	0.781	19.8	3.45	87.63	0.125	3.2	0.312	7.9

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- AS50151 crimp
- EN2997 & EN3646
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection

M85049/24 11 W	
Dash number	Material and plating
3 thru 75	B = Stainless steel, black cadmium N = Aluminum, electroless nickel S = Stainless steel, passivated W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray

Dimensions



Dash number	Shell size	Style	B ±.125"/3.1 inches mm	C ref. inches mm	Ø D max inches mm	E ±.125"/3.1 inches mm	F max inches mm	Cable entry min inches mm	Cable entry max inches mm
3	8	1	1.200 30.4	1.027 26.0	0.617 15.6	0.541 13.7	1.09 27.6	0.125 3.1	0.250 6.3
4	10	1	1.920 48.7	1.027 26.0	0.734 18.6	0.636 16.1	1.18 29.9	0.125 3.1	0.312 7.9
5	10	1	1.320 33.5	1.027 26.0	0.734 18.6	0.636 16.1	1.27 32.2	0.250 6.3	0.375 9.5
6	12	1	1.940 49.2	1.027 26.0	0.858 21.7	0.641 16.2	1.18 29.9	0.125 3.1	0.312 7.9
7	12	1	1.940 49.2	1.027 26.0	0.858 21.7	0.641 16.2	1.28 32.5	0.250 6.3	0.437 11.0
8	12	1	1.335 33.9	1.027 26.0	0.858 21.7	0.641 16.2	1.37 34.7	0.350 8.8	0.500 12.7
9	14	1	2.010 51.0	1.027 26.0	0.984 24.9	0.741 18.8	1.38 35.0	0.250 6.3	0.437 11.0
10	14	1	1.655 42.0	1.027 26.0	0.984 24.9	0.741 18.8	1.47 37.3	0.350 8.8	0.575 14.6
11	16	1	2.100 53.3	1.027 26.0	1.112 28.2	0.926 23.5	1.59 40.3	0.250 6.3	0.437 11.0

Continued on pages 39 and 40

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/24 Series - EMI/RFI non-environmental backshell - Aluminum & stainless steel 90° (continued)

Dash number	Shell size	Style	B ±.125"/3.1 inches	mm	C inches	mm	Ø D max inches	mm	E ±.125"/3.1 inches	mm	F max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
12	16	1	1.745	44.3	1.059	26.8	1.112	28.2	0.926	23.5	1.77	44.9	0.500	12.7	0.700	17.7
13	18	1	2.270	57.6	1.027	26.0	1.218	30.9	1.016	25.8	1.80	45.7	0.350	8.8	0.625	15.8
14	18	1	1.920	48.7	1.156	29.3	1.218	30.9	1.016	25.8	1.97	50.0	0.625	15.8	0.779	19.7
15	20	1	2.270	57.6	1.027	26.0	1.345	34.1	1.016	25.8	1.80	45.7	0.350	8.8	0.625	15.8
16	20	1	1.920	48.7	1.156	29.3	1.345	34.1	1.016	25.8	1.97	50.0	0.625	15.8	0.904	22.9
17	22	1	2.380	60.4	1.059	26.8	1.468	37.2	1.166	29.6	2.11	53.5	0.500	12.7	0.750	19.0
18	22	1	2.025	51.4	1.375	34.9	1.468	37.2	1.166	29.6	2.29	58.1	0.875	22.2	1.029	26.1
19	24	1	2.380	60.4	1.059	26.8	1.593	40.4	1.166	29.6	2.11	53.5	0.500	12.7	0.750	19.0
20	24	1	2.025	51.4	1.375	34.9	1.593	40.4	1.166	29.6	2.29	58.1	0.875	22.2	1.144	29.0
21	28	1	2.550	64.7	1.156	29.3	1.969	50.0	1.266	32.1	2.33	59.1	0.625	15.8	0.937	23.7
22	28	1	2.195	55.7	1.500	38.0	1.969	50.0	1.266	32.1	2.51	63.7	1.000	25.4	1.375	34.9
23	32	1	2.800	71.1	1.156	29.3	2.219	56.3	1.616	41.0	2.81	71.3	0.625	15.8	0.937	23.7
24	32	1	2.800	71.1	1.375	34.9	2.219	56.3	1.616	41.0	2.81	71.3	0.875	22.2	1.250	31.7
25	32	1	2.445	62.1	1.781	45.2	2.219	56.3	1.616	41.0	3.07	77.9	1.250	31.7	1.625	41.2
26	36	1	2.770	70.3	1.156	29.3	2.469	62.7	1.816	46.1	3.13	79.5	0.625	15.8	0.937	23.7
27	36	1	2.770	70.3	1.500	38.0	1.469	37.3	1.816	46.1	3.13	79.5	1.000	25.4	1.375	34.9
28	36	1	2.415	61.3	1.830	46.4	2.469	62.7	1.816	46.1	3.39	86.1	1.437	36.4	1.840	46.7
29	40	1	2.770	70.3	1.156	29.3	2.719	69.0	2.566	65.1	3.88	98.5	0.625	15.8	0.937	23.7
30	40	1	2.770	70.3	1.500	38.0	2.719	69.0	2.566	65.1	3.88	98.5	1.000	25.4	1.375	34.9
31	40	1	2.415	61.3	1.830	46.4	2.719	69.0	2.566	65.1	4.14	105.1	1.437	36.4	1.875	47.6
32	44	1	2.770	70.3	1.156	29.3	2.969	75.4	2.566	65.1	3.88	98.5	0.625	15.8	0.937	23.7
33	44	1	2.770	70.3	1.500	38.0	2.969	75.4	2.566	65.1	3.88	98.5	1.000	25.4	1.375	34.9
34	44	1	2.415	61.3	1.830	46.4	2.969	75.4	2.566	65.1	4.14	105.1	1.437	36.4	1.875	47.6
35	48	1	2.770	70.3	1.156	29.3	3.219	81.7	2.566	65.1	3.88	98.5	0.625	15.8	0.937	23.7
36	48	1	2.770	70.3	1.500	38.0	3.219	81.7	2.566	65.1	3.88	98.5	1.000	25.4	1.375	34.9
37	48	1	2.415	61.3	1.830	46.4	3.219	81.7	2.566	65.1	4.14	105.1	1.437	36.4	1.875	47.6
40	16	1	2.100	53.3	1.027	26.0	1.112	28.2	0.926	23.5	1.66	42.1	0.350	8.8	0.625	15.8
41	18	1	2.270	57.6	1.027	26.0	1.218	30.9	1.016	25.8	1.80	45.7	0.125	3.1	0.312	7.9
42	18	1	2.270	57.6	1.027	26.0	1.218	30.9	1.016	25.8	1.80	45.7	0.250	6.3	0.437	11.0
43	20	1	2.270	57.6	1.027	26.0	1.345	34.1	1.016	25.8	1.80	45.7	0.250	6.3	0.437	11.0
44	22	1	2.380	60.4	1.027	26.0	1.468	37.2	1.166	29.6	2.11	53.5	0.125	3.1	0.312	7.9
45	22	1	2.380	60.4	1.027	26.0	1.468	37.2	1.166	29.6	2.11	53.5	0.250	6.3	0.437	11.0
46	24	1	2.380	60.4	1.027	26.0	1.593	40.4	1.166	29.6	2.11	53.5	0.350	8.8	0.625	15.8
47	36	1	2.770	70.3	1.059	26.8	2.469	62.7	1.816	46.1	3.13	79.5	0.500	12.7	0.750	19.0
48	40	1	2.770	70.3	1.059	26.8	2.719	69.0	1.816	46.1	3.88	98.5	0.500	12.7	0.750	19.0
49	10	2	1.940	49.2	1.027	26.0	0.734	18.6	1.381	35.0	2.03	51.5	0.250	6.3	0.437	11.0
50	14	2	2.270	57.6	1.059	26.8	0.984	24.9	1.766	44.8	2.61	66.2	0.500	12.7	0.750	19.0
51	16	2	2.380	60.4	1.156	29.3	1.112	28.2	1.916	48.6	2.87	72.8	0.625	15.8	0.937	23.7
52	18	1	2.270	57.6	1.059	26.8	1.218	30.9	1.016	25.8	1.86	47.2	0.500	12.7	0.750	19.0
54	20	1	2.270	57.6	1.059	26.8	1.345	34.1	1.016	25.8	1.86	47.2	0.500	12.7	0.750	19.0
55	20	2	2.550	64.7	1.375	34.9	1.345	34.1	2.016	51.2	3.14	79.7	0.875	22.2	1.250	31.7
56	22	1	2.380	60.4	1.027	26.0	1.468	37.2	1.166	29.6	2.11	53.5	0.350	8.8	0.625	15.8
57	22	1	2.380	60.4	1.156	29.3	1.468	37.2	1.166	29.6	2.12	53.8	0.625	15.8	0.937	23.7

Continued on page 40

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

Dash number	Shell size	Style	B ±.125"/ 3.1		C		Ø D max		E ±.125"/ 3.1		F max		Cable entry min		Cable entry max	
			inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
58	22	2	2.550	64.7	1.375	34.9	1.468	37.2	2.016	51.2	3.14	79.7	0.875	22.2	1.250	31.7
59	24	1	2.380	60.4	1.156	29.3	1.593	40.4	1.166	29.6	2.14	54.3	0.625	15.8	0.937	23.7
60	28	1	2.550	64.7	1.059	26.8	1.969	50.0	1.266	32.1	2.33	59.1	0.500	12.7	0.750	19.0
61	28	1	2.550	64.7	1.375	34.9	1.969	50.0	1.266	32.1	2.39	60.7	0.875	22.2	1.250	31.7
62	32	1	2.800	71.1	1.500	38.1	2.219	56.3	1.616	41.0	2.86	72.6	1.000	25.4	1.375	34.9
63	36	1	2.770	70.3	1.375	34.9	2.469	62.7	1.816	46.1	3.13	79.5	0.875	22.2	1.250	31.7
64	36	1	2.770	70.3	1.781	45.2	2.469	62.7	1.816	46.1	3.27	83.0	1.250	31.7	1.625	41.2
65	40	1	2.770	70.3	1.375	34.9	2.719	69.0	2.566	65.1	3.88	98.5	0.875	22.2	1.250	31.7
66	40	1	2.770	70.3	1.781	45.2	2.719	69.0	2.566	65.1	4.02	102.1	1.250	31.7	1.625	41.2
67	44	1	2.770	70.3	1.375	34.9	2.969	75.4	2.566	65.1	3.88	98.5	0.875	22.2	1.250	31.7
68	44	1	2.770	70.3	1.781	45.2	2.969	75.4	2.566	65.1	4.02	102.1	1.250	31.7	1.625	41.2
69	48	1	2.770	70.3	1.375	34.9	3.219	81.7	2.566	65.1	3.88	98.5	0.875	22.2	1.250	31.7
70	48	1	2.770	70.3	1.781	45.2	3.219	81.7	2.566	65.1	4.02	102.1	1.250	31.7	1.625	41.2
71	12	2	2.100	53.3	1.027	26.0	0.858	21.7	1.686	42.8	2.42	61.4	0.350	8.8	0.625	15.8
72	18	2	2.380	60.4	1.156	29.3	1.218	30.9	1.925	48.8	2.88	73.1	0.625	15.8	0.937	23.7
73	24	2	2.550	64.7	1.375	34.9	1.593	40.4	2.026	51.4	3.15	80.0	0.875	22.2	1.250	31.7
74	14	1	2.010	51.0	1.027	26.0	0.984	24.9	0.741	18.8	1.31	33.2	0.125	3.1	0.312	7.9
75	16	1	2.100	53.3	1.027	26.0	1.112	28.2	0.926	23.5	1.59	40.3	0.125	3.1	0.312	7.9


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/25 Series - EMI/RFI non-environmental backshell - Aluminum & stainless steel straight


For connectors:

- AS50151 crimp
- EN2997 & EN3646
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection



Dimensions



Style 2

Style 1

Dash number	Shell size	Style	B ±.125"/ 3.2 inches	mm	Ø D max inches	mm	F max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
5	8	1	2.00	50.8	0.617	15.6	3.15	80.0	0.125	3.1	0.250	6.3
6	8	1	3.00	76.1	0.617	15.6	4.15	105.4	0.125	3.1	0.250	6.3
7	8	2	2.75	69.8	0.617	15.6	3.90	99.0	0.250	6.3	0.437	11.0
8	8	2	3.75	95.2	0.617	15.6	4.90	124.4	0.250	6.3	0.437	11.0
9	10	1	2.00	50.8	0.734	18.6	3.15	80.0	0.125	3.1	0.312	7.9
10	10	1	3.00	76.1	0.734	18.6	4.15	105.4	0.125	3.1	0.312	7.9
11	10	2	2.75	69.8	0.734	18.6	3.90	99.0	0.250	6.3	0.437	11.0
12	10	2	3.75	95.2	0.734	18.6	4.90	124.4	0.250	6.3	0.437	11.0
13	12	1	2.00	50.8	0.858	21.7	3.15	80.0	0.250	6.3	0.437	11.0
14	12	1	3.00	76.1	0.858	21.7	4.15	105.4	0.250	6.3	0.437	11.0
15	12	2	2.75	69.8	0.858	21.7	3.90	99.0	0.350	8.8	0.625	15.8
16	12	2	3.75	95.2	0.858	21.7	4.90	124.4	0.350	8.8	0.625	15.8
17	14	1	2.00	50.8	0.984	24.9	3.15	80.0	0.350	8.8	0.575	14.6

Continued on pages 42 to 45

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/25 Series - EMI/RFI non-environmental backshell - Aluminum & stainless steel straight
(continued)

Dash number	Shell size	Style	B ±.125"/ 3.2 inches	mm	Ø D max inches	mm	F max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
18	14	1	3.00	76.2	0.984	24.9	4.15	105.4	0.350	8.8	0.575	14.6
19	14	2	2.75	69.8	0.984	24.9	3.93	99.8	0.500	12.7	0.750	19.0
20	14	2	3.75	95.2	0.984	24.9	5.04	128.0	0.500	12.7	0.750	19.0
21	16	1	2.00	50.8	1.112	28.2	3.18	80.7	0.500	12.7	0.700	17.7
22	16	1	3.00	76.2	1.112	28.2	4.18	106.1	0.500	12.7	0.700	17.7
23	16	2	2.75	69.8	1.112	28.2	4.02	102.1	0.625	15.8	0.937	23.7
24	16	2	3.75	95.2	1.112	28.2	5.02	127.5	0.625	15.8	0.937	23.7
25	18	1	2.00	50.8	1.218	30.9	3.15	80.0	0.350	8.8	0.625	15.8
26	18	1	3.00	76.2	1.218	30.9	4.15	105.4	0.350	8.8	0.625	15.8
27	18	1	2.00	50.8	1.218	30.9	3.18	80.7	0.500	12.7	0.750	19.0
28	18	1	3.00	76.2	1.218	30.9	4.18	106.1	0.500	12.7	0.750	19.0
29	18	2	2.75	69.8	1.218	30.9	4.02	102.1	0.625	15.8	0.937	23.7
30	18	2	3.70	93.9	1.218	30.9	5.02	127.5	0.625	15.8	0.937	23.7
31	20	1	3.00	76.2	1.345	34.1	4.15	105.4	0.350	8.8	0.625	15.8
32	20	1	4.00	101.6	1.345	34.1	5.15	130.8	0.350	8.8	0.625	15.8
33	20	1	3.00	76.2	1.345	34.1	4.18	106.1	0.500	12.7	0.750	19.0
34	20	1	4.00	101.6	1.345	34.1	5.18	131.5	0.500	12.7	0.750	19.0
35	20	2	3.75	95.2	1.345	34.1	5.02	127.5	0.625	15.8	0.937	23.7
36	20	2	4.75	120.6	1.345	34.1	6.02	152.9	0.625	15.8	0.937	23.7
37	20	2	3.75	95.2	1.345	34.1	5.24	133.0	0.875	22.2	1.250	31.7
38	20	2	4.75	120.6	1.345	34.1	6.24	158.4	0.875	22.2	1.250	31.7
39	22	1	3.00	76.2	1.468	37.2	4.15	105.4	0.350	8.8	0.625	15.8
40	22	1	4.00	101.6	1.468	37.2	5.15	130.8	0.350	8.8	0.625	15.8
41	22	1	3.00	76.2	1.468	37.2	4.18	106.1	0.500	12.7	0.750	19.0
42	22	1	4.00	101.6	1.468	37.2	5.18	131.5	0.500	12.7	0.750	19.0
43	22	1	3.00	76.2	1.468	37.2	4.27	108.4	0.625	15.8	0.937	23.7
44	22	1	4.00	101.6	1.468	37.2	5.27	133.8	0.625	15.8	0.937	23.7
45	22	2	3.75	95.2	1.468	37.2	5.24	133.0	0.875	22.2	1.250	31.7
46	22	2	4.75	120.6	1.468	37.2	6.24	158.4	0.875	22.2	1.250	31.7
47	24	1	3.00	76.2	1.593	40.4	4.18	106.1	0.500	12.7	0.750	19.0
48	24	1	4.00	101.6	1.593	40.4	5.18	131.5	0.500	12.7	0.750	19.0
49	24	1	3.00	76.2	1.593	40.4	4.27	108.4	0.625	15.8	0.812	20.6
50	24	1	4.00	101.6	1.593	40.4	5.27	133.8	0.625	15.8	0.812	20.6
51	24	1	3.00	76.2	1.593	40.4	4.27	108.4	0.625	15.8	0.937	23.7
52	24	1	4.00	101.6	1.593	40.4	5.27	133.8	0.625	15.8	0.937	23.7
53	24	2	3.75	95.2	1.593	40.4	5.24	133.0	0.875	22.2	1.250	31.7
54	24	2	4.75	120.6	1.593	40.4	6.24	158.4	0.875	22.2	1.250	31.7
55	28	1	3.00	76.2	1.969	50.0	4.16	105.6	0.500	12.7	0.750	19.0
56	28	1	4.00	101.6	1.969	50.0	5.16	131.0	0.500	12.7	0.750	19.0
57	28	1	3.00	76.2	1.969	50.0	4.26	108.2	0.625	15.8	0.937	23.7
58	28	1	4.00	101.6	1.969	50.0	5.26	133.6	0.625	15.8	0.937	23.7
59	28	1	3.00	76.2	1.969	50.0	4.48	113.7	0.875	22.2	1.250	31.7
60	28	1	4.00	101.6	1.969	50.0	5.48	139.1	0.875	22.2	1.250	31.7

Continued on pages 43 to 45

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/25 Series - EMI/RFI non-environmental backshell - Aluminum & stainless steel straight
(continued)

Dash number	Shell size	Style	B ±.125"/ 3.1 inches	mm	Ø D max inches	mm	F max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
61	28	1	3.00	76.2	1.969	50.0	4.60	116.8	1.000	25.4	1.375	34.9
62	28	1	4.00	101.6	1.969	50.0	5.60	142.2	1.000	25.4	1.375	34.9
63	32	1	3.00	76.2	2.219	56.3	4.26	108.2	0.625	15.8	0.937	23.7
64	32	1	4.00	101.6	2.219	56.3	5.26	133.6	0.625	15.8	0.937	23.7
65	32	1	3.00	76.2	2.219	56.3	4.48	113.7	0.875	22.2	1.250	31.7
66	32	1	4.00	101.6	2.219	56.3	5.48	139.1	0.875	22.2	1.250	31.7
67	32	1	3.00	76.2	2.219	56.3	4.60	116.8	1.000	25.4	1.375	34.9
68	32	1	4.00	101.6	2.219	56.3	5.60	142.2	1.000	25.4	1.375	34.9
69	32	1	3.00	76.2	2.219	56.3	4.89	124.2	1.250	31.7	1.625	41.2
70	32	1	4.00	101.6	2.219	56.3	5.89	149.6	1.250	31.7	1.625	41.2
71	36	1	4.00	101.6	2.469	62.7	5.49	139.4	0.875	22.2	1.250	31.7
72	36	1	5.00	127.0	2.469	62.7	6.49	164.8	0.875	22.2	1.250	31.7
73	36	1	4.00	101.6	2.469	62.7	5.60	142.2	1.000	25.4	1.375	34.9
74	36	1	5.00	127.0	2.469	62.7	6.60	167.6	1.000	25.4	1.375	34.9
75	36	1	4.00	101.6	2.469	62.7	5.89	149.6	1.250	31.7	1.625	41.2
76	36	1	5.00	127.0	2.469	62.7	6.89	175.0	1.250	31.7	1.625	41.2
77	36	2	4.88	123.9	2.469	62.7	6.81	172.9	1.437	36.4	1.875	47.6
78	36	2	5.88	149.3	2.469	62.7	7.81	198.3	1.437	36.4	1.875	47.6
79	40	1	4.00	101.6	2.719	69.0	5.48	139.1	0.875	22.2	1.250	31.7
80	40	1	5.00	127.0	2.719	69.0	6.48	164.5	0.875	22.2	1.250	31.7
81	40	1	4.00	101.6	2.719	69.0	5.60	142.2	1.000	25.4	1.375	34.9
82	40	1	5.00	127.0	2.719	69.0	6.60	167.6	1.000	25.4	1.375	34.9
83	40	1	4.00	101.6	2.719	69.0	5.89	149.6	1.250	31.8	1.625	41.3
84	40	1	5.00	127.0	2.719	69.0	6.89	175.0	1.250	31.8	1.625	41.3
85	40	1	4.00	101.6	2.719	69.0	5.93	150.6	1.437	36.5	1.875	47.6
86	40	1	5.00	127.0	2.719	69.0	6.93	176.0	1.437	36.5	1.875	47.6
87	44	1	4.00	101.6	2.969	75.4	5.48	139.2	0.875	22.2	1.250	31.8
88	44	1	5.00	127.0	2.969	75.4	6.48	164.6	0.875	22.2	1.250	31.8
89	44	1	4.00	101.6	2.969	75.4	5.60	142.2	1.000	25.4	1.375	34.9
90	44	1	5.00	127.0	2.969	75.4	6.60	167.6	1.000	25.4	1.375	34.9
91	44	1	4.00	101.6	2.969	75.4	5.89	149.6	1.250	31.8	1.625	41.3
92	44	1	5.00	127.0	2.969	75.4	6.89	175.0	1.250	31.8	1.625	41.3
93	44	1	4.00	101.6	2.969	75.4	5.93	150.6	1.437	36.5	1.875	47.6
94	44	1	5.00	127.0	2.969	75.4	6.93	176.0	1.437	36.5	1.875	47.6
95	48	1	4.00	101.6	3.219	81.8	5.48	139.2	0.875	22.2	1.250	31.8
96	48	1	5.00	127.0	3.219	81.8	6.48	164.6	0.875	22.2	1.250	31.8
97	48	1	4.00	101.6	3.219	81.8	5.60	142.2	1.000	25.4	1.375	34.9
98	48	1	5.00	127.0	3.219	81.8	6.60	167.6	1.000	25.4	1.375	34.9
99	48	1	4.00	101.6	3.219	81.8	5.89	149.6	1.250	31.8	1.625	41.3
100	48	1	5.00	127.0	3.219	81.8	6.89	175.0	1.250	31.8	1.625	41.3
101	48	1	4.00	101.6	3.219	81.8	5.93	150.6	1.437	36.5	1.875	47.6
102	48	1	5.00	127.0	3.219	81.8	6.93	176.0	1.437	36.5	1.875	47.6
111	12	1	2.00	50.8	0.858	21.8	3.15	80.0	0.350	8.9	0.500	12.7

Continued on pages 44 to 45

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/25 Series - EMI/RFI non-environmental backshell - Aluminum & stainless steel straight
(continued)

Dash number	Shell size	Style	B ±.125"/.3.2 inches	mm	Ø D max inches	mm	F max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
112	16	1	2.00	50.8	1.112	28.2	3.15	80.0	0.250	6.4	0.437	11.1
113	16	1	3.00	76.2	1.112	28.2	4.15	105.4	0.250	6.4	0.437	11.1
114	12	1	2.00	50.8	0.858	21.8	3.15	80.0	0.125	3.2	0.312	7.9
115	12	1	3.00	76.2	0.858	21.8	4.15	105.4	0.125	3.2	0.312	7.9
116	14	1	2.00	50.8	0.984	25.0	3.15	80.0	0.250	6.4	0.437	11.1
117	14	1	3.00	76.2	0.984	25.0	4.15	105.4	0.250	6.4	0.437	11.1
118	16	1	2.00	50.8	1.112	28.2	3.15	80.0	0.350	8.9	0.625	15.9
119	16	1	3.00	76.2	1.112	28.2	4.15	105.4	0.350	8.9	0.625	15.9
120	18	1	2.00	50.8	1.218	30.9	3.15	80.0	0.125	3.2	0.312	7.9
121	18	1	3.00	76.2	1.218	30.9	4.15	105.4	0.125	3.2	0.312	7.9
122	18	1	2.00	50.8	1.218	30.9	3.15	80.0	0.250	6.4	0.437	11.1
123	18	1	3.00	76.2	1.218	30.9	4.15	105.4	0.250	6.4	0.437	11.1
124	20	1	3.00	76.2	1.345	34.2	4.15	105.4	0.250	6.4	0.437	11.1
125	20	1	4.00	101.6	1.345	34.2	5.15	130.8	0.250	6.4	0.437	11.1
126	22	1	3.00	76.2	1.468	37.3	4.15	105.4	0.125	3.2	0.312	7.9
127	22	1	4.00	101.6	1.468	37.3	5.15	130.8	0.125	3.2	0.312	7.9
128	22	1	3.00	76.2	1.468	37.3	4.15	105.4	0.250	6.4	0.437	11.1
129	22	1	4.00	101.6	1.468	37.3	5.15	130.8	0.250	6.4	0.437	11.1
130	24	1	3.00	76.2	1.593	40.5	4.15	105.4	0.350	8.9	0.625	15.9
131	24	1	4.00	101.6	1.593	40.5	5.15	130.8	0.350	8.9	0.625	15.9
132	36	1	4.00	101.6	2.469	62.7	5.32	135.1	0.500	12.7	0.750	19.1
133	36	1	5.00	127.0	2.469	62.7	6.32	160.5	0.500	12.7	0.750	19.1
134	40	1	4.00	101.6	2.719	69.1	5.16	131.1	0.500	12.7	0.750	19.1
135	40	1	5.00	127.0	2.719	69.1	6.16	156.5	0.500	12.7	0.750	19.1
136	10	1	2.00	50.8	0.734	18.6	3.15	80.0	0.250	6.4	0.375	9.5
137	10	1	3.00	76.2	0.734	18.6	4.15	105.4	0.250	6.4	0.375	9.5
138	12	1	2.00	50.8	0.858	21.8	3.15	80.0	0.350	8.9	0.500	12.7
139	12	1	3.00	76.2	0.858	21.8	4.15	105.4	0.350	8.9	0.500	12.7
140	20	1	3.00	76.2	1.345	34.2	4.27	108.5	0.625	15.9	0.904	23.0
141	20	1	4.00	101.6	1.345	34.2	5.27	133.9	0.625	15.9	0.904	23.0
142	22	1	3.00	76.2	1.468	37.3	4.49	114.0	0.875	22.2	1.029	26.1
143	22	1	4.00	101.6	1.468	37.3	5.49	139.4	0.875	22.2	1.029	26.1
144	24	1	3.00	76.2	1.593	40.5	4.49	114.0	0.875	22.2	1.144	29.1
145	24	1	4.00	101.6	1.593	40.5	5.49	139.4	0.875	22.2	1.144	29.1
146	36	1	4.00	101.6	2.469	62.7	5.93	150.6	1.437	36.5	1.840	46.7
147	36	1	5.00	127.0	2.469	62.7	6.93	176.0	1.437	36.5	1.840	46.7
148	36	1	4.00	101.6	2.469	62.7	5.26	133.6	0.625	15.9	0.937	23.8
149	36	1	5.00	127.0	2.469	62.7	6.26	159.0	0.625	15.9	0.937	23.8
150	14	1	2.00	50.8	0.984	25.0	3.15	80.0	0.125	3.2	0.312	7.9
151	14	1	3.00	76.2	0.984	25.0	4.15	105.4	0.125	3.2	0.312	7.9
152	16	1	2.00	50.8	1.112	28.2	3.15	80.0	0.125	3.2	0.312	7.9
153	16	1	3.00	76.2	1.112	28.2	4.15	105.4	0.125	3.2	0.312	7.9
154	44	1	4.00	101.6	2.969	75.4	5.26	133.6	0.625	15.9	0.937	23.8

Continued on page 45

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/25 Series - EMI/RFI non-environmental backshell - Aluminum & stainless steel straight
(continued)


Dash number	Shell size	Style	B ±.125"/ 3.1 inches	mm	Ø D max inches	mm	F max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
155	44	1	5.00	127.0	2.969	75.4	6.26	159.0	0.625	15.9	0.937	23.8
156	40	1	4.00	101.6	2.719	69.1	5.26	133.6	0.625	15.9	0.937	23.8
157	40	1	5.00	127.0	2.719	69.1	6.26	159.0	0.625	15.9	0.937	23.8

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- AS50151 crimp
- EN2997 & EN3646
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection



Dimensions



Shell size	$\varnothing A \pm 0.031'' / 0.7$ inches	mm	$\varnothing E \pm 0.015'' / 0.3$ inches	mm	$\varnothing F \pm 0.010'' / 0.2$ inches	mm
3	0.669	17.0	0.250	6.4	0.337	8.6
8	0.617	15.7	0.250	6.4	0.337	8.6
10	0.734	18.6	0.325	8.3	0.488	12.4
12	0.858	21.6	0.420	10.7	0.500	12.7
14	0.984	25.0	0.540	13.7	0.620	15.7
16	1.112	28.2	0.670	17.0	0.750	19.1
18	1.218	30.9	0.789	20.0	0.880	22.4
20	1.345	34.2	0.914	23.2	1.000	25.4
22	1.468	37.3	1.039	26.4	1.120	25.4
24	1.593	40.5	1.112	28.2	1.192	30.3
28	1.969	50.0	1.389	35.3	1.545	39.2
32	2.219	56.4	1.635	41.5	1.795	45.6
36	2.469	62.7	1.850	47.0	2.045	51.9
40	2.719	69.1	2.065	52.5	2.295	58.3
44	2.969	75.4	2.320	58.9	2.545	64.6
48	3.219	81.8	2.570	65.3	2.795	71.0
61	1.653	42.0	1.210	30.7	1.359	34.5

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/26-2 Series - Crimp ring for EMI/RFI backshell

For connectors:


- AS85049/20
- AS85049/26-1
- AS85049/33-2

Catalog number selection

M85049/26-2 12

Dash number
08, 10, 12, 14, 16, 18, 20, 22, 24, 28, 32, 36, 40, 44, 48, 61

Dimensions




Dash number	For AS85049/26-1 and AS85049/33-2 shell size	For AS85049/20 shell size	Ø A min inches	mm	Ø A max inches	mm	Ø B min inches	mm	Ø B max inches	mm	L $\pm 0.020"/0.5$ inches	mm
08	08	09	0.400	10.2	0.410	10.4	0.448	11.4	0.458	11.6	0.250	6.4
10	10	11	0.585	14.9	0.595	15.1	0.660	16.8	0.680	17.3		
12	12	13	0.585	14.9	0.595	15.1	0.660	16.8	0.680	17.3		
14	14	15	0.705	17.9	0.715	18.2	0.780	19.8	0.800	20.3		
16	16	17	0.835	21.2	0.845	21.5	0.910	23.1	0.930	23.6		
18	18	19	1.005	25.5	1.015	25.8	1.080	27.4	1.100	27.9		
20	20	21	1.125	28.6	1.135	28.8	1.200	30.5	1.220	31.0		
22	22	23	1.245	31.6	1.255	31.9	1.320	33.5	1.340	34.0		
24	24	25	1.327	33.7	1.337	34.0	1.402	35.6	1.422	36.1	0.440	11.2
28	28	—	1.665	42.3	1.675	42.5	1.740	44.2	1.760	44.7		
32	32	—	1.915	48.6	1.925	48.9	1.990	50.5	2.010	51.4		
36	36	—	2.165	55.0	2.175	55.2	2.240	56.9	2.260	57.4		
40	40	—	2.415	61.3	2.425	61.6	2.490	63.2	2.510	63.8		
44	44	—	2.665	67.7	2.675	67.9	2.740	69.6	2.760	70.1		
48	48	—	2.915	74.0	2.925	74.3	2.990	75.9	3.010	76.5		
61	61	—	1.435	36.4	1.445	36.7	1.510	38.4	1.530	38.9		


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

For connectors:

- MIL-DTL-27599
- MIL-DTL-38999 Series I & II

Catalog number selection**Dimensions**

0.54"/13.7mm max (non self-locking)
 0.59"/15.0mm max (self-locking)



Dash number	Ø A max - Self-locking		Ø A max - Non Self-locking	
	inches	mm	inches	mm
08	0.859	21.82	0.75	19.10
10	0.984	24.99	0.85	21.60
12	1.156	29.36	1.00	25.40
14	1.281	32.54	1.10	27.90
16	1.406	35.71	1.25	31.80
18	1.516	38.51	1.40	35.60
20	1.641	41.68	1.50	38.10
22	1.766	44.86	1.65	41.90
24	1.891	48.03	1.75	44.50


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/29 Series - Strain relief backshell - Aluminum, straight


For connectors:

- MIL-DTL-27599
- MIL-DTL-38999 Series I & II

Catalog number selection



Dimensions



Clamp size

Dash number	Clamp size min	Clamp size max
08	01	02
10	01	03
12	02	04
14	02	05
16	02	06
18	03	07
20	03	08
22	03	09
24	04	10

Length code

Code	Length inches $\pm 0.32"/0.80$	mm
Standard	1.0	25.4
A	2.0	50.8
B	3.0	70.2
C	4.0	101.6


Clamp size	Y max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
01	0.781	19.84	0.062	1.57	0.125	3.18
02	0.969	24.61	0.125	3.18	0.250	6.35
03	1.062	26.97	0.250	6.35	0.375	9.53
04	1.156	29.36	0.312	7.92	0.500	12.70
05	1.250	31.75	0.437	11.10	0.625	15.88
06	1.375	34.93	0.562	14.27	0.750	19.05
07	1.500	38.10	0.687	17.45	0.875	22.23
08	1.625	41.28	0.812	20.62	1.000	25.40
09	1.750	44.45	0.937	23.80	1.125	28.58
10	1.875	47.63	1.062	26.97	1.250	31.75

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
 Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.



For connectors:

- AS50151 crimp
- EN2997 & EN3646
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection



Dimensions




Holes for 0.20" / 0.51mm max dia safety wire for devices only (3 equally spaced)

Shell size	Ø A max inches	mm	B max inches	mm	C max inches	mm	Ø E max inches	mm
8	0.617	15.67					0.270	6.85
10	0.734	18.64					0.375	9.52
12	0.858	21.79					0.511	12.97
14	0.984	24.99					0.585	14.85
16	1.112	28.24			0.540	13.71	0.710	18.03
18	1.218	30.93					0.789	20.04
20	1.345	34.16					0.914	23.21
22	1.468	37.28	0.220	5.58			1.039	26.39
24	1.593	40.46					1.154	29.31
28	1.969	50.01					1.389	35.28
32	2.219	56.36					1.635	41.52
36	2.469	62.71					1.850	46.99
40	2.719	69.06			0.702	17.83	2.065	52.45
44	2.969	75.41					2.320	58.92
48	3.219	81.76					2.570	65.27
61	1.653	41.98			0.540	13.71	1.194	30.32

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

Dimensions



Shell size	Ø A max inches	mm	B max inches	mm	C max inches	mm	Ø E max inches	mm
8	0.885	22.47					0.270	6.85
10	1.010	25.65					0.375	9.52
12	1.135	28.82					0.511	12.97
14	1.260	32.00					0.585	14.85
16	1.385	35.17	0.39	9.90	0.710	13.71	0.710	18.03
18	1.510	38.35					0.784	20.04
20	1.635	41.52					0.914	23.21
22	1.760	44.70					1.039	26.39
24	1.885	47.87					1.154	29.31
28	2.135	54.22					1.389	35.28
32	2.395	60.83					1.635	41.52
36	2.635	66.92					1.850	46.99
40	2.885	73.27	0.41	10.41	0.890	17.83	2.065	52.45
44	3.135	79.62					2.320	58.92
48	3.385	85.97					2.570	65.27

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

For connectors:

- MIL-DTL-27599
- MIL-DTL-38999 Series I & II


Catalog number selection

M85049/33-2 10 W

Dash number										
08, 10, 12, 14, 16, 18, 20, 22, 24										
Shell size 38999 I	09	11	13	15	17	19	21	23	25	
= Shell size 38999 II	08	10	12	14	16	18	20	22	24	

Material and plating	
N	Aluminum, electroless nickel
W	Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray

Dimensions



Dash number	Ø A max inches	mm	C max inches	mm	Ø D max inches	mm	Ø E max inches	mm
08	0.75	19.05	0.516	13.11	0.337	8.56	0.250	6.35
10	0.85	21.59	0.641	16.28	0.488	12.40	0.325	8.26
12	1.00	25.40	0.766	19.46	0.500	12.70	0.420	10.67
14	1.10	27.94	0.891	22.63	0.620	15.75	0.540	13.72
16	1.25	31.75	1.016	25.81	0.750	19.05	0.670	17.02
18	1.40	35.56	1.141	28.98	0.880	22.35	0.789	20.04
20	1.50	38.10	1.265	32.13	1.000	25.40	0.914	23.22
22	1.65	41.91	1.391	35.33	1.120	28.45	1.039	26.39
24	1.75	44.45	1.516	38.51	1.192	30.28	1.112	28.24


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/36 Series - EMI/RFI non-environmental backshell - Aluminum straight


For connectors:

- MIL-DTL-27599
- MIL-DTL-38999 Series I & II

Catalog number selection



Dimensions



Clamp size

Dash number	Clamp size min	Clamp size max
08	01	02
10	01	03
12	02	04
14	02	05
16	02	06
18	03	07
20	03	08
22	03	09
24	04	10

Length code

Code	Length inches	Length mm $\pm 0.32/0.80$
Standard	1.5	38.1
A	2.5	63.5
B	3.5	88.9
C	4.5	114.3

Clamp size	Y max inches	Y max mm	Cable entry min inches	Cable entry min mm	Cable entry max inches	Cable entry max mm
01	0.781	19.84	0.062	1.57	0.125	3.18
02	0.969	24.61	0.125	3.18	0.250	6.35
03	1.062	26.97	0.250	6.35	0.375	9.53
04	1.156	29.36	0.312	7.92	0.500	12.70
05	1.250	31.75	0.437	11.10	0.625	15.88
06	1.375	34.93	0.562	14.27	0.750	19.05
07	1.500	38.10	0.687	17.45	0.875	22.23
08	1.625	41.28	0.812	20.62	1.000	25.40
09	1.750	44.45	0.937	23.80	1.125	28.58
10	1.875	47.63	1.062	26.97	1.250	31.75

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
 Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- MIL-DTL-27599
- MIL-DTL-38999 Series I & II

Catalog number selection

M85049/37 24 W 05 L										
Dash number										
08, 10, 12, 14, 16, 18, 20, 22, 24										
Shell size 38999 I 09 11 13 15 17 19 21 23 25										
= Shell size 38999 II 08 10 12 14 16 18 20 22 24										
Material and plating										
N = Aluminum, electroless nickel										
W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray										
Hole										
L = Encapsulating hole										
D = 3 drain holes										
Clamp size										
01, 02, 03, 04, 05, 06, 07, 08, 09.										
See table below										

Dimensions



Dash number	Clamp size		A max		Ø B max		C max		D reference	
	min	max	inches	mm	inches	mm	inches	mm	inches	mm
08	01	02	2.88	73.15	0.750	19.05	0.720	18.29	1.21	30.73
10	01	03	2.92	74.17	0.850	21.59	0.720	18.29	1.25	31.75
12	02	04	3.06	77.72	1.000	25.40	0.800	20.32	1.36	34.54
14	02	05	3.24	82.30	1.100	27.94	0.850	21.59	1.47	37.33
16	02	06	3.44	87.38	1.250	31.75	0.910	23.11	1.60	40.64
18	03	06	3.73	94.74	1.400	35.56	1.000	25.40	1.75	44.44
20	03	07	3.94	100.08	1.500	38.10	1.050	26.67	1.82	46.22
22	03	08	4.14	105.16	1.650	41.91	1.100	27.94	1.97	50.03
24	04	09	4.19	106.43	1.750	44.45	1.200	30.48	2.15	54.60

Clamp size	Y max		Cable entry min		Cable entry max	
	inches	mm	inches	mm	inches	mm
01	0.781	19.84	0.062	1.57	0.125	3.18
02	0.969	24.61	0.125	3.18	0.250	6.35
03	1.062	26.97	0.250	6.35	0.375	9.53
04	1.156	29.36	0.312	7.92	0.500	12.70
05	1.250	31.75	0.437	11.10	0.625	15.88
06	1.375	34.93	0.562	14.27	0.750	19.05
07	1.500	38.10	0.687	17.45	0.875	22.23
08	1.625	41.28	0.812	20.62	1.000	25.40
09	1.750	44.45	0.937	23.80	1.125	28.58

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/38 Series - Cable clamp strain relief - Aluminum straight

For connectors:

- EN 3645
- MIL-DTL-38999 Series III & IV

Catalog number selection

M85049/38

S

11

N

Self-locking option

S = Self-locking, detented—utilizes an audible detented anti-decoupling device

N = Self-locking, non detented—utilizes an internal captivated anti-decoupling device (Self-Seating) with no audible clicking mechanism

– = Non self-locking

Material and plating

A = Aluminum, black anodized

N = Aluminum, electroless nickel


S = Stainless steel, passivated

W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray

Shell size

9, 11, 13, 15, 16, 17, 19, 21, 23, 25

Dimensions




Shell size	A max inches	mm	D max inches	mm	Ø F max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
9	0.91	23.11	0.85	21.60	0.858	21.79	0.098	2.49	0.234	5.94
11	0.91	23.11	0.90	22.90	0.984	24.99	0.153	3.89	0.234	5.94
13	1.01	25.65	1.10	27.90	1.157	29.39	0.19	4.83	0.328	8.33
15	1.06	26.92	1.15	29.20	1.279	32.49	0.26	6.60	0.457	11.61
17	1.16	29.46	1.30	33.00	1.406	35.71	0.283	7.19	0.614	15.60
19	1.41	35.81	1.50	38.10	1.516	38.51	0.325	8.26	0.634	16.10
21	1.51	38.35	1.60	40.60	1.642	41.71	0.343	8.71	0.698	17.73
23	1.66	42.16	1.70	43.20	1.768	44.91	0.381	9.68	0.823	20.90
25	1.76	44.70	1.80	45.70	1.889	47.98	0.418	10.62	0.853	21.67

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- EN 3645
- MIL-DTL-38999 Series III & IV

Catalog number selection



Dimensions



Shell size	A max inches	mm	Ø D max inches	mm	F max inches	mm	G max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
9	1.01	25.7	0.858	21.79	1.00	25.4	0.85	21.6	0.098	2.49	0.234	5.94
11	1.01	25.7	0.984	24.99	1.10	27.9	0.90	22.9	0.153	3.89	0.234	5.94
13	1.21	30.7	1.157	29.39	1.10	27.9	1.10	27.9	0.190	4.83	0.328	8.33
15	1.26	32.0	1.279	32.49	1.25	31.8	1.15	29.2	0.260	6.60	0.457	11.61
17	1.41	35.81	1.406	35.71	1.30	33.0	1.30	33.0	0.283	7.19	0.614	15.60
19	1.51	38.4	1.516	38.51	1.35	34.3	1.50	38.1	0.325	8.26	0.634	16.10
21	1.66	42.2	1.642	41.71	1.60	40.6	1.60	40.6	0.343	8.71	0.698	17.73
23	1.76	44.7	1.768	44.91	1.75	44.5	1.70	43.2	0.381	9.68	0.823	20.90
25	2.91	73.9	1.889	47.98	1.85	47.0	1.80	45.7	0.418	10.62	0.853	21.67


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/42 Series - Cable clamp strain relief - Aluminum straight


For connectors:

- AS50151 solder

Catalog number selection



Dimensions




Shell size	B max inches	mm	D $\pm 0.020"/0.50$ inches	mm	E Cable entry min inches	mm	E Cable entry max inches	mm	G $\pm 0.020"/0.50$ inches	mm
4D	0.937	23.8	0.937	23.8	0.125	3.2	0.312	7.9	1.281	32.5
6D	1.031	26.2	1.125	28.6	0.250	6.4	0.437	11.1	1.281	32.5
8D	1.250	31.8	1.312	33.3	0.312	7.9	0.562	14.3	1.281	32.5
10D	1.250	31.8	1.312	33.3	0.350	8.9	0.625	15.9	1.281	32.5
12D	1.437	36.5	1.531	38.9	0.500	12.7	0.750	19.1	1.312	33.3
16D	1.688	42.9	1.750	44.5	0.625	15.9	0.937	23.8	1.406	35.7
20D	2.000	50.8	2.093	53.2	0.875	22.2	1.250	31.8	1.593	40.4
24D	2.250	57.2	2.343	59.5	1.000	25.4	1.375	34.9	1.625	41.3
28D	2.500	63.5	2.750	69.9	1.250	31.8	1.625	41.3	1.900	48.3
32D	2.750	69.9	3.000	76.2	1.437	36.5	1.875	47.6	1.900	48.3

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
 Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.



For connectors:

- EN2997 & EN3646
- AS50151 solder
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection



Dimensions



Shell size	Ø A max inches	mm	Gmax inches	mm	M max inches	mm	Z max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
8	0.617	15.67	0.782	19.86	1.650	41.91	0.772	19.61	0.125	3.20	0.204	5.20
10	0.734	18.64	0.862	21.89	1.694	43.03	0.803	20.40	0.187	4.70	0.286	7.30
12	0.858	21.79	1.018	25.86	1.768	44.91	0.866	21.00	0.291	7.40	0.416	10.60
14	0.984	24.99	1.076	27.33	1.840	46.74	0.928	23.57	0.351	8.90	0.476	12.10
16	1.112	28.24	1.349	34.26	1.916	48.67	0.991	25.17	0.501	12.70	0.625	15.90
18	1.218	30.93	1.481	37.62	2.034	51.66	1.110	28.19	0.518	13.20	0.706	17.90
20	1.345	34.16	1.587	40.31	2.078	52.78	1.172	29.77	0.581	14.80	0.831	21.10
22	1.468	37.28	1.688	42.88	2.122	53.90	1.235	31.37	0.644	16.40	0.956	24.30
24	1.593	40.46	1.805	45.85	2.166	55.02	1.297	32.94	0.706	17.90	1.081	27.50
28	1.969	50.01	2.050	52.07	2.461	62.51	1.543	39.19	0.750	19.10	1.187	30.10
32	2.219	56.36	2.416	61.37	2.549	64.75	1.668	42.37	0.875	22.20	1.250	31.80
36	2.469	62.71	2.526	64.16	2.595	65.91	1.793	45.54	0.938	23.80	1.375	34.90
40	2.719	69.06	2.596	65.94	2.599	66.01	1.918	48.72	0.938	23.80	1.500	38.10
44	2.969	75.41	2.890	73.41	2.860	72.64	2.132	54.15	1.188	30.20	1.750	44.50
48	3.219	81.76	3.374	85.70	2.918	74.12	2.257	57.33	1.312	33.30	1.875	47.60

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/45 Series - Strain relief - Flexible plastic body - Straight

For connectors:

- MIL-DTL-27599
- MIL-DTL-38999 Series I & II

Catalog number selection

M85049/45 W 10

Material and plating

A = Aluminum, black anodized


W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray

Dash number

08, 10, 12, 14, 16, 18, 20, 22, 24

Shell size 38999 I	09	11	13	15	17	19	21	23	25
= Shell size 38999 II	08	10	12	14	16	18	20	22	24

Dimensions



Dash number	Ø A max inches	mm	B max inches	mm	Cable diameter min inches	mm	Cable diameter max inches	mm
08	0.578	14.68	1.344	34.14	0.094	2.39	0.203	5.16
10	0.703	17.86			0.141	3.58	0.250	6.35
12	0.828	21.03			0.172	4.37	0.323	8.20
14	0.953	24.21			0.203	5.16	0.422	10.72
16	1.078	27.38			0.234	5.94	0.500	12.70
18	1.203	30.56	1.422	36.12	0.265	6.73	0.562	14.27
20	1.328	33.73			0.297	7.54	0.625	15.88
22	1.453	36.91			0.328	8.33	0.703	17.86
24	1.578	40.08			0.359	9.12	0.765	19.43

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- MIL-DTL-27599
- MIL-DTL-38999 Series I & II

Catalog number selection

Material and plating		Dash number									
A = Aluminum, black anodized		08, 10, 12, 14, 16, 18, 20, 22, 24									
W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray		Shell size 38999 I	09	11	13	15	17	19	21	23	25
		= Shell size 38999 II	08	10	12	14	16	18	20	22	24

Dimensions



Dash number	Ø A max inches	mm	D max inches	mm	E max inches	mm	Cable diameter min inches	mm	Cable diameter max inches	mm
08	0.578	14.68	0.656	16.66	1.015	25.78	0.094	2.39	0.203	5.16
10	0.703	17.86	0.688	17.48	1.062	26.97	0.141	3.58	0.250	6.35
12	0.828	21.03	0.750	19.05	1.125	28.58	0.172	4.37	0.323	8.20
14	0.953	24.21	0.859	21.82	1.328	33.73	0.203	5.16	0.422	10.72
16	1.078	27.38	0.937	23.80	1.392	35.36	0.234	5.94	0.500	12.70
18	1.203	30.56	1.000	25.40	1.453	36.91	0.265	6.73	0.562	14.27
20	1.328	33.73	1.062	26.97	1.609	40.87	0.297	7.54	0.625	15.88
22	1.453	36.91	1.141	28.98	1.656	42.06	0.328	8.33	0.703	17.86
24	1.578	40.08	1.203	30.56	1.719	43.66	0.359	9.12	0.765	19.43

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/47 Series - Cable clamp strain relief - Aluminum 90°

For connectors:

- MIL-DTL-27599
- MIL-DTL-38999 Series I & II

Catalog number selection

M85049/47 S W 10

Self-locking option

S = Self-locking, detented—utilizes an audible detented anti-decoupling device

N = Self-locking, non detented—utilizes an internal captivated anti-decoupling device (Self-Seating) with no audible clicking mechanism

- = Non self-locking

Shell size

08, 10, 12, 14, 16, 18, 20, 22, 24


Shell size 38999 I	09	11	13	15	17	19	21	23	25
= Shell size 38999 II	08	10	12	14	16	18	20	22	24

Material and plating

N = Aluminum, electroless nickel

W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray

Dimensions



Dash number	A max inches	mm	Ø D max inches	mm	F max inches	mm	G max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
08	1.16	29.5	0.86	21.8	1.00	25.4	0.85	21.6	0.098	2.49	0.234	5.94
10	1.16	29.5	0.98	24.9	1.10	27.9	0.90	22.9	0.153	3.89	0.234	5.94
12	1.24	31.5	1.16	29.5	1.10	27.9	1.10	27.9	0.190	4.83	0.328	8.33
14	1.41	35.8	1.28	32.5	1.25	31.8	1.15	29.2	0.260	6.60	0.457	11.61
16	1.58	40.1	1.41	35.8	1.30	33.0	1.30	33.0	0.283	7.19	0.614	15.60
18	1.60	40.6	1.52	38.6	1.35	34.3	1.50	38.1	0.325	8.26	0.634	16.10
20	1.68	42.7	1.64	41.7	1.60	40.60	1.60	40.6	0.343	8.71	0.698	17.73
22	1.82	46.2	1.77	45.0	1.75	44.5	1.70	43.2	0.381	9.68	0.823	20.90
24	1.93	49.0	1.89	48.0	1.85	47.0	1.80	45.7	0.418	10.62	0.853	21.67

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

For connectors:

- MIL-DTL-27599
- MIL-DTL-38999 Series I & II

Catalog number selection



M85049/49-2 S 10 N

Self-locking option	
S	= Self-locking, detented—utilizes an audible detented anti-decoupling device
N	= Self-locking, non detented—utilizes an internal captivated anti-decoupling device (Self-Seating) with no audible clicking mechanism
-	= Non self-locking

Shell size										
08, 10, 12, 14, 16, 18, 20, 22, 24										
Shell size 38999 I	09	11	13	15	17	19	21	23	25	
= Shell size 38999 II	08	10	12	14	16	18	20	22	24	

Material and plating	
A	= Aluminum, black anodized
N	= Aluminum, electroless nickel
S	= Stainless steel, passivated
W	= Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray

Dimensions



Shell size	A max inches	mm	D max inches	mm	E Cable entry min inches	mm	E Cable entry max inches	mm	Ø F max inches	mm
8	0.91	23.1	0.85	21.6	0.098	2.49	0.234	5.94	0.86	21.8
10	0.91	23.1	0.91	23.1	0.153	3.89	0.234	5.94	0.98	24.9
12	1.01	25.7	1.10	27.9	0.190	4.83	0.328	8.33	1.16	29.5
14	1.06	26.9	1.15	29.2	0.260	6.60	0.457	11.61	1.28	32.5
16	1.16	29.5	1.30	33.0	0.283	7.19	0.614	15.60	1.41	35.8
18	1.41	35.8	1.50	38.1	0.325	8.26	0.634	16.10	1.52	38.6
20	1.51	38.4	1.60	40.6	0.343	8.71	0.698	17.73	1.64	41.7
22	1.66	42.2	1.70	43.2	0.381	9.68	0.823	20.90	1.77	45.0
24	1.76	44.7	1.80	45.7	0.418	10.62	0.853	21.67	1.89	48.0

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/51 Series - Cable clamp strain relief - Aluminum 90°

For connectors:

- EN2997 & EN3646
- AS50151 solder
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection

M85049/51 S 10 N

Self-locking option

S = Self-locking, detented—utilizes an audible detented anti-decoupling device

N = Self-locking, non detented—utilizes an internal captivated anti-decoupling device (Self-Seating) with no audible clicking mechanism

– = Non self-locking

Dash number

8, 10, 12, 14, 16, 18, 20, 22, 21, 28, 32, 36, 40, 44, 48


Material and plating

A = Aluminum, black anodized

N = Aluminum, electroless nickel

W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray


Dimensions - Non-self locking version



Dash number	Ø A max inches	mm	G max inches	mm	X max inches	mm	Z ±0.062"/1.57 inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
8	0.617	15.6	0.782	19.9	0.78	19.8	0.746	18.9	0.125	3.2	0.204	5.2
10	0.734	18.6	0.862	21.9	0.86	21.8	0.805	20.4	0.187	4.7	0.286	7.3
12	0.858	21.7	1.003	25.5	1.05	26.6	0.867	22.0	0.291	7.4	0.416	10.6
14	0.984	24.9	1.061	26.9	1.11	28.1	0.930	23.6	0.351	8.9	0.476	12.1
16	1.112	28.2	1.334	33.9	1.26	32.0	0.994	25.2	0.501	12.7	0.626	15.9
18	1.218	30.9	1.466	37.2	1.37	34.7	1.171	29.7	0.518	13.2	0.706	17.9
20	1.345	34.1	1.572	39.9	1.50	38.0	1.234	31.2	0.581	14.8	0.831	21.1
22	1.468	37.2	1.688	42.9	1.62	41.1	1.296	32.9	0.644	16.4	0.956	24.3
24	1.593	40.4	1.790	45.5	1.75	44.4	1.358	34.5	0.706	17.9	0.081	27.5
28	1.969	50.0	2.035	51.7	1.89	48.0	1.572	39.9	0.750	19.1	1.187	30.1
32	2.219	56.3	2.386	60.6	1.95	49.5	1.797	45.6	0.875	22.2	1.250	31.8
36	2.469	62.7	2.496	63.4	2.07	52.5	1.922	48.8	0.938	23.8	1.375	34.9
40	2.719	69.0	2.566	65.2	2.20	55.8	2.047	52.0	0.938	23.8	1.500	38.1
44	2.969	75.4	2.860	72.6	2.45	62.2	2.296	58.3	1.188	30.2	1.750	44.5
48	3.219	81.7	3.344	84.9	2.57	65.2	2.421	61.5	1.312	33.3	1.875	47.6

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

Dimensions - Self locking version



Dash number	Ø A max inches	mm	G max inches	mm	X max inches	mm	Z ± 0.062 / 1.57 inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
8	0.885	22.5	0.782	19.9	0.93	23.6	0.746	18.9	0.125	3.2	0.204	5.2
10	1.010	25.7	0.862	21.9	1.02	25.9	0.805	20.4	0.187	4.7	0.286	7.3
12	1.135	28.8	1.003	25.5	1.21	30.7	0.867	22.0	0.291	7.4	0.416	10.6
14	1.260	32.0	1.061	26.9	1.27	32.2	0.930	23.6	0.351	8.9	0.476	12.1
16	1.385	35.2	1.334	33.9	1.42	36.0	0.994	25.2	0.501	12.7	0.626	15.9
18	1.510	38.4	1.466	37.2	1.53	38.8	1.171	29.7	0.518	13.2	0.706	17.9
20	1.635	41.5	1.572	39.9	1.65	41.9	1.234	31.2	0.581	14.8	0.831	21.1
22	1.760	44.7	1.688	42.9	1.78	45.2	1.296	32.9	0.644	16.4	0.956	24.3
24	1.885	47.9	1.790	45.5	1.90	48.2	1.358	34.5	0.706	17.9	0.081	27.5
28	2.135	54.2	2.035	51.7	2.20	55.8	1.572	39.9	0.750	19.1	1.187	30.1
32	2.395	60.8	2.386	60.6	2.27	57.6	1.797	45.6	0.875	22.2	1.250	31.8
36	2.635	66.9	2.496	63.4	2.39	60.7	1.922	48.8	0.938	23.8	1.375	34.9
40	2.885	73.3	2.566	65.2	2.52	64.0	2.047	52.0	0.938	23.8	1.500	38.1
44	3.135	79.6	2.860	72.6	2.77	70.3	2.296	58.3	1.188	30.2	1.750	44.5
48	3.385	86.0	3.344	84.9	2.89	73.4	2.421	61.5	1.312	33.3	1.875	47.6

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/52 Series - Cable clamp strain relief - Aluminum straight

For connectors:

- EN2997 & EN3646
- AS50151 solder
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection

M85049/52 S 10 N

Self-locking option

S = Self-locking, detented—utilizes an audible detented anti-decoupling device

N = Self-locking, non detented—utilizes an internal captivated anti-decoupling device (Self-Seating) with no audible clicking mechanism

– = Non self-locking

Dash number

8, 10, 12, 14, 16, 18, 20, 22, 21, 28, 32, 36, 40, 44, 48


Material and plating

A = Aluminum, black anodized

N = Aluminum, electroless nickel

W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray


Dimensions - Non-self locking version



Dash number	Ø A max inches	mm	G max inches	mm	M max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
8	0.617	15.6	0.782	19.8	0.63	16.0	0.125	3.2	0.204	5.2
10	0.734	18.6	0.862	21.8	0.74	18.7	0.187	4.7	0.286	7.3
12	0.858	21.7	1.003	25.4	0.86	21.8	0.291	7.4	0.416	10.6
14	0.984	24.9	1.061	26.9	0.86	21.8	0.351	8.9	0.476	12.1
16	1.112	28.2	1.334	33.8	0.99	25.1	0.501	12.7	0.626	15.9
18	1.218	30.9	1.466	37.2	1.24	31.4	0.518	13.2	0.706	17.9
20	1.345	34.1	1.572	39.9	1.36	34.5	0.581	14.8	0.831	21.1
22	1.468	37.2	1.688	42.8	1.49	37.8	0.644	16.4	0.956	24.3
24	1.593	40.4	1.790	45.4	1.61	40.8	0.706	17.9	0.081	27.5
28	1.969	50.0	2.035	51.6	1.76	44.7	0.750	19.1	1.187	30.1
32	2.219	56.3	2.386	60.6	1.95	49.5	0.875	22.2	1.250	31.8
36	2.469	62.7	2.496	63.4	2.33	59.1	0.938	23.8	1.375	34.9
40	2.719	69.0	2.566	65.1	2.51	63.7	0.938	23.8	1.500	38.1
44	2.969	75.4	2.860	72.6	2.89	73.4	1.188	30.2	1.750	44.5
48	3.219	81.7	3.344	84.9	3.26	82.8	1.312	33.3	1.875	47.6

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

Dimensions - Self locking version



Dash number	Ø A max inches	mm	G max inches	mm	X max inches	mm	Z $\pm 0.062^{+1.57}$ inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
8	0.885	22.5	0.782	19.8	0.73	18.5	0.125	3.2	0.204	5.2	0.204	5.2
10	1.010	25.7	0.862	21.8	0.85	21.6	0.187	4.7	0.286	7.3	0.286	7.3
12	1.135	28.8	1.003	25.4	0.98	24.9	0.291	7.4	0.416	10.6	0.416	10.6
14	1.260	32.0	1.061	26.9	0.98	24.9	0.351	8.9	0.476	12.1	0.476	12.1
16	1.385	35.2	1.334	33.8	1.10	27.9	0.501	12.7	0.626	15.9	0.626	15.9
18	1.510	38.4	1.466	37.2	1.35	34.3	0.518	13.2	0.706	17.9	0.706	17.9
20	1.635	41.5	1.572	39.9	1.98	50.3	0.581	14.8	0.831	21.1	0.831	21.1
22	1.760	44.7	1.688	42.8	2.73	69.3	0.644	16.4	0.956	24.3	0.956	24.3
24	1.885	47.9	1.790	45.4	2.88	73.2	0.706	17.9	0.081	27.5	0.081	27.5
28	2.135	54.2	2.035	51.6	2.528	64.2	0.750	19.1	1.187	30.1	1.187	30.1
32	2.395	60.8	2.386	60.6	2.591	65.8	0.875	22.2	1.250	31.8	1.250	31.8
36	2.635	66.9	2.496	63.4	2.13	54.1	0.938	23.8	1.375	34.9	1.375	34.9
40	2.885	73.3	2.566	65.1	2.44	62.0	0.938	23.8	1.500	38.1	1.500	38.1
44	3.135	79.6	2.860	72.6	3.00	76.2	1.188	30.2	1.750	44.5	1.750	44.5
48	3.385	86.0	3.344	84.9	3.40	86.4	1.312	33.3	1.875	47.6	1.875	47.6


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/53, 54, 55 Series - Cable tie strain relief - Aluminum straight, 45° and 90°


For connectors:

- EN2997 & EN3646
- AS50151 crimp
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3
- AS81703 Series 3


Catalog number selection




Dimensions - Non-self locking version



53 Series



54 Series



55 Series

Shell size	A max inches	mm	Ø C max 53 Series inches	mm	54 & 55 Series inches	mm	D1 max inches	mm	D2 max inches	mm	G max inches	mm	F max inches	mm	Cable entry max inches	mm
3	0.954	24.0	0.669	16.99	0.782	19.86	1.110	28.2	1.290	32.8	1.232	31.3	0.431	10.94	0.260	6.6
8	0.954	24.0	0.617	15.67	0.657	16.68	1.110	28.2	1.220	31.0	1.232	31.3	0.431	10.94	0.260	6.6
10	0.954	24.0	0.734	18.64	0.782	19.86	1.110	28.2	1.290	32.8	1.232	31.3	0.431	10.94	0.365	9.3
12	0.954	24.0	0.858	21.79	0.937	23.79	1.110	28.2	1.620	41.1	1.232	31.3	0.431	10.94	0.501	12.7
14	1.204	30.6	0.984	24.99	1.050	26.66	1.200	30.5	1.660	42.2	1.232	31.3	0.431	10.94	0.575	14.6
16	1.204	30.6	1.112	28.24	1.239	31.47	1.200	30.5	1.720	43.7	1.232	31.3	0.431	10.94	0.700	17.8
18	1.204	30.6	1.218	30.93	1.378	35.00	1.300	33.0	1.720	43.7	1.232	31.3	0.456	11.58	0.779	19.8
20	1.310	33.3	1.345	34.16	1.500	38.09	1.300	33.0	1.790	45.5	1.482	37.6	0.456	11.58	0.904	23.0
22	1.430	36.3	1.468	37.28	1.631	41.42	1.400	35.5	1.850	47.0	1.482	37.6	0.456	11.58	1.029	26.1
24	1.560	39.6	1.593	40.46	1.750	44.44	1.400	35.5	1.910	48.5	1.482	37.6	0.456	11.58	1.144	29.1
28	1.560	39.6	1.969	50.01	1.970	50.03	1.500	38.1	2.06	52.3	1.469	37.3	0.448	11.37	1.379	35.0

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

For connectors:


- MIL-DTL-38999 Series I & II

Catalog number selection

Self-locking option		Material and plating	
G = Self-locking detented with ground lug H = Self-locking non-detented with ground lug N = Self-locking non detented S = Self-locking detented		A = Aluminum, black anodized N = Aluminum, electroless nickel W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray	

Shell size											
08, 10, 12, 14, 16, 18, 20, 22, 24											
Shell size 38999 I	09	11	13	15	17	19	21	23	25		
= Shell size 38999 II	08	10	12	14	16	18	20	22	24		

Dimensions



Shell size	Ø C max inches	mm	D max inches	mm	Cable entry max inches	mm	E max inches	mm
8	0.860	21.8	0.88	22.4	0.264	6.7	1.21	30.7
10	0.980	24.9	0.88	22.4	0.392	9.9	1.21	30.7
12	1.160	29.5	0.94	23.9	0.506	12.9	1.39	35.3
14	1.280	32.5	1.25	31.8	0.631	16.0	1.39	35.3
16	1.410	35.8	1.31	33.3	0.756	19.2	1.39	35.3
18	1.520	38.6	1.38	35.1	0.845	21.5	1.39	35.3
20	1.640	41.7	1.50	38.1	0.970	24.6	1.39	35.3
22	1.770	45.0	1.69	42.9	1.095	27.8	1.39	35.3
24	1.890	48.0	1.75	44.5	1.220	30.9	1.39	35.3

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/58 Series - Potting boot ring - Aluminum

For connectors:

- MIL-DTL-38999 Series I & II


Catalog number selection

M85049/58 24

Dash number
08, 10, 12, 14, 16, 18, 20, 22, 24

Olive drab cadmium finish

Dimensions




Dash number	Shell size	Ø A max inches	mm	Ø E ± 0.005 inches	mm	Ø F inches	mm
8	8/9	0.600	15.2	0.344	8.7	0.500	12.7
10	10/11	0.726	18.4	0.472	12.0	0.625	15.8
12	12/13	0.850	21.6	0.586	14.9	0.750	19.0
14	14/15	0.976	24.8	0.711	18.1	0.875	22.2
16	16/17	1.102	27.9	0.836	21.2	1.000	25.4
18	18/19	1.226	31.1	0.942	23.9	1.125	28.5
20	20/21	1.352	34.3	1.067	27.1	1.250	31.7
22	22/23	1.476	37.5	1.192	30.3	1.375	34.9
24	24/25	1.602	40.7	1.317	33.5	1.500	38.0

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- EN2997
- EN3646
- AS50151 crimp
- AS81703 Series 3
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection



Dimensions



Shell size	$\varnothing A$ inches +0.000"/0.00 -0.045"/1.14	mm	$\varnothing B$ min inches	mm	$\varnothing F$ inches +0.000"/0.00 -0.020"/0.50	mm	M max inches	mm
3	0.669	16.99	0.250	6.40	0.533	13.50	0.832	21.10
8	0.617	15.67	0.250	6.40	0.533	13.50		
10	0.734	18.64	0.355	9.00	0.605	15.40		
12	0.858	21.79	0.491	12.50	0.774	19.70		
14	0.984	24.99	0.565	14.40	0.838	21.30		
16	1.112	28.24	0.690	17.50	0.963	24.50		
18	1.218	30.93	0.769	19.50	1.042	26.50		
20	1.345	34.16	0.894	22.70	1.217	30.90		
22	1.468	37.28	1.019	25.90	1.355	34.40		
24	1.593	40.46	1.134	28.80	1.443	36.70		
28	1.969	50.01	1.369	34.80	1.709	43.40	0.994	25.30
32	2.219	56.36	1.615	41.00	1.919	48.70		
36	2.469	62.71	1.830	46.50	2.169	55.10		
40	2.719	69.06	2.045	51.90	2.402	61.00		
44	2.969	75.41	2.300	58.40	2.657	67.50		
48	3.219	81.76	2.550	64.80	2.907	73.80	0.832	21.10
61	1.653	41.98	1.174	29.80	1.529	38.80		


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/60-2G Series - Low profile shrink boot adapter - Aluminum, straight


For connectors:

- EN2997 & EN3646
- AS50151 crimp
- AS81703 Series 3
- MIL-DTL-26482 Series 2

Catalog number selection



Dimensions



Shell size	$\varnothing A$ $\begin{matrix} +0.00''/0.0 \\ -0.45''/11.43 \end{matrix}$ inches	mm	R max inches	mm	S $\pm 0.031''/0.78$ inches	mm
3	0.750	19.04	0.540	13.71	0.406	10.3
8	0.688	17.47	0.540	13.71	0.406	10.3
10	0.803	20.39	0.540	13.71	0.406	10.3
12	0.938	23.82	0.540	13.71	0.406	10.3
14	1.063	27.00	0.540	13.71	0.406	10.3
16	1.238	31.44	0.540	13.71	0.406	10.3
18	1.310	33.27	0.540	13.71	0.406	10.3
20	1.436	36.47	0.540	13.71	0.406	10.3
22	1.560	39.62	0.540	13.71	0.406	10.3
24	1.686	42.82	0.540	13.71	0.406	10.3
28	2.062	52.37	0.702	17.83	0.406	10.3
32	2.312	58.72	0.702	17.83	0.563	14.3
36	2.562	65.07	0.702	17.83	0.563	14.3
40	2.812	71.42	0.702	17.83	0.563	14.3
44	3.062	77.77	0.702	17.83	0.563	14.3
48	3.312	84.12	0.702	17.83	0.563	14.3
61	1.748	44.39	0.540	13.71	0.406	10.3

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- MIL-DTL-27599

Catalog number selection

M85049/61 10

Dash number									
08, 10, 12, 14, 16, 18, 20, 22, 24									
Shell size 38999 I	09	11	13	15	17	19	21	23	25
= Shell size 38999 II	08	10	12	14	16	18	20	22	24

Dimensions

Dash number	Ø A max inches	mm	Ø C inches +0.010/-0.000	mm	Ø D inches ±0.010/0.25	mm
8	0.594	15.1	0.516	13.10	0.476	12.1
10	0.734	18.6	0.642	16.30	0.602	15.3
12	0.844	21.4	0.766	19.45	0.726	18.4
14	0.969	24.6	0.892	22.65	0.852	21.6
16	1.094	27.8	1.018	25.85	0.978	24.8
18	1.234	31.3	1.142	29.00	1.102	28.0
20	1.344	34.1	1.268	32.20	1.228	31.2
22	1.469	37.3	1.392	35.35	1.352	34.3
24	1.594	40.5	1.518	38.55	1.478	37.5

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/62 Series - Shrink boot adapter - Aluminum, straight

For connectors:

- MIL-DTL-27599
- MIL-DTL-38999 Series I & II

Catalog number selection

M85049/62

10

N


D

Shell size										
08, 10, 12, 14, 16, 18, 20, 22, 24										
Shell size 38999 I	09	11	13	15	17	19	21	23	25	
= Shell size 38999 II	08	10	12	14	16	18	20	22	24	

Drain hole
D = With drain hole
empty = Without drain hole

Material and plating
A = Aluminum, black anodized
N = Aluminum, electroless nickel
W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray

Dimensions



Shell size	Ø A max inches	mm	C max inches	mm	Ø E max inches	mm	Ø F min inches	mm
8	0.750	19.05			0.533	13.54	0.250	6.35
10	0.850	21.59			0.605	15.37	0.375	9.53
12	1.000	25.40			0.774	19.66	0.500	12.70
14	1.100	27.94			0.838	21.29	0.625	15.88
16	1.250	31.75	1.000	25.40	0.963	24.46	0.750	19.05
18	1.400	35.56			1.042	26.47	0.812	20.62
20	1.500	38.10			1.217	30.91	0.937	23.80
22	1.650	41.91			1.355	34.42	1.062	26.97
24	1.750	44.45			1.443	36.65	1.188	30.18

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


Backshells

AS85049/63 Series - Cable tie strain relief - Aluminum 90°


For connectors:

- MIL-DTL-38999 Series I & II

Catalog number selection



Dimensions



Shell size	Ø C max inches	mm	D max inches	mm	E max inches	mm	Cable entry max inches	mm
8	0.860	21.8	1.220	31.0	0.690	17.5	0.264	6.7
10	0.980	24.9	1.290	32.8	0.690	17.5	0.392	9.9
12	1.160	29.5	1.620	41.1	0.690	17.5	0.506	12.8
14	1.280	32.5	1.660	42.2	0.700	17.8	0.631	16.0
16	1.410	35.8	1.720	43.7	0.700	17.8	0.756	19.2
18	1.520	38.6	1.720	43.7	0.730	18.5	0.845	21.4
20	1.640	41.7	1.790	45.5	0.730	18.5	0.970	24.6
22	1.770	45.0	1.850	47.0	0.730	18.5	1.095	27.8
24	1.890	48.0	1.910	48.5	0.730	18.5	1.220	31.0


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/69 Series - Shrink boot adapter - Aluminum, straight


For connectors:

- EN3645
- MIL-DTL-38999 Series III & IV

Catalog number selection



Dimensions



Shell size	Ø A max inches	mm	Ø B max inches	mm	Ø C max inches	mm
9	0.750	19.10	0.250	6.35	0.533	13.54
11	0.850	21.60	0.375	9.52	0.605	15.37
13	1.000	25.40	0.500	12.70	0.774	19.66
15	1.150	29.20	0.625	15.88	0.838	21.29
17	1.250	31.80	0.750	19.05	0.963	24.46
19	1.400	35.60	0.812	20.62	1.042	26.47
21	1.550	39.40	0.937	23.80	1.217	30.91
23	1.650	41.90	1.062	26.97	1.355	34.42
25	1.850	47.00	1.188	30.18	1.443	36.65

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

For connectors:

- MIL-DTL-38999 Series I & II


Catalog number selection

M85049/76 10 W 01										
Dash number										
08, 10, 12, 14, 16, 18, 20, 22, 24										
Shell size 38999 I	09	11	13	15	17	19	21	23	25	
= Shell size 38999 II	08	10	12	14	16	18	20	22	24	

Clamp size	
01, 02, 03, 04, 05, 06, 07, 08, 09, 10. See table below	

Material and plating	
N = Aluminum, electroless nickel	
W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray	

Dimensions



Clamp size	Y max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
01	0.800	20.32	0.062	1.57	0.125	3.18
02	1.000	25.40	0.125	3.18	0.250	6.35
03	1.100	27.94	0.250	6.35	0.375	9.53
04	1.200	30.48	0.375	9.53	0.500	12.70
05	1.250	31.75	0.500	12.70	0.625	15.88
06	1.400	35.56	0.625	15.88	0.750	19.05
07	1.500	38.10	0.750	19.05	0.875	22.23
08	1.650	41.91	0.875	22.23	1.000	25.40
09	1.750	44.45	1.000	25.40	1.125	28.58
10	1.900	48.26	1.125	28.58	1.250	31.75

Dash number	Clamp size min	max	Ø A max inches	mm	B inches ±0.156/3.96	mm	C inches ±0.188/4.77	mm	D max inches	mm
08	01	02	0.750	19.05	0.532	13.51	3.267	82.98	1.19	30.2
10	01	03	0.850	21.59	0.627	15.93	3.387	86.03	1.34	34.0
12	02	04	1.000	25.40	0.642	16.31	3.407	86.54	1.44	36.6
14	02	05	1.150	29.20	0.719	18.26	3.477	88.32	1.50	38.1
16	02	06	1.250	31.75	0.774	19.66	3.567	90.60	1.63	41.4
18	03	07	1.400	35.56	0.854	21.69	3.737	94.92	1.76	44.7
20	03	08	1.550	39.37	0.899	22.83	3.737	94.92	1.88	47.8
22	03	09	1.650	41.91	1.009	25.63	3.847	97.71	2.04	51.8
24	04	10	1.850	47.00	1.024	26.01	3.847	97.71	2.13	54.1

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/77 Series - EMI/RFI environmental backshell - Aluminum 45°

For connectors:

- MIL-DTL-38999 Series I & II


Catalog number selection

M85049/77 10 W 01									
Dash number									
08, 10, 12, 14, 16, 18, 20, 22, 24									
Shell size 38999 I	09	11	13	15	17	19	21	23	25
= Shell size 38999 II	08	10	12	14	16	18	20	22	24

Clamp size									
01, 02, 03, 04, 05, 06, 07, 08, 09, 10. See table below									

Material and plating									
N = Aluminum, electroless nickel W = Aluminum, olive drab cadmium over electroless nickel, 1000 hours salt spray									

Dimensions



Clamp size	Y max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
01	0.800	20.32	0.062	1.57	0.125	3.18
02	1.000	25.40	0.125	3.18	0.250	6.35
03	1.100	27.94	0.250	6.35	0.375	9.53
04	1.200	30.48	0.375	9.53	0.500	12.70
05	1.250	31.75	0.500	12.70	0.625	15.88
06	1.400	35.56	0.625	15.88	0.750	19.05
07	1.500	38.10	0.750	19.05	0.875	22.23
08	1.650	41.91	0.875	22.23	1.000	25.40
09	1.750	44.45	1.000	25.40	1.125	28.58
10	1.900	48.26	1.125	28.58	1.250	31.75


Dash number	Clamp size min	max	Ø A max inches	mm	B $\pm 0.156/3.96$ inches	mm	C $\pm 0.188/4.77$ inches	mm	D max inches	mm
08	01	02	0.750	19.05	0.398	10.11	3.088	78.44	3.06	77.72
10	01	03	0.850	21.59	0.458	11.63	3.148	79.96	3.20	81.28
12	02	04	1.000	25.40	0.518	13.16	3.208	81.48	3.34	84.84
14	02	05	1.150	29.20	0.588	14.94	3.298	83.77	3.49	88.65
16	02	06	1.250	31.75	0.678	17.22	3.408	86.56	3.71	94.23
18	03	07	1.400	35.56	0.868	22.05	3.598	91.39	4.01	101.85
20	03	08	1.550	39.37	0.868	22.05	3.598	91.39	4.13	104.90
22	03	09	1.650	41.91	0.958	24.33	3.748	95.20	4.36	110.74
24	04	10	1.850	47.00	0.958	24.33	3.748	95.20	4.41	112.01

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- MIL-DTL-38999 Series III & IV

Catalog number selection



Dimensions



Clamp size	Y max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
01	0.800	20.32	0.062	1.57	0.125	3.18
02	1.000	25.40	0.125	3.18	0.250	6.35
03	1.100	27.94	0.250	6.35	0.375	9.53
04	1.200	30.48	0.375	9.53	0.500	12.70
05	1.250	31.75	0.500	12.70	0.625	15.88
06	1.400	35.56	0.625	15.88	0.750	19.05
07	1.500	38.10	0.750	19.05	0.875	22.23
08	1.650	41.91	0.875	22.23	1.000	25.40
09	1.750	44.45	1.000	25.40	1.125	28.58
10	1.900	48.26	1.125	28.58	1.250	31.75

Dash number	Clamp size min	max	Ø A max inches	mm	B $\pm 0.062"/1.57\text{mm}$ inches	mm	C $\pm 0.062"/1.57\text{mm}$ inches	mm	D $\pm 0.062"/1.57\text{mm}$ inches	mm
09	01	02	0.750	19.05	0.398	10.11	3.088	78.44	2.85	72.39
11	01	03	0.850	21.59	0.458	11.63	3.148	79.96	2.98	75.69
13	02	04	1.000	25.40	0.518	13.16	3.208	81.48	3.13	79.50
15	02	05	1.150	29.20	0.588	14.94	3.298	83.77	3.32	84.33
17	02	06	1.250	31.75	0.678	17.22	3.408	86.56	3.53	89.66
19	03	07	1.400	35.56	0.868	22.05	3.598	91.39	3.91	99.31
21	03	08	1.550	39.37	0.868	22.05	3.598	91.39	3.96	100.58
23	03	09	1.650	41.91	0.958	24.33	3.748	95.20	4.19	106.43
25	04	10	1.850	47.00	0.958	24.33	3.748	95.20	4.24	107.70


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/79 Series - EMI/RFI environmental backshell - Aluminum 90°


For connectors:

- MIL-DTL-38999 Series III & IV

Catalog number selection



Dimensions



Clamp size	Y max inches	mm	Cable entry min inches	mm	Cable entry max inches	mm
01	0.800	20.32	0.062	1.57	0.125	3.18
02	1.000	25.40	0.125	3.18	0.250	6.35
03	1.100	27.94	0.250	6.35	0.375	9.53
04	1.200	30.48	0.375	9.53	0.500	12.70
05	1.250	31.75	0.500	12.70	0.625	15.88
06	1.400	35.56	0.625	15.88	0.750	19.05
07	1.500	38.10	0.750	19.05	0.875	22.23
08	1.650	41.91	0.875	22.23	1.000	25.40
09	1.750	44.45	1.000	25.40	1.125	28.58
10	1.900	48.26	1.125	28.58	1.250	31.75


Dash number	Clamp size min	max	Ø A max inches	mm	B inches ±0.156/3.96	mm	C inches ±0.188/4.77	mm	D max inches	mm
09	01	02	0.750	19.05	0.532	13.51	3.267	82.98	1.19	30.2
11	01	03	0.850	21.59	0.627	15.93	3.387	86.03	1.34	34.0
13	02	04	1.000	25.40	0.642	16.31	3.407	86.54	1.44	36.6
15	02	05	1.150	29.20	0.719	18.26	3.477	88.32	1.50	38.1
17	02	06	1.250	31.75	0.774	19.66	3.567	90.60	1.63	41.4
19	03	07	1.400	35.56	0.854	21.69	3.737	94.92	1.76	44.7
21	03	08	1.550	39.37	0.899	22.83	3.737	94.92	1.88	47.8
23	03	09	1.650	41.91	1.009	25.63	3.847	97.71	2.04	51.8
25	04	10	1.850	47.00	1.024	26.01	3.847	97.71	2.13	54.1

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
 Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

For connectors:


- EN2997
- EN3646
- AS50151 crimp
- AS81703 Series 3
- MIL-DTL-26482 Series 2
- MIL-DTL-83723 Series 3

Catalog number selection



Notes: * - utilizes an audible detented anti-decoupling device.
** - utilizes an internal captivated anti-decoupling device (Self-Seating) with no audible clicking mechanism.

Dimensions



Shell size	Ø A max inches	mm	D1 max inches	mm	E1 max inches	mm	D2 max inches	mm	E2 max inches	mm	Cable entry Size 02 inches	mm	Cable entry Size 03 inches	mm
8	0.885	22.47	0.870	22.10	1.160	29.50	1.188	30.20	1.417	36.00	N/A	N/A	0.250	6.40
10	1.010	25.70	0.890	22.60	1.180	30.00	1.281	32.50	1.480	37.60	N/A	N/A	0.312	7.90
12	1.135	28.82	0.920	23.40	1.200	30.50	1.406	35.70	1.542	39.20	0.312	7.90	0.438	11.10
14	1.260	32.00	0.940	23.90	1.220	31.00	1.531	38.90	1.605	40.80	0.438	11.10	0.562	14.30
16	1.385	35.17	0.960	24.40	1.250	31.80	1.656	42.10	1.667	42.30	0.500	12.70	0.625	15.90
18	1.510	38.40	0.980	24.90	1.260	32.00	1.718	43.60	1.730	43.90	0.625	15.90	0.750	19.10
20	1.635	41.52	1.000	25.40	1.290	32.80	1.844	46.80	1.792	45.50	0.625	15.90	0.812	20.60
22	1.760	44.70	1.030	26.20	1.310	33.30	1.938	49.20	1.850	47.00	0.688	17.50	0.938	23.80
24	1.885	47.87	1.050	26.70	1.340	34.00	2.093	53.20	1.917	48.70	0.750	19.10	1.000	25.40
28	2.135	54.22	1.100	27.90	1.380	35.10	2.531	64.30	2.042	51.90	0.875	22.20	1.125	28.60


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/85, 86, 87 Series - Banding backshell - Aluminum straight, 45° and 90°


For connectors:

- MIL-DTL-27599
- MIL-DTL-38999 Series I & II

Catalog number selection



Dimensions




Shell size	Ø A max inches mm		D1 max inches mm		E1 max inches mm		D2 max inches mm		E2 max inches mm		Cable entry for AS85049/85, Straight version				Cable entry for AS85049/86 and AS85049/87, 45° & 90°			
											Size 01 inches mm	Size 02 inches mm	Size 03 inches mm	Size 04 inches mm	Size 02 inches mm	Size 03 inches mm	Size 04 inches mm	Size 05 inches mm
08	0.859	21.81	0.870	22.10	1.160	29.50	1.375	34.90	1.417	36.00	N/A	N/A	0.250	6.40	N/A	N/A	0.250	6.40
10	0.986	25.04	0.900	22.90	1.190	30.20	1.437	36.50	1.480	37.60	N/A	N/A	0.312	7.90	N/A	N/A	0.312	7.90
12	1.156	29.36	0.920	23.40	1.210	30.70	1.562	39.70	1.553	39.40	0.312	7.90	0.438	11.10	0.312	7.90	0.438	11.10
14	1.281	32.53	0.950	24.10	1.240	31.50	1.687	42.80	1.614	41.00	0.438	11.10	0.562	14.30	0.438	11.10	0.562	14.30
16	1.406	35.71	0.980	24.90	1.260	32.00	1.750	44.50	1.678	42.60	0.500	12.70	0.625	15.90	0.500	12.70	0.625	15.90
18	1.516	38.50	0.980	24.90	1.270	32.30	1.875	47.60	1.733	44.00	0.625	15.90	0.750	19.10	0.625	15.90	0.750	19.10
20	1.641	41.68	1.010	25.70	1.300	33.00	1.938	49.20	1.796	45.60	0.625	15.90	0.812	20.60	0.625	15.90	0.812	20.60
22	1.766	44.85	1.040	26.40	1.330	33.80	2.062	52.40	1.859	47.20	0.688	17.50	0.938	23.80	0.688	17.50	0.938	23.80
24	1.891	48.03	1.070	27.20	1.350	34.30	2.125	54.00	1.919	48.70	0.750	19.10	1.000	25.40	0.750	19.10	1.000	25.40

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification.
 Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.


For connectors:

- EN3645
- MIL-DTL-38999 Series III & IV

Catalog number selection



Dimensions



Shell size	Ø A max inches	mm	D1 max inches	mm	E1 max inches	mm	D2 max inches	mm	E2 max inches	mm	Cable entry Size 02 inches	mm	Cable entry Size 03 inches	mm
9	0.858	21.8	1.010	25.70	1.160	29.50	1.375	34.90	1.417	36.00	N/A	N/A	0.250	6.40
11	0.984	25.1	1.030	26.20	1.190	30.20	1.437	36.50	1.480	37.60	N/A	N/A	0.312	7.90
13	1.157	29.4	1.060	26.90	1.210	30.70	1.562	39.70	1.553	39.40	0.312	7.90	0.438	11.10
15	1.279	32.5	1.080	27.40	1.240	31.50	1.687	42.80	1.614	41.00	0.438	11.10	0.562	14.30
17	1.406	35.7	1.110	28.20	1.260	32.00	1.750	44.50	1.678	42.60	0.500	12.70	0.625	15.90
19	1.516	38.5	1.120	28.40	1.270	32.30	1.875	47.60	1.773	45.03	0.625	15.90	0.750	19.10
21	1.642	41.7	1.150	29.20	1.300	33.00	1.938	49.20	1.796	45.60	0.625	15.90	0.812	20.60
23	1.738	44.9	1.170	29.70	1.330	33.80	2.062	52.40	1.859	47.20	0.688	17.50	0.938	23.80
25	1.889	48.0	1.200	30.50	1.350	34.30	2.125	54.00	1.919	48.70	0.750	19.10	1.000	25.40


Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

AS85049/91,92 Series - Cable clamp strain relief - Composite straight and 90°


For connectors:

- EN3645
- MIL-DTL-38999 Series III & IV

Catalog number selection



Dimensions



Shell size	Ø A max inches	mm	B max inches	mm	C ^{±0.031"} inches	mm	H ^{±.062"} inches	mm	K max inches	mm
09	0.858	21.79	0.98	24.89	0.219	5.56	0.875	22.2	1.06	26.92
11	0.984	24.99	1.05	26.67	0.264	6.71	0.937	23.8	1.10	27.94
13	1.157	29.39	1.20	30.48	0.344	8.74	1.031	26.2	1.18	29.97
15	1.280	33.51	1.30	33.02	0.460	11.68	1.125	28.6	1.30	33.02
17	1.406	35.71	1.42	36.07	0.545	13.84	1.312	33.3	1.38	35.05
19	1.516	38.51	1.52	38.61	0.615	15.62	1.375	34.9	1.45	36.83
21	1.642	41.51	1.64	41.66	0.698	17.73	1.500	38.1	1.54	39.12
23	1.768	44.91	1.77	44.96	0.780	19.81	1.625	41.3	1.62	41.15
25	1.890	48.01	1.89	48.01	0.850	21.59	1.750	44.5	1.69	42.93

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

For connectors:


- EN3645
- MIL-DTL-38999 Series III & IV

Catalog number selection

M85049/ 103 15

Angle	Shell size
103 = Straight	09, 11, 13, 15, 17, 19, 21, 23, 25
104 = 45°	
105 = 90°	

Dimensions





Shell size	Ø A max inches/mm	B max inches/mm	Ø C ^{±.031"} inches/mm ^{±0.79mm}	L1 max inches/mm	L2 max inches/mm	L3 max inches/mm	N Hex inches	mm	Ø P min inches/mm	R1 max inches/mm	R2 max inches/mm
09	0.858 21.79	0.98 24.89	0.265 6.73	0.939 23.85	1.128 28.65	1.128 28.65	0.750/736	19.05/18.69	0.264 6.71	0.901 22.89	0.94 23.88
11	0.984 24.99	1.05 26.67	0.310 7.87	1.059 26.90	1.168 29.67	1.168 29.67	0.875/860	22.23/21.84	0.390 9.91	0.964 24.39	1.00 25.40
13	1.157 29.39	1.20 30.48	0.390 9.91	1.199 30.45	1.248 31.70	1.248 31.70	1.000/980	25.40/24.89	0.504 12.80	1.050 26.67	1.12 28.45
15	1.280 32.51	1.30 33.02	0.506 12.85	1.199 30.45	1.368 34.75	1.368 34.75	1.125/1.100	31.75/31.09	0.630 16.00	1.112 28.24	1.19 30.23
17	1.406 35.71	1.44 36.58	0.591 15.01	1.329 33.76	1.448 36.78	1.448 36.78	1.250/1.224	31.75/31.09	0.756 19.20	1.175 29.85	1.37 34.80
19	1.516 38.51	1.56 39.62	0.661 16.79	1.509 38.33	1.528 38.81	1.528 38.81	1.375/1.348	34.94/34.24	0.843 21.41	1.230 31.24	1.44 36.58
21	1.642 41.71	1.69 42.93	0.744 18.90	1.609 40.87	1.648 41.86	1.648 41.86	1.500/1.469	38.10/37.31	0.969 24.61	1.293 32.84	1.56 39.62
23	1.768 44.91	1.77 44.96	0.826 20.98	1.759 44.68	1.688 42.88	1.688 42.88	1.625/1.581	41.28/40.16	1.091 27.71	1.365 34.67	1.69 42.93
25	1.890 48.01	1.89 48.01	0.896 22.76	1.859 47.22	1.758 44.65	1.758 44.65	1.750/1.690	44.45/42.93	1.217 30.91	1.417 35.99	1.81 45.97

Notes: All dimensions are in inches and millimeters. For complete dimensions, see the applicable Military Specification. Cable entry is defined as the envelope area of the cable or wire bundle. It is not intended for inspection criteria.

For connectors:

- AS50151

Catalog number selection**Dimensions**

Size	Thread A	ØC max inches	mm	ØD inches	^{+0.010"/0.254mm} _{0.005"/0.127mm} mm	E inches	mm	L max inches	mm
8	1/2 - 28 UNEF	0.562	14.27	0.156	3.96	4.00	101.6	0.969	24.61
10	5/8 - 24 UNEF	0.687	17.44						
12	3/4 - 20 UNEF	0.812	20.62						
14	7/8 - 20 UNEF	0.937	23.79			4.50	114.3		
16	1 - 20 UNEF	1.062	26.97						
18	1 1/8 - 18 UNEF	1.187	30.14	0.187	4.74	5.00	127.0	1.156	29.36
20	1 1/4 - 18 UNEF	1.312	33.32						
22	1 3/8 - 18 UNEF	1.437	36.49						
24	1 1/2 - 18 UNEF	1.562	39.67			5.50	139.7		
28	1 3/4 - 18 UNS	1.812	46.02						
32	2 - 18 UNS	2.062	52.37	0.218	5.53	7.75	196.85		
36	2 1/4 - 16 UN	2.312	58.72						
40	2 1/2 - 16 UN	2.562	65.07						
44	2 3/4 - 16 UN	2.812	71.42						
48	3 - 16 UN	3.062	77.77						

Notes: All dimensions are in inches and millimeters.

3


Protective covers

AS25043 Series - Threaded connector covers


For connectors:

- AS50151

Catalog number selection



Dimensions



Size	Thread A	ØC max inches	mm	ØD inches	^{+0.010"/0.254mm} _{-0.005"/0.127mm} mm	E inches	mm	L max inches	mm
8	1/2 - 28 UNEF	0.688	17.47	0.140	3.55	4.00	101.6	0.750	19.04
10	5/8 - 24 UNEF	0.815	20.70						
12	3/4 - 20 UNEF	1.000	25.40						
14	7/8 - 20 UNEF	1.125	28.57						
16	1 - 20 UNEF	1.188	30.17	0.171	4.34	4.50	114.3		
18	1 1/8 - 18 UNEF	1.344	34.13						
20	1 1/4 - 18 UNEF	1.469	37.31						
22	1 3/8 - 18 UNEF	1.594	40.48						
24	1 1/2 - 18 UNEF	1.719	43.66			5.00	127.0		
28	1 3/4 - 18 UNS	1.969	50.01						
32	2 - 18 UNS	2.219	56.36	0.187	4.74	5.50	139.7		
36	2 1/4 - 16 UN	2.469	62.71						
40	2 1/2 - 16 UN	2.719	69.06						
44	2 3/4 - 16 UN	2.969	75.41						
48	3 - 16 UN	3.188	80.97					7.75	196.85


Notes: All dimensions are in inches and millimeters.

D38999/32 Series - Threaded connector covers


For connectors:

- EN3645
- MIL-DTL-38999 Series III

Catalog number selection



Dimensions



Size	Thread A	ØB max inches	mm	ØE min inches	mm	G inches	mm
9	0.6250-0.1P-0.3L-TS	0.905	23.0	0.512	13.0		
11	0.7500-0.1P-0.3L-TS	1.023	26.0	0.709	18.0		
13	0.8750-0.1P-0.3L-TS	1.220	31.0	0.787	20.0		
15	1.0000-0.1P-0.3L-TS	1.299	33.0	0.905	23.0		
17	1.1875-0.1P-0.3L-TS	1.457	37.0	1.023	26.0	5.00 ^{+0.512\"/>} _{-0.276\"/>}	127.0 ^{+13\"/>} _{-7\"/>}
19	1.2500-0.1P-0.3L-TS	1.575	40.0	1.142	29.0		
21	1.3750-0.1P-0.3L-TS	1.732	44.0	1.260	32.0		
23	1.5000-0.1P-0.3L-TS	1.811	46.0	1.339	34.0		
25	1.6250-0.1P-0.3L-TS	1.968	50.0	1.535	39.0		

Notes: All dimensions are in inches and millimeters.

3


Protective covers

D38999/33 Series - Threaded connector covers


For connectors:

- EN3645
- MIL-DTL-38999 Series III

Catalog number selection



Dimensions





Size	Thread A	ØB max inches	mm	ØD min inches	mm	F inches	mm
9	0.6250-0.1P-0.3L-TS	0.905	23.0	0.690	17.64		
11	0.7500-0.1P-0.3L-TS	1.102	28.0	0.860	21.97		
13	0.8750-0.1P-0.3L-TS	1.220	31.0	0.990	25.12		
15	1.0000-0.1P-0.3L-TS	1.260	32.0	1.180	29.92		
17	1.1875-0.1P-0.3L-TS	1.457	37.0	1.260	32.00	5.00 ^{+0.512"} _{-0.276"}	127.0 ⁺¹³ ₋₇
19	1.2500-0.1P-0.3L-TS	1.535	39.0	1.430	36.27		
21	1.3750-0.1P-0.3L-TS	1.653	42.0	1.510	38.25		
23	1.5000-0.1P-0.3L-TS	1.772	45.0	1.680	42.62		
25	1.6250-0.1P-0.3L-TS	1.929	49.0	1.750	44.45		

Notes: All dimensions are in inches and millimeters.

For connectors:

- MIL-DTL-38999 Series I

Catalog number selection**Dimensions**


Size	ØF max inches	mm	H ^{+0.500\"/>+0.250\"} inches	mm
9	0.82	20.80	3.00	76.19
11	0.94	23.90		
13	1.07	27.20		
15	1.19	30.20		
17	1.32	33.52	3.50	88.89
19	1.44	36.60		
21	1.57	39.90		
23	1.69	42.90	4.00	101.6
25	1.82	46.20		

Notes: All dimensions are in inches and millimeters.


For connectors:

- MIL-DTL-38999 Series I

Catalog number selection



Dimensions



Size	ØQ max inches	mm	H inches	mm	ØN min inches	mm
9	0.86	21.84	3.00	76.19	0.70	17.77
11	0.98	24.89			0.84	21.33
13	1.16	29.46			1.01	25.65
15	1.28	32.51			1.14	28.95
17	1.41	35.81	3.50	88.89	1.26	32.00
19	1.52	38.60			1.39	35.30
21	1.65	41.91			1.51	38.35
23	1.77	44.95	4.00	101.6	1.64	41.65
25	1.89	48.00			1.76	44.70


Notes: All dimensions are in inches and millimeters.

MS27510 Series - Bayonet connector covers


For connectors:

- MIL-DTL-38999 Series II

Catalog number selection



Dimensions



Size	ØQ max inches	mm	H ^{+0.500\"/>+12.7/-6.35mm} inches	mm
8	0.72	18.28	3.00	76.19
10	0.85	21.59		
12	1.00	25.40		
14	1.13	28.70		
16	1.25	31.75	3.50	88.89
18	1.38	35.05		
20	1.50	38.09		
22	1.63	41.40	4.00	101.6
24	1.75	44.44		

Notes: All dimensions are in inches and millimeters.

3


Protective covers

MS27511 Series - Bayonet connector covers


For connectors:

- MIL-DTL-38999 Series II

Catalog number selection



Dimensions



Size	ØQ max inches	mm	H inches	mm
8	0.750	19.04	3.00	76.19
10	0.859	21.81		
12	1.031	26.18		
14	1.156	29.36		
16	1.281	32.53	3.50	88.89
18	1.406	35.71		
20	1.531	38.88		
22	1.641	41.68	4.00	101.6
24	1.766	44.85		


Notes: All dimensions are in inches and millimeters.

MS3180 Series - Bayonet connector covers


For connectors:

- MIL-DTL-26482 Series 2

Catalog number selection



Dimensions



Size	ØF max inches	mm	H max inches +0.500"/-0.250" +12.7/-6.35mm	mm	L max inches	mm
8	0.719	18.26	3.00	76.20	0.562	14.27
10	0.844	21.44				
12	1.000	25.40				
14	1.125	28.58	3.5	88.90	0.625	15.88
16	1.250	31.75				
18	1.375	34.92				
20	1.500	38.150	4.00	101.60	0.658	16.71
22	1.625	41.28				
24	1.750	44.45				

Notes: All dimensions are in inches and millimeters.

3


Protective covers

MS3181 Series - Bayonet connector covers


For connectors:

- MIL-DTL-26482 Series 2

Catalog number selection



Dimensions



Size	ØQ max inches	mm	H max inches +0.500"/+0.250" -0.127/-6.35mm	mm	L max inches	mm	ØN min inches	mm
8	0.734	18.64	3.00	76.20	0.562	14.27	0.578	14.68
10	0.859	21.82					0.703	17.86
12	1.000	25.40					0.891	22.63
14	1.125	28.58	3.5	88.90			1.016	15.81
16	1.250	31.75					1.141	28.98
18	1.375	34.92					1.266	32.16
20	1.500	38.10	4.00	101.60	0.602	15.29	1.391	35.33
22	1.625	41.28					1.516	38.51
24	1.750	44.45					1.641	41.68

Notes: All dimensions are in inches and millimeters.


Catalog number selection

M85049/93 04

Dash number

04, 06, 08, 10, 12, 14, 16, 18, 20, 22, 24, 26, 28

Dimensions



Dash number	A ^{±.0100"} inches _{±0.254mm}	mm	B max inches	mm
04	0.250	6.35	0.390	9.9
06	0.375	9.52	0.515	13.1
08	0.500	12.70	0.640	16.3
10	0.625	15.88	0.770	19.6
12	0.750	19.05	0.903	22.9
14	0.875	22.22	1.094	26.5
16	1.000	25.40	1.173	29.8
18	1.125	28.58	1.310	33.3
20	1.250	31.75	1.447	36.8
22	1.375	34.92	1.578	40.1
24	1.500	38.10	1.703	43.3
26	1.625	41.28	1.828	46.4
28	1.750	44.45	1.953	49.6


Notes: All dimensions are in inches and millimeters.

Catalog number selection

M85049/127 01

Order
01, 02, 03

Dimensions



Order	A $\pm 0.031''$ $\pm 0.8\text{mm}$ inches	mm	Used on size /118, /120, /121, /12	Used on size /124, /126
01	0.312	7.92	03-16	09-17
02	0.440	11.18	18-24 & 61	19-25
03	0.560	14.22	28-40	-

Notes: All dimensions are in inches and millimeters.


AS85049/128 Series - Clamping bands - Stainless steel

Catalog number selection

M85049/128 1

Configuration
1, 2, 3, 4

Dimensions



Configuration	A inches	mm	B $\pm 0.031"$ $\pm 0.76\text{mm}$ inches	mm	C $\pm 0.010"$ $\pm 0.25\text{mm}$ inches	mm	D $\pm 0.003"$ $\pm 0.08\text{mm}$ inches	mm	E $\pm 0.015"$ $\pm 0.38\text{mm}$ inches	mm	G max inches	mm	H ref inches	mm
1	13.94	354.07	0.328	8.33	0.245	6.22	0.19	0.48	0.100	2.54	—	—	—	—
	14.31	363.47												
2	—	—	—	—	—	—	—	—	—	—	0.140	3.56	1.750	44.45
3	14.19	360.42	0.350	8.89	0.245	6.22	0.019	0.48	0.074	1.88	—	—	—	—
	14.31	363.47												
4	—	—	—	—	—	—	—	—	—	—	0.150	3.81	1.750	44.45

Notes: All dimensions are in inches and millimeters.

Backshells

AS85049/6	P.08
AS85049/7	P.11
AS85049/8	P.14
AS85049/9	P.17
AS85049/10	P.20
AS85049/11	P.24
AS85049/14	P.28
AS85049/15	P.29
AS85049/16	P.29
AS85049/17	P.30
AS85049/18	P.31
AS85049/19	P.32
AS85049/20	P.33
AS85049/21	P.34
AS85049/23	P.35
AS85049/24	P.38
AS85049/25	P.41
AS85049/26-1	P.46
AS85049/26-2	P.47
AS85049/26-3	P.46
AS85049/27	P.48
AS85049/29	P.49
AS85049/31	P.50
AS85049/33-2	P.52
AS85049/36	P.53
AS85049/37	P.54
AS85049/38	P.55
AS85049/39	P.56
AS85049/42	P.57
AS85049/43	P.58
AS85049/45	P.59
AS85049/46	P.60
AS85049/47	P.61
AS85049/49-2	P.62
AS85049/51	P.63
AS85049/52	P.65
AS85049/53	P.67
AS85049/54	P.67
AS85049/55	P.67
AS85049/57	P.68
AS85049/58	P.69
AS85049/60-1	P.70
AS85049/60-2G	P.71
AS85049/61	P.72
AS85049/62	P.73
AS85049/63	P.74
AS85049/69	P.75
AS85049/76	P.76
AS85049/77	P.77
AS85049/78	P.78
AS85049/79	P.79
AS85049/82	P.80
AS85049/83	P.80
AS85049/84	P.80
AS85049/85	P.81
AS85049/86	P.81
AS85049/87	P.81
AS85049/88	P.82
AS85049/89	P.82
AS85049/90	P.82
AS85049/91	P.83
AS85049/92	P.83
AS85049/103	P.84
AS85049/104	P.84
AS85049/105	P.84

Protective Cover

AS25042	P.85
AS25043	P.86
D38999/32	P.87
D38999/33	P.88
MS27501	P.89
MS27502	P.90
MS27510	P.91
MS27511	P.92
MS3180	P.93
MS3181	P.94

Accessories

AS85049/93	P.95
AS85049/127	P.96
AS85049/128	P.97

