

Reference Design

Circuit Providing Backup Power From an EDLC Super Capacitor



FEATURES

- Can supply high peak currents (1 A to 5 A peak inductor current limit)
- Super capacitor based backup circuit
- Low quiescent current

KEY COMPONENTS

- [EDLC ENYCAP™ super capacitor](#)
- [IHL P0806 inductor](#)
- [T55 vPolyTan™ tantalum capacitors](#)

APPLICATIONS

- Handheld equipment
- Portable devices with removable batteries
- Industrial sensor and actuators
- Aftermarket automotive tracking
- Energy storage for IoT devices
- Graceful shutdown of embedded systems

LINKS TO ADDITIONAL RESOURCES

- [EDLCBU-3V3](#)

DESCRIPTION

The EDLCBU-3V3 is a circuit providing backup power from an EDLC super capacitor to a 3.3 V circuit intended to bridge gaps in the power supply, such as while changing batteries, switching power sources, or allowing for a graceful shutdown after power loss.

Further, the circuit can be used to supply photovoltaic powered IoT nodes with energy during darkness or can provide the needed energy to tracking devices even after the main battery was disconnected.

To achieve these tasks, a buck-boost converter is used to interface between the EDLC's super capacitor energy storage and the 3.3 V rail of the application, charging the supercapacitor under normal operation and providing a stable voltage of 3 V during backup operation.

OVERALL SYSTEM BLOCK DIAGRAM




Fig. 1 - Overall System Block Diagram



APPLICATION DESCRIPTION

The EDLCBU-3V3 uses two (or more) parallel EDLC super capacitors to store energy in normal operation and to provide energy to the application during backup operation.

To achieve this task, the EDLC super capacitors and the 3.3 V rail of the protected circuit are connected via a buck-boost DC/DC converter based on the MAX38890 2.5 V to 5.5 V, 5 A reversible buck-boost regulator for backup applications and the IHLP0806ABEZR47M5A inductor.

As long as the system voltage VSYS is above 3.08 V the DC/DC converter charges the EDLC energy storage to a maximum voltage of 3 V using an average current of up to 2.5 A, reaching peak inductor currents of 5 A. If the system voltage VSYS drops below 3.08 V the DC/DC converter switches to backup mode and provides the energy stored in the EDLC to the system rail regulating the output to 3.0 V or the max. allowed current until the energy stored in the ELDC is expended.

The maximum EDLC charging and discharging current can be set using the trimmer R12 and determines the lowest voltage for the storage capacitor at which the DC/DC converter drops out.

The development kit offer access to all signal pins of the MAX38890 and can be mounted on standard bread boards. Further EDLCs can be added on J4 and J5, increasing the energy storage capability for prototyping purposes.

For an exact description of the DC/DC converter, its configuration options, and reset conditions, please consult the MAX38890 datasheet.

Under normal operating conditions the EDLC is charged up to 2.7 V and can be discharged down to 0.8 V. Therefore, the energy available to the system rail can be approximated by:

E = 1/2 * C * V^2 = C * 0.5 * (2.7^2 * V^2 - 0.8^2 * V^2) = C * 3.325 V^2

Should the DC/DC converter IC not allow the discharge down to 0.8 V (e.g., as can be the case when limiting the peak inductor current to low values), the accessible energy can be lower. In the best case the configuration is such that the IC discharges the capacitor down to 0.5 V, allowing for the use more energy from the same capacitance value. The exact cut of voltage depends on the maximum allowed peak inductor current and load current. For more information, please consult the MAX38890 datasheet.

Table with 4 columns: DEVELOPMENT KIT VPN, CAPACITOR VPN, CAPACITY, ENERGY AVAILABLE. Rows include capacitor types like 3.3VEDLCMB050F and their capacities and energy values.

Note

- Available on request

Higher capacitances can be prototyped by paralleling extra capacitors to the existing two capacitors using J4 and J5.

Time Available in Backup Mode

To calculate the time available in backup mode, it is best to use the worst case end of life capacitance of the chosen EDLC storage capacitor calculate the energy available to the DC/DC converter and then compare this to the energy consumption of the circuit to be operated in backup mode.

Current and Voltage Waveform Examples Using 2 x 40 F EDLCs

The following graph shows the system rail voltage VSYS and super capacitor voltage over time while in backup mode with a load of 4.7 Ohms. The combined capacitance of 80 F is discharged over a 4.7 Ohm load.




Fig. 2 - Backup Operation on 4.7 Ω Load

With a higher load impedance, the circuit discharges to lower voltages. With 6.5 Ω load and a peak inductor current setting of 5 A, the EDLC is discharged down to 0.55 V. The circuit supplies 0.5 A at 3.0 V for about 200 s before it drops out.




Fig. 3 - Backup Operation on 6.5 Ω Load

Set to minimum inductor current, charging of the 80 F of the EDLC capacitance requires approximately 440 s.




Fig. 4 - Charging at Minimum Peak Inductor Current

When set to maximum peak inductor current, the charging time decreases to about 90 s, as seen in the following graph. Alongside the charging curve, the graph shows the IC recharging the capacitor to maintain the capacitor voltage compensating resistance parallel to the capacitor such as voltage dividers, IC current draw, and leakage resistance.




Fig. 5 - Charging at Maximum Peak Inductor Current



Disclaimer

1. Vishay Intertechnology, Inc. and its affiliates (“**Vishay**”) provides the reference design to which this disclaimer is attached (the “**reference design**”), and may provide certain products, parts and components to implement the reference design (each, an “**evaluation kit**”), solely to assist customers and potential customers (each, a “**user**”) who, in a research and development setting, are developing products and applications that incorporate Vishay products. This disclaimer supplements the terms of and conditions under which the user gains access to the reference design and / or evaluation kit (the “**terms and conditions**”). If and to the extent this disclaimer conflicts with the terms and conditions, this disclaimer will control.
2. Vishay and their respective directors, officers, agents, and employees (collectively, the “**Vishay parties**”), disclaim any and all warranties concerning the reference design or evaluation kits, and all liability for any errors, inaccuracies, incompleteness or other defects in the reference design or evaluation kits. Without limiting the foregoing:
 - 2.1. Users are responsible for (a) using their independent analysis, evaluation and judgment to validate the operating parameters, including typical parameters, for each component specified by the reference design or included in an evaluation kit, (b) assuring the safety of the products they develop and the compliance of those products with all applicable regulations, laws and other applicable requirements, and (c) obtaining any licenses to third party intellectual property rights that may be necessary for their products.
 - 2.2. Vishay makes no warranty, representation, or guarantee regarding the suitability of the reference design or evaluation kits for any particular purpose. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any design or product, (ii) any and all liability, including without limitation special, consequential, or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement, and merchantability. The aggregate liability of all Vishay parties will not exceed the amount the Vishay parties received in exchange for the reference design or evaluation kit giving rise to the claim.
3. Users acknowledge that (i) the reference design was created under laboratory conditions, and no Vishay party has conducted any testing other than as may be specifically described in the reference design, (ii) any information in the reference design related to third party components described by a reference design or included in an evaluation kit (“**third party products**”) does not constitute a license to use any third party product, or a warranty or endorsement of any third party product, and use of any such information, products or services may require a license from a third party under patents or other intellectual property rights and (iii) Vishay may make corrections, enhancements, improvements and other changes to their respective products and services, reference design, or evaluation kit, and to discontinue any product or service. Vishay has no obligations and makes no claims, representations, warranties, or guarantees regarding third party products included in a reference design or evaluation kit.
 - 2.4. Statements regarding the suitability of the reference design, evaluation kit, or other Vishay product for certain types of applications are based on Vishay’s knowledge of typical requirements often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of the reference design, evaluation kit, or other Vishay product for a particular application. It is the customer’s responsibility to validate that a particular reference design, evaluation kit, or other Vishay product with the properties described in the reference design or included in the evaluation kit is suitable for a particular application.
 - 2.5. The reference design is not fault-tolerant and is not intended for high risk applications, including without limitation in the operation of nuclear facilities, aircraft navigation or control systems, air traffic control, life support machines, weapons systems, or any other application in which the failure of the reference design could lead to death, personal injury, or severe physical or environmental damages. Any use of the reference design in connection with high risk applications or any other applications is fully at the user’s own risk. Neither the evaluation kits nor their components are intended for commercial products or in consumer or household environments.
3. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.
4. This disclaimer will be governed by the laws of the Commonwealth of Pennsylvania without reference to conflict of laws principles. User and the Vishay parties agree that the sole and exclusive jurisdiction for any dispute regarding the reference design or evaluation kits will be the state and federal courts sitting in Philadelphia, Pennsylvania.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.