


Managed Flash Memory Solutions

Universal Flash Storage (UFS) and e-MMC

Our UFS (Universal Flash Storage) and e-MMC Managed Flash solutions integrate flash memory and a KIOXIA controller in a single package. An ideal replacement for e-MMC, UFS combines the high performance, power efficiency and enhanced reliability demanded by mobile applications, including smartphones, tablets, AR/VR, automotive and more.



DESIGN CONSIDERATIONS

Use UFS when:

- Higher densities are needed (from 32GB to 512GB)
- Enhanced performance is required
- SoC supporting UFS interface is available

Use e-MMC when:

- Lower densities are needed (from 4GB to 128GB)
- SoC supporting UFS interface is not available

WHAT'S NEW:

- Added new products and extended our e-MMC roadmap
- For new UFS designs, we recommend v2.1 for 32GB/64GB.
- For UFS 128GB and above, we recommend v3.1 depending on processor support capability.
- Lead time: stock – 12 weeks

UFS KEY FEATURES

- Embedded controller
- Serial interface
- High speed reads/writes
- Low pin count
- 32GB - 512GB
- BiCS FLASH™ 3D memory
- 11.5 x 13mm 153ball BGA package
- JEDEC standard

UFS Focus Products

- 32GB, 64GB, 128GB, 256GB, 512GB

e-MMC KEY FEATURES

- Embedded controller
- Parallel interface
- BiCS FLASH™ 3D memory from 16GB
- C Temp (-25°C to +85°C) 4GB - 128GB
- I Temp (-40°C to +105°C) 8GB - 64GB
- 11.5 x 13mm 153ball BGA package
- JEDEC standard
- 4GB also offered in 11 x 10mm package

e-MMC Focus Products

- 4GB, 8GB MLC product 16GB, 32GB, 64GB, 128GB BiCS FLASH™ 3D product

KEY APPLICATIONS



Smartphones



AR/VR



Tablets/2-in-1



Automotive



Streaming Media



Smart Speakers

Contact your local KIOXIA sales representative or franchised distributor for additional information.

MANAGED FLASH | UFS

Consumer Grade	Part Number	Capacity	e-MMC Version	Max Data Rate (MB/s)	Supply Voltage			Operating Temp (°C)	Package (mm)
					V _{cc} (V)	V _{ccq} (V)	V _{ccq2} (V)		
Consumer Grade	THGAF8G8T23BAIL	32GB	2.1	1160	2.7 to 3.6	— ¹	1.70 to 1.95	-25 to 85	11.5 x 13 x 0.8
	THGAF8G9T43BAIR	64GB							11.5 x 13 x 1.0
	THGAF8T0T43BAIR	128GB							11.5 x 13 x 0.8
	THGAF8T1T83BAIR	256GB							11.5 x 13 x 1.0
	THGJCT0T44BAIL	128GB	3.0	2320	2.4 to 2.7, 2.7 to 3.6	1.14 to 1.26	— ²	-25 to 85	11.5 x 13 x 0.8
	THGJCT1T84BAIC	256GB							11.5 x 13 x 0.95
	THGJCT2T84BAIC	512GB							11.5 x 13 x 0.8
	THGJFAT0T44BAIL	128GB	3.1	2320	2.4 to 2.7, 2.7 to 3.6	1.14 to 1.26	— ²	-25 to 85	11.5 x 13 x 1.0
	THGJFAT1T84BAIR	256GB							11.5 x 13 x 1.0
	THGJFAT2T84BAIR	512GB							11.5 x 13 x 1.0

(1) Dual-supply operation at V_{cc} and V_{ccq2}. V_{ccq} need not be supplied. (2) Dual-supply operation at V_{cc} and V_{ccq}. V_{ccq2} need not be supplied.

Note: While UFS performance is higher Ver 3.1 > 3.0 > 2.1, the SoC will likely determine which version UFS is required. JEDEC intends each UFS version to be backward compatible with previous versions, but please confirm by evaluating the power supply voltage and SoC.

MANAGED FLASH | e-MMC

Consumer Grade	Part Number	Capacity	e-MMC Version	Process	Max Data Rate (MB/s)	Supply Voltage		Operating Temp (°C)	Package (mm)					
						V _{cc} (V)	V _{ccq} (V)							
Consumer Grade	THGBMNG5D1LBAIT	4GB	5.0	FG NAND	400	2.7 to 3.6	1.70 to 1.95 2.7 to 3.6	-25 to 85	11 x 10 x 0.8					
	THGBMNG5D1LBAIL								11.5 x 13 x 0.8					
	THGBMJG6C1LBAIL	8GB							11.5 x 13 x 0.8					
	THGBMJG7C1LBAIL	16GB							11.5 x 13 x 0.8					
	THGBMJG8C2LBAIL	32GB	5.1						11.5 x 13 x 0.8					
	THGAMRG7T13BAIL	16GB							11.5 x 13 x 0.8					
	THGAMRG8T13BAIL	32GB							11.5 x 13 x 0.8					
	THGAMRG9T23BAIL	64GB							11.5 x 13 x 0.8					
Industrial Grade	THGAMRT0T43BAIR	128GB	5.1	BiCS	400	2.7 to 3.6	1.70 to 1.95	-25 to 85	11.5 x 13 x 1.0					
	THGBMJG6C1LBAU7	8GB							11.5 x 13 x 1.0					
	THGBMJG7C2LBAU8	16GB							11.5 x 13 x 1.2					
	THGBMJG8C4LBAU8	32GB							11.5 x 13 x 1.2					
	THGBMJG9C8LBAU8	64GB							11.5 x 13 x 1.2					

(1) Tc=115°C max. Contact your KIOXIA sales representative for sample schedule

Definition of capacity: KIOXIA Corporation defines a megabyte (MB) as 1,000,000 bytes, a gigabyte (GB) as 1,000,000,000 bytes and a terabyte (TB) as 1,000,000,000,000 bytes. A computer operating system, however, reports storage capacity using powers of 2 for the definition of 1GB = 2³⁰ = 1,073,741,824 bytes and therefore shows less storage capacity. Available storage capacity (including examples of various media files) will vary based on file size, formatting, settings, software and operating system, such as Microsoft Operating System and/or pre-installed software applications, or media content. Actual formatted capacity may vary.