




AHEAD OF WHAT'S POSSIBLE™

POWER SOLUTIONS FOR PRECISION TECHNOLOGY SIGNAL CHAINS

PRECISION LOW POWER
Multichannel Voltage, Current and Biosignal Measurement
Noise Optimized



Rev. 0 | Apr. 2022

©2022 Analog Devices, Inc. All rights reserved.
Trademarks and registered trademarks are the
property of their respective owners.

This document is interactive. You can click on any underlined text to navigate through the document.

For the resources:

APPENDIX	<u>Parts Guide</u>
	<u>Power Requirements</u>



Left-click the Parts Guide and Power Requirements to go through the list of power devices and other references.

The Power Components are listed on the Appendix, and you may click on the part to go through its product page online.

PART #	DESCRIPTION
<u>LT3471</u>	Dual 1.3A, 1.2MHz Boost/Inverter in 3mm × 3mm DFN
<u>LT8604</u>	High Efficiency 42V/120mA Synchronous Buck
<u>LT8570-1</u>	Boost/SEPIC/Inverting DC/DC Converter with 65V Switch, Soft-Start and Sync.

For the individual pages:

Non-isolated
<u>1-Channel</u>



Left-click the specific signal chain to go through its respective block diagram or power tree.

POWER RE

PARAMETER

Supply Voltage

Supply Current

PSRR

APPENDIX

Parts Guide


USER GUIDE

Power Requirements

Voltage, Current & Biosignal Measurement

Noise Optimized - Multichannel

Non-isolated	Isolated
1.5V Supply	
3.7V Supply	5V Supply
>5.5V Supply	



APPENDIX

Parts Guide


USER GUIDE

Power Requirements

Voltage, Current & Biosignal Measurement

Noise Optimized - Multichannel

Non-isolated	Isolated
1.5V Supply	
3.7V Supply	5V Supply
>5.5V Supply	



APPENDIX

Parts Guide


USER GUIDE

Power Requirements

Voltage, Current & Biosignal Measurement

Noise Optimized - Multichannel

Non-isolated	Isolated
1.5V Supply	
3.7V Supply	5V Supply
> 5.5V Supply	



APPENDIX

Parts Guide


Power Requirements

USER GUIDE

Voltage, Current & Biosignal Measurement

Noise Optimized - Multichannel

Non-isolated	Isolated
1.5V Supply	
3.7V Supply	5V Supply
>5.5V Supply	



Precision Low Power

Voltage, Current & Biosignal Measurement

Noise Optimized - Multichannel

Non-isolated	Isolated
1.5V Supply	
3.7V Supply	5V Supply
>5.5V Supply	

PART #	DESCRIPTION
<u>MAX77642</u>	Ultra Configurable PMIC Featuring 93% Peak Efficiency Single-Inductor, 3-Output Buck-Boost, 1-LDO for Long Battery Life
<u>MAX17220</u>	400mV to 5.5V Input, nanoPower Synchronous Boost Converter with True Shutdown
<u>MAX17530</u>	4V to 42V, 25mA, Ultra-Small, High-Efficiency, Synchronous Step-Down DC-DC Converter with 22 μ A No-Load Supply Current
<u>ADP150</u>	Ultralow Noise, 150 mA CMOS Linear Regulator
<u>ADuM5028</u>	Low Emission Isolated DC to DC Converter

Non-isolated	Isolated
1.5V Supply	
3.7V Supply	
> 5.5V Supply	5V Supply

POWER REQUIREMENTS

PARAMETER	STAGES	Amplifier		ADC			Reference	Isolation		
	Part #	AD8237		AD4696				ADR3425	ADuM1441	
		Pin	+V _S	-V _S	AV _{DD}	LDO_IN	V _{IO}		IN	V _{DD1}
Supply Voltage	V		3.3	-	3.3	3.3	1.8	3.3	2.5	2.5
Supply Current	mA		0.15	-	0.052	6.6	0.36	0.1	0.9	0.9
PSRR	dB		73 (100Hz)		79 (1MHz)	95 (1MHz)	100 (1MHz)	54 (100kHz)	-	

Note 1: The supply currents indicated are the maximum quiescent current of the supply rails. For overall full load or short circuit current specifications, refer to the datasheets of the signal chain components.

Note 2: The supply voltages indicated are the values for typical applications.

Note 3: Consult the corresponding datasheets for details on power dissipation if needed.

Note 4: The actual supply current requirement shall be multiplied depending on the number of channels on the signal chain.