

# PSOC™ Edge E81 Microcontrollers

## The Next Generation of Low-Power Microcontrollers

The PSOC™ Edge E8 series of Arm® Cortex®-M microcontrollers feature high-performance, low-power, secured MCUs with integrated ML hardware acceleration, designed specifically for enabling efficient and responsive ML compute applications in edge devices. These MCUs are ideal for a variety of consumer and industrial applications including HMI, smart home, wearables, robotics, and other smart connected IoT products. In addition, PSOC™ Edge is supported by a rich set of enablement with the industry-recognized ModusToolbox™ software including integration with the DEEPCRAFT™ Studio AI solution and its off-the shelf ML models.

The PSOC™ Edge E81 microcontrollers are based on high-performance Arm® Cortex®-M55, including Helium DSP support, and also a low-power Arm® Cortex®-M33 paired with Infineon's ultra-low power NNLite hardware accelerator, while featuring always-on acoustic activity detection and wake word detection efficient HMI operations and extended battery life. The PSOC™ Edge E81 includes support for voice and audio communications with keyword spotting and wake word detection, as well as features such as anomaly detection and predictive maintenance.

### Power Performance Efficiency and Next-Gen ML Acceleration

- Multi-domain architecture for high-performance and fine-grained power optimization
- High-performance Arm® Cortex®-M55 CPU with Helium DSP
- Low-power Arm® Cortex®-M33 with FPU and DSP, and NNLite for low power AI/ML hardware acceleration

### Advanced HMI Interfaces

- Audio multi-microphone interface for far-field applications
- Keyword spotting and Wake word detection

### State-of-the-art Security

- Lockstep secured enclave in low-power always-on domain
- Infineon Edge Protect Category 4/Platform Security Architecture (PSA) Level 4
- Off-the-shelf trusted Firmware-M enablement and Mbed-TLS for crypto operations

### Ease-of-use for developers

- ModusToolbox™ software
  - Comprehensive collection of multi-platform tools and software libraries
  - Includes board support packages (BSPs), peripheral driver library (PDL), and middleware
- End-to-end ML solution with DEEPCRAFT™ Edge AI software and tools

For more information visit [PSOC™ Edge E81](#)



### Key features

#### 32-Bit MCU Subsystems

- Up to 400MHz Arm® Cortex®-M55 with Helium DSP
- Up to 200MHz Arm® Cortex®-M33

#### Machine Learning

- Infineon's NNLite for low-power AI/ML
- End-to-end ML with DEEPCRAFT™

#### Memory and SoC Integration

- High-capacity memory
- Ultra-low power RRAM
- Rich peripherals to reduce system cost
- Integrated low-power analog subsystem

#### Security

- Up to EPC4/PSA L4

#### HMI

- Keyword spotting and wake word detection

#### Packages

- WLB-154, BGA-220

#### Operating Temperature

- Ta: -20 to 70°C, -40 to 105°C


### Target applications

- HMI
- Smart Home
- Wearables
- Robotics
- Security Camera



## PRODUCT BRIEF

### Block Diagram



### Orderable Part Numbers and Kits

Kit	Function	Part Number
PSOC™ Edge E84 Evaluation Kit	General purpose evaluation kit for PSOC™ Edge with full function integration of all interfaces	KIT_PSE84_EVAL
PSOC™ Edge E84 AI Kit	Low-cost kit with multiple sensors for evaluation of AI capabilities and fast prototyping	KIT_PSE84_AI

Part Number	Package	Max Frequency	RRAM	Total SRAM	Ethernet & CAN	Security	Temp (Ta)
PSE812GOS2DFNC4T	WLB-154	400 MHz	512kB	5MB	-	PSA L2	-20 to 70 °C
PSE813GOS2DBZC4	BGA-220	400 MHz	512kB	5MB	Yes	PSA L2	-20 to 70 °C
PSE813GOS2DBZQ3	BGA-220	320 MHz	512kB	5MB	Yes	PSA L2	-40 to 105 °C

Additional parts can be found on [Infineon.com/PSOCEdgeE81](https://www.infineon.com/PSOCEdgeE81)

Published by  
 Infineon Technologies AG  
 Am Campeon 1-15, 85579 Neubiberg  
 Germany

© 2025 Infineon Technologies AG  
 All rights reserved.

Public

Version: V2.0\_EN  
 Date: 10/2025

**Please note!**  
 This Document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

**Additional information**  
 For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

**Warnings**  
 Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.



Scan QR code and explore offering  
[www.infineon.com](https://www.infineon.com)