

| SMALL MOBILE BOOM CRANE EXTENSION

Background

Mobile boom cranes can be used in construction, landscaping, demolitions and a whole lot of other, similar activities. Like all cranes, the crane operator needs to keep close track of the weight they are handling, the angle of the boom and how far out the boom extension is. Without careful attention to these three things, there is a significant risk that the boom will be overloaded and collapse or cause the whole mobile platform to tip over.

As the boom is extended or retracted, the end of the Draw-Wire will move right along with it and the operator can tell exactly how much the boom has been extended

Solution

One of the most critical parameters to keep track of is the boom extension. For small booms like the one shown in the picture, installing a draw-wire assembly is the perfect solution. As the boom is extended or retracted, the end of the Draw-Wire will move right along with it and the operator can tell exactly how much the boom has been extended. Together with the weight and the angle (using other measuring devices) the operator can stay completely in the safe zone.






RECOMMENDED PRODUCTS

Reference on Diagram	Product	Type	Features	Features	Brand
1		CD120 Draw-Wire Encoder	Up to 10' of Measurement	• Length (Distance) Measurement	BEI Sensors
2		CD150 (Analog) Draw-Wire	Up to 19.7' of measurement	• Analog length Measurement	BEI Sensors
3		CDS12 (Analog) Draw-Wire	Up to 49.2' of measurement	• Analog length Measurement	BEI Sensors



TRUCK MOUNTED BOOM CRANE



Page 2

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. **HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY**

RIGHT, AND

NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

CONTACT US

Americas

+1 (800) 350 2727 – Option 1
sales.beisensors@sensata.com

Europe, Middle East & Africa

+33 (3) 88 20 8080
position-info.eu@sensata.com

Asia Pacific

sales.isasia@list.sensata.com
 China +86 (21) 2306 1500
 Japan +81 (45) 277 7117
 Korea +82 (31) 601 2004
 India +91 (80) 67920890
 Rest of Asia +886 (2) 27602006 ext 2808